

**PHILIPS**

EcoPro  
LED work lights



**Quality light  
to get the job done**

# Versatile and powerful LED work lights for every day use

## Philips EcoPro61 Slim Slim and foldable hand lamp



- **Ultra-slim design:** to light up narrow spaces
- **3 light modes:** 500, 250 and 50 lm
- **Very long autonomy:** up to 20 hours in Eco mode
- **Versatile and easy to use:** strong magnetic mounting accessory and 360° retractable hook
- **High-precision spotlight:** 140 lm

Ordering number	GOC	EAN1	EAN3	MOQ
RC620X1	00484031	8719018004840	8719018004857	6

## Philips EcoPro40 Rechargeable hand lamp



- **Bright LED light:** up to 300 lumen (Boost mode)
- **Strong bright light:** 6500 K
- **Enhanced autonomy:** up to 8 hours
- **Handy work light:** non-slip grip and lightweight
- **Versatile for hands-free use:** strong magnets and 360° retractable hooks

Ordering number	GOC	EAN1	EAN3	MOQ
RC420B1	05057145	8719018050571	8719018050700	3

## Philips EcoPro50 Aluminum portable projector



- **Powerful LED light:** up to 1,000 lumen
- **Powerful bright white light:** 6500 K
- **Long autonomy:** up to 6 hours with battery life indicator
- **Strong impact (IK08) and water resistance (IP54)**
- **Versatile and easy to use:** strong magnetic mounting accessory
- **Power bank:** to charge other devices

Ordering number	GOC	EAN1	EAN3	MOQ
RC520C1	05071745	8719018050717	8719018050724	3

## Philips EcoPro30 Rechargeable slim lamp



- **Dual-mode light:** 150 and 300 lm
- **Bright natural light:** 6000 K
- **Rechargeable long-life battery:** high-energy Li-ion battery
- **Versatile for hands-free use:** large 120° beam angle, 360° rotatable hook, strong magnet
- **Enhanced autonomy:** up to 8 hours, rechargeable via USB-C
- **Strong impact (IK07) and water resistance (IP54)**

Ordering number	GOC	EAN1	EAN3	MOQ
RC220X1	01769731	8719018017697	8719018017703	6

## Philips EcoPro20

### Convenient pocket lamp



- **LED light:** up to 220 lumen
- **Bright comfortable light:** 6500 K
- **Good autonomy:** up to 3.5 hours
- **Versatile pocket lamp:** magnetic 180° pivoting base and 360° retractable hook
- **Power bank:** to charge other devices

Ordering number	GOC	EAN1	EAN3	MOQ
RC320B1	05055745	8719018050557	8719018050564	3

## Philips EcoPro10

### Portable inspection tool

NEW



- **Ultra-compact design:** lightweight (less than 100 g) for everyday use
- **High-quality light:** equipped with 5 durables LEDs
- **Bright natural light:** 6000 K
- **Long autonomy:** up to 6.5 hours
- **Versatile pocket lamp:** spotlight, clip

Ordering number	GOC	EAN1	EAN3	MOQ
RC120B1	01765940	8719018017659	8719018017666	20
RC120X1	01767330	8719018017673	8719018017680	10

## Ordering information

Product name	Ordering number	GOC	EAN1	EAN3	Packaging quantity
EcoPro61 Slim	RC620X1	00484031	8719018004840	8719018004857	6
EcoPro50	RC520C1	05071745	8719018050717	8719018050724	3
EcoPro40	RC420B1	05057145	8719018050571	8719018050700	3
EcoPro30	RC220X1	01769731	8719018017697	8719018017703	6
EcoPro20	RC320B1	05055745	8719018050557	8719018050564	3
EcoPro10	RC120B1	01765940	8719018017659	8719018017666	20
	RC120X1	01767330	8719018017673	8719018017680	10



## Product feature explanations



**Micro-USB charge**  
Charge of the work light via micro-USB.



**Power bank**  
Possibility to charge other devices from the work light.



**Compact size**  
Compact shape for easy handling and access to confined spaces.



**Ingress protection marking**  
The higher IP rating, the more resistant to water and dust.



**Shock impact resistance**  
The higher IK rating, the more robust to shock.



**Strong magnet**  
In-built retractable magnet to work hands-free.



**Hook**  
Retractable and rotating hook to work hands-free.



**Clip**  
Fixture to enable hands-free working.

