

PHILIPS

Automotive lighting

LED signaling lights



Which LED lamp do you need?



Brigter, elegant signals

Ultinon Pro6000




Light color



Lifetime

Up to 5000 h



Stand out from the crowd

Ultinon Pro3000




Light color



Lifetime

Up to 5000 h



Product index

LED lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
11065AU60X2	SL-AMBER [=W21W]	U60	12	2,3	WX3x16d	01558730	8719018015587	-	8719018015594	5
11065CU60X2	SL-WHITE [=W21W]	U60	12	2,3	W3x16d	01554930	8719018015549	-	8719018015556	5
11065RU60X2	SL-RED [=W21W]	U60	12	2,3	W3x16d	01564830	8719018015648	-	8719018015655	5
11065U30CWB2	SL-WHITE [=W21W]	U30	12	1,75	W3x16d	00684430	8719018006844	-	8719018006851	7
11065U30RB2	SL-RED [=W21W]	U30	12	1,75	W3x16d	00686830	8719018006868	-	8719018006875	7
11066AU60X2	SL-AMBER [=W21/5W]	U60	12	2,5/0,5	W3x16q	01556330	8719018015563	-	8719018015570	5
11066CU60X2	SL-WHITE [=W21/5W]	U60	12	2,5/0,5	W3x16q	01550130	8719018015501	-	8719018015518	5
11066RU60X2	SL-RED [=W21/5W]	U60	12	2,5/0,5	W3x16q	01552530	8719018015525	-	8719018015532	5
11066U30RB2	SL-RED [=W21/5W]	U30	12	0,8/1,75	W3x16q	00642430	8719018006424	-	8719018006431	7
11067CU60X1	SL-T16 [=W16W]	U60	12	2,4	W2,1x9,5d	01566230	8719018015662	-	8719018015679	5
11498AU60X2	SL-AMBER [=P21W]	U60	12	2,3	BAU15S	01548830	8719018015488	-	8719018015495	5
11498CU60X2	SL-WHITE [=P21W]	U60	12	2,3	BA15S	01540230	8719018015402	-	8719018015419	5
11498RU60X2	SL-RED [=P21W]	U60	12	2,3	BA15S	01542630	8719018015426	-	8719018015433	5
11498U30CWB2	SL-WHITE [=P21W]	U30	12	1,75	BA15S	00680630	8719018006806	-	8719018006813	7
11498U30RB2	SL-RED [=P21W]	U30	12	1,75	BA15S	00640030	8719018006400	-	8719018006417	7
11499AU60X2	SL-AMBER [=P21/5W]	U60	12	2,5/0,5	BAY15d	01546430	8719018015464	-	8719018015471	5
11499CU60X2	SL-WHITE [=P21/5W]	U60	12	2,5/0,5	BAY15d	01544030	8719018015440	-	8719018015457	5
11499RU60X2	SL-RED [=P21/5W]	U60	12	2,5/0,5	BAY15d	01538930	8719018015389	-	8719018015396	5
11499U30RB2	SL-RED [=P21/5W]	U30	12	0,8/1,75	BAY15D	00682030	8719018006820	-	8719018006837	7
11854CU60X1	SL-FEST 38mm 6000K	U60	12	1	SV8,5	01532730	8719018015327	-	8719018015334	5
11854U30CWB1	SL-FEST 38mm 6000K	U30	12	0,6	SV8,5	00676930	8719018006769	-	8719018006776	7
11854WU60X1	SL-FEST 38mm 4000K	U60	12	1	SV8,5	01526630	8719018015266	-	8719018015273	5
11860CU60X1	SL-FEST 30mm 6000K	U60	12	1	SV8,5	01530330	8719018015303	-	8719018015310	5
11860U30CWB1	SL-FEST 30mm 6000K	U30	12	0,6	SV8,5	00674530	8719018006745	-	8719018006752	7
11860WU60X1	SL-FEST 30mm 4000K	U60	12	1	SV8,5	01524230	8719018015242	-	8719018015259	5
11864U30CWB1	SL-FEST 43 mm 6000K	U30	12	0,6	SV8,5	00678330	8719018006783	-	8719018006790	7
11866CU60X1	SL-FEST 43mm 6000K	U60	12	1	SV8,5	01534130	8719018015341	-	8719018015358	5
11866WU60X1	SL-FEST 43mm 4000K	U60	12	1	SV8,5	01528030	8719018015280	-	8719018015297	5
11961AU60X2	SL-AMBER [=W5W]	U60	12	0,5	W2,1x9,5d	01560030	8719018015600	-	8719018015617	5
11961CU60X2	SL-T10 [=W5W] 6000K	U60	12	0,9	W21x9.5d	01516730	8719018015167	-	8719018015174	5
11961U30CWB2	SL-T10 [=W5W] 6000K	U30	12	0,6	W21x9.5d	00694330	8719018006943	-	8719018006950	7
11961WU60X2	SL-T10 [=W5W] 4000K	U60	12	0,9	W21x9.5d	01514330	8719018015143	-	8719018015150	5
11961XU60X2	SL-T10 [=W5W] 8000K	U60	12	0,7	W21x9.5d	01522830	8719018015228	-	8719018015235	5
24805CU60X2	SL-WHITE [=R5W/R10W]	U60	12/24	1	BA15s	01562430	8719018015624	-	8719018015631	5
24844CU60X1	SL-FEST 30mm 6000K	U60	24	1,5	SV8,5	01536530	8719018015365	-	8719018015372	5
24961CU60X2	SL-T10 [=W5W] 6000K	U60	24	1	W2,1x9,5d	01520430	8719018015204	-	8719018015211	5
24961WU60X2	SL-T10 [=W5W] 4000K	U60	24	1	W2,1x9,5d	01518130	8719018015181	-	8719018015198	5



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.



Ultinon Pro6000 SL

Brighter, elegant signals

The all-new Ultinon Pro6000 LED bulbs offer superior visibility and style for your car. Philips high-end LED technology offers enhanced performance and easy replacement for greater safety and elegant appearance. Select from this range of bright interior and signaling lights that will transform your driving experience.

Superior visibility

- Powerful light with high lumen output
- Variety of powerful white light: 4000/6000/8000K for T10 [=W5W]
- Instant-on technology for more safety
- Uniform light distribution

High-end, elegant signaling

- Stylish LED signaling light available in white, vibrant red and vibrant amber

Performance made to last

- High-end LED technology
- Long lifetime up to 5000 hours
- *HeatShield* technology to endure any thermal challenge for T10 bulbs

Simple plug-and-play replacement


- Electrically compatible with most cars.
- No flickering thanks to dark-current immunity for Festoons
- Standard caps and polarity-free for quick and easy replacement (W5W, W16, W21/5W, P21/5W, R5/R10)
- Large portfolio for car and truck applications




Ultinon Pro6000 SL

Available in

12V



24V





Ultinon Pro3000 SL

Stand out from the crowd

All new Ultinon Pro3000 provides the best value for your money. Whether you're looking for a bright, new interior or a head turning exterior, Philips leading edge LED technology makes the difference with instant on stop signal and uniform light distribution.



Powerful brightness & performance

- Stylish white light of up to 6000K for T10 (≈ W5W), Festoon, W21 and P21
- Red signaling available in P21, P21/5W, W21, W21/5W
- Matching the performance standard*

Simple plug and play

- Easily upgrade from conventional bulb to LED with simple plug and play thanks to the LED standard caps.

Philips Reliability

- Longer lifetime of 3000 hours

Compatible with major vehicle models

- 12V compatible
- Optional CANbus available for troubleshooting

*Comply with ECE R37 lumen output requirement (for indication use only)



Ultinon Pro3000 SL

Available in

12V



LED-SL
[≈Festoon 30]



LED-SL
[≈Festoon 38]



LED-SL
[≈Festoon 43]



LED-SL
[≈W5W]



LED-SL
[≈W21W]



LED-SL
[≈P21W]



LED-SL
[≈P21/5W]



LED-SL
[≈W21W]



LED-SL
[≈P21W]



LED-SL
[≈W21/5W]



Adapter CANbus



- Prevents flickering
- Easy installation



Available in



SL [≈5W]
SL [≈21W]

Available in X2 packaging



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12956X2	12	5	-	39722294	8 727900 397222	-	8719018005007	-	4

Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18957X2	12	21	-	39587794	8 727900 395877	-	8719018004956	-	4



Which LED for which function?



Ultinon Pro9000 HL	Ultinon Pro6000 SL					
HL [=H1] 5800K HL [=H3] 5800K HL [=H4] 5800K HL [=H7] 5800K FL [=H8/H11/H16] 5800K	SL-T10 [=W5W] 4000K SL-AMB [=P21W] 6000K SL-AMB [=P21W] 6000K SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K SL-AMB [=W5W] 6000K	SL-T10 [=W5W] 4000K SL-AMB [=P21W] 6000K SL-AMB [=P21W] 6000K SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K SL-AMB [=W5W] 6000K	SL-T10 [=W5W] 4000K SL-AMB [=P21W] 6000K SL-AMB [=P21W] 6000K SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K SL-AMB [=W5W] 6000K	SL-T10 [=W5W] 4000K SL-AMB [=P21W] 6000K SL-AMB [=P21W] 6000K SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K SL-AMB [=W5W] 6000K	SL-T10 [=W5W] 4000K SL-AMB [=P21W] 6000K SL-AMB [=P21W] 6000K SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K SL-AMB [=W5W] 6000K	SL-T10 [=W5W] 4000K SL-AMB [=P21W] 6000K SL-AMB [=P21W] 6000K SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K SL-AMB [=W5W] 6000K
HL [=HB3/HB4] 5800K HL [=H11] 5800K HL [=HIR2] 5800K	SL-WHITE [=R5/R10] 6000K SL-AMB [=W21W] 6000K SL-AMB [=W21W] 6000K SL-FEST 30/38/43 mm 4000K SL-T10 [=W5W] 6000K SL-T10 [=W5W] 6000K	SL-WHITE [=R5/R10] 6000K SL-AMB [=W21W] 6000K SL-AMB [=W21W] 6000K SL-FEST 30/38/43 mm 4000K SL-T10 [=W5W] 6000K SL-T10 [=W5W] 6000K	SL-WHITE [=R5/R10] 6000K SL-AMB [=W21W] 6000K SL-AMB [=W21W] 6000K SL-FEST 30/38/43 mm 4000K SL-T10 [=W5W] 6000K SL-T10 [=W5W] 6000K	SL-WHITE [=R5/R10] 6000K SL-AMB [=W21W] 6000K SL-AMB [=W21W] 6000K SL-FEST 30/38/43 mm 4000K SL-T10 [=W5W] 6000K SL-T10 [=W5W] 6000K	SL-WHITE [=R5/R10] 6000K SL-AMB [=W21W] 6000K SL-AMB [=W21W] 6000K SL-FEST 30/38/43 mm 4000K SL-T10 [=W5W] 6000K SL-T10 [=W5W] 6000K	SL-WHITE [=R5/R10] 6000K SL-AMB [=W21W] 6000K SL-AMB [=W21W] 6000K SL-FEST 30/38/43 mm 4000K SL-T10 [=W5W] 6000K SL-T10 [=W5W] 6000K
Ultinon Pro5000 HL	Ultinon Pro3000 SL					
HL [=H1] 5800K HL [=H3] 5800K HL [=H4] 5800K HL [=H7] 5800K FL [=H8/H11/H16] 5800K	SL-WHITE [=P21/W] 6000K SL-WHITE [=P21/W] 6000K SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-WHITE [=P21/W] 6000K SL-WHITE [=P21/W] 6000K SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-WHITE [=P21/W] 6000K SL-WHITE [=P21/W] 6000K SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-WHITE [=P21/W] 6000K SL-WHITE [=P21/W] 6000K SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-WHITE [=P21/W] 6000K SL-WHITE [=P21/W] 6000K SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-WHITE [=P21/W] 6000K SL-WHITE [=P21/W] 6000K SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K
HL [=HB3/HB4] 5800K HL [=H11] 5800K HL [=HIR2] 5800K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K
Ultinon Pro3000 HL	LED adapters					
HL [=H1] 6500K HL [=H3] 6500K HL [=H4] 6500K HL [=H7] 6500K FL [=H8/H11/H16] 6500K	SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K	SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K	SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K	SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K	SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K	SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K IL/SL-WHITE [=W5W] 6000K
HL [=HB3/HB4] 6500K HL [=H11] 6500K HL [=HIR2] 6500K	IL/SL-WHITE Fest 30/38/43 mm 6000K	IL/SL-WHITE Fest 30/38/43 mm 6000K	IL/SL-WHITE Fest 30/38/43 mm 6000K	IL/SL-WHITE Fest 30/38/43 mm 6000K	IL/SL-WHITE Fest 30/38/43 mm 6000K	IL/SL-WHITE Fest 30/38/43 mm 6000K
LED adapters	LED adapters					
CANbus adapter HL [=H4], [=H7]	Light Repair HL [=H1], [=H7]	CANbus adapter FL [=H8/H11/H16]	CANbus adapter SL [=5W]	CANbus adapter SL [=21W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]
CANbus adapter SL [=5W]	CANbus adapter SL [=21W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]



Ultinon Pro9000 HL	Ultinon Pro6000 SL								
SL-T10 [=W5W] 4000K SL-RED [=P21/W] 6000K	SL-AMB [=P21W] 6000K SL-RED [=P21W] 6000K	SL-AMB [=P21W] 6000K SL-RED [=P21W] 6000K	SL-AMB [=P21W] 6000K SL-RED [=P21W] 6000K	SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K	SL-T10 [=W5W] 4000K SL-T10 [=W5W] 4000K	SL-RED [=P21W] 6000K SL-RED [=P21W] 6000K	SL-RED [=P21W] 6000K SL-RED [=P21W] 6000K	SL-RED [=P21W] 6000K SL-RED [=P21W] 6000K	SL-WHITE [=P21W] 6000K SL-WHITE [=P21W] 6000K
SL-FEST 30/38/43 mm 4000K SL-WHITE [=R5/R10] 6000K	SL-RED [=W21/W] 6000K	SL-AMB [=P21/W] 6000K SL-AMB [=P21/W] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-FEST 30/38/43 mm 4000K SL-WHITE [=R5/R10] 6000K	SL-FEST 30/38/43 mm 4000K SL-WHITE [=R5/R10] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K
SL-WHITE [=R5/R10] 6000K	SL-AMB [=W21/W] 6000K SL-AMB [=W21/W] 6000K	SL-AMB [=W21/W] 6000K SL-AMB [=W21/W] 6000K	SL-AMB [=W21/W] 6000K SL-AMB [=W21/W] 6000K	SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-WHITE [=R5/R10] 6000K SL-WHITE [=R5/R10] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-T16 [=W16W] 6000K SL-WHITE [=W21/W] 6000K
Ultinon Pro5000 HL	Ultinon Pro3000 SL								
IL/SL-WHITE [=W5W] 6000K SL-RED [=P21/W] 6000K	SL-RED [=P21W] 6000K SL-RED [=P21W] 6000K	IL/SL-WHITE [=W5W] 6000K SL-WHITE [=W5W] 6000K	SL-WHITE [=W5W] 6000K SL-RED [=P21W] 6000K	IL/SL-WHITE [=W5W] 6000K SL-WHITE [=W5W] 6000K	SL-WHITE [=W5W] 6000K SL-RED [=P21W] 6000K	SL-RED [=P21W] 6000K SL-RED [=P21W] 6000K	SL-RED [=P21W] 6000K SL-RED [=P21W] 6000K	SL-RED [=P21W] 6000K SL-RED [=P21W] 6000K	SL-WHITE [=P21W] 6000K SL-WHITE [=P21W] 6000K
IL/SL-WHITE Fest 30/38/43 mm 6000K SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K SL-WHITE Fest 30/38/43 mm 6000K	SL-WHITE Fest 30/38/43 mm 6000K SL-RED [=W21/W] 6000K	IL/SL-WHITE Fest 30/38/43 mm 6000K SL-WHITE Fest 30/38/43 mm 6000K	SL-WHITE Fest 30/38/43 mm 6000K SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-RED [=W21/W] 6000K SL-RED [=W21/W] 6000K	SL-WHITE [=W21/W] 6000K SL-WHITE [=W21/W] 6000K
CANbus adapter SL [=5W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]

philips.com/led-bulbs

It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

Philips Ultinon Essential is not available in all countries. For more information, please contact your Philips representative.



2021 © Lumileds Holding B.V. All rights reserved.

The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. Specifications are subject to change without notice.

philips.com/led-bulbs