

Which **LED** lamp do you need?



Original automotive performance in LED

Ultinon Pro9000

Lumileds
TopContact
OEM LED*

2
years


+3
extended
warranty



Beam performance*



Light color



Lifetime



Available in

LED-HL [~H1], [~H3], [~H4], [~H7],
[~HB3/4], [~H11], [~HIR2]

LED-FL [~H8/H11/H16]

The perfect blend
of **performance**
and **durability**

Ultinon Pro5000

Automotive
grade LED

2
years


+1
extended
warranty



Beam performance*



Light color



Lifetime



Available in

LED-HL [~H1], [~H3], [~H4], [~H7],
[~HB3/4], [~H11], [~HIR2]

LED-FL [~H8/H11/H16]

Transform
your car lights


Ultinon Essential



Beam performance*



Light color



Lifetime



Available in

LED-HL [~H1], [~H3], [~H4], [~H7],
[~HB3/4], [~H11], [~HIR2]

LED-FL [~H8/H11/H16]

Images for illustration purposes only.

* Applies to Ultinon Pro9000 HL [~H4], [~H7], [~HB3/4], [~H11], [~HIR2] and FOG [~H8/H11/H16].

** Compared to the minimum legal standard for halogen bulbs. Up to +200% for Ultinon Pro9000 HL [~H1] and [~H3] types.



It is your own responsibility to ensure
that the use of the LED retrofit lights complies
with applicable local legal requirements.