

PHILIPS

Home lighting

Collection 2016-2017



InStyle Lirio



InStyle

Lirio

2016-2017



InStyle



Create your style with light

Create the style you want for your home. Philips InStyle is a contemporary collection of premium indoor luminaires with the accent on smart and trendy style. Its distinctive design ideas make use of premium materials like aluminium and ultra-clear glass in organic shapes, complemented by chrome highlights and textile shades in natural colours. Mix and match from the extensive range to add a unique personal touch to your prized interior decor.

Philips InStyle's high-tech LED light not only provides high-quality energy-saving light and ambience, it also permits never-before-seen luminaire designs. Smart features like touch controls and dimmers complete the picture for lighting the whole family will love.

Philips InStyle – lighting just the way you like it.

Light inspires, Light creates

With Lirio by Philips we continuously challenge ourselves to shape a light portfolio that brings both compelling designs as much as it intrigues with the light it creates. LED is taking an important role in the portfolio, allowing the design team of LIRIO to craft new, unique designs and forms.

As the light bulb replaced candles, the LED will now replace the bulb; a paradigm shift, allowing light to gain a new meaning in the home. The role of design is to enable this shift from styling luminaires to designing light itself.

Keeping in mind the important role that light takes in your life, LIRIO by Philips wants to offer you a collection that inspires and adds personality. Offering a true match between imaginative design and a human approach to innovation, LIRIO by Philips is an invitation to all to express yourself in your interior.

Lirio by Philips is a beautiful story to share.



Lirio





Index

Introduction	2
Decorative	9
Wall & Ceiling	57
Spots	69
Bathroom	75
Index	140

InStyle

Lirio

Introduction	88
Decorative	91
Spots , Wall & Ceiling	123
Index	140



InStyle




Decorative

Byzantin



Byzantin 36446/11/P1



1 124 → 450 ↗ 450
LED - 6x 5W incl. - 2400 lm
⊕ - IP20
glass



Byzantin 36557/11/P1

1 1682 → 1204 ↗ 100
LED - 6x 5W incl. - 2400 lm
⊕ - IP20
glass





Arago



Arago 37167/31/16



1 1500 → 261 ↗ 261
LED - 3x 4,5W incl. - 1500 lm
⊕ - IP20
metal - glass



Arago 37168/31/16



1 1500 → 970 ↗ 120
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
metal - glass




Arago 37169/31/16



1 1500 → 1340 ↗ 120
LED - 6x 4,5W incl. - 3000 lm
⊕ - IP20
metal - glass





Meton



Meton 37312/56/16

1 153 → 157 / 94
LED - 1x 3,5W incl. - 320 lm
☐ - IP20
glass



Meton 37313/56/16

1 131 → 225 / 225
LED - 3x 4,5W incl. - 1500 lm
⊙ - IP20
metal - glass



Meton 37316/56/16

1 1500 → 261 / 261
LED - 3x 4,5W incl. - 1500 lm
⊙ - IP20
metal - glass



Meton 37318/56/16

1 1500 → 970 / 103
LED - 4x 4,5W incl. - 2000 lm
⊙ - IP20
metal - glass





Meton
37319/56/16

1 1500 → 1323 / 103
LED - 6x 4,5W incl. - 3000 lm
⊕ - IP20
metal - glass



Matrix



Matrix 40925/30/16



1 42 → 315 ↗ 315
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
glass - metal



Matrix 40927/30/16



1 42 → 390 ↗ 400
LED - 6x 4,5W incl. - 3000 lm
⊕ - IP20
glass - metal



Matrix 40942/30/16



1 64 → 270 ↗ 120
LED - 1x 4,5W incl. - 500 lm
⊕ - IP20
glass - metal



Matrix 40926/30/16



1 1500 → 1040 ↗ 180
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
glass - metal





Matrix
40929/30/16

1 30 → 470 ↗ 520
LED - 8x 4,5W incl. - 4000 lm
⊕ - IP20
glass - metal



Matrix
40928/30/16

1 1500 → 1210 ↗ 180
LED - 6x 4,5W incl. - 3000 lm
⊕ - IP20
glass - metal





Matrix
40929/60/16




I 30 → 470 ↗ 520
LED - 8x 4,5W incl. - 4000 lm
⊕ - IP20
glass - metal



Matrix
40927/60/16



I 42 → 390 ↗ 400
LED - 6x 4,5W incl. - 3000 lm
⊕ - IP20
glass - metal





**Matrix
40925/60/16**



↑ 42 → 315 ↙ 315
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
glass - metal



**Matrix
40926/60/16**



↑ 1500 → 1040 ↙ 180
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
glass - metal



**Matrix
40928/60/16**



↑ 1500 → 1210 ↙ 180
LED - 6x 4,5W incl. - 3000 lm
⊕ - IP20
glass - metal



**Matrix
40942/60/16**



↑ 64 → 270 ↙ 120
LED - 1x 4,5W incl. - 500 lm
⊕ - IP20
glass - metal







Hanging domes of light.

These slim, futuristic flat-shaped pendants hanging elegantly from a thin cord are distinctive and elegant indeed. Each provides strong warm white light without glare from a large frosted glass dome.

Attilio

Attilio

Attilio 40909/17/16


1 1500 → 166 ↗ 166
LED - 1x 4,5W incl. - 500 lm
☐ - IP20
metal



Attilio 40910/17/16

1 1500 → 970 ↗ 140
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
metal





Siger - Tasso



Siger
43280/56/16

1 153 → 192 / 192
LED - 1x 3,5W incl. - 320 lm
□ - IP20
glass



Tasso
43282/56/16

1 219 → 184 / 184
LED - 1x 3,5W incl. - 320 lm
□ - IP20
glass - metal





**Dubois
36106/11/16**

1 1200 → 500 ↗ 500
E27 - 2x 70W incl. - 2x 1200 lm
⊕ - IP20
metal - glass




**Branca
37778/17/16**

1 1621 → 240 ↗ 243
E27 - 3x 20W incl. - 3x 1220 lm
⊕ - IP20
metal - glass



Bent - Tulip



Bent 40826/31/16

↑ 1500 ↔ 485 ↙ 430
E27 - 1x 70W incl. - 1200 lm
⊕ - IP20
metal



Tulip 40825/31/16

↑ 2000 ↔ 556 ↙ 551
E27 - 1x 105W incl. - 1980 lm
⊕ - IP20
synthetics



Tulip 40825/38/16

↑ 2000 ↔ 556 ↙ 551
E27 - 1x 105W incl. - 1980 lm
⊕ - IP20
synthetics









Sleek good looks and timeless design, the refreshing glow of the Beauvais table lamp creates the perfect LED task lighting or subtle accent, wherever you need it.

Beauvais

Beauvais



Beauvais
43284/17/PO

1 398 ↔ 380 ↗ 342
LED - 1x 6W incl.- 600 lm
☐ - IP20
metal









A modern classic pendant to suit any home. Hang at your preferred height, individually, or in a row to add a new-vintage feel to the kitchen or hallway. At its best paired with our E27 LED - opal bulb.

Hook Arch

Hook - Arch

Hook 40956/30/PN

1 1835 → 396 / 396
E27 - 1x max. 60W excl.
⊕ - IP20
metal



Arch 40957/30/PN

1 1816 → 399 / 399
E27 - 1x max. 60W excl.
⊕ - IP20
metal





Breton

Breton 36167/30/E7


1 1850 → 500 ↗ 500
E27 - 1x max. 20W
☐ - IP20
metal




Breton 36167/31/E7

1 1850 → 500 ↗ 500
E27 - 1x max. 20W
☐ - IP20
metal









Gilbert
36038/38/E7

† 530 ↔ 250 / 250
E27 - 1x max. 40W excl.
☐ - IP20
textile - wood



Gilbert
36039/38/E7

† 1580 ↔ 530 / 530
E27 - 1x max. 40W excl.
☐ - IP20
textile - wood








The perfect complement to any contemporary living or work space, our Nonagon LED pendant combines natural style notes with the contemporary clean lines of a modern hanging lamp. The addition of a step dimmer brings high performance control with maximum efficiency.

Nonagon





**Nonagon
49020/31/P1***



1 128 → 505 ↗ 505
LED - 2x 10W incl. - 2100 lm
⊕ - IP20
wood



**Nonagon
49021/31/P1***



1 1500 → 505 ↗ 505
LED - 2x 10W incl. - 2100 lm
⊕ - IP20
wood



**Nonagon
49023/31/P1***



1 385 → 283 ↗ 283
LED - 1x 7W incl. - 660 lm
◇ - IP20
wood



*with step dimmer



Kubiz

Philips InStyle Kubiz is a cool cube table lamp with a rubberised beech frame that you can stand on any side. The bright white interior glows with no visible bulb and has a playful space in the middle thanks to an amazing LED light.



Kubiz



Kubiz 43268/73/16


1 125 ↔ 125 ↗ 125
LED - 2x 2,5W incl.- 370 lm
□ - IP20
wood - metal



Kubiz 43268/86/16

1 125 ↔ 125 ↗ 125
LED - 2x 2,5W incl.- 370 lm
□ - IP20
wood - metal





Ortega



Ortega 37307/06/16



1 1500 → 970 ↗ 95
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
metal - glass



Ortega 37305/06/16



1 132 → 216 ↗ 216
LED - 3x 4,5W incl. - 1500 lm
⊕ - IP20
metal - glass



Ortega 37302/38/16



1 116 → 110 ↗ 110
LED - 1x 3,5W incl. - 320 lm
⊕ - IP20
glass



Ortega 37309/06/16



1 100 → 157 ↗ 95
LED - 1x 3,5W incl. - 320 lm
⊕ - IP20
glass





Ortega
37308/06/16

1 1500 → 1315 ↙ 95
LED - 6x 4,5W incl. - 3000 lm
⊕ - IP20
metal - glass



Ortega
37326/06/16

1 92 → 216 ↙ 216
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
metal - glass







Wonderful wheels of light.
With a sweeping silhouette that's sleek and chic, these smart circular ceiling lamps with chrome accents make a stylish centerpiece to any room. The clever design with glass diffuser casts light up as well as down, for a pleasant ambiance.

Flora



Flora
37481/17/16

1 216 → 450 ↗ 450
E14 - 3x 42W incl. - 3x 630 lm
⊕ - IP20
textile




Flora
37480/17/16

1 1700 → 450 ↗ 450
E14 - 3x 42W incl. - 3x 630 lm
⊕ - IP20
textile



Flora
37481/30/16

1 216 → 450 ↗ 450
E14 - 3x 42W incl. - 3x 630 lm
⊕ - IP20
textile



Flora
37480/30/16

1 1700 → 450 ↗ 450
E14 - 3x 42W incl. - 3x 630 lm
⊕ - IP20
textile





Fabio

Fabio 40397/30/16


1 1870 → 600 ↗ 600
E27 - 1x 20W incl. - 1140 lm
⊕ - IP20
synthetics - metal



Fabio 40397/31/16

1 1870 → 600 ↗ 600
E27 - 1x 20W incl. - 1140 lm
⊕ - IP20
synthetics - metal







Shady
40795/26/16

l 2600 → 1180 ↙ 250
E27 - 3x 20W incl.- 3x 1220 lm
⊕ - IP20
aluminium



Cano
37269/17/16

l 431 → 130 ↙ 243
E27 - 1x 18W incl.- 1100 lm
⊞ - IP20
textile - metal





Wall & Ceiling

Stonez



Stonez 40828/38/16



1 59 ↔ 345 ↙ 341
LED - 9x 2,5W incl. - 1650 lm
⊕ - IP20
aluminium - synthetics



Stonez 40828/87/16



1 59 ↔ 345 ↙ 341
LED - 9x 2,5W incl. - 1650 lm
⊕ - IP20
aluminium - synthetics



Stonez 40829/38/16



1 75 ↔ 444 ↙ 444
LED - 12x 2,5W incl. - 2200 lm
⊕ - IP20
aluminium - synthetics




Stonez 40829/87/16



1 75 ↔ 444 ↙ 444
LED - 12x 2,5W incl. - 2200 lm
⊕ - IP20
aluminium - synthetics









Alexa
30206/30/16

1 196 ↔ 442 ↗ 442
2GX13 - 1x 60W incl. - 5000 lm
⊕ - IP20
glass - textile



Alexa
30206/31/16

1 196 ↔ 442 ↗ 442
2GX13 - 1x 60W incl. - 5000 lm
⊕ - IP20
metal - textile



Candace



Candace 30207/17/16

1 62 → 450 ↗ 450
2GX13 - 1x 40W incl. - 3300 lm
⊕ - IP20
metal - synthetics



Candace 30207/31/16

1 62 → 450 ↗ 450
2GX13 - 1x 40W incl. - 3300 lm
⊕ - IP20
metal - synthetics





Hour



Hour
30939/31/16


170 → 336 ↗ 336
LED - 12x 1W incl. - 1230 lm
⊕ - IP20
metal - synthetics



Hour
30939/17/16

170 → 336 ↗ 336
LED - 12x 1W incl. - 1230 lm
⊕ - IP20
metal - synthetics





Magna



Magna 31207/31/16

140 → 330 / 170
LED - 2x 4,5W incl. - 1000 lm
⊕ - IP20
metal



Magna 31208/31/16

140 → 490 / 169
LED - 3x 4,5W incl. - 1500 lm
⊕ - IP20
metal





Feuille

Plain sailing.

This thin, delicate wall light made from premium aluminium is curved gently outwards at the edges, like a sail caught in the breeze.

This directs a wash of warm white light upwards and downwards, creating a pleasing silhouette on your wall.





Feuille
33604/11/16



↑ 195 ↔ 127 ↙ 55
LED - 2x 2W incl. - 260 lm
⊕ - IP20
aluminium



Feuille
33604/31/16




↑ 195 ↔ 127 ↙ 55
LED - 2x 2W incl. - 260 lm
⊕ - IP20
aluminium



InStyle




Spots



Quine
31214/31/16

1 28 → 240 ↗ 240
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
metal





**Quine
31211/31/16**

1 28 → 160 ↗ 110
LED - 1x 4,5W incl.- 500 lm
⊕ - IP20
metal



**Quine
31212/31/16**

1 28 → 240 ↗ 110
LED - 2x 4,5W incl.- 1000 lm
⊕ - IP20
metal



**Quine
31213/31/16**

1 28 → 500 ↗ 110
LED - 3x 4,5W incl.- 1500 lm
⊕ - IP20
metal



Scope



Scope 57180/31/16



172 → 168 ↗ 130
LED - 1x 4,5W incl. - 500 lm
⊕ - IP20
metal



Scope 57182/31/16



173 → 315 ↗ 133
LED - 2x 4,5W incl. - 1000 lm
⊕ - IP20
metal



Scope 57183/31/16




173 → 497 ↗ 133
LED - 3x 4,5W incl. - 1500 lm
⊕ - IP20
metal






Scope
57184/31/16

173 → 284 ↗ 284
LED - 4x 4,5W incl. - 2000 lm
⊕ - IP20
metal






Bathroom



Careful attention to materials and performance means InStyle bathroom products are suited to a humid environment. Sealed tight, they're rated IP44* or IP65* and certified water resistant, so you'll be able to go about your grooming safely, even with lighting that's placed near a shower, sink or bath. The fully sealed premium surrounds are sleek and smooth, which means they look great too.



- Well-being in the bathroom, with high quality light
- Safe, perfectly suited for humid environments
- Elegant designs, made of premium material
- Energy saving lights, saving up to 80%.



* The IP rate identifies the Ingress Protection against humidity and dust. The IP level is described by 2 two figures: the first one is referred to the protection level against dust, the second against water.



IP44



IP65



Mira



Mira 32208/11/16

1 56 → 300 / 120
LED - 2x 4,5W incl. - 1000 lm
⊕ - IP44
metal - glass



Mira 32209/11/16


1 56 → 320 / 320
LED - 3x 4,5W incl. - 1500 lm
⊕ - IP44
metal - glass



Mira 34208/11/16

1 136 → 101 / 140
LED - 1x 4,5W incl. - 500 lm
⊕ - IP44
metal - glass





Vanna - Hole



Vanna 32201/11/16

1 112 → 394 / 394
2GX13 - 1x 40W incl. - 3300 lm
☐ - IP44
synthetics - metal



Vanna 32202/11/16


1 113 → 474 / 474
2GX13 - 1x 60W incl. - 5000 lm
☐ - IP44
synthetics - metal



Hole 32207/11/16

1 87 → 454 / 454
2GX13 - 1x 60W incl. - 5000 lm
☐ - IP44
aluminium - synthetics





Plano



Plano 32203/17/16

176 → 344 ↗ 344
2GX13 - 1x 40W incl. - 3300 lm
☒ - IP44
metal - synthetics



Plano 32204/17/16

176 → 446 ↗ 446
2GX13 - 1x 60W incl. - 5000 lm
☒ - IP44
metal - synthetics



Plano 34203/17/16

157 → 321 ↗ 112
2G7 - 1x 11W incl. - 900 lm
☒ - IP44
metal - synthetics



Plano

Squares of light.

A family of industrial design-inspired square and bar lights, each with a stunning machined aluminium surround, rounded corners and plenty of energy saving light. Flip the switch and the entire glass panel comes alive with light.







Tubo
34206/31/16

1 95 → 632 / 91
G5 - 1x 14W incl.- 1350 lm
□ - IP44
synthetics



Tubo
34207/31/16

1 95 → 1232 / 91
G5 - 1x 28W incl.- 2900 lm
□ - IP44
synthetics





Lirio[®]
by
PHILIPS

Lirio
by
PHILIPS



Decorative



Piculet

Inspired by a 'woodpecker' bird. The head and foot of the Piculet can be assembled by its owner, showing off a playful, accentuated mark at the rear where the braided wire creeps out. It comes in a variety of soft tones and a luxurious finish.

Inside the head there is warm white LED module inside. The light is warmly diffused by the diffuser creating a nice ambiance. The light can be turned on by the rubber switch on the head.

Lirio
by
PHILIPS





Piculet
43500/31/LI
1 343 ↔ 200 ↗ 180
LED - 2x 2,5W incl.- 370 lm
☐ - IP20
synthetics



Piculet
43500/34/LI
1 343 ↔ 200 ↗ 180
LED - 2x 2,5W incl.- 370 lm
☐ - IP20
synthetics





**Piculet
43500/32/LI**

1 343 ↔ 200 ↗ 180
LED - 2x 2,5W incl. - 370 lm
☐ - IP20
synthetics



**Piculet
43500/38/LI**

1 343 ↔ 200 ↗ 180
LED - 2x 2,5W incl. - 370 lm
☐ - IP20
synthetics



**Piculet
43500/35/LI**

1 343 ↔ 200 ↗ 180
LED - 2x 2,5W incl. - 370 lm
☐ - IP20
synthetics



**Piculet
43500/93/LI**

1 360 ↔ 200 ↗ 180
LED - 2x 2,5W incl. - 370 lm
☐ - IP20
synthetics



Piculet




Piculet 42500/31/LI

† 1190 → 220 ↗ 220
LED - 2x 2,5W incl.- 370 lm
☐ - IP20
synthetics



Piculet 42500/38/LI

† 1190 → 220 ↗ 220
LED - 2x 2,5W incl.- 370 lm
☐ - IP20
synthetics



Piculet 42500/93/LI

† 1190 → 220 ↗ 220
LED - 2x 2,5W incl.- 370 lm
☐ - IP20
synthetics





touch & dim



**Posada
37362/30/LI**

1 455 → 313 ↗ 451
E27 - 1x 70W incl.- 1200 lm
⊕ - IP20
metal



**Posada
37364/30/LI**

1 611 → 400 ↗ 447
E27 - 2x 70W incl.- 2x 1200 lm
⊕ - IP20
metal



**Posada
37363/30/LI**

1 1838 → 500 ↗ 911
E27 - 2x 70W incl.- 2x 1200 lm
⊕ - IP20
metal





touch & dim



Posada
37362/31/LI

1 455 ↔ 313 ↗ 451
E27 - 1x 70W incl.- 1200 lm
⊕ - IP20
metal



Posada
37364/31/LI

1 611 ↔ 400 ↗ 447
E27 - 2x 70W incl.- 2x 1200 lm
⊕ - IP20
metal



Posada
37363/31/LI

1 1838 ↔ 500 ↗ 911
E27 - 2x 70W incl.- 2x 1200 lm
⊕ - IP20
metal







La Lente

Lost and found again

Dressed up in its own trendy colors - white and soft blue abyss - this small and compact table lamp is your trustworthy companion to bring a light accent on your bedside table, in your living room or in your hallway.

Emitting a diffuse glow without using a light bulb, La Lente lights up only by touching the back-side.







**La Lente
43300/31/LI**

↑ 235 ↔ 175 ↙ 180
LED - 2x 2,5W incl.- 370 lm
☐ - IP20
synthetics



**La Lente
43300/35/LI**

↑ 235 ↔ 175 ↙ 180
LED - 2x 2,5W incl.- 370 lm
☐ - IP20
synthetics





**Lucebar
42230/31/LI**

↑ 1796 ↔ 289 ↘ 289
2G11 - 2x 55W incl. - 2x 4800 lm
⊕ - IP20
glass



**Lucebar
42230/48/LI**

↑ 1796 ↔ 289 ↘ 289
2G11 - 2x 55W incl. - 2x 4800 lm
⊕ - IP20
glass





turn & dim





What is it about light that we can't grasp?

Light is all around us, yet we can't put our finger on it. Ecliptic is just as mystifying as light. It's a body with a glowing cavity, mass and void, all in one. It looks like it's from outer space.

Ecliptic appeals and amazes. It is a mysterious interpretation of light.

Ecliptic

Ecliptic



**Ecliptic
40755/31/LI**

1 3000 → 650 / 650
LED - 16x 2,5W incl. - 3000 lm
☐ - IP20
metal



**Ecliptic
40755/93/LI**

1 3000 → 650 / 650
LED - 16x 2,5W incl. - 3000 lm
☐ - IP20
metal





**Ecliptic
40756/31/LI**

1 3000 ↔ 475 ↗ 475
LED - 12x 2,5W incl. - 2250 lm
☐ - IP20
metal



**Ecliptic
40756/93/LI**

1 3000 ↔ 475 ↗ 475
LED - 12x 2,5W incl. - 2250 lm
☐ - IP20
metal





reddot design award
winner 2012



product
design award
2012



Cielo

Where is light coming from?

Cielo keeps a secret inside and makes the impossible possible: to emit light without a bulb. Bathing in eternal light, the shade lights up from the inside. See through Cielo – it is pure magic.

The combination of a classic shape and integrated LEDs, makes Cielo the essence of sophisticated lighting. A true Lirio by Philips classic 2012 iF and Red Dot Design award winner.







Cielo
40550/01/LI



1 3210 ↔ 593 ↗ 593
LED - 24x 2W incl. - 2350 lm
☐ - IP20
aluminium - synthetics



Cielo
40550/30/LI



1 3210 ↔ 593 ↗ 593
LED - 24x 2W incl. - 2350 lm
☐ - IP20
aluminium - synthetics



Cielo
40550/31/LI



1 3210 ↔ 593 ↗ 593
LED - 24x 2W incl. - 2350 lm
☐ - IP20
aluminium - synthetics







Skive
40380/30/LI

1 3000 ↔ 700 ↗ 700
E27 - 3x 70W incl.- 3x 1200 lm
⊕ - IP20
aluminium - glass




Skive
40380/31/LI

1 3000 ↔ 700 ↗ 700
E27 - 3x 70W incl.- 3x 1200 lm
⊕ - IP20
aluminium - glass



Bunch






Bunch
41050/31/LI

1 2200 ↔ 650 / 650
E27 - 3x 20W incl. - 3x 1220 lm
⊕ - IP20
glass







Teres
40205/11/LI

↑ 2600 ↔ 844 ↙ 64
G9 - 7x 28W incl.- 7x 370 lm
⊕ - IP20
metal



Teres
40205/17/LI

↑ 2600 ↔ 844 ↙ 64
G9 - 7x 28W incl.- 7x 370 lm
⊕ - IP20
metal



Teres
40206/11/LI


↑ 2590 ↔ 1184 ↙ 64
G9 - 11x 28W incl.- 1370 lm
⊕ - IP20
metal



Teres
40206/17/LI

↑ 2590 ↔ 1184 ↙ 64
G9 - 11x 28W incl.- 1370 lm
⊕ - IP20
metal





Spots, wall & ceiling



Bloq
57000/30/LI

1 122 ↔ 163 ↗ 163
G53 - 1x 50W incl. - 530 lm
⊕ - IP20
metal



Bloq
57002/30/LI

1 122 ↔ 313 ↗ 163
G53 - 2x 50W incl. - 2x 530 lm
⊕ - IP20
metal



Bloq
57003/30/LI

1 122 ↔ 463 ↗ 163
G53 - 3x 50W incl. - 3x 530 lm
⊕ - IP20
metal



Bloq
57004/30/LI

1 122 ↔ 313 ↗ 313
G53 - 4x 50W incl. - 4x 530 lm
⊕ - IP20
metal









Bloq
57000/31/LI

1 122 ↔ 163 ↗ 163
G53 - 1x 50W incl. - 530 lm
⊕ - IP20
metal



Bloq
57002/31/LI

1 122 ↔ 313 ↗ 163
G53 - 2x 50W incl. - 2x 530 lm
⊕ - IP20
metal



Bloq
57003/31/LI

1 122 ↔ 463 ↗ 163
G53 - 3x 50W incl. - 3x 530 lm
⊕ - IP20
metal



Bloq
57004/31/LI

1 122 ↔ 313 ↗ 313
G53 - 4x 50W incl. - 4x 530 lm
⊕ - IP20
metal





Bonq
57981/31/16

1 101 ↔ 141 / 141
G53 - 1x 30W incl. - 390 lm
⊕ - IP20
aluminium



Bonq
57982/31/16

1 101 ↔ 281 / 141
G53 - 2x 30W incl. - 2x 390 lm
⊕ - IP20
aluminium



Bonq
57981/48/16

1 101 ↔ 141 / 141
G53 - 1x 30W incl. - 390 lm
⊕ - IP20
aluminium



Bonq
57982/48/16

1 101 ↔ 281 / 141
G53 - 2x 30W incl. - 2x 390 lm
⊕ - IP20
aluminium





Bonq
57984/31/16

l 101 ↔ 881 / 141
G53 - 4x 30W incl.- 4x 390 lm
⊕ - IP20
aluminium



Bonq
57984/48/16

l 101 ↔ 881 / 141
G53 - 4x 30W incl.- 4x 390 lm
⊕ - IP20
aluminium





**Retroplanet
57035/31/LI**

1 108 ↔ 94 ↗ 94
GU10 - 1x 5,5W incl. - 350 lm
☑ - IP20
aluminium



**Retroplanet
57035/44/LI**

1 108 ↔ 94 ↗ 94
GU10 - 1x 5,5W incl. - 350 lm
☑ - IP20
aluminium



**Retroplanet
57035/48/LI**

1 108 ↔ 94 ↗ 94
GU10 - 1x 5,5W incl. - 350 lm
☑ - IP20
aluminium



**Retroplanet
57035/53/LI**

1 108 ↔ 94 ↗ 94
GU10 - 1x 5,5W incl. - 350 lm
☑ - IP20
aluminium







Planet
57030/48/PN*

1 82 → 80 / 80
 GU10 - 1x max. 50W excl.
 ⊕ - IP20
 aluminium



Planet
57032/48/PN*


1 95 → 195 / 80
 GU10 - 2x max. 50W excl.
 ⊕ - IP20
 aluminium



Planet
57034/48/PN*

1 95 → 195 / 195
 GU10 - 4x max. 50W excl.
 ⊕ - IP20
 aluminium





Planet
57036/48/PN*

l 107 → 1055 / 82
GU10 - 6x max. 50W excl.
⊕ - IP20
aluminium





**Planet Led
57030/31/P0**

1 82 → 80 / 80
LED GU10 - 1x 3,2W incl- 230lm
⊕ - IP20
aluminium



**Planet
57030/31/PN***

1 82 → 80 / 80
GU10 - 1x max. 50W
⊕ - IP20
aluminium



**Planet Led
57034/31/P0**

1 95 → 195 / 195
LED GU10 - 4x 3,2W incl- 4x 230lm
⊕ - IP20
aluminium



**Planet
57034/31/PN***

1 95 → 195 / 195
GU10 - 4x max. 50W
⊕ - IP20
aluminium



*bulb not included



**Planet Led
57032/31/P0**

1 95 → 195 / 80
LED GU10 - 2x 3,2W incl- 2x 230lm
⊕ - IP20
aluminium



**Planet
57032/31/PN***

1 95 → 195 / 80
GU10 - 2x max. 50W
⊕ - IP20
aluminium



**Planet Led
57036/31/P0**

1 107 → 1055 / 82
LED GU10 - 6x 3,2W incl- 6x 230lm
⊕ - IP20
aluminium



**Planet
57036/31/PN***

1 107 → 1055 / 82
GU10 - 6x max. 50W
⊕ - IP20
aluminium



*bulb not included

Rima



Rima
33607/31/16

1 117 ↔ 827 / 65
G5 - 1x 14W incl.- 1350 lm
□ - IP20
aluminium





Rando













































































Rando
32515/48/LI

1 82 ↔ 504 ↗ 504
2GX13 - 1x 60W incl. - 5000 lm
☐ - IP20
synthetics



30206/30/16 915003152001  8 717943 763016	30206/31/16 915003152101  8 717943 763023	30207/17/16 915003152401  8 717943 763054	30207/31/16 915003151901  8 717943 763009	30939/17/16 915004413701  8 718291 503873	30939/31/16 915004413601  8 718291 503866
 ⌘ 63	 ⌘ 63	 ⌘ 64	 ⌘ 64	 ⌘ 66	 ⌘ 66
31207/31/16 915005055101  8 718696 127247	31208/31/16 915005055201  8 718696 127254	31211/31/16 915005054501  8 718696 127186	31212/31/16 915005054801  8 718696 127216	31213/31/16 915005054601  8 718696 127193	31214/31/16 915005054701  8 718696 127209
 ⌘ 67	 ⌘ 67	 ⌘ 73	 ⌘ 73	 ⌘ 73	 ⌘ 72
32201/11/16 915002308901  8 717943 019359	32202/11/16 915002309001  8 717943 019366	32203/17/16 915002293801  8 717943 016082	32204/17/16 915002315301  8 717943 025879	32207/11/16 915002384001  8 717943 035564	32208/11/16 915002298701  8 717943 017041
 ⌘ 82	 ⌘ 82	 ⌘ 84	 ⌘ 84	 ⌘ 82	 ⌘ 80
32209/11/16 915002294201  8 717943 016129	32515/48/LI 915002000401  5 413987 044571	33604/11/16 915002290401  8 717943 015030	33604/31/16 915002290501  8 717943 015047	33607/31/16 915002381901  8 717943 035342	34203/17/16 915002298401  8 717943 017010
 ⌘ 80	 ⌘ 141	 ⌘ 69	 ⌘ 69	 ⌘ 136	 ⌘ 84
34206/31/16 915002293901  8 717943 016099	34207/31/16 915002294101  8 717943 016112	34208/11/16 915002395101  8 717943 036981	36038/38/E7 915005217901  8 718696 132821	36039/38/E7 915005218001  8 718696 132838	36106/11/16 915003538101  8 717943 771110
 ⌘ 87	 ⌘ 87	 ⌘ 80	 ⌘ 39	 ⌘ 39	 ⌘ 25
36167/30/E7 915005224101  8 718696 133446	36167/31/E7 915005218801  8 718696 132913	36446/11/P1 915005303701  8 718696 154434	36557/11/P1 915005308501  8 718696 154731	37167/31/16 915005053201  8 718696 127056	37168/31/16 915005053101  8 718696 127049
 ⌘ 36	 ⌘ 36	 ⌘ 10	 ⌘ 10	 ⌘ 12	 ⌘ 12

<p>37169/31/16 915005053301</p>  <p>8 718696 127063</p>  <p>⌘ 12</p>	<p>37269/17/16 915003463101</p>  <p>8 717943 765904</p>  <p>⌘ 57</p>	<p>37302/38/16 915005052401</p>  <p>8 718696 127001</p>  <p>⌘ 48</p>	<p>37305/06/16 915005052601</p>  <p>8 718696 126974</p>  <p>⌘ 48</p>	<p>37307/06/16 915005052501</p>  <p>8 718696 126967</p>  <p>⌘ 48</p>	<p>37308/06/16 915005053001</p>  <p>8 718696 127032</p>  <p>⌘ 49</p>
<p>37309/06/16 915005052901</p>  <p>8 718696 127025</p>  <p>⌘ 48</p>	<p>37312/56/16 915005054001</p>  <p>8 718696 127131</p>  <p>⌘ 14</p>	<p>37313/56/16 915005053901</p>  <p>8 718696 127124</p>  <p>⌘ 14</p>	<p>37316/56/16 915005053701</p>  <p>8 718696 127100</p>  <p>⌘ 14</p>	<p>37318/56/16 915005053501</p>  <p>8 718696 127087</p>  <p>⌘ 14</p>	<p>37319/56/16 915005054201</p>  <p>8 718696 127155</p>  <p>⌘ 15</p>
<p>37326/06/16 915005052701</p>  <p>8 718696 127575</p>  <p>⌘ 49</p>	<p>37362/30/LI 915001919401</p>  <p>5 413987 032622</p>  <p>⌘ 98</p>	<p>37362/31/LI 915001919501</p>  <p>5 413987 032639</p>  <p>⌘ 100</p>	<p>37363/30/LI 915001869701</p>  <p>5 413987 027635</p>  <p>⌘ 98</p>	<p>37363/31/LI 915001837301</p>  <p>5 413987 027642</p>  <p>⌘ 100</p>	<p>37364/30/LI 915001838001</p>  <p>5 413987 027659</p>  <p>⌘ 98</p>
<p>37364/31/LI 915001869801</p>  <p>5 413987 027666</p>  <p>⌘ 100</p>	<p>37480/17/16 915003482801</p>  <p>8 717943 767427</p>  <p>⌘ 52</p>	<p>37480/30/16 915003482901</p>  <p>8 717943 767434</p>  <p>⌘ 52</p>	<p>37481/17/16 915003482501</p>  <p>8 717943 767397</p>  <p>⌘ 52</p>	<p>37481/30/16 915003482601</p>  <p>8 717943 767403</p>  <p>⌘ 52</p>	<p>37778/17/16 915003155001</p>  <p>8 717943 763313</p>  <p>⌘ 25</p>
<p>40205/11/LI 915001405901</p>  <p>5 412253 952367</p>  <p>⌘ 121</p>	<p>40205/17/LI 915001409101</p>  <p>5 412253 952626</p>  <p>⌘ 121</p>	<p>40206/11/LI 915001406001</p>  <p>5 412253 952374</p>  <p>⌘ 121</p>	<p>40206/17/LI 915001409201</p>  <p>5 412253 952633</p>  <p>⌘ 121</p>	<p>40380/30/LI 915000119701</p>  <p>5 413987 044489</p>  <p>⌘ 117</p>	<p>40380/31/LI 915000119801</p>  <p>5 413987 044496</p>  <p>⌘ 117</p>
<p>40397/30/16 915003483001</p>  <p>8 717943 767441</p>  <p>⌘ 54</p>	<p>40397/31/16 915003483101</p>  <p>8 717943 767458</p>  <p>⌘ 54</p>	<p>40550/01/LI 915002364201</p>  <p>5 413987 074790</p>  <p>⌘ 115</p>	<p>40550/30/LI 915002364301</p>  <p>5 413987 074806</p>  <p>⌘ 115</p>	<p>40550/31/LI 915002364401</p>  <p>5 413987 074813</p>  <p>⌘ 115</p>	<p>40755/31/LI 915003927201</p>  <p>5 413987 133213</p>  <p>⌘ 110</p>

40755/93/LI 915003927301  5 413987 133220  ⌘ 110	40756/31/LI 915003927401  5 413987 133237  ⌘ 111	40756/93/LI 915003927501  5 413987 133244  ⌘ 111	40795/26/16 915004061001  8 718291 433323  ⌘ 57	40825/31/16 915004182401  8 718291 452904  ⌘ 26	40825/38/16 915004182501  8 718291 452911  ⌘ 26
40826/31/16 915004183901  8 718291 452966  ⌘ 26	40828/38/16 915004194301  8 718291 453574  ⌘ 60	40828/87/16 915004194401  8 718291 453581  ⌘ 60	40829/38/16 915004195201  8 718291 453666  ⌘ 60	40829/87/16 915004195301  8 718291 453673  ⌘ 60	40909/17/16 915005055301  8 718696 127261  ⌘ 22
40910/17/16 915005055401  8 718696 127278  ⌘ 22	40925/30/16 915005057501  8 718696 127377  ⌘ 16	40925/60/16 915005057601  8 718696 127384  ⌘ 19	40926/30/16 915005058001  8 718696 127421  ⌘ 16	40926/60/16 915005057901  8 718696 127414  ⌘ 19	40927/30/16 915005057801  8 718696 127407  ⌘ 16
40927/60/16 915005057701  8 718696 127391  ⌘ 18	40928/30/16 915005058201  8 718696 127445  ⌘ 17	40928/60/16 915005058101  8 718696 127438  ⌘ 19	40929/30/16 915005058301  8 718696 127452  ⌘ 17	40929/60/16 915005058401  8 718696 127469  ⌘ 18	40942/30/16 915005058501  8 718696 127476  ⌘ 16
40942/60/16 915005058601  8 718696 127483  ⌘ 19	40956/30/PN 915005311801  8 718696 156629  ⌘ 34	40957/30/PN 915005311901  8 718696 156636  ⌘ 34	41050/31/LI 915002313001  5 413987 071225  ⌘ 119	42230/31/LI 915002317101  5 413987 071522  ⌘ 106	42230/48/LI 915002389201  5 413987 075926  ⌘ 106
42500/31/LI 915004285001  5 413987 148897  ⌘ 96	42500/38/LI 915004285101  5 413987 148903  ⌘ 96	42500/93/LI 915004302201  5 413987 148989  ⌘ 96	43268/73/16 915004194801  8 718291 453628  ⌘ 46	43268/86/16 915004194901  8 718291 453635  ⌘ 46	43280/56/16 915005054301  8 718696 127162  ⌘ 24

43282/56/16 915005054401  8 718696 127179	43284/17/PO 915005311701  8 718696 156612	43300/31/LI 915004284801  5 413987 148873	43300/35/LI 915004284901  5 413987 148880	43500/31/LI 915004284301  5 413987 148828	43500/32/LI 915004284401  5 413987 148835
 ⌘ 24	 ⌘ 30	 ⌘ 105	 ⌘ 105	 ⌘ 94	 ⌘ 95
43500/34/LI 915004284501  5 413987 148842	43500/35/LI 915004284601  5 413987 148859	43500/38/LI 915004284701  5 413987 148866	43500/93/LI 915004302101  5 413987 148972	49020/31/P1 915005317201  8 718696 156667	49021/31/P1 915005317001  8 718696 156643
 ⌘ 94	 ⌘ 95	 ⌘ 95	 ⌘ 95	 ⌘ 43	 ⌘ 43
49023/31/P1 915005317101  8 718696 156650	57000/30/LI 915001842101  5 413987 004445	57000/31/LI 915001384201  5 412253 950547	57002/30/LI 915001842201  5 413987 004452	57002/31/LI 915001384301  5 412253 950554	57003/30/LI 915001842301  5 413987 004469
 ⌘ 43	 ⌘ 124	 ⌘ 127	 ⌘ 124	 ⌘ 127	 ⌘ 124
57003/31/LI 915001384401  5 412253 950561	57004/30/LI 915001842401  5 413987 004476	57004/31/LI 915001384501  5 412253 950578	57030/31/PO 915001380703  5 413987 235641	57030/31/PN 915001380702  5 413987 235689	57030/48/PN 915001380502  5 413987 235672
 ⌘ 127	 ⌘ 124	 ⌘ 127	 ⌘ 134	 ⌘ 134	 ⌘ 132
57032/31/PO 915001382903  5 413987 235597	57032/31/PN 915001382902  5 413987 235702	57032/48/PN 915001382802  5 413987 235696	57034/31/PO 915001383103  5 413987 235627	57034/31/PN 915001383102  5 413987 235726	57034/48/PN 915001383002  5 413987 235719
 ⌘ 135	 ⌘ 135	 ⌘ 132	 ⌘ 134	 ⌘ 134	 ⌘ 132
57035/31/LI 915004319901  5 413987 149535	57035/44/LI 915004320101  5 413987 149559	57035/48/LI 915004320001  5 413987 149542	57035/53/LI 915004320201  5 413987 149566	57036/31/PO 915001383303  5 413987 235603	57036/31/PN 915001383302  5 413987 235740
 ⌘ 130	 ⌘ 130	 ⌘ 130	 ⌘ 130	 ⌘ 135	 ⌘ 135

<p>57036/48/PN 915001383202</p>  <p>5 413987 235733</p>  <p>⌘ 133</p>	<p>57180/31/16 915005056201</p>  <p>8 718696 127292</p>  <p>⌘ 74</p>	<p>57182/31/16 915005056501</p>  <p>8 718696 127322</p>  <p>⌘ 74</p>	<p>57183/31/16 915005056301</p>  <p>8 718696 127308</p>  <p>⌘ 74</p>	<p>57184/31/16 915005056401</p>  <p>8 718696 127315</p>  <p>⌘ 75</p>	<p>57981/31/16 915002381101</p>  <p>8 717943 035267</p>  <p>⌘ 128</p>
<p>57981/48/16 915002381201</p>  <p>8 717943 035274</p>  <p>⌘ 128</p>	<p>57982/31/16 915002381301</p>  <p>8 717943 035281</p>  <p>⌘ 128</p>	<p>57982/48/16 915002381401</p>  <p>8 717943 035298</p>  <p>⌘ 128</p>	<p>57984/31/16 915002381501</p>  <p>8 717943 035304</p>  <p>⌘ 129</p>	<p>57984/48/16 915002381601</p>  <p>8 717943 035311</p>  <p>⌘ 129</p>	
























©2016 Philips Lighting Holding B.V.

All rights reserved.

Philips Consumer Luminaires - InStyle | Lirio Collection 2016

CEE

Explanation of symbols

-  On/off switch
 -  Two switches included
 -  Dimmer on article
 -  Touch dimmer included
 -  Compatible with wall dimmer
 -  Motion sensor
 -  Day and night sensor
 -  Integrated switch box
 -  Directional light
 -  Bi-Directional light
 -  Adjustable height
 -  Adjustable light source
 -  Rotates freely
 -  Suitable for horizontal and vertical mounting
 -  Suitable for wall and ceiling installation
 -  No wire needed
 -  Batteries included
 -  Energy class of the bulb (in this example A⁺)
 -  Bulb compatible with range of energy classes... (in this example A⁺-A-B-C-D-E)
-  Dimensions
 -  Recessed size
 -  Cutout size
 -  Class I - II - III

Light sources

-  G4
-  G9
-  GU10
-  GU10
-  E14
-  E14
-  E14
-  E14
-  E27
-  E27
-  E27
-  GX53
-  G53
-  2GX13
-  G5
-  T5
-  2G11
-  2G7
-  G23
-  G24Q1



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips Lighting reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.philips.ee
www.philips.lv
www.philips.lt
www.philips.ro

www.philips.si
www.philips.bg
www.philips.hr
www.philips.rs