



































# Which LED for which function?









-   
 Head-lights
-   
 Front/rear position/parking lights
-   
 Front fog lights
-   
 Dashboard lights
-   
 Interior lights
-   
 Glove compartment lights
-   
 Rear fog lights
-   
 Trunk lights
-   
 License plate lights
-   
 Reversing light
-   
 3rd stop light
-   
 Stop lights

## X-tremeUltinon LED – Brighter. Whiter. Stronger.

 LED-HL [≈H4] 6500K	 LED-T10 [≈W5W] 6000K 8000K	 LED-FOG [≈H8/H11/H16] 6500K	 LED-T10 [≈W5W] 4000K	 LED-T10 [≈W5W] 4000K	 LED-T10 [≈W5W] 4000K	 LED-RED [≈P21W] RED	 LED-T10 [≈W5W] 4000K	 LED-T10 [≈W5W] 6000K 8000K	 LED-WHITE [≈P21W] WHITE	 LED-RED [≈P21W] RED	 LED-RED [≈P21W] RED
 LED-HL [≈H7] 6500K	 LED-RED [≈P21/5W] RED		 LED-FEST 30mm 4000K	 LED-FEST 30mm 4000K	 LED-FEST 30mm 4000K	 LED-RED [≈P21W] RED	 LED-FEST 30mm 4000K	 LED-FEST 30mm 6000K	 LED-T20-WHITE [≈W21W] WHITE	 LED-RED [≈P21/5W] RED	 LED-RED [≈P21/5W] RED
			 LED-FEST 38mm 4000K	 LED-FEST 38mm 4000K	 LED-FEST 38mm 4000K		 LED-FEST 38mm 4000K	 LED-FEST 38mm 6000K			
			 LED-FEST 43mm 4000K	 LED-FEST 43mm 4000K	 LED-FEST 43mm 4000K		 LED-FEST 43mm 4000K	 LED-FEST 43mm 6000K			

## Vision LED – Bright signals. Stylish driving.

 LED-RED [≈P21/5W] RED	 LED-T10 [≈W5W] 4000K	 LED-T10 [≈W5W] 4000K	 LED-T10 [≈W5W] 4000K	 LED-T20-RED [≈W21W] RED	 LED-T10 [≈W5W] 4000K	 LED-T10 [≈W5W] 6000K	 LED-T20-RED [≈W21W] RED	 LED-RED [≈P21(5)W] RED
						 LED-FEST 38mm 6000K		 LED-T20-RED [≈W21(5)W] RED

## CANbus adapter for optimal control

 CANbus 5W	 CANbus 5W	 CANbus 5W	 CANbus 5W	 CANbus 5W	 CANbus 5W
--	--	--	--	---	--

### LED interior lighting

This LED retrofit light is suitable for the interior functions of your car. It is your own responsibility that the use of the LED retrofit light complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability.

### LED headlighting and signaling

**Important:** This LED retrofit light is specifically designed and intended for off-road use only, such as rally and race track driving, and is therefore subject to a technical check for installation. The LED retrofit light cannot legally be installed in on-road vehicles. Lumileds cannot accept any responsibility and/or liability. It is your own responsibility that the use of the LED Retrofit lights complies with applicable legal requirements.

Designed for rally and race tracks. Not for use on public roads.

The LED retrofit headlights and exterior signaling lighting cannot be sold in Germany, Spain, Slovakia, Cyprus, UK, Netherlands, Czech Republic, Greece, Hungary, Latvia, Luxembourg, Malta and Slovenia.

