

PHILIPS

Automotive

Dibujos técnicos de las Bases

Bases de metal

H6 - (H6W)   BAX 9s 12V 12036	H21 - (H21W)   BAY 9s 12V 12356 24V 24356	H21 Ámbar - (HY21W)   BAW 9s 12V 12146
Festoon 5W 38mm (C5W)   SV8,5-8 12V 12844 24V 13844 LED 128016000KB1	Festoon 10W 38mm (C10W)   SV8,5-8 12V 12854 LED 128016000KB1	Festoon 10W 43mm   SV8,5-8 12V 12866 24V 13866 LED 11864ULWX1
1 Polo - 1141 (P21W)   BA 15s 12V 12498 24V 13498 LED 11498ULWX2/ 12839REDX2	1 Polo - (P22 - 15W)   BA 15s 12V 12403 24V 13401	Ámbar - 1056 (PY21W)   BAU 15s 12V 12496 24V 13496 LED 11498ULAX2
2 Polos - 1034 (P21/5W)   BAY 15d 12V 12499 24V 13499 LED 11499ULRX2	2 Polos (P25 - 21/5W)   BA 15d 12V 12502 24V 13405	2 Polos Roja (PR21/5W)   BAW 15d 12V 12495
67 5W (R5W)   BA 15s 12V 12821 24V 13821	67 10W (R10W)   BA 15s 12V 12814 24V 13814	67 Ámbar 10W (RY10W)   BAU 15s 12V 12093
53 (T2W)   BA 9s 12V 12913 24V 13913	69 4W (T4W)   BA 9s 12V 12929 24V 13929	