

# PHILIPS

Fully automatic  
espresso machines

Philips 5400 Series

12 Beverages

LatteGo milk solution

Chrome

FTF display

EP5447/90



## 12 delicious fresh bean coffees, easier than ever LatteGo, the fastest to clean milk system ever\*

Easily make aromatic coffee varieties like Espresso, Coffee, Cappuccino and Latte Macchiato at the touch of a button. LatteGo tops milk varieties with silky smooth froth, is easy to set up and can be cleaned in as little as 15 seconds\*

### A variety of coffees customized to your taste

- Enjoy 12 coffees at your fingertips, including café au lait
- Silky smooth milk froth thanks to high speed LatteGo system
- Easy selection of your coffee with the intuitive display
- Adjust aroma and volume with the coffee customizer
- Your perfect cup, every time, thanks to 4 user profiles

### High quality coffee from fresh beans

- Even more flavor thanks to the extra shot function
- The perfect temperature, aroma and crema cup after cup\*
- Easily adjust to your taste with 12-step grinder levels
- 20,000 cups of finest coffee with durable ceramic grinders

### Effortless use and cleaning for everyday enjoyment

- Exceptionally easy to clean with LatteGo: 2 parts, no tubes
- Up to 5000 cups\* without descaling thanks to AquaClean
- Easy cleaning thanks to fully removable brew group

# Highlights

## 12 delicious coffees



Every moment has its own kind of coffee to enjoy. From powerful espresso to indulgent cappuccino, your fully automatic espresso machine delivers a perfect in-cup result without any fuss in no time.

## LatteGo milk system



Top your coffee off with a silky-smooth layer of milk froth. The LatteGo mixes milk and air at high speed in the round frothing chamber, then adds a splash-free, creamy layer of milk froth to your cup at just the right temperature.

## Intuitive display



There's little standing between you and your next delicious cup of coffee with our easy-to-use display. In a few steps you can customize your fresh-bean flavor and flow smoothly from craving to cup.

## Coffee customizer



Make any coffee your own with the coffee customizer's easily adjustable settings for intensity, coffee and milk length.

## User profiles

Enjoy coffee you love the same way every time with four user profiles that store your customized recipes. With an extra guest profile, your visitors can savor a coffee exactly the way they like, without changing yours.

## Extra shot function



Boost your drink's intensity with the coffee customizer's extra-shot feature, which adds powerful flavor without the bitterness.


## Perfect temperature and aroma



The Aroma Extract system intelligently strikes the optimum balance between brewing temperature and aroma extraction by keeping

the water temperature between 90 and 98°C, while regulating the water flow rate, so you can enjoy delicious coffees.

## 12-step grinder adjustment




Our durable ceramic grinders can be adjusted in 12 steps, so you can turn your beans into anything from ultra-fine powder to coarse grindings.

## 100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20,000 cups.

## Exceptionally easy to clean



For your convenience, you can put LatteGo drip tray and the coffee ground container in the dishwasher. This will save time and ensure a hygienic cleaning.

# Specifications

## Country of origin

Designed in: Italy  
Made in: Romania

## General specifications

Type of display: TFT  
Adjustable spout height: 85 - 145 mm  
Milk Solution: LatteGo  
Dishwasher safe parts: Drip tray, LatteGo

## Technical specifications

Capacity milk carafe: 0.265 L  
Capacity waste container: 12 servings  
Frequency: 50 Hz  
Max. cup height: 150 mm  
Voltage: 230 V  
Color(s): Black  
Finishing: Chromed  
Cord length: 100 cm  
Filter compatibility: AquaClean  
Waste container: Frontal access  
Water tank: Frontal access  
Weight of product: 8 kg

Product dimensions: 246x372x433 mm  
Coffee bean capacity: 275 g  
Capacity water tank: 1.8 L  
Pump pressure: 15 bar

## Customization

Aroma Strength Settings: 5  
Grinder Settings: 12  
Pre Brew Aroma control  
User Profiles: 4, Guest  
Temperature settings: 3  
Coffee and Milk Length: Adjustable

## Variety

Beverages: Espresso, Coffee, Americano, Cappuccino, Latte Macchiato, Flat white, Café au Lait, Caffè Latte, Caffè crema, Ristretto, Espresso Lungo, Travel mug function, Frothed milk, Hot water  
Coffee Powder Option  
Double Cup  
Milk Double Cup: No

## Other features

Removable brew group  
Aroma Seal  
Guided descaling  
AquaClean

## Accessories

Included: Measuring scoop, Water hardness test strip, AquaClean filter

## Service

2-year guarantee

## Sustainability

ECO setting  
Power consumption brewing: 1500 W  
Recyclable packaging material: > 95%

## Bazaarvoice\_DA\_CO\_FAM

S5400: PHI 5400 LatteGo

