

PHILIPS

SmartBright



Trusted



Reliable



Great value

REAL
PROs
REAL
QUALITY



SmartBright Weatherproof Batten

Real professionals choose **Philips SmartBright** for their everyday lighting installations.

Trusted performance, everyday.

Available in both 600mm and 1,200mm lengths, the new tri-colour/dual power weatherproof batten is an ideal replacement for 1x18W and 1x36W T8 weatherproof battens.

The new range offers high efficacy and high output of bespoke quality light, plus an excellent service life and warranty – making it an ideal and flexible choice for your outdoor applications.


Features and benefits

- ✓ Available in 600mm and 1,200mm lengths
- ✓ 3 colour temperatures and dual power settings in each part number
- ✓ Quick clip cover removal – fast and easy installation
- ✓ Long service life with excellent reliability
- ✓ High degree of protection for outdoor applications (IP65/IK08)

Applications

- ✓ All general outdoor building applications
- ✓ Commercial, office and industrial properties
- ✓ Factories, parking garages, correctional facilities, underpasses, airports etc.

Product highlights



Dual
power

5
year
warranty


50,000
hours
L70

IP65
IK08

Product data

	WT067C SWT SCCT LED L600 PSU AU	WT067C SWT SCCT LED L1200 PSU AU
Power (selectable)	10/20W	20/40W
System lumens	1000/2000lm	2000/4000lm
System efficacy	100lm/W	
CCT (Selectable)	4000/5000/6500K	
CRI	> 80	
SDCM	4000K and 6500K: SDCM < 5; 5000K: SDCM < 7	
Beam angle	110°	
IP / IK rating	IP65/IK08	
Operating temperature	-20°C to +40°C	
Lifetime	50,000 hrs (L70)	
Input voltage	220-240V, 50/60Hz	
Power factor	> 0.9	
Electrical class	Class I	
Driver	Fixed Output	
Mounting type	Surface mount with bracket	
Housing colour	RAL7035 light grey	
Material	Housing: Polycarbonate (PC) Diffuser: Polycarbonate (PC)	
Dimensions	L 656mm x W 107mm x H 72mm	L 1,265mm x W 107mm x H 72mm
Weight	1kg	1.8kg

Dimensions



Order information

Order code	Barcode	Power (W)	Light Output (lm)	CCT (K)	Length (mm)
WT067CSWTL600P	8710163344300	10/20	1000/2000	4000/5000/6500	600
WT067CSWTL1200P	8710163344317	20/40	2000/4000	4000/5000/6500	1,200