

PHILIPS

Woonkamer/Séjour





3.



2.



1.



4.

1. **Particon 53150 48 16**
 H115 L150 D125
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 aluminium



2. **Particon 53152 48 16**
 H115 L289 D125
 Power LED - 2x 7,5W incl. - 2x 350lm
 Class I - IP20
 aluminium



3. **Particon 53154 48 16**
 H115 L567 D125
 Power LED - 4x 7,5W incl. - 4x 350lm
 Class I - IP20
 aluminium



4. **Particon 53159 48 16**
 H1500 L747 D171
 Power LED - 3x 7,5W incl. - 3x 350lm
 Class I - IP20
 aluminium






1.



2.



3.

1. **Balance 40235 17 16**
 H1160 L485 D485
 2GX13 - 1x 40W incl. - 3300lm
 Class I - IP20
 metal - glass



2. **Alive 40855 56 16**
 H1700 L340 D340
 E27 - 1x 20W incl. - 1250lm
 Class I - IP20
 glass - metal



3. **Alpha 69050 48 16**
 H2500 L300 D300
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 glass - aluminium





1.



4.



2.



3.

1. **Amaze 40233 31 16**
 H1400 L434 D434
 2GX13 - 1x 60W incl. - 5000lm
 Class I - IP20
 metal - synthetics



2. **Amaze 40233 48 16**
 H1400 L434 D434
 2GX13 - 1x 60W incl. - 5000lm
 Class I - IP20
 aluminium - synthetics



3. **Fair 40339 48 16**
 H1600 L444 D444
 2GX13 - 1x 55W incl. - 4200lm
 Class I - IP20
 glass - metal



4. **Fair 40340 48 16**
 H99 L444 D444
 2GX13 - 1x 60W incl. - 5000lm
 Class I - IP20
 glass - metal

1.



2.

1. **Nio 31610 17 16**
H65 L120 D120
Power LED - 1x 7,5W incl. - 350lm
Class I - IP20
aluminium



2. **Nio 31610 31 16**
H65 L120 D120
Power LED - 1x 7,5W incl. - 350lm
Class I - IP20
aluminium





1.



2.



3.



4.

1. **Quart 31607 48 16**
 H50 L160 D160
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 glass - aluminium



2. **Quart 31608 48 16**
 H51 L320 D160
 Power LED - 2x 7,5W incl. - 2x 350lm
 Class I - IP20
 glass - aluminium



3. **Row 69067 31 16**
 H55 L212 D212
 Power LED - 4x 7,5W incl. - 4x 350lm
 Class I - IP20
 aluminium



4. **Row 69068 31 16**
 H55 L127 D127
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 aluminium





1.



2.

1. **Styla 32157 31 16**
H36 L230 D230
Power LED - 9x 2,5W incl. - 9x 120lm
Class I - IP20
aluminium



2. **Syma 32158 31 16**
H47 L240 D240
Power LED - 6x 2,5W incl. - 6x 120lm
Class I - IP20
aluminium - glass





1.



2.

1. **Being 32610 48 16**
 H50 L350 D350
 2GX13 - 1x 40W incl. - 3300lm
 Class I - IP20
 aluminium - synthetics




2. **Playful 33100 31 16**
 H59 L414 D287
 2G7 - 2x 11W incl. - 900lm
 Class II - IP20
 synthetics





1.



2.



3.

1. **Peace 30185 31 16**
H60 L286 D98
2G7 - 1x 11W incl. - 900lm
Class II - IP20
metal - synthetics



2. **Peace 30422 31 16**
H60 L510 D98
2G11 - 1x 36W incl. - 2900lm
Class I - IP20
metal - synthetics



3. **Peace 33422 31 16**
H79 L486 D75
2G7 - 1x 36W incl. - 2900lm
Class I - IP20
metal - synthetics



1.



2.



3.



4.

1. **Galax 45590 17 16**
 H100 L133 D31
 LED - 2x 2,5W incl. - 2x 180lm
 15.000 hrs - Class I - IP20
 metal



2. **Galax 45590 31 16**
 H100 L133 D31
 LED - 2x 2,5W incl. - 2x 180lm
 15.000 hrs - Class I - IP20
 metal



3. **Galax 45591 17 16**
 H103 L213 D31
 LED - 4x 2,5W incl. - 2x 350lm
 15.000 hrs - Class I - IP20
 metal



4. **Galax 45591 31 16**
 H103 L213 D31
 LED - 4x 2,5W incl. - 2x 350lm
 15.000 hrs - Class I - IP20
 metal





1. **Metric 69087 31 16**
 H119 L74 D70
 Power LED - 2x 2,5W incl. - 2x 120lm
 Class I - IP20
 aluminium



3. **Fireside 33261 17 16**
 H125 L100 D478
 Power LED - 1x 6,5 W incl. 270 lm
 Class I - IP20
 mat chrome



2. **Metric 69087 87 16**
 H119 L74 D70
 Power LED - 2x 2,5W incl. - 2x 120lm
 Class I - IP20
 aluminium





1.



2.



1. **Milio 69085 31 16**
H65 L131 D131
Power LED - 2x 2,5W incl. - 2x 120lm
Class I - IP20
synthetics - aluminium



2. **Milio 69085 87 16**
H65 L131 D131
Power LED - 2x 2,5W incl. - 2x 120lm
Class I - IP20
synthetics - aluminium





1.



2.



3.



4.

1. **Syon 32159 31 16**
 H57 L158 D158
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 aluminium



2. **Syon 32159 48 16**
 H57 L158 D158
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 aluminium



3. **Sequence 53160 31 16**
 H120 L92 D92
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 metal



4. **Sequence 53162 31 16**
 H120 L182 D92
 Power LED - 2x 7,5W incl. - 2x 350lm
 Class I - IP20
 metal





1.



2.

1.

Avior 59040 17 16
 L167 D167 R80 C155 x155
 G53 - 1x 30W incl.
 Class 2&3 - IP23
 metal



2.

Lakeport 33232 17 16
 H80 L301 D83
 E14 - 1x 12W incl.
 Class I - IP20
 mat chrome - metal



1.



2.



3.



1. **Teqno 56420 48 16**
 H181 L90 D115
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 metal



2. **Teqno 56422 48 16**
 H115 L265 D90
 Power LED - 2x 7,5W incl. - 2x 350lm
 Class I - IP20
 metal



3. **Teqno 56424 48 16**
 H115 L525 D90
 Power LED - 4x 7,5W incl. - 4x 350lm
 Class I - IP20
 metal





1.



2.

-
1. **Novum 36052 17 16**
H155 L153 D107
Power LED - 1x 4,5 W incl. 340 lm
Class I - IP20
mat chrome - metal



-
2. **Novum 36052 31 16**
H155 L153 D107
Power LED - 1x 4,5 W incl. 340 lm
Class I - IP20
white - metal





1.



2.



3.

1. Vaganza 57915 31 16

H234 L218 D202

Power LED - 2x 7,5W incl. - 2x 350lm

Class I - IP20

aluminium


2. Vaganza 57916 31 16

H230 L409 D218

Power LED - 4x 7,5W incl. - 4x 350lm

Class I - IP20

aluminium


3.
Vaganza 57917 31 16

H367 L177 D95

Power LED - 1x 7,5W incl. - 350lm

Class I - IP20

aluminium





1.



2.



3.



4.



5.



6.

1. **Universa 57945 31 16**
 H108 L151 D82
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 aluminium



3. **Universa 57947 31 16**
 H123 L591 D82
 Power LED - 3x 7,5W incl. - 3x 350lm
 Class I - IP20
 aluminium



5. **Universa 57946 17 16**
 H108 L212 D82
 Power LED - 2x 7,5W incl. - 2x 350lm
 Class I - IP20
 aluminium



2. **Universa 57946 31 16**
 H108 L212 D82
 Power LED - 2x 7,5W incl. - 2x 350lm
 Class I - IP20
 aluminium



4. **Universa 57945 17 16**
 H108 L151 D82
 Power LED - 1x 7,5W incl. - 350lm
 Class I - IP20
 aluminium



6. **Universa 57947 17 16**
 H123 L591 D82
 Power LED - 3x 7,5W incl. - 3x 350lm
 Class I - IP20
 aluminium





1.





2.






3.






4.

1. **Fast single spot 53060 48 16**
 H190 L162 D97
 G9 - 1x 42 W incl.
 Class I - IP20
  brushed aluminium - metal

3. **Fast bar spot 53063 48 16**
 H183 L466 D126
 G9 - 3x 42 W incl.
 Class I - IP20
  brushed aluminium - metal

2. **Fast special form 53062 48 16**
 H343 L162 D126
 G9 - 2x 42 W incl.
 Class I - IP20
  brushed aluminium - metal

4. **Fast pendant 53069 48 16**
 H1500 L760 D194
 G9 - 3x 42 W incl.
 Class I - IP20
   brushed aluminium - metal

1.



2.



1.

Yed 57996 31 16

L216 D216 R72 C200 x200
Power LED - 1x 15W incl. - 435lm
Class 2&3 - IP20
aluminium



2.

Yed 57996 48 16

L216 D216 R72 C200 x200
Power LED - 1x 15W incl. - 435lm
Class 2&3 - IP20
aluminium





1.



2.



3.



4.

1. **Sculptor 57962 31 16**
 L122 D122 R105 C110 x110
 Power LED - 1x 7,5W incl. - 350lm
 Class 2&3 - IP23
 aluminium



3. **Sculptor 57963 31 16**
 L122 D122 R105 C110 x110
 Power LED - 3x 7,5W incl. - 3x 350lm
 Class III - IP23
 aluminium



2. **Sculptor 57962 48 16**
 L122 D122 R105 C110 x110
 Power LED - 1x 7,5W incl. - 350lm
 Class III - IP23
 aluminium



4. **Sculptor 57963 48 16**
 L122 D122 R105 C110 x110
 Power LED - 3x 7,5W incl. - 3x 350lm
 Class III - IP23
 aluminium





3.



2.

1. **Zaia 57987 31 16**
 L133 D133 R65 C105 x105
 Power LED - 1x 7,5W incl. - 350lm
 Class 2&3 - IP21
 aluminium



3. **Carnet 59855 31 16**
 L120 D120 R80 C108 x108
 Power LED - 1x 7,5W incl. - 350lm
 Class 2&3 - IP23
 aluminium



2. **Skyon 57989 17 16**
 L125 D125 R90 C110 x110
 Power LED - 1x 7,5W incl. - 350lm
 Class 2&3 - IP21
 aluminium





1.



1.

Stardust 57971 17 16

L78 D78 R77 C67 x67

Power LED - 1x 7,5W Incl. - 350lm

Class 2&3 - IP23

aluminium





1.



2.



3.



4.



1. **Talitha 57983 31 16**
 L75 D75 R80 C65 x65
 Power LED - 3x 2,5W incl. - 3x 120lm
 Class 2&3 - IP23
 aluminium



2. **Talitha 57983 48 16**
 L75 D75 R80 C65 x65
 Power LED - 3x 2,5W incl. - 3x 120lm
 Class 2&3 - IP23
 aluminium



3. **Aquila 59830 31 16**
 L110 D110 R49 C85 x85
 Power LED - 1x 7,5W incl. - 350lm
 Class 2&3 - IP23
 aluminium



4. **Aquila 59830 48 16**
 L110 D110 R49 C85 x85
 Power LED - 1x 7,5W incl. - 350lm
 Class 2&3 - IP23
 aluminium





1.



2.



3.



4.

1. Race single spot 55520 48 16

H131 L114 D114
 GU10 - 1x 35 W incl.
 Class 1 - IP20



brushed aluminium - metal

2. Race ceiling plate 55522 48 16

H131 L305 D80
 GU10 - 2x 35 W incl.
 Class 1 - IP20



brushed aluminium - metal

3. Race ceiling plate 55523 48 16

H131 L525 D80
 GU10 - 3x 35 W incl.
 Class 1 - IP20



brushed aluminium - metal

4. Race ceiling plate 55524 48 16

H130 L243 D243
 GU10 - 4x 35 W incl.
 Class 1 - IP20



brushed aluminium - metal



1. **Pillar ceiling plate 56330 30 16**
H120 D103
GU10 - 1x 35 W incl.
Class 1 - IP20
black - metal



2. **Pillar ceiling plate 56330 31 16**
H120 D103
GU10 - 1x 35 W incl.
Class 1 - IP20
white - metal



3. **Pillar ceiling plate 56332 30 16**
H120 L193 D103
GU10 - 2x 35 W incl.
Class 1 - IP20
black - metal



4. **Pillar ceiling plate 56332 31 16**
H120 L193 D103
GU10 - 2x 35 W incl.
Class 1 - IP20
white - metal



5. **Pillar plate/spiral 56333 30 16**
H120 L203 D190
GU10 - 3x 35 W incl.
Class 1 - IP20
black - metal



6. **Pillar plate/spiral 56333 31 16**
H120 L203 D190
GU10 - 3x 35 W incl.
Class 1 - IP20
white - metal





1.



2.

1. **Merope recessed LED 59843 31 16**

H32 D80

Power LED - 3x 2 W incl. 320 lm

Class 2&3 - IP23

white - aluminium



2. **Merope recessed LED 59843 48 16**

H32 D80

Power LED - 3x 2 W incl. 320 lm

Class 2&3 - IP23

brushed aluminium - aluminium





1.



2.



4.



3.

1. **Runner single spot 53090 48 16**

H107 L110 D90
GU10 - 1x 35 W incl.
Class 1 - IP20



brushed aluminium - metal

2. **Runner bar/tube 53092 48 16**

H109 L305 D90
GU10 - 2x 35 W incl.
Class 1 - IP20



brushed aluminium - metal

3. **Runner bar/tube 53093 48 16**

H109 L480 D90
GU10 - 3x 35 W incl.
Class 1 - IP20



brushed aluminium - metal

4. **Runner plate/spiral 53094 48 16**

H109 L240 D240
GU10 - 4x 35 W incl.
Class 1 - IP20



brushed aluminium - metal



1.



2.



4.



3.

1. Runner single spot 53090 31 16

H107 L110 D90
 GU10 - 1x 35 W incl.
 Class 1 - IP20
 white - metal



2. Runner bar/tube 53092 31 16

H109 L305 D90
 GU10 - 2x 35 W incl.
 Class 1 - IP20
 white - metal



3. Runner bar/tube 53093 31 16


H109 L480 D90
 GU10 - 3x 35 W incl.
 Class 1 - IP20
 white - metal




4. Runner plate/spiral 53094 31 16

H109 L240 D240
 GU10 - 4x 35 W incl.
 Class 1 - IP20
 white - metal







1.



2.



3.



4.

1. **Skien pendant LED 40892 67 16**
H1500 D335
Power LED - 1x 4,5 W incl. 430 lm
Class II - IP20
mat glass - glass



2. **Var pendant LED 40895 87 16**
H1500 D350
Power LED - 1x 4,5 W incl. 430 lm
Class II - IP20
grey - metal




3. **Var pendant LED 40895 38 16**
H1500 D350
Power LED - 1x 4,5 W incl. 430 lm
Class II - IP20
cream - metal




4. **Var pendant LED 40895 53 16**
H1500 D350
Power LED - 1x 4,5 W incl. 430 lm
Class II - IP20
orange - metal






1.



2.



3.

1. **Fado pendant LED 40898 33 16**
 H1500 D355
 Power LED - 1x 4,5 W incl. 430 lm
 Class II - IP20
 green - metal



2. **Fado pendant LED 40898 38 16**
 H1500 D355
 Power LED - 1x 4,5 W incl. 430 lm
 Class II - IP20
 green/cream - metal



3. **Fado pendant LED 40898 87 16**
 H1500 D355
 Power LED - 1x 4,5 W incl. 430 lm
 Class II - IP20
 grey - metal





1.



2.



3.



4.

1. Cypress single spot LED 53220 11 16

H120 L76 D135

Power LED - 1x 3 W incl. 170 lm

Class I - IP20

chrome - synthetics

**2. Cypress bar/tube LED 53222 11 16**

H139 L355 D135

Power LED - 1x 3 W incl. 330 lm

Class I - IP20

chrome - synthetics

**3. Cypress plate/spiral LED 53229 11 16**

H139 L325 D323

Power LED - 3x 3 W incl. 500 lm

Class I - IP20

chrome - synthetics

**4. Cypress special form LED 53224 11 16**

H139 L967 D160

Power LED - 4x 3 W incl. 670 lm

Class I - IP20

chrome - synthetics





1.



2.



3.



4.



5.



6.

1. Clockwork single spot LED 53170 31 16

H90 L110 D110
Power LED - 1x 4 W incl. 280 lm
Class 1 - IP20
white - metal


2. Clockwork single spot LED 53170 48 16

H90 L110 D110
Power LED - 1x 4 W incl. 280 lm
Class 1 - IP20
aluminium - metal


3. Clockwork bar/tube LED 53172 31 16

H90 L255 D93
Power LED - 2x 4 W incl. 560 lm
Class 1 - IP20
white - metal


4. Clockwork bar/tube LED 53172 48 16

H90 L255 D93
Power LED - 2x 4 W incl. 560 lm
Class 1 - IP20
aluminium - metal


5. Clockwork bar/tube LED 53174 31 16

H90 L628 D93
Power LED - 4x 4 W incl. 1120 lm
Class 1 - IP20
white - metal


6. Clockwork bar/tube LED 53174 48 16

H90 L628 D93
Power LED - 4x 4 W incl. 1120 lm
Class 1 - IP20
aluminium - metal





1.



2.




3.



4.



5.



6.

1. **Millenium single spot LED 53190 31 16**

H127 L110 D110

Power LED - 1x 4 W incl. 280 lm

Class 1 - IP20

white - metal



2. **Millenium single spot LED 53190 48 16**

H127 L110 D110

Power LED - 1x 4 W incl. 280 lm

Class 1 - IP20

aluminium - metal



3. **Millenium bar/tube LED 53192 31 16**

H127 L260 D70

Power LED - 2x 4 W incl. 560 lm

Class 1 - IP20

white - metal



4. **Millenium bar/tube LED 53192 48 16**

H127 L260 D70

Power LED - 2x 4 W incl. 560 lm

Class 1 - IP20

aluminium - metal



5. **Millenium bar/tube LED 53194 31 16**

H149 L1006 **D106**

Power LED - 4x 4 W incl. 1120 lm

Class 1 - IP20

white - metal



6. **Millenium bar/tube LED 53194 48 16**

H149 L1006 **D160**

Power LED - 4x 4 W incl. 1120 lm

Class 1 - IP20

aluminium - metal





1.



2.



3.



4.

1. **Afzelia plate/spiral LED 53200 31 16**
 H90 L90 D90
 Power LED - 1x 3 W incl. 170 lm
 Class 1 - IP20
 white - metal



2. **Afzelia plate/spiral LED 53200 48 16**
 H90 L90 D90
 Power LED - 1x 3 W incl. 170 lm
 Class 1 - IP20
 aluminium - metal



3. **Afzelia plate/spiral LED 53202 31 16**
 H90 L176 D90
 Power LED - 2x 3 W incl. 330 lm
 Class 1 - IP20
 white - metal



4. **Afzelia plate/spiral LED 53202 48 16**
 H90 L176 D90
 Power LED - 2x 3 W incl. 330 lm
 Class 1 - IP20
 aluminium - metal





1.



2.



3.



4.

1. **Rimur single spot LED 53270 31 16**
 H112 L70 D138
 Power LED - 1x 3 W incl. 170 lm
 Class 1 - IP20
 white - metal



2. **Rimur single spot LED 53270 48 16**
 H112 L70 D138
 Power LED - 1x 3 W incl. 170 lm
 Class 1 - IP20
 aluminium - metal



3. **Rimur bar/tube LED 53272 31 16**
 H95 L243 D70
 Power LED - 2x 3 W incl. 330 lm
 Class 1 - IP20
 white - metal



4. **Rimur bar/tube LED 53272 48 16**
 H95 L243 D70
 Power LED - 2x 3 W incl. 330 lm
 Class 1 - IP20
 aluminium - metal





1.



2.



3.



4.

1. Rimur plate/spiral LED 53279 31 16

H95 D199

Power LED - 3x 3 W incl. 500 lm

Class 1 - IP20

white - metal


2. Rimur plate/spiral LED 53279 48 16

H95 D199

Power LED - 3x 3 W incl. 500 lm

Class 1 - IP20

aluminium - metal


3. Rimur bar/tube LED 53274 31 16

H95 L633 D70

Power LED - 4x 3 W incl. 670 lm

Class 1 - IP20

white - metal


4. Rimur bar/tube LED 53274 48 16

H95 L633 D70

Power LED - 4x 3 W incl. 670 lm

Class 1 - IP20

aluminium - metal





1.



2.



3.



5.



4.



6.

1. **Ellipse recessed LED 59031 11 16**

H39 D91
Power LED - 1x 3 W incl. 170 lm
Class 2&3 - IP20
chrome - aluminium



2. **Ellipse recessed LED 59031 17 16**

H39 D91
Power LED - 1x 3 W incl. 170 lm
Class 2&3 - IP20
mat chrome - aluminium



3. **Ellipse recessed LED 59031 31 16**

H39 D100
Power LED - 2x 4 W incl. 560 lm
Class 2&3 - IP20
white - aluminium



4. **Galileo recessed LED 59081 11 16**

H39 L100 D100
Power LED - 1x 3 W incl. 170 lm
Class 2&3 - IP20
chrome - aluminium



5. **Galileo recessed LED 59081 17 16**

H39 L100 D100
Power LED - 1x 3 W incl. 170 lm
Class 2&3 - IP20
mat chrome - aluminium



6. **Galileo recessed LED 59081 31 16**

H39 L100 D100
Power LED - 1x 3 W incl. 170 lm
Class 2&3 - IP20
white - aluminium





1.



2.

1. **Watch wall lamp LED 33620 31 16**

H207 L105 D30
Power LED - 1x 2,5 W incl. 190 lm
Class I - IP20
white - metal

2. **Watch wall lamp LED 33620 48 16**

H207 L105 D30
Power LED - 1x 2,5 W incl. 190 lm
Class I - IP20
aluminium - metal



1.



2.



3.

1. Countdown wall lamp LED 33621 31 16

H172 L170 D30
Power LED - 1x 2,5 W incl. 190 lm
Class I - IP20
white - metal

2. Countdown wall lamp LED 33621 48 16

H172 L170 D30
Power LED - 1x 2,5 W incl. 190 lm
Class I - IP20
aluminium - metal

3. Date wall lamp 33622 31 16

H200 L200 D35
Power LED - 1x 1 W 210 lm
Class I - IP20
white - metal



1.



2.



3.

1. **Acamar recessed 59300 17 16**
 H39 L100 D100
 GU10 - 1x 35 W Incl.
 Class 2 - IP23
 mat chrome - metal



2. **Nash recessed 59273 17 16**
 H100 D84
 Power LED - 1x 3,5 W Incl.
 Class 2 - IP23
 mat chrome - aluminium



3. **Nash recessed 59273 31 16**
 H100 D84
 Power LED - 1x 3,5 W Incl.
 Class 2 - IP23
 white - aluminium





1.



2.



3.



5.



4.

1. **Buckeye wall lamp LED 33051 11 16**
 H140 L151 D80
 Power LED - 1x 3,0 W incl. 270 lm
 Class 2 - IP20
 white-glass

2. **Celadon wall lamp LED 33052 17 16**
 H100 L179 D80
 Power LED - 1x 3,0 W incl. 270 lm
 Class 2 - IP20
 white-glass

3. **Oval wall lamp LED 31074 31 16**
 H159 L135 D93
 Power LED - 1x 3,0 W incl. 270 lm
 Class 2 - IP20
 white-glass

4. **Oval wall lamp LED 31074 87 16**
 H159 L135 D93
 Power LED - 1x 3,0 W incl. 270 lm
 Class 2 - IP20
 white/grey-glass

5. **Oval wall lamp LED 31074 56 16**
 H159 L135 D93
 Power LED - 1x 3,0 W incl. 270 lm
 Class 2 - IP20
 mat opal-glass