


DLE 1205 Leading Edge Dimmer Controller

Economical lighting control in small commercial applications

The DLE1205 is a 12 channel leading edge dimmer controller with a maximum load per channel of 5A. It is suitable for use with incandescent and neon light sources, as well as iron core and leading edge electronic transformers.

- Fully rated device The combination of load capacity and sub-circuit protection delivers a superior solution for small scale commercial applications.
- Interference suppression Iron powder core toroidal choke lessens effects of interference from other equipment, such as transformers.
- Naturally ventilated Requires no forced cooling or maintenance.
- Soft start and voltage regulation technologies — Protects lamps from over voltage and dramatically improves lamp life, reducing maintenance costs.
- Diagnostic functionality Device Online/ Offline status reporting.
- User controls Incorporates service override switch and three phase indicator LED. Hardware bypass switches are provided for each channel.
- Options available Including circuit breaker trip reporting, earth leakage and overload protection on each channel, provision of two or three pole circuit breakers, or neutral disconnect circuit breakers.



For detailed product information, please refer to the product information pages at www.philips.com/dynalite and follow the links.




Specifications

Due to continuous improvements and innovations, specifications may change without notice.

Item	Specification	Details
Electrical	Input Voltage	100 - 240 VAC 50 / 60 Hz 3 Phase 人 @ 20 A per phase or; 100 - 240 VAC 50 / 60 Hz Single Phase @ 60 A
	DyNet DC Supply	12 VDC @ 200 mA (supply for approx 10 user interfaces)
	Outputs	12 x dimmed outputs leading edge phase control @ 5 A
	Protection	12 x 6 A 6 kA single pole thermal magnetic circuit breakers
	Regulating Device	Triac - 40 A nom., 600 V, 400 A surge
	Power Conditioning	Regulated outputs Over voltage protection Surge protection Brownout / Sag protection Spike protection Soft start 16 bit fade resolution (65,536 steps) Active phase angle firing compensation
	Interference Suppression	Iron powder toroidal choke
	Auxiliary Micro Supply	12 V @ I A
	Rise Time	100μS @ 230 V
Control	Control Inputs/Outputs	One RS-485 DyNet serial port One DMX512 receive port One programmable dry contact AUX input
	User Controls	Service override switch/Override Diagnostic LED 3 Phase indicator LED Hardware bypass switch for each channel
	Preset Scenes	170
	Diagnostic Functions	Device online/offline status
Physical	Supply Terminals	L1, L2, L3 I x I0 mm² max conductor size
	Output Terminals	Line for each channel I \times 4 mm ² max conductor size Neutral Link bar provided Earth Link bar provided
	Cable Entries	Mains - 4 \times 25 mm dia. knockouts mounted on 100 mm \times 50 mm removable gland plate and 6 \times 25 mm dia. knockouts on right side of enclosure Data - I \times 25 mm dia. knockout
	Cooling System	Naturally ventilated, no forced cooling, no maintenance
	Dimensions (H x W x D)	620 mm × 255 mm × 176 mm (24.4" × 10.0" × 6.9")
	Packed Weight	14.0 kg
	Construction	Alloy / Steel wall mount case with epoxy finish
	Operating Conditions	Temperature: -0 to 40° C ambient Humdity: 0 to 95% non-condensing
	Storage & Transport	Temperature: -25 to 60° C ambient Humidity: 0 to 90% non-condensing
Certification	Certification	CE, C-Tick
Options & Ordering	Standard product Circuit breaker trip reporting Double pole cct breakers Three pole cct breakers Neutral disconnect cct breakers Earth leakage/overload	DLE1205 (Philips 12NC - 913703010009) DLE1205-BT (Philips 12NC - 913703010309) DLE1205-DP (Philips 12NC - 913703003309) DLE1205-3POLE (Philips12NC - 913703010109) DLE1205-ND (Philips 12NC - 913703010409)
	protection	DLE1205-RCBO (Philips 12NC - 913703010509)

Electrical Diagram







Specifications subject to change without notice. @WMGD Pty Ltd Trading as Dynalite. Unit 6, 691 Gardeners Road Mascot 2020 Australia. ABN 33 097 246 921. All rights reserved. Dynalite, DyNet and associated logos are the registered trademarks of WMGD Pty Ltd. Not to be reproduced without permission.



Philips Dynalite 6 / 691 Gardeners Road Mascot, NSW 2020 Australia Tel: +61 2 8338 9899 Email: dynalite.info@philips.com Web: www.philips.com/dynalite