



PHILIPS



Product description	Wattage	Luminous Flux (lm)	Luminous Efficacy (lm/W)	CRI (Ra)	PF	Lifetime	Beam Angle
Essential LEDtube 1200mm 16W=28W 840 G5 I	16W	1,850	>115	>83	>0.92	>30Khrs	240D
Essential LEDtube 1200mm 16W=28W 865 G5 I	16W	1,850	>115	>83	>0.92	>30Khrs	240D
Essential LEDtube 600mm 8W=14W 840 G5 I	8W	900	>110	>83	>0.92	>30Khrs	240D
Essential LEDtube 600mm 8W=14W 865 G5 I	8W	900	>110	>83	>0.92	>30Khrs	240D

- Voltaje 100-240V
- Conexión directa a Línea
- No necesita balastro
- ON/OFF
- Tempo de vida 30,000 Hrs
- CRI >83
- CCT 4000K y 6500K
- Versiones sustitutas de 14W y 28W en Fluorescencia T5

Diagrama de Conexión



Diagrama A







Diagrama B



Dimensiones (mm)



Potencia	C
8W	600
16W	1200

Potencia	C
8W	600
16W	1200