


35ED23.5/LED/740/ND 120-277V E40 G2 4/1 929001818112


1 x 5000 lm

Polar intensity diagram



Light output ratio 1.00
 Service upward 0.50
 Service downward 0.50
 CIE flux code 12 36 67 50 100

Quantity estimation diagram



Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.10	0.10	0.00	0.00	0.00	0.00
0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.31	0.30	0.29	0.28	0.27	0.20	0.16	0.12	0.12	0.09	0.03	0.03
0.80	0.40	0.38	0.36	0.35	0.34	0.26	0.21	0.17	0.17	0.13	0.06	0.06
1.00	0.47	0.44	0.43	0.41	0.40	0.32	0.26	0.21	0.20	0.16	0.08	0.08
1.25	0.55	0.50	0.49	0.47	0.46	0.38	0.31	0.26	0.24	0.20	0.11	0.11
1.50	0.60	0.55	0.55	0.52	0.50	0.42	0.35	0.30	0.28	0.24	0.13	0.13
2.00	0.69	0.62	0.63	0.60	0.57	0.50	0.41	0.36	0.33	0.29	0.18	0.18
2.50	0.76	0.67	0.69	0.65	0.62	0.55	0.46	0.41	0.37	0.33	0.21	0.21
3.00	0.81	0.71	0.73	0.69	0.65	0.59	0.49	0.45	0.40	0.37	0.23	0.23
4.00	0.88	0.76	0.79	0.74	0.70	0.64	0.54	0.50	0.44	0.41	0.27	0.27
5.00	0.92	0.79	0.83	0.78	0.73	0.68	0.58	0.54	0.47	0.45	0.30	0.30

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	25345	24169	22537	20451	21385	22659	24274
50.0	27215	25902	24012	21545	22748	24354	26363
55.0	28865	27470	25362	22541	23950	25807	28114
60.0	30273	28789	26483	23356	25129	27219	29625
65.0	31533	30055	27613	24206	26152	28443	31079
70.0	32854	31227	28571	24886	27056	29566	32415
75.0	34045	32353	29591	25760	27997	30639	33686
80.0	35238	33403	30488	26492	28990	31822	34988
85.0	36477	34634	31621	27439	29999	32980	36381
90.0	37651	35615	32495	28289	30887	33999	37625

(cd/m²)

2017-08-30