

# Professional workshop lamps

Ideal for brief inspection

90  
lumens



Penlight  
★★★★★

40°

20  
lm

LED pointer



Battery



Clip



Ultra-slim

IK06 Shock resistance



IP20 Water resistance



120  
lumens



Penlight Profes-  
sional  
★★★★★

40°

20  
lm

LED pointer



Battery



Clip



Ultra-slim

IK07 Shock resistance



IP54 Water resistance



Grease and solvent  
resistant

New

145  
lumens



Penlight  
Premium  
★★★★★

80°

120  
lm

LED pointer



Rechargeable



Clip, magnet



Ultra-slim

IK07 Shock resistance



IP54 Water resistance



Grease and solvent  
resistant

New

120  
lumens



Penlight  
Premium  
★★★★★

80°

90  
lm

LED pointer



Rechargeable



Clip, magnet



Ultra-slim

IK07 Shock resistance



IP54 Water resistance



Grease and solvent  
resistant