




ERP Ban DIM 2 Stufe 3: Directional lamps (EU/1194/2012)

BU Name	MAG Name	AG Name	CAG Name	GPC	EAN1	EOC	Short EOC	Material Name	Brand	GPC	EAN1	EOC	Alternative Com1	Remark	Alternative LED Handl	Remark	
										neu	neu	neu					
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflec	929800010581	8718291252641	8718291252641	25264101	ECOCLASSIC 28W E14 B35/NR50 1CT/17 SRP	Philips	-	-	-	no replacement in Halogen		LED 40W E14 WW 230V R50 36D DIM/4		
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	92564004235	8727900252743	8727900252743	25274304	ECOCLASSIC 28W E14 230V NR50 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 40W E14 WW 230V R50 36D DIM/4		
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	92563604223	8727900251951	8727900251951	25195104	ECOCLASSIC 42W E27 230V NR63 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 60W E27 WW 230V R63 36D DIM/4		
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925714044205	8718291684300	8718291684300	68430001	ECOCLASSIC 42W E14 230V NR50 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 60W E14 WW 230V R50 36D DIM/4	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	92564004229	8718291760832	8718291760832	76083200	ECOCLASSIC 28W E14 230V NR50 2CT/8 SRP	Philips	-	-	-	no replacement in Halogen		LED 40W E14 WW 230V R50 36D DIM/4		
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	92564004223	8727900951219	8727900951219	95121900	ECOCLASSIC 28W E14 230V NR50 30D 3F/5	Philips	-	-	-	no replacement in Halogen		LED 40W E14 WW 230V R50 36D DIM/4		
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925645244210	8727900820423	8727900820423	82042304	ECOCLASSIC 18W E14 230V NR50 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 25W E14 WW 230V R50 36D ND/4	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925645344213	8727900820461	8727900820461	82046104	ECOCLASSIC 28W E27 230V NR63 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 40W E27 WW 230V R63 36D DIM/4	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925645444208	8727900835304	8727900835304	83530401	ECOCLASSIC 42W E27 R80 25D 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 60W E14 WW 230V R80 36D ND/4	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925719044202	8718291757214	8718291757214	75721400	ECOCLASSIC 28W E14 230V R39 45D 1CT/10	Philips	-	-	-	no replacement in Halogen		LED 40W E14 WW 230V R39 36D ND/4	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925645544205	87279008354201	87279008354201	83542001	ECOCLASSIC 70W E27 R80 25D 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 100W E14 WW 230V R80 36D ND/4	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925640044234	8710619361998	8710619361998	36199801	ECOCL ATT 28W E14 230V NR50 1CT/10 SRP	Attralux	-	-	-	no replacement in Halogen		ATR LED 40W R50 WW 36D 18C/6	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	92563604222	8710619363244	8710619363244	36324401	ECOCL ATT 42W E27 230V NR63 1CT/10 SRP	Attralux	-	-	-	no replacement in Halogen		ATR LED 60W R63 WW 36D 18C/6	NEU	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925718944203	8718291709611	8718291709611	77096101	ECOCLASSIC 42W E27 E80 55D 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 60W E14 WW 230V R80 36D ND/4	R80 Bauform	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925645244209	8710619363220	8710619363220	36322001	ECOCL ATT 18W E14 230V NR50 1CT/10 SRP	Attralux	-	-	-	no replacement in Halogen		LED 25W E14 WW 230V R50 36D ND/4	A-Markenportfolio Philips	
	Halogen Retrofit	Retrofit ES Reflecto	EcoClassic ES Reflect	925645344212	8710619364197	8710619364197	36419701	ECOCL ATT 28W E27 230V NR63 1CT/10 SRP	Attralux	-	-	-	no replacement in Halogen		LED 40W E27 WW 230V R63 36D DIM/4	A-Markenportfolio Philips	
	Halogen Retrofit	Retrofit ES Deco	EcoClassic ES Deco	925719044204	8718291757214	8718291757214	75721401	ECOCLASSIC 28W E14 R39 45D 1CT/10 SRP	Philips	-	-	-	no replacement in Halogen		LED 40W E14 WW 230V R39 36D ND/4		
		Halogen Non Retrofit	LV Reflectors	Dichroic MR Basic	924049517112	8711500413215	8711500413215	41321525	HAL-DICH 2Y 20W GU5.3 12V 36D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 20W GU5.3 12V 36D 28C/10	Upgrade 2000h to 4000h	LED 20W GU5.3 WW 12V MR16 36D ND/4	
		Halogen Non Retrofit	LV Reflectors	Dichroic MR Basic	924049617106	8711500413284	8711500413284	41328425	HAL-DICH 2Y 35W GU5.3 12V 36D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 35W GU5.3 12V 36D 28C/10	Upgrade 2000h to 4000h	LED 35W GU5.3 WW 12V MR16 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	LV Reflectors	Dichroic MR Basic	924049717110	8711500413222	8711500413222	41322225	HAL-DICH 2Y 50W GU5.3 12V 36D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 50W GU5.3 12V 36D 28C/10	Upgrade 2000h to 4000h	LED 50W GU5.3 WW 12V MR16 36D Silver Dim/4	
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	924884017104	8711500649898	8711500649898	64989825	HAL-DICH 2Y 20W GU4 12V 30D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 20W GU4 12V 30D 28C/10	Upgrade 2000h to 4000h	LED 20W GU4 WW 12V MR11 36D ND/4	NEU	
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	926000850030	8718291742098	8718291742098	74209800	HAL-DICH 2Y 20W GU5.3 12V 36D 38C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 20W GU5.3 12V 36D 28C/10	Upgrade 2000h to 4000h	LED 20W GU5.3 WW 12V MR16 36D ND/4		
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	924049617192	8718291742135	8718291742135	74213500	HAL-DICH 2Y 35W GU5.3 12V 36D 38C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 35W GU5.3 12V 36D 28C/10	Upgrade 2000h to 4000h	LED 35W GU5.3 WW 12V MR16 36D ND/4	auch in dimmbar verfügbar	
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	926000850025	8710619364517	8710619364517	36451700	HAL-DICH 2Y ATT 20W GU5.3 12V 36D 38C/10	Attralux	tbd	tbd	tbd	NEW Hal-Dich 4y Att 20W GU5.3 12V 36D 38C/10	Upgrade 2000h to 4000h	ATR LED 20W GU5.3 WW 36D 18C/6		
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	924049617193	8710619364531	8710619364531	36453100	HAL-DICH 2Y ATT 35W GU5.3 12V 36D 38C/10	Attralux	tbd	tbd	tbd	NEW Hal-Dich 4y Att 35W GU5.3 12V 36D 38C/10	Upgrade 2000h to 4000h	ATR LED 35W GU5.3 WW 36D 18C/6		
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	924884117104	8711500650443	8711500650443	65044325	HAL-DICH 2Y 35W GU4 12V 30D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 35W GU4 12V 30D 28C/10	Upgrade 2000h to 4000h	keine LED Alternative in Planung	20W GU4 als LED Alternative	
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	926000850031	8718291742111	8718291742111	74211100	HAL-DICH 2Y 50W GU5.3 12V 36D 38C/10	Philips	tbd	tbd	tbd	no replacement in Halogen		LED 50W GU5.3 WW 12V MR16 36D Silver Dim/4		
Halogen Non Retrofit		LV Reflectors	Dichroic MR Basic	924049517116	8727900252422	8727900252422	25242260	HAL-DICH 2Y 20W GU5.3 12V 36D 1CT/10X5F	Philips	tbd	tbd	tbd	NEW Accent 20W 4000H GU5.3 12V 36D 1CT/10X5F	Upgrade 2000h to 4000h	LED 20W GU5.3 WW 12V MR16 36D ND/4		
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924713544287	8727900252538	8727900252538	25253825	HAL-TWIST 2Y 50W GU10 230V CL 28C/10	Philips	-	-	-	no replacement in Halogen		LED 50W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924713444246	8727900252545	8727900252545	25254525	HAL-TWIST 2Y 35W GU10 230V CL 28C/10	Philips	-	-	-	no replacement in Halogen		LED 35W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	926000850024	8710619364494	8710619364494	36449400	HAL-TWIST 2Y ATT 50W GU10 40D 38C/10	Attralux	-	-	-	no replacement in Halogen		ATR LED 50W GU10 WW 230V 36D ND/4	
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	926000850029	8718291742074	8718291742074	74207400	HAL-TWIST 2Y 50W GU10 230V 40D 38C/10	Philips	-	-	-	no replacement in Halogen		LED 50W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924713442096	8710619364470	8710619364470	36447000	HAL-TWIST 2Y ATT 35W GU10 40D 38C/10	Attralux	-	-	-	no replacement in Halogen		ATR LED 35W GU10 WW 230V 36D ND/4	
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924713442096	8718291742012	8718291742012	74201200	HAL-TWIST 2Y 35W GU10 230V 40D 38C/10	Philips	-	-	-	no replacement in Halogen		LED 35W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	926000305104	8727900252545	8727900252545	25254500	HAL-TWIST 2Y 35W GU10 230V 40D 28C/8 SRP	Philips	-	-	-	no replacement in Halogen		LED 35W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	925640544212	8710619364739	8710619364739	36473900	HAL-TWIST 2Y ATT 25W GU10 25D 38C/10	Attralux	-	-	-	no replacement in Halogen		LED 25W GU10 WW 230V 36D ND/4	NEU; A-Markenportfolio Philips
		Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924881544208	8727900252613	8727900252613	25261325	HAL-TWIST 2Y 25W GU10 230V 25D 28C/10	Philips	-	-	-	no replacement in Halogen		LED 25W GU10 WW 230V 36D ND/4	NEU
	Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924881644203	8711500651471	8711500651471	65147125	HAL-TWIST 2Y 75W GU10 230V 25D CL 18L/10	Philips	-	-	-	no replacement in Halogen		keine LED Alternative in Planung		
	Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924713444245	8711500652362	8711500652362	65236265	HAL-TWIST 2Y 35W GU10 230V 40D 1CT/50	Philips	-	-	-	no replacement in Halogen		LED 35W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar	
	Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924713544235	8711500412584	8711500412584	41258460	HAL-TWIST 2Y 50W GU10 230V 40D 1CT/10X5F	Philips	-	-	-	no replacement in Halogen		LED 50W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar	
	Halogen Non Retrofit	MV Twist Reflectors	Twistline GU10 Basic	924891644203	8711500652925	8711500652925	65292525	HAL-TWIST 2Y 50W GU10 230V 25D 18C/10	Philips	-	-	-	no replacement in Halogen		LED 50W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar	
		Halogen Non Retrofit	LV ES Reflectors	EcoHalo Dichroic MR	925642517101	8727900250886	8727900250886	25088600	ECOHALO 25W GU5.3 12V MR16 18C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 35W GU5.3 12V 30D 28C/10	Upgrade 2000h to 4000h	LED 35W GU5.3 WW 12V MR16 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	LV ES Reflectors	EcoHalo Dichroic MR	925635717101	8727900250893	8727900250893	25089325	ECOHALO 35W GU5.3 12V MR16 18C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 50W GU5.3 12V 30D 28C/10	Upgrade 2000h to 4000h	LED 50W GU5.3 WW 12V MR16 36D Silver Dim/4	
		Halogen Non Retrofit	LV ES Reflectors	EcoHalo Dichroic MR	925644817101	8727900228885	8727900228885	22888500	ECOHALO 14W GU5.3 12V MR16 36D 18C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 20W GU5.3 12V 36D 28C/10	Upgrade 2000h to 4000h	LED 20W GU5.3 WW 12V MR16 36D ND/4	
		Halogen Non Retrofit	LV ES Reflectors	EcoHalo Dichroic MR	925644917101	8727900823608	8727900823608	82360800	ECOHALO 14W GU4 12V MR11 30D 18C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 20W GU4 12V 30D 28C/10	Upgrade 2000h to 4000h	LED 20W GU4 WW 12V MR11 36D ND/4	NEU
		Halogen Non Retrofit	LV ES Reflectors	EcoHalo Dichroic MR	925642517107	8718291204060	8718291204060	20406000	ECOHALO 25W GU5.3 12V MR16 36D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 35W GU5.3 12V 30D 28C/10	Upgrade 2000h to 4000h	LED 35W GU5.3 WW 12V MR16 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	LV ES Reflectors	EcoHalo Dichroic MR	925645017101	8727900823622	8727900823622	82362200	ECOHALO 25W GU5.3 12V MR11 30D 18C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 35W GU4 12V 30D 28C/10	Upgrade 2000h to 4000h	keine LED Alternative in Planung	20W GU4 als LED Alternative
		Halogen Non Retrofit	LV ES Reflectors	EcoHalo Dichroic MR	925635717112	8718291204046	8718291204046	20404600	ECOHALO 35W GU5.3 12V MR16 36D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 50W GU5.3 12V 30D 28C/10	Upgrade 2000h to 4000h	LED 50W GU5.3 WW 12V MR16 36D Silver Dim/4	
Halogen Non Retrofit		LV ES Reflectors	EcoHalo Dichroic MR	925644817110	8718291204084	8718291204084	20408400	ECOHALO 14W GU5.3 12V MR16 36D 28C/10	Philips	tbd	tbd	tbd	NEW Hal-Dich 4y 20W GU5.3 12V 36D 28C/10	Upgrade 2000h to 4000h	LED 20W GU5.3 WW 12V MR16 36D ND/4		
		Halogen Non Retrofit	MV ES Twist Reflecto	EcoHalo Core Twistli	925641044202	8727900252958	8727900252958	25295825	ECOHALO TW 35W GU10 230V 40D 18C/10	Philips	-	-	-	no replacement in Halogen		LED 50W GU10 WW 230V 36D ND/4	auch in dimmbar verfügbar
		Halogen Non Retrofit	MV ES Twist Reflecto	EcoHalo Core Twistli	925641044216	8718291204121	8718291204121										