

LED Inspection lamps

Ideal for brief inspection

LED Work lamps

Ideal for maintenance and inspection work

120
lumens



Penlight Professional



- Shock resistance IK07
- Water resistance IP54
- Grease and solvent resistant


- Battery
- Clip
- Ultra-slim

★★★★☆
Overall performance

120
lumens



Penlight Premium



- Shock resistance IK07
- Water resistance IP54
- Grease and solvent resistant

- Rechargeable
- Clip, magnet
- Ultra-slim

★★★★☆
Overall performance

200
lumens



RCH20



- Shock resistance IK07
- Water resistance IP65
- Grease and solvent resistant

- Rechargeable
- Hook, magnet
- Compact

★★★★☆
Overall performance

220
lumens



RCH30



- Shock resistance IK09
- Water resistance IP66
- Grease and solvent resistant

- Rechargeable
- Hook, magnet
- Compact

★★★★☆
Overall performance

300
lumens



CBL20



- Shock resistance IK07
- Water resistance IP54
- Grease and solvent resistant


- 100-240V cable
- Hook
- Slim

★★★★☆
Overall performance

330
lumens



CBL30



- Shock resistance IK07
- Water resistance IP54
- Grease and solvent resistant

- 100-240V cable
- Hook, magnet
- Ultra-slim

★★★★☆
Overall performance

600
lumens



MDLS
Multidirectional lighting system



- Shock resistance IK07
- Water resistance IP54
- Grease and solvent resistant

- Rechargeable
- Clamp, magnet
- 3 modules

★★★★★
Overall performance