


PHILIPS

Cinema lamps



Philips Digital Xenon Lamp XDC 6500BI for IMAX GEN III (Barco) Projector

Philips has released a new Cinema Xenon lamp model specifically designed for the IMAX Gen III (Barco) projection system. The XDC 6500BI has a rated maximum power of 6.5 kW and a broad operating range to accommodate a wide range of screen sizes and formats. In addition, this lamp features exceptional arc stability, long life and robust construction. The XDC 6500BI further extends Philips broad portfolio of digital cinema xenon lamps.

But behind every Philips Cinema Xenon lamp there is much more than just high quality. Our global network of cinema lighting specialists offers you personal support whenever you need it. From Total Cost of Ownership checks and online comparisons to training and installation advice.

Product data

Features


Wide operating power range
High arc stability
Robust construction

Benefits

Stable operation at all screen sizes
Low flicker
Long life

Technical specifications

Power (W)	6500
Current (A)	170
Power Range (W)	3400 - 6500
Cooling (min. Air flow ft./s)	7
Burning position	± 15 °
Average Lifetime (h)	500
Ordering code	9284 186 06301
A Length distance (mm)	170.5
B Length max (mm)	391
C Length max (mm)	433
D Diameter (mm)	70
E Lead length	152
Anode / Cathode Base Dia	30/30
Anode pin diameter	9.4
Cathode pin dia or thread type	7.9
Arc/gap (mm)	7.5



Contact us

Your local representative is happy to provide you with more information or simply visit www.philips.com/cinematlamps

