

**PHILIPS**

CorePro LEDtube

600 & 1200 mm



Made  
from  
glass

# The most affordable switch

CorePro LEDtubes offer even better value. Thanks to the new glass housing they're even more affordable. Plus we've improved the energy consumption from 80 to 100 lm/W to make them even more efficient. A simple, retrofit replacement, the 600mm and 1200mm CorePro LEDtubes offer low energy consumption with instant savings. Perfect for basic applications that demand an affordable solution.

**NEW!**



240°  
beam angle

- ✓ Uniform light spread for car parks, storage rooms, warehouses
- ✗ Not for high lux applications like offices or industry

# CorePro LEDtube 600 & 1200 mm



Product	System Wattage	Color temperature	Lumen output	Operation	CRI	12NC	EOC
	W	K	lm				
600mm	8	4000	800	EM & Mains	80	929001173202	871869649277200
600mm	8	6500	800	EM & Mains	80	929001173302	871896649279600
1200mm	16	6500	1600	EM & Mains	80	929001173002	871869649281900
1200mm	16	4000	1600	EM & Mains	80	929001173102	871869649283300

