

Projector Manufacturer	Projector Model	Philips Lamp Models	Christie/Ushio	Osram
Sony	SRX-R220/R320	XDC 4200S XDC 4200SL XDC 3000S XDC 2000S	DXL-40SRX DXL-40SRX/LL DXL-30SRX DXL-20SRX	XBO 4200 W/HPS XBO 4200 W/HPS LL XBO 3000 W/HPS XBO 2000 W/HPS
NEC	NC2500S/3200S/3240S	XDC 7000N XDC 6000NL LongPlay XDC 6000N XDC 4500NL LongPlay XDC 4500N	DXL-70SN DXL-60SN/L DXL-60SN DXL-45SN/L DXL-45SN	- XBO 6000 W/HPN L XBO 6000 W/HPN XBO 4500 W/HPN L XBO 4500 W/HPN
	NC2000C/1600C	XDC 4000NL LongPlay XDC 4000N XDC 4001N XDC 4002N XDC 3000NL LongPlay	DXL-40SN/L DXL-40SN DXL-40SCN DXL-40SN2 DXL-30SN/L	- XBO 4000 W/HPN - XBO 4000 W/HPN L XBO 3000 W/HPN
	NC2000C/NC1600C/NC1200C	XDC 2000N	DXL-20SN3	XBO 2000 W/HPN
Barco	DP4K-32B/DP2K-32B DP-90/100/3000	XDC 6500BL LongPlay XDC 6500B XDC 6000BL LongPlay XDC 6000B XDC 4500BL LongPlay XDC 4500B XDC 3001B	- DXL-65BA2 DXL-60BA2/L DXL-60BA DXL-45BA/L DXL-45BA DXL-30BA/L	- XBO 6500 W/DHP XBO 6000 W/DHP L XBO 6000 W/DHP XBO 4500 W/DHP L XBO 4500 W/DHP XBO 3000 W/DHS
	DP2K-20C/23B/DP4K-23B DP-1500/2000	XDC 4000BL LongPlay XDC 4000B	DXL-40BAF/L DXL-40BAF	XBO 4000 W/DHP L XBO 4000 W/DHP
	DP2K-15C/19B/20C/23B/ DP4K-23B/DP-1500/2000	XDC 3000BL LongPlay XDC 3000B	DXL-30BAF/L DXL-30BAF	XBO 3000 W/DHP L XBO 3000 W/DHP
	DP2K-10S/12C/15C/19B/ 20C/23B/DP4K-23B/ DP-1500/2000	XDC 2200B XDC 2000BL LongPlay XDC 2000B	DXL-22BAF/L DXL-20BAF/L DXL-20BAF	XBO 2200 W/DHP XBO 2000 W/DHP L XBO 2000 W/DHP
	DP2K-8S/10S/12C/15C/ 19B/20C/23B/DP4K-23B/ DP-1200/1500/2000	XDC 1200B	DXL-12BAF	XBO 1200 W/DHP
Christie	CP2230/4230 CP2000-XB	XDC 6000CL LongPlay XDC 6000C	CDXL-60SP CDXL-60	XBO 6000 W/DTP L XBO 6000 W/DTP
	CP2230/4230 CP2000-SB	XDC 4500CL LongPlay XDC 4500C	CDXL-45SP CDXL-45	XBO 4500 W/DTP L XBO 4500 W/DTP
	CP2220/4220/CP2000-ZX	XDC 3001C	CDXL-30SD	XBO 3000 W/DTS
	CP2220/2230/4220/4230 CP2000-SB/XB/ZX	XDC 3000CL LongPlay XDC 3000C XDC 2000CL LongPlay XDC 2000C	CDXL-30SP CDXL-30 CDXL-20SP CDXL-20	- XBO 3000 W/DTP XBO 2000 W/DTP L XBO 2000 W/DTP
	CP2210/2215/CP2000-M	XDC 2001C XDC 1800C	CDXL-20SD CDXL-18SD	XBO 2000 W/DTS XBO 1800 W/DTS
	CP2208/2210/2215 Solaria One/One+	XDC 1600C XDC 1400C	CDXL-16M CDXL-14M	- -
IMAX	Gen III (Barco)	XDC 6500BI	DXL-65BA2	-

The right Philips Digital Cinema Xenon lamp for each projector model

Philips lamp models Barco projector models

Philips lamp models	DP2K-8S	DP2K-10SX	DP2K-12C	DP2K-15C	DP2K-19B	DP2K-20C	DP2K-23B	DP4K-23B	DP2K-32B	DP4K-32B	DP-90	DP-100	DP-1200	DP-1500	DP-2000	DP-3000
XDC 1200 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 2000 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 2000BL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 2200 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 3000 BL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 3000 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 4000 BL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 4000 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 3001 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 4500BL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 4500 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 6000 BL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 6000 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 6500 B	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 6500 BL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓

Philips lamp models NEC projector models

Philips lamp models	NC1200C	NC1600C	NC2000C	NC2500S	NC3200S	NC3240S
XDC 2000N	✓	✓	✓	✓	✓	✓
XDC 3000 NL	✓	✓	✓	✓	✓	✓
XDC 4000 NL	✓	✓	✓	✓	✓	✓
XDC 4000 N	✓	✓	✓	✓	✓	✓
XDC 4001 N	✓	✓	✓	✓	✓	✓
XDC 4002 N	✓	✓	✓	✓	✓	✓
XDC 4500 NL	✓	✓	✓	✓	✓	✓
XDC 4500 N	✓	✓	✓	✓	✓	✓
XDC 6000 NL	✓	✓	✓	✓	✓	✓
XDC 6000 N	✓	✓	✓	✓	✓	✓
XDC 7000 N	✓	✓	✓	✓	✓	✓

Philips lamp models Sony projector models

Philips lamp models	SRX-R220	SRX-R320
XDC 2000 S	✓	✓
XDC 3000 S	✓	✓
XDC 4200 SL	✓	✓
XDC 4200 S	✓	✓

Philips lamp models IMAX projector models

Philips lamp models	Gen III
XDC 6500 BI	✓

✓ This lamp fits in this projector

Date of release: April 2017

Philips lamp models Christie projector models

Philips lamp models	Solaria One/One+	CP2208	CP2210	CP2215	CP2220	CP2230	CP4220	CP4230	CP2000-M	CP2000-SB	CP2000-XB	CP2000-ZX
XDC 1400 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 1600 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 1800 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 2000 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 2000 CL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 2001 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 3000 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 3000 CL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 3001 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 4500 CL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 4500 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 6000 C	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
XDC 6000 CL	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓

PHILIPS