


LUMIWARE



LED

LIGHT ON ENERGY, LOW ON PRICE.

When you need a lighting solution that high on energy savings and low on maintenance, look no further than the LUMIWARE range of lamps and tubes.



GREAT QUALITY LIGHTING DOESN'T
HAVE TO COME WITH A PREMIUM
PRICE TAG. HERE'S WHY.

4 BULBS

6 CANDLES

& LUSTRES

8 SPOTS

10 TUBES

Today's LED technology is so advanced, it's guaranteed to offer excellent performance and efficiency, which is why we've used it throughout our LUMIWARE range. It means your customers can enjoy great quality lighting that's light on energy - and low on price.

Designed for performance, the LUMIWARE range promises high light quality with a reliable lifetime of up to 25,000 hours. From LED tubes to dimmable spots, bulbs, candles and lustres, the range offers a great choice of designs, color temperatures and beam angles. Add to that up to 85% in energy savings, and you can exceed your customers' expectations, without going over budget.

"I know good, solid quality when I see it. LUMIWARE is a brand that I can really buy into for tenders that need high volumes of lighting for an affordable price."
Mick Taylor, Installer



A CLASSIC DESIGN FOR INSTANT ENERGY SAVINGS.

Retrofit, LED filament bulbs light relaxing spaces that can be dimmed to create a cozier ambience that saves even more on energy.



40W E27 835 A60 CL D 1CT/6
40W ► **4.5W** 470lm
2700K Dimmable
220-240V . 60x105mm . CRI80



40W E27 835 A60 FR D 1CT/6
40W ► **4.5W** 470lm
2700K Dimmable
220-240V . 60x105mm . CRI80



60W E27 835 A60 CL D 1CT/6
60W ► **7W** 806lm
2700K Dimmable
220-240V . 60x105mm . CRI80



60W E27 835 A60 FR D 1CT/6
60W ► **7W** 806lm
2700K Dimmable
220-240V . 60x105mm . CRI80



75W E27 835 A60 CL D 1CT/6
75W ► **8.5W** 1055lm
2700K Dimmable
220-240V . 60x105mm . CRI80



75W E27 835 A60 FR D 1CT/6
75W ► **8.5W** 1055lm
2700K Dimmable
220-240V . 60x105mm . CRI80

4 BULBS



15,000h



EEI label



CRI



20,000x



220-240V



dimmmable



6 pack

Product type	Replaced wattage	Lamp wattage claim	Energy consumption	Lumen	Input current	Frequency	Dimension W x H	12NC	EOC/6NC
LUMIWARE LED	W	W		lm	mA	Hz	mm		
40W E27 835 A60 CL D 1CT/6	40	4.5	5	470	26	50/60	60x105	929001993462	872790096636700
40W E27 835 A60 FR D 1CT/6	40	4.5	5	470	26	50/60	60x105	929001993562	872790096638100
60W E27 835 A60 CL D 1CT/6	60	7	7	806	43	50/60	60x105	929001993662	872790096640400
60W E27 835 A60 FR D 1CT/6	60	7	7	806	43	50/60	60x105	929001993762	872790096642800
75W E27 835 A60 CL D 1CT/6	75	8.5	9	1055	47	50/60	60x105	929001993862	872790096644200
75W E27 835 A60 FR D 1CT/6	75	8.5	9	1055	47	50/60	60x105	929001993962	872790096646600



SAVE ENERGY WITHOUT COMPROMISING STYLE.

LED filament candles and lustres provide the familiar shape and warm light that customers love, for decorative fixtures that save energy without compromising style.



25W E14 835 B35 FR D 1CT10
25w ► **2.5w** 250lm
2700K Dimmable
220-240V . 35x97mm . CRI80



40W E14 835 B35 FR D 1CT10
40w ► **4.5w** 470lm
2700K Dimmable
220-240V . 35x97mm . CRI80



25W E14 835 P45 FR D 1CT10
25w ► **2.5w** 250lm
2700K Dimmable
220-240V . 45x81mm . CRI80



25W E27 835 P45 FR D 1CT10
25w ► **2.5w** 250lm
2700K Dimmable
220-240V . 45x79mm . CRI80



40W E14 835 P45 FR D 1CT10
40w ► **4.5w** 470lm
2700K Dimmable
220-240V . 45x81mm . CRI80



40W E27 835 P45 FR D 1CT10
40w ► **4.5w** 470lm
2700K Dimmable
220-240V . 45x79mm . CRI80

6 CANDLES & LUSTRES



15,000h



EEI label



CRI



20,000x



220-240V



dimmable



6 pack

Product type	Replaced wattage	Lamp wattage claim	Energy consumption	Lumen	Input current	Frequency	Dimension W x H	12NC	EOC/6NC
LUMIWARE LED	W	W		lm	mA	Hz	mm		
25W E14 WW B35 FR D 1CT10	25	2.5	3	250	15	50/60	35x97	929001994062	872790096648000
40W E14 WW B35 FR D 1CT10	40	4.5	5	470	26	50/60	35x97	929001994162	872790096650300
25W E14 WW P45 FR D 1CT10	25	2.5	3	250	15	50/60	45x81	929001994262	872790096652700
25W E27 WW P45 FR D 1CT10	25	2.5	3	250	15	50/60	45x79	929001994362	872790096654100
40W E14 WW P45 FR D 1CT10	40	4.5	5	470	26	50/60	45x81	929001994462	872790096656500
40W E27 WW P45 FR D 1CT10	40	4.5	5	470	26	50/60	45x79	929001994562	872790096658900



PUT THE **ACCENT ON VALUE.**

LED spots are a stylish way to create energy-efficient accents and highlights in a wide range of applications.



35W GU10 35W 827 36D D 1CT/10
35w ▶ **3.6w** 230lm
2700K Dimmable
220-240V . 50x54mm . CRI80



50W GU10 50W 827 36D D 1CT/10
50w ▶ **5w** 350lm
2700K Dimmable
220-240V . 50x54mm . CRI80

8 SPOTS



Product type	Lamp type	Replaced wattage	Lamp wattage claim	Energy consumption	Lumen	MBCP	Input current	Frequency	Dimension W x H	12NC	EOC/6NC
LUMIWARE LED		W	W		lm	cd	mA	Hz	mm		
GU10 35W 827 36D D 1CT/10	PAR16	35	3.6	4	230	500	19	50/60	50x54	929001994662	872790096632900
GU10 50W 827 36D D 1CT/10	PAR16	50	5	5	350	650	25	50/60	50x54	929001994762	872790096634300



A BRIGHT WAY TO MAKE SAVINGS.

Our LEDtubes come in a range of lengths for brighter, safer and more efficient lighting in offices, warehouses and indoor parking lots.



36W 1200mm UO 16W 840 T8
36W ▶ **16W** 2500lm
4000K Non dimmable
220-240V . 28x1213.6mm . CRI83




58W 1500mm UO 24W 840 T8
58W ▶ **24W** 3700lm
4000K Non dimmable
220-240V . 28x1514.2mm . CRI83

10TUBES



Product type	Lamp type	Replaced wattage	Lamp wattage claim	Energy consumption	Lumen	Input current	Frequency	Dimension W x H	12NC	EOC/6NC
LUMIWARE LEDtube		W	W		lm	mA	Hz	mm		
1200mm UO 16W 840 T8	Tube EM/Mains	36	16	16	2500	68-75	50/60	28x1213.6	929001978202	872790096660200
1500mm UO 24W 840 T8	Tube EM/Mains	58	24	24	3700	103-112	50/60	28x1514.2	929001978502	872790096662600



LUMIWARE