

# LUMIWARE BULBS

## A CLASSIC DESIGN FOR INSTANT ENERGY SAVINGS.

Retrofit, LED filament bulbs light relaxing spaces that can be dimmed to create a cozier ambience that saves even more on energy.

80  
CRI

15,000h

A<sup>++</sup>  
EEI label

20,000x

dimmable

6 pack

Product type	Cap	Type	Lamp Wattage	Replaced Wattage	Lumen	Energy Consumption	Input current	Bulb finish	Voltage	Frequency	12NC	EOC/6NC
LUMIWARE LED			W	W	Lm		mA		Vac	Hz	92900199	8727900966
40W E27 835 A60 CL D 1CT/6	E27	A60	4.5	40	470	5	26	Clear	220 - 240	50/60	3462	36700
40W E27 835 A60 FR D 1CT/6	E27	A60	4.5	40	470	5	26	Frosted	220 - 240	50/60	3562	38100
60W E27 835 A60 CL D 1CT/6	E27	A60	7	60	806	7	43	Clear	220 - 240	50/60	3662	40400
60W E27 835 A60 FR D 1CT/6	E27	A60	7	60	806	7	43	Frosted	220 - 240	50/60	3762	42800
75W E27 835 A60 CL D 1CT/6	E27	A60	8.5	75	1055	9	47	Clear	220 - 240	50/60	3862	44200
75W E27 835 A60 FR D 1CT/6	E27	A60	8.5	75	1055	9	47	Frosted	220 - 240	50/60	3962	46600

CCT	2700K	Power factor	0.7
Country of origin	China	Starting time	0.4
Energy saving product	Yes	Warm up time to 60% light	0.4
Colour consistency	6SDCM	Suitable for accent lighting	No
Lamp lumen maintenance factor at end of nominal lifetime (=70%)	70%	Degree of protection (IP)	IP20

# LUMIWARE BULBS

A CLASSIC DESIGN FOR INSTANT ENERGY SAVINGS.

