

LUMIWARE TUBES

A BRIGHTER WAY TO MAKE SAVINGS.

Our LEDtubes come in a range of lengths for brighter, safer and more efficient lighting in offices, warehouses and indoor parking lots.

83
CRI



50,000h

A⁺⁺
EEI label

200,000x

non dimmable

10 pack

Product type	Cap	Type	Lamp Wattage	Replaced Wattage	Lumen	Energy Consumption	Input current	Voltage	Frequency	12NC	EOC/6NC
LUMIWARE LEDtube			W	W	Lm		mA	Vac	Hz	9290019	8727900966
1200mm UO 16W 840 T8	G13	Tube EM/Mains	16	36	2500	16	68 - 75	220 - 240	50/60	78202	60200
1500mm UO 24W 840 T8	G13	Tube EM/Mains	24	58	3700	24	103 - 112	220 - 240	50/60	78502	62600

CCT	4000K
Country of origin	China
Energy saving product	Yes
Colour consistency	6SDCM
Lamp lumen maintenance factor at end of nominal lifetime (=70%)	70%
Power factor	>0.9
Starting time	<0.5
Warm up time to 60% light	<0.5
Degree of protection (IP)	IP20

