## **Specifications**

Due to continuous improvements and innovations, specifications may change without notice.

#### Luminous ceiling prefab

General Characteristics		Default	panel dimensions an	d weights (w	ithout packaging)
Light level (100%)			parlet dimensions an	3000 K	Tunable white
Europe	3,200 lm/m <sup>2</sup> (for 4000K version)			or 4000 K	2700 to 6500 K
United States	Typical 300 lm/ft <sup>2</sup> (300 FC)	Metric	1,200 × 1,200 mm	17 kg	17 kg
CCT LED Color			1,200 × 2,400 mm 1,200 × 3,000 mm	28 kg 34 kg	30 kg 36 kg
single color tunable white	3000 K, 4000 K 2700 to 6500 K		1,500 × 3,000 mm 1,500 × 1,500 mm 1,800 × 2,700 mm	24 kg 42 kg	26 kg 45 kg
Color rendering index	> 88 R9 > 35	US	4.0 ft × 4.0 ft 4.0 ft × 8.0 ft 4.0 ft × 10.0 ft 5.0 ft × 10.0 ft 6.0 ft × 9.0 ft	37 lb 64 lb	40 lb 71 lb
Maintenance factor L70	50,000 hours			77 lb	82 lb
Dimming	Between 10 and 100%			93 lb 95 lb	99 lb 101 lb
Acoustic properties	$a_w 0.6$ class C EN 11654 $a_w 0.8$ class in speech area			5515	
Noise Reduction Coefficient	NRC 0.6 ASTM C423 – 99 NRC 0.85 in speech area	Control interface Europe		DALI (Digital Addressable	
Product characteristics				Lighting Int	
Ceiling panel		United States		DALI or 0-1	0 V
Luminaire type	Non-user replaceable light source		ltage / power		
		Europe (CE version)		220 to 240 VAC / 50 to 60 Hz	
Thickness	140 mm total height 120 mm frame height Thickness excludes	United S (UL vers	States / Canada ion)	120 to 277 \	/AC / 50 to 60 Hz
		Temper	ature characteristics		
	mounting and hoisting parts	Ambient temperature		5 to 35 °C (41 to 95 °F)	
Front material	Polyester	Relative humidity		< 95% non-condensing	
Frame edge color	Matte black (standard) Matte white (optional)	Approb	ation / compliance		
E-box		Fire rati	ng		
Dimensions	205 mm × 540 mm (8.1 in × 21.3 in)	Europe		Fabric (EN 13501) B-s1, d0 Panel (EN 13501) B-s2, d0	
Thickness	30 mm (1.2 in)	United States UL723 (ASTM E84)		M E84)	
Contains	Drivers and terminal block	Emerge	ncy Lighting		
Use	Only for use with OneSpace luminous ceiling prefab		centrally supplied ncy luminaire	IEC60598-	2-22*
	panels (default mounted on	Approb	ation		
	the back of the panel)	Europe		CE	

The light engine (LED module) is an integrated component of this OneSpace prefab panel, and may not be used as a stand-alone light engine. It is only suitable for connection to a SELV driver

\* The CE version of this OneSpace prefab panel is certified as a centrally supplied emergency luminaire according to IEC60598-2-22. The OneSpace pefab panel should be supplied with a suitable DC voltage (200 to 250 Vdc) in order to change-over to emergency luminaire function. In this state, the prefab panel generates a total light output of at least 120 lm for the smallest size.

#### OneSpace prefab accessories (not included)

Accessories	12 NC order number	Pieces in one set	Required sets per panel
Mounting Kit Wire CE	9137 052 00075	4	1
Mounting Kit Wire UL	9137 052 00076	4	1
Mounting Kit Magnet (CE, UL)	9137 052 00152	2	2 TO 4*
A man and a set of the			

\* Depending on the panel size.

© 2018 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.



largeluminoussurfaces.com/onespace
December 2018

United States / Canada

UL and c-UL listed

## **PHILIPS**



Philips OneSpace luminous ceiling prefab









# **OneSpace** – your vision

You asked us to re-think the ceiling, so we did. Now it's a blank canvas awaiting your vision. Our revolutionary OneSpace luminous ceiling prefab is a modular panel that liberates you from the constraints of conventional ceiling design so you're free to pursue uncluttered minimalistic visions – and transform any interior into one cohesive space with beautiful homogeneous light.



OneSpace enhances people's perceptions of public spaces by delivering improved acoustics and a superior daylight experience.

## "The ceiling becomes the light, the light becomes the ceiling."



Superior homogeneous light OneSpace prefab integrates LED lights with textile to create a white light ceiling surface that hides the source of light completely. It delivers excellent uniform light distribution for an enhanced daylight experience, which makes it a perfect functional light for any interior. The result is a smooth and clutter-free ceiling of homogeneous light that feels as good as it looks.

### Choice of color temperatures

To make it even more versatile, OneSpace prefab is available in 3000 K and 4000 K versions, as well as a tunable white version ranging from 2700 K to 6500 K. So you can tailor the light exactly to your needs.

#### Liberating design possibilities

OneSpace prefab opens up new minimalistic design opportunities and transforms any ceiling into a serene and calm space. For design flexibility the thin, compact units are based on a modular system with a minimum dimension of 900 × 900 mm (3 × 4 ft for US) and a maximum dimension of 1,800 × 3,000 mm (6 × 10 ft). There is also the option to choose the panel's edge color.

#### Simply smarter

The ceiling-mounted panels are simple to install and easy to maintain. They also integrate perfectly with your building management system.



The thin compact units blend absolutely into a minimalist design.



E-box mounted to the back.

#### Sensory enhancing

OneSpace prefab not only makes spaces look great, it enhances your experience of them. It delivers bright, uniform glare-free light that eliminates shadows completely, so you can see more clearly and view objects in their true light. It even enhances room acoustics by reducing disturbing sound reflections.

#### Supremely safe

OneSpace prefab combines classleading features and competitive pricing to offer excellent value. It also exceeds industry safety standards for both fire and mounting. The ceiling panels have a B-s2 safety rating, and the fabric a B-s1 safety rating.



OneSpace is ideal for showcasing hero products in their true light as it delivers uniform, shadow-free illumination

Re-think your next ceiling design at: largeluminoussurfaces.com/onespace