



## CUSTOMIZE YOUR LINEAR SYSTEM indoor/outdoor

### P02

P02 è un profilo lineare in alluminio anodizzato naturale adatto per le applicazioni in interni ed esterni (usando il tubo di protezione).  
P02 is a natural anodized aluminum linear profile for indoor and outdoor applications (using the protection tube).

#### INFORMAZIONI GENERALI GENERAL INFORMATION

Dimensioni Dimensions	max 3m
Colore/finitura apparecchio Luminaire color/finish	alluminio anodizzato anodized aluminium

#### FINITURA FINISHING


**AA** Alluminio anodizzato naturale / Natural anodized aluminium

#### NASTRI LED COMPATIBILI COMPATIBLE LED STRIPS

<b>N01</b>	LED strip bianca / White LED strip
<b>N16</b>	LED strip bianca / White LED strip
<b>N15</b>	LED strip bianca / White LED strip
<b>N09</b>	LED strip bianca / White LED strip
<b>N10</b>	LED strip bianca / White LED strip
<b>N11</b>	LED strip bianca / White LED strip
<b>N18</b>	LED strip bianca / White LED strip
<b>N12</b>	LED strip bianco dinamico 12VDC / Tunable white LED strip 12VDC
<b>N06</b>	LED strip bianco dinamico 24VDC / Tunable white LED strip 24VDC
<b>N04</b>	LED strip RGB / RGB LED strip
<b>N14</b>	LED strip RGB / RGB LED strip
<b>N13</b>	LED strip RGB / RGB LED strip

#### DISEGNO TECNICO DIMENSIONAL DRAWINGS

Dimensioni (mm)  
Dimensions (mm)




#### SCHEMI COMPATIBILI COMPATIBLE SCREENS

<b>S01</b>	Schermo trasparente / transparent screen
<b>S02</b>	Schermo opale / Opal screen
<b>S03</b>	Tubo trasparente / Transparent tube (ø20mm)
<b>S04</b>	Tubo opale / opal tube (ø20mm)




#### FISSAGGIO FIXATION

**F01**  
Plafone/Ceiling



**F04**  
Parete/wall



Esempio di composizione prodotto/ Product composition example

P02-AA-N02-S04-F01 Profilo in alluminio con incluso nastro LED 24V, tubo in policarbonato opale, fissaggio a plafone/ Profile with 24V LED strip, opal polycarbonate tube, ceiling fixation