

Sigla Marchio	Codice Prodotto Produttore	Codice EAN	Descrizione prodotto	Quantità cartone	Quantità multipla ordinazione
PHL	XXL4033	8711500261373	TL-X XL 40W/33-640 SLV/25	25	25
PHL	XXL2033	8711500261359	TL-X XL 20W/33-640 SLV/25	25	25
PHL	TUVG64T5	8711500640796	TUV 64T5 HE SP UNP/32	32	32
PHL	TUVG36T5	8711500640369	TUV 36T5 SP NO/32	32	32
PHL	TUV9	8711500618245	TUV PL-S 9W/2P 1CT/6X10BOX	60	60
PHL	TUV8	8711500623683	TUV 8W FAM/10X25BOX	250	25
PHL	TUV75	8711500618511	TUV 75W HO 1SL/6	6	6
PHL	TUV6WM	8711500623645	TUV 6W FAM/10X25BOX	250	25
PHL	TUV55	8711500618665	TUV 55W HO 1SL/6	6	6
PHL	TUV4	8711500638724	TUV 4W FAM/10X25BOX	250	25
PHL	TUV36	8711500618542	TUV 36W SLV/6	6	6
PHL	TUV30	8711500726209	TUV 30W 1SL/25	25	25
PHL	TUV25	8711500641618	TUV 25W 1SL/25	25	25
PHL	TUV16	8711500638694	TUV 16W FAM/10X25BOX	250	25
PHL	TUV15	8711500726179	TUV 15W SLV/25	25	25
PHL	TUV130XPT	8711500209436	TUV 130W XPT SE UNP/20	20	20
PHL	TORN8WWE14	8718291217015	EconomyTwister 8W WW E14 220-240V 1PF/6	6	6
PHL	TORN8WW	8718291216995	EconomyTwister 8W WW E27 220-240V 1PF/6	6	6
PHL	TORN8CDLE14	8710163406138	EconomyTwister 8W CDL E14 220-240V 1PF/6	6	6
PHL	TORN8CDL	8710163406121	EconomyTwister 8W CDL E27 220-240V 1PF/6	6	6
PHL	TORN23WW	8718291217176	EconomyTwister 23W WW E27 220-240V 1PF/6	6	6
PHL	TORN23CDL	8718291217152	EconomyTwister 23W CDL E27 1PF/6	6	6
PHL	TORN20WW	8718291680086	EconomyTwister 20W WW E27 220-240V 1PF/6	6	6
PHL	TORN20CDL	8718291679394	EconomyTwister 20W CDL E27 1PF/6	6	6
PHL	TORN15WW	8718291217091	EconomyTwister 15W WW E27 220-240V 1PF/6	6	6
PHL	TORN15CDL	8718291217077	EconomyTwister 15W CDL E27 1PF/6	6	6
PHL	TORN12WW	8718291217039	EconomyTwister 12W WW E27 220-240V 1PF/6	6	6
PHL	TORN12CDLE14	8710163406152	EconomyTwister 12W CDL E14 1PF/6	6	6
PHL	TORN12CDL	8710163406145	EconomyTwister 12W CDL E27 1PF/6	6	6
PHL	TLE25E27CDL	8711500317056	Circular ES 24W CDL E27 220-240V 1CT/6	6	6
PHL	TLE25E27	8711500315274	Circular ES 24W WW E27 220-240V 1CT/6	6	6
PHL	TLD808	8711500951045	TL 8W BLB 1FM/10X25CC	250	25
PHL	TLD608	8711500950987	TL 6W BLB 1FM/10X25CC	250	25
PHL	TLD4010	8711500260260	Actinic BL TL 40W/10 SLV/25	25	25

Signify Classified - Internal

PHL	TLD1810	8711500263254	Actinic BL TL-D 18W/10 1SL/25	25	25
PHL	TL5C6084	8711500642615	MASTER TL5 Circular 60W/840 1CT/10	10	10
PHL	TL5C6083	8711500642592	MASTER TL5 Circular 60W/830 1CT/10	10	10
PHL	TL5C5584	8711500642516	MASTER TL5 Circular 55W/840 1CT/10	10	10
PHL	TL5C5583	8711500642790	MASTER TL5 Circular 55W/830 1CT/10	10	10
PHL	TL5C4084	8711500642233	MASTER TL5 Circular 40W/840 1CT/10	10	10
PHL	TL5C4083	8711500640970	MASTER TL5 Circular 40W/830 1CT/10	10	10
PHL	TL5C2284	8711500642219	MASTER TL5 Circular 22W/840 1CT/10	10	10
PHL	TL5C2283	8711500640956	MASTER TL5 Circular 22W/830 1CT/10	10	10
PHL	TL58086	8711500710475	MASTER TL5 HO 80W/865 SLV/40	40	40
PHL	TL58084XTRA	8711500263032	MASTER TL5 HO Xtra 80W/840 SLV/20	20	20
PHL	TL58084	8711500710451	MASTER TL5 HO 80W/840 SLV/20	20	20
PHL	TL58083	8711500710406	MASTER TL5 HO 80W/830 SLV/40	40	40
PHL	TL57383HOECO	8727900825961	MASTER TL5 HO Eco 73=80W/830 UNP/40	40	40
PHL	TL55496	8711500869838	MASTER TL5 HO 90 De Luxe 54W/965 1SL20	20	20
PHL	TL55495	8711500890665	MASTER TL5 HO 90 De Luxe 54W/950 1SL20	20	20
PHL	TL55494	8711500869050	MASTER TL5 HO 90 De Luxe 54W/940 1SL20	20	20
PHL	TL55486	8711500643919	MASTER TL5 HO 54W/865 SLV/40	40	40
PHL	TL55484XTRA	8711500263520	MASTER TL5 HO Xtra 54W/840 SLV/20	20	20
PHL	TL55484	8711500643186	MASTER TL5 HO 54W/840 SLV/20	20	20
PHL	TL55483XTRA	8711500263230	MASTER TL5 HO Xtra 54W/830 SLV/20	20	20
PHL	TL55483	8711500643162	MASTER TL5 HO 54W/830 SLV/20	20	20
PHL	TL55084HOSLECO	8727900908343	MASTER TL5 HO Eco 50=54W/840 1SL/40	40	40
PHL	TL54996	8711500869722	MASTER TL5 HO 90 De Luxe 49W/965 1SL20	20	20
PHL	TL54995	8711500890627	MASTER TL5 HO 90 De Luxe 49W/950 1SL20	20	20
PHL	TL54994	8711500868978	MASTER TL5 HO 90 De Luxe 49W/940 1SL20	20	20
PHL	TL54986	8711500643896	MASTER TL5 HO 49W/865 SLV/40	40	40
PHL	TL54984XTRA	8711500262530	MASTER TL5 HO Xtra 49W/840 SLV/20	20	20
PHL	TL54984	8711500639561	MASTER TL5 HO 49W/840 SLV/20	20	20
PHL	TL54983	8711500639547	MASTER TL5 HO 49W/830 SLV/20	20	20
PHL	TL54584HOSLECO	8727900908404	MASTER TL5 HO Eco 45=49W/840 1SL/40	40	40
PHL	TL54584HOECO	8727900825954	MASTER TL5 HO Eco 45=49W/840 UNP/40	40	40
PHL	TL54583HOECO	8727900825947	MASTER TL5 HO Eco 45=49W/830 UNP/40	40	40
PHL	TL53986	8711500643872	MASTER TL5 HO 39W/865 SLV/40	40	40
PHL	TL53984	8711500639646	MASTER TL5 HO 39W/840 SLV/20	20	20
PHL	TL53983	8711500639622	MASTER TL5 HO 39W/830 SLV/40	40	40
PHL	TL53586	8711500710185	MASTER TL5 HE 35W/865 SLV/40	40	40
PHL	TL53584	8711500639523	MASTER TL5 HE 35W/840 SLV/20	20	20
PHL	TL53583	8711500639509	MASTER TL5 HE 35W/830 SLV/20	20	20
PHL	TL53582	8711500643247	MASTER TL5 HE 35W/827 SLV/40	40	40
PHL	TL53484HOSLECO	8727900918083	MASTER TL5 HO Eco 34=39W/840 1SL/40	40	40
PHL	TL53284HESLECO	8727900908268	MASTER TL5 HE Eco 32=35W/840 1SL/40	40	40
PHL	TL52886	8711500710154	MASTER TL5 HE 28W/865 SLV/40	40	40
PHL	TL52884	8711500639486	MASTER TL5 HE 28W/840 1SL/20	20	20

PHL	TL52883	8711500639462	MASTER TL5 HE 28W/830 1SL/20	20	20
PHL	TL52882	8711500643223	MASTER TL5 HE 28W/827 SLV/40	40	40
PHL	TL52584HESLECO	8727900908206	MASTER TL5 HE Eco 25=28W/840 1SL/40	40	40
PHL	TL52584HEECO	8727900825893	MASTER TL5 HE Eco 25=28W/840 UNP/40	40	40
PHL	TL52496	8711500261304	MASTER TL5 HO 90 De Luxe 24W/965 1SL20	20	20
PHL	TL52495	8711500890641	MASTER TL5 HO 90 De Luxe 24W/950 1SL20	20	20
PHL	TL52494	8711500868954	MASTER TL5 HO 90 De Luxe 24W/940 1SL20	20	20
PHL	TL52486	8711500643933	MASTER TL5 HO 24W/865 SLV/40	40	40
PHL	TL52484	8711500639608	MASTER TL5 HO 24W/840 1SL/20	20	20
PHL	TL52483	8711500639585	MASTER TL5 HO 24W/830 SLV/40	40	40
PHL	TL52186	8711500710116	MASTER TL5 HE 21W/865 SLV/40	40	40
PHL	TL52184	8711500639448	MASTER TL5 HE 21W/840 SLV/20	20	20
PHL	TL52183	8711500639424	MASTER TL5 HE 21W/830 SLV/20	20	20
PHL	TL52182	8711500643209	MASTER TL5 HE 21W/827 SLV/40	40	40
PHL	TL52083HOECO	8727900880847	MASTER TL5 HO Eco 20=24W/830 UNP/40	40	40
PHL	TL51984HESLECO	8727900918144	MASTER TL5 HE Eco 19=21W/840 1SL/40	40	40
PHL	TL51486	8711500710093	MASTER TL5 HE 14W/865 SLV/40	40	40
PHL	TL51484	8711500639400	MASTER TL5 HE 14W/840 1SL/20	20	20
PHL	TL51483	8711500639387	MASTER TL5 HE 14W/830 1SL/20	20	20
PHL	TL51482	8711500641021	MASTER TL5 HE 14W/827 SLV/40	40	40
PHL	TL51384HESLECO	8727900908060	MASTER TL5 HE Eco 13=14W/840 1SL/40	40	40
PHL	TL51384HEECO	8727900880830	MASTER TL5 HE Eco 13=14W/840 UNP/40	40	40
PHL	TL410	8711500951427	Actinic BL TL MINI 4W/10	250	25
PHL	TL408	8711500951014	TL 4W BLB 1FM/10X25CC	250	25
PHL	TL1110	8711500951458	Actinic BL TL 11W/10	250	25
PHL	T8Y32CDB1	8727900886603	TORNADO ES 32W CDL E27 1BC/6	6	6
PHL	T8Y32B1	8727900886580	Tornado T3 32W WW E27 220-240V 1BC/6	6	6
PHL	T10Y8B1	8718291117506	Tornado T2 8W WW E27 220-240V 1BC/6	6	6
PHL	T10Y23CDB1	8727900929669	Tornado T2 23W CDL E27 220-240V 1BC/6	6	6
PHL	T10Y23B1	8727900929706	Tornado T2 23W WW E27 220-240V 1BC/6	6	6
PHL	T10Y20CDB1	8727900929584	Tornado T2 20W CDL E27 220-240V 1BC/6	6	6
PHL	T10Y20B1	8727900929508	Tornado T2 20W WW E27 220-240V 1BC/6	6	6
PHL	T10Y15CDB1	8727900929423	Tornado T2 15W CDL E27 220-240V 1BC/6	6	6
PHL	T10Y15B1	8727900929461	Tornado T2 15W WW E27 220-240V 1BC/6	6	6
PHL	T10Y12E14CDB1	8718291122098	Tornado T2 12W CDL E14 220-240V 1BC/6	6	6
PHL	T10Y12CDB1	8718291117643	Tornado T2 12W CDL E27 220-240V 1BC/6	6	6
PHL	T10Y12B1	8718291117520	Tornado T2 12W WW E27 220-240V 1BC/6	6	6
PHL	SX76	8711500916402	SX 76 220-240V 50/60Hz	20	1
PHL	SX74	8711500915696	SX 74 220-240V 50/60Hz	20	1
PHL	SX73	8711500920058	SX 73 220-240V 50/60Hz	48	1
PHL	SX72	8711500915610	SX 72 220-240V 50/60Hz	20	1
PHL	SX70	8711500915498	SX 70 220-240V 50/60Hz	20	1
PHL	SX131	8711500915894	SX 131 220-240V 50/60Hz	48	1
PHL	SOXE91	8711500179807	MASTER SOX-E 91W BY22d 1SL/12	12	12

PHL	SOXE66	8711500179784	MASTER SOX-E 66W BY22d 1SL/12	12	12
PHL	SOXE36	8711500179760	MASTER SOX-E 36W BY22d 1SL/12	12	12
PHL	SOXE26	8711500179746	MASTER SOX-E 26W BY22d 1SL/12	12	12
PHL	SOXE18	8711500192806	MASTER SOX-E 18W BY22d 1SL/12	12	12
PHL	SOXE131	8711500179821	MASTER SOX-E 131W BY22d 1SL/6	6	6
PHL	SOX90	8711500179777	SOX 90W BY22d 1SL/12	12	12
PHL	SOX55	8711500179753	SOX 55W BY22d 1SL/12	12	12
PHL	SOX35	8711500179739	SOX 35W BY22d 1SL/12	12	12
PHL	SOX180	8711500179814	SOX 180W BY22d 1SL/6	6	6
PHL	SOX135	8711500179791	SOX 135W BY22d 1SL/12	12	12
PHL	SONTPLUS70	8711500192660	MST SON-T PIA Plus 70W/220 E27 1SL/12	12	12
PHL	SONTPLUS600	8711500197429	MST SON-T PIA Plus 600W/220 E40 1SL/12	12	12
PHL	SONTPLUS50	8711500192653	MST SON-T PIA Plus 50W/220 E27 1SL/12	12	12
PHL	SONTPLUS400	8711500179883	MST SON-T PIA Plus 400W E E40 1SL/12	12	12
PHL	SONTPLUS250	8711500179876	MST SON-T PIA Plus 250W E E40 1SL/12	12	12
PHL	SONTPLUS150	8711500192295	MST SON-T PIA Plus 150W/220 E40 - 1SL/12	12	12
PHL	SONTPLUS100	8711500192301	MST SON-T PIA Plus 100W/220 E40 1SL/12	12	12
PHL	SONTAPIA70	8727900922905	MST SON-T APIA Plus Xtra 70W E27 1SL/12	12	12
PHL	SONTAPIA400ECO	8727900885149	MST SON-T APIA Plus Hg Free 400W E40 1SL	12	12
PHL	SONTAPIA400	8727900927412	MST SON-T APIA Plus Xtra 400W E40 1SL/12	12	12
PHL	SONTAPIA250ECO	8727900885125	MST SON-T APIA Plus Hg Free 250W E40 1SL	12	12
PHL	SONTAPIA250	8727900927375	MST SON-T APIA Plus Xtra 250W E40 1SL/12	12	12
PHL	SONTAPIA150	8727900927337	MST SON-T APIA Plus Xtra 150W E40 1SL/12	12	12
PHL	SONTAPIA100	8727900923230	MST SON-T APIA Plus Xtra 100W E40 1SL/12	12	12
PHL	SONTAGRO400	8711500707505	MASTER Agro 400W E40 1SL/12	12	12
PHL	SONT1000	8711500184122	SON-T 1000W E40 1SL/4	4	4
PHL	SONPLUS70	8711500204264	MASTER SON PIA Plus 70W/220 I E27 1CT/24	24	24
PHL	SONPLUS400	8711500193452	MASTER SON PIA Plus 400W/220 E40 1SL/12	12	12
PHL	SONPLUS250	8711500193445	MASTER SON PIA Plus 250W/220 E40 1SL/12	12	12
PHL	SONPLUS150	8711500182289	MASTER SON PIA Plus 150W/220 E40 1SL/12	12	12
PHL	SONPLUS100	8711500182258	MASTER SON PIA Plus 100W/220 E40 1SL/12	12	12
PHL	SONE70	8711500210241	SON 70W E E27 CO 1CT/24	24	24
PHL	SON70	8711500181862	SON 70W/220 I E27 1CT/24	24	24
PHL	SON50	8711500181893	SON 50W/220 I E27 1CT/24	24	24
PHL	SOFT8YGLOBO20	8711500830159	Softone Globe 20W WW E27 G120 1CH/4	4	4
PHL	SND88T5	8711500910349	SND 88 400V 50/60Hz	120	120
PHL	SND58	8711500930682	SND 58 220-240V 50/60Hz	48	1
PHL	SN59	8711500915573	SN 59 220-240V 50/60Hz	20	1
PHL	SN56	8711500915603	SN 56 220-240V 50/60Hz	20	1
PHL	SKD578VITE	8727900895698	SKD 578-S 220-240V 50/60Hz	20	1
PHL	SKD578	8727900895674	SKD 578 220-240V 50/60Hz	48	1
PHL	SI54	8711500915481	SI 54 380-415V 50/60Hz	20	1
PHL	SI52	8711500915542	SI 52 220-240V 50/60Hz	48	1
PHL	SI51	8711500915535	SI 51 220-240V 50/60Hz	48	1

PHL	SETUV64	8711500642325	TUV 64T5 HE 4P SE UNP/32	32	32
PHL	SETUV36HO	8711500869708	TUV 36T5 HO 4P SE UNP/32	32	32
PHL	SETUV36	8711500642318	TUV 36T5 HE 4P SE UNP/32	32	32
PHL	SETUV16	8711500643858	TUV 16W 4P SE UNP/32	32	32
PHL	SDWTG50	8711500203236	MST SDW-TG Mini 50W/825 GX12-1 1CT/12	12	12
PHL	SDWTG100	8711500202338	MST SDW-TG Mini 100W/825 GX12-1 1CT/12	12	12
PHL	SDWT50	8711500734037	MASTER SDW-T 50W/825 PG12-1 1SL/12	12	12
PHL	SDWT35	8711500734020	MASTER SDW-T 35W/825 PG12-1 1SL/12	12	12
PHL	SDWT100	8711500734044	MASTER SDW-T 100W/825 PG12-1 1SL/12	12	12
PHL	S2EL	8711500764980	S2E 18-22W SER 220-240V BL/20X25CT	500	25
PHL	S2	8711500697509	S2 4-22W SER 220-240V WH EUR/12X25CT	300	300
PHL	S10EL	8711500764973	S10E 18-75W SIN 220-240V BL/20X25CT	500	25
PHL	S10B2	8711500698322	S10 4-65W SIN 220-240V WH 2BC/10	10	10
PHL	S10	8711500697691	S10 4-65W SIN 220-240V WH EUR/12X25CT	300	300
PHL	PLTTOP57844P	8711500610348	MASTER PL-T TOP 57W/840/4P 1CT/5X10BOX	50	10
PHL	PLTTOP57834P	8711500610225	MASTER PL-T TOP 57W/830/4P 1CT/5X10BOX	50	10
PHL	PLTTOP42844P	8711500610089	MASTER PL-T TOP 42W/840/4P 1CT/5X10BOX	50	10
PHL	PLTTOP42834P	8711500610041	MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX	50	10
PHL	PLTTOP42824P	8711500272089	MASTER PL-T TOP 42W/827/4P 1CT/5X10BOX	50	50
PHL	PLTTOP32844P	8711500560261	MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX	50	50
PHL	PLTTOP32834P	8711500560230	MASTER PL-T TOP 32W/830/4P 1CT/5X10BOX	50	10
PHL	PLTTOP26844P	8711500889478	MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX	50	50
PHL	PLTTOP26834P	8711500889447	MASTER PL-T TOP 26W/830/4P 1CT/5X10BOX	50	10
PHL	PLTTOP18844P	8711500889416	MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX	50	10
PHL	PLTTOP18834P	8711500889089	MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX	50	50
PHL	PLTCS57844P	8711500611451	MASTER PL-T 57W/840/4P 1CT/5X10BOX	50	10
PHL	PLTCS57834PXTRA	8711500897527	MASTER PL-T Xtra 57W/830/4P 1CT/5X10BOX	50	50
PHL	PLTCS57834P	8711500611406	MASTER PL-T 57W/830/4P 1CT/5X10BOX	50	10
PHL	PLTCS42844P	8711500611376	MASTER PL-T 42W/840/4P 1CT/5X10BOX	50	10
PHL	PLTCS42834PXTRA	8711500897466	MASTER PL-T Xtra 42W/830/4P 1CT/5X10BOX	50	50
PHL	PLTCS42834P	8711500611345	MASTER PL-T 42W/830/4P 1CT/5X10BOX	50	10
PHL	PLTCS42824P	8711500560025	MASTER PL-T 42W/827/4P 1CT/5X10BOX	50	10
PHL	PLTCS32844P	8711500611314	MASTER PL-T 32W/840/4P 1CT/5X10BOX	50	10
PHL	PLTCS32834PXTRA	8711500897404	MASTER PL-T Xtra 32W/830/4P 1CT/5X10BOX	50	50
PHL	PLTCS32834P	8711500611284	MASTER PL-T 32W/830/4P 1CT/5X10BOX	50	10
PHL	PLTCS32824P	8711500559968	MASTER PL-T 32W/827/4P 1CT/5X10BOX	50	10
PHL	PLTCS26844P	8711500611253	MASTER PL-T 26W/840/4P 1CT/5X10BOX	50	10
PHL	PLTCS2684	8711500611130	MASTER PL-T 26W/840/2P 1CT/5X10BOX	50	10
PHL	PLTCS26834P	8711500611208	MASTER PL-T 26W/830/4P 1CT/5X10BOX	50	10
PHL	PLTCS2683	8711500611024	MASTER PL-T 26W/830/2P 1CT/5X10BOX	50	10
PHL	PLTCS26824P	8711500559937	MASTER PL-T 26W/827/4P 1CT/5X10BOX	50	10
PHL	PLTCS2682	8711500559883	MASTER PL-T 26W/827/2P 1CT/5X10BOX	50	10
PHL	PLTCS18844P	8711500610997	MASTER PL-T 18W/840/4P 1CT/5X10BOX	50	10
PHL	PLTCS1884	8711500610614	MASTER PL-T 18W/840/2P 1CT/5X10BOX	50	10

PHL	PLTCS18834P	8711500610768	MASTER PL-T 18W/830/4P 1CT/5X10BOX	50	10
PHL	PLTCS1883	8711500610508	MASTER PL-T 18W/830/2P 1CT/5X10BOX	50	10
PHL	PLTCS18824P	8711500559821	MASTER PL-T 18W/827/4P 1CT/5X10BOX	50	10
PHL	PLTCS1882	8711500559791	MASTER PL-T 18W/827/2P 1CT/5X10BOX	50	10
PHL	PLSLED2P9830	8718699596668	CorePro LED PLS 5W 830 2P G23	20	20
PHL	PLSLED2P11840	8718699596682	CorePro LED PLS 5W 840 2P G23	20	20
PHL	PLS910	8711500951946	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	60	10
PHL	PLS908	8711500950901	PL-S 9W BLB/2P 1CT/6X10CC	60	10
PHL	PLRECO17844P	8711500266040	MASTER PL-R Eco 17W/840/4P 1CT/5X10BOX	50	10
PHL	PLRECO17834P	8711500266019	MASTER PL-R Eco 17W/830/4P 1CT/5X10BOX	50	10
PHL	PLRECO14844P	8711500265982	MASTER PL-R Eco 14W/840/4P 1CT/5X10BOX	50	10
PHL	PLRECO14834P	8711500265951	MASTER PL-R Eco 14W/830/4P 1CT/5X10BOX	50	10
PHL	PLQ388354P	8711500271730	PL-Q 38W/835/4P 1CT/10BOX	10	10
PHL	PLQ38834P	8711500271723	PL-Q 38W/830/4P 1CT/10BOX	10	10
PHL	PLQ288354P	8711500269676	PL-Q 28W/835/4P 1CT/10BOX	10	10
PHL	PLQ28834P	8711500269928	PL-Q 28W/830/4P 1CT/10BOX	10	10
PHL	PLQ168354P	8711500272065	PL-Q 16W/835/4P 1CT/10BOX	10	10
PHL	PLQ16835	8711500269669	PL-Q 16W/835/2P 1CT/10BOX	10	10
PHL	PLQ16834P	8711500269898	PL-Q 16W/830/4P 1CT/10BOX	10	10
PHL	PLQ1683	8711500269874	PL-Q 16W/830/2P 1CT/10BOX	10	10
PHL	PLQ1682	8711500269652	PL-Q 16W/827/2P 1CT/10BOX	10	10
PHL	PLLTUV55	8711500633798	TUV PL-L 55W/4P HF 1CT/25	25	25
PHL	PLLTUV18	8711500624925	TUV PL-L 18W/4P 1CT/25	25	25
PHL	PLLED4P55865	8718696828434	CorePro LED PLL HF 24W 865 4P 2G11	10	10
PHL	PLLED4P55840	8718696828410	CorePro LED PLL HF 24W 840 4P 2G11	10	10
PHL	PLLED4P55830	8718696828397	CorePro LED PLL HF 24W 830 4P 2G11	10	10
PHL	PLLED4P36865	8718696739761	CorePro LED PLL HF 16.5W 865 4P 2G11	10	10
PHL	PLLED4P36840	8718696739747	CorePro LED PLL HF 16.5W 840 4P 2G11	10	10
PHL	PLLED4P36830	8718696739662	CorePro LED PLL HF 16.5W 830 4P 2G11	10	10
PHL	PLL3601	8711500868893	PL-L 36W/01/4P 1CT/25	25	25
PHL	PLL1810	8711500260185	PL-L 18W/10/4P 1CT/25	25	25
PHL	PLET33DL	8727900210354	MASTER PLE-R 33W/865 E27 220-240V 1CT/6	6	6
PHL	PLET33	8711500659996	MASTER PLE-R 33W/827 E27 220-240V 1CT/6	6	6
PHL	PLET27DL	8711500543899	MASTER PLE-R 27W/865 E27 220-240V 1CT/6	6	6
PHL	PLET27	8711500543851	MASTER PLE-R 27W/827 E27 220-240V 1CT/6	6	6
PHL	PLET20	8711500751430	MASTER PLE-R 20W/827 E27 220-240V 1CT/6	6	6
PHL	PLET15	8711500751423	MASTER PL-E 15W/827 E27 230-240V 1CT/6	6	6
PHL	PLEDPRO23CDL	8711500469069	Softone Globe 23W CDL E27 G120 1CH/4	4	4
PHL	PLCLED4P26840	8718696541173	CorePro LED PLC 9W 840 4P G24q-3	10	10
PHL	PLCLED4P26830	8718696541159	CorePro LED PLC 9W 830 4P G24q-3	10	10
PHL	PLCLED4P18840	8718696541210	CorePro LED PLC 6.5W 840 4P G24q-2	10	10
PHL	PLCLED4P18830	8718696541197	CorePro LED PLC 6.5W 830 4P G24q-2	10	10
PHL	PLCLED4P13840	8718696706657	CorePro LED PLC 4.5W 840 4P G24q-1	10	10
PHL	PLCLED4P13830	8718696706633	CorePro LED PLC 4.5W 830 4P G24q-1	10	10

Signify Classified - Internal

PHL	PLCLED2P26840	8718696541258	CorePro LED PLC 8.5W 840 2P G24d-3	10	10
PHL	PLCLED2P26830	8718696541234	CorePro LED PLC 8.5W 830 2P G24d-3	10	10
PHL	PLCLED2P18840	8718696541296	CorePro LED PLC 6.5W 840 2P G24d-2	10	10
PHL	PLCLED2P18830	8718696541272	CorePro LED PLC 6.5W 830 2P G24d-2	10	10
PHL	PLCLED2P13840	8718696706619	CorePro LED PLC 4.5W 840 2P G24d-1	10	10
PHL	PLCLED2P13830	8718696706596	CorePro LED PLC 4.5W 830 2P G24d-1	10	10
PHL	PLC2686	8711500635310	MASTER PL-C 26W/865/2P 1CT/5X10BOX	50	10
PHL	PLC26844P	8711500623362	MASTER PL-C 26W/840/4P 1CT/5X10BOX	50	10
PHL	PLC2684	8711500621009	MASTER PL-C 26W/840/2P 1CT/5X10BOX	50	10
PHL	PLC26834P	8711500623355	MASTER PL-C 26W/830/4P 1CT/5X10BOX	50	10
PHL	PLC2683	8711500620989	MASTER PL-C 26W/830/2P 1CT/5X10BOX	50	10
PHL	PLC26824P	8711500623287	MASTER PL-C 26W/827/4P 1CT/5X10BOX	50	10
PHL	PLC2682	8711500620958	MASTER PL-C 26W/827/2P 1CT/5X10BOX	50	10
PHL	PLC18844P	8711500623348	MASTER PL-C 18W/840/4P 1CT/5X10BOX	50	10
PHL	PLC1884	8711500620934	MASTER PL-C 18W/840/2P 1CT/5X10BOX	50	10
PHL	PLC1883XTRA	8711500898951	MASTER PL-C Xtra 18W/830/2P 1CT/5X10BOX	50	50
PHL	PLC18834P	8711500623331	MASTER PL-C 18W/830/4P 1CT/5X10BOX	50	10
PHL	PLC1883	8711500620910	MASTER PL-C 18W/830 /2P 1CT/5X10BOX	50	10
PHL	PLC18824P	8711500623270	MASTER PL-C 18W/827/4P 1CT/5X10BOX	50	10
PHL	PLC1882	8711500620880	MASTER PL-C 18W/827/2P 1CT/5X10BOX	50	10
PHL	PLC13844P	8711500623324	MASTER PL-C 13W/840/4P 1CT/5X10BOX	50	10
PHL	PLC1384	8711500620866	MASTER PL-C 13W/840/2P 1CT/5X10BOX	50	10
PHL	PLC13834P	8711500623317	MASTER PL-C 13W/830/4P 1CT/5X10BOX	50	10
PHL	PLC1383	8711500620842	MASTER PL-C 13W/830/2P 1CT/5X10BOX	50	10
PHL	PLC1382	8711500620811	MASTER PL-C 13W/827/2P 1CT/5X10BOX	50	10
PHL	PLC10844P	8711500623300	MASTER PL-C 10W/840/4P 1CT/5X10BOX	50	50
PHL	PLC1084	8711500704986	MASTER PL-C 10W/840/2P 1CT/5X10BOX	50	10
PHL	PLC1083	8711500707246	MASTER PL-C 10W/830/2P 1CT/5X10BOX	50	10
PHL	PLC1082	8711500706812	MASTER PL-C 10W/827/2P 1CT/5X10BOX	50	10
PHL	PL9844P	8711500260963	MASTER PL-S 9W/840/4P 1CT/5X10BOX	50	10
PHL	PL984	8711500260871	MASTER PL-S 9W/840/2P 1CT/5X10CC	50	10
PHL	PL9834P	8711500260932	MASTER PL-S 9W/830/4P 1CT/5X10BOX	50	10
PHL	PL983	8711500260840	MASTER PL-S 9W/830/2P 1CT/5X10BOX	50	10
PHL	PL9824P	8711500260901	MASTER PL-S 9W/827/4P 1CT/5X10BOX	50	10
PHL	PL982	8711500260796	MASTER PL-S 9W/827/2P 1CT/5X10BOX	50	10
PHL	PL8084	8711500867124	MASTER PL-L 80W/840/4P 1CT/25	25	25
PHL	PL8083	8711500867087	MASTER PL-L 80W/830/4P 1CT/25	25	25
PHL	PL7844P	8711500260765	MASTER PL-S 7W/840/4P 1CT/5X10BOX	50	10
PHL	PL784	8711500260659	MASTER PL-S 7W/840/2P 1CT/5X10BOX	50	10
PHL	PL783	8711500260628	MASTER PL-S 7W/830/2P 1CT/5X10BOX	50	10
PHL	PL782	8711500260574	MASTER PL-S 7W/827/2P 1CT/5X10BOX	50	10
PHL	PL5844P	8711500260543	MASTER PL-S 5W/840/4P 1CT/5X10BOX	50	10
PHL	PL584	8711500260482	MASTER PL-S 5W/840/2P 1CT/5X10BOX	50	10
PHL	PL582	8711500260451	MASTER PL-S 5W/827/2P 1CT/5X10BOX	50	10

Signify Classified - Internal

PHL	PL5586	8711500261700	MASTER PL-L 55W/865/4P 1CT/25	25	25
PHL	PL5584XTRA	8711500897640	MASTER PL-L Xtra 55W/840/4P 1CT/25	25	25
PHL	PL5584	8711500615428	MASTER PL-L 55W/840/4P 1CT/25	25	25
PHL	PL5583	8711500615411	MASTER PL-L 55W/830/4P 1CT/25	25	25
PHL	PL4084	8711500610973	MASTER PL-L 40W/840/4P 1CT/25	25	25
PHL	PL4083	8711500610942	MASTER PL-L 40W/830/4P 1CT/25	25	25
PHL	PL36TUV	8711500628787	TUV PL-L 36W/4P 1CT/25	25	25
PHL	PL3684XTRA	8711500897602	MASTER PL-L Xtra 36W/840/4P 1CT/25	25	25
PHL	PL3684	8711500706751	MASTER PL-L 36W/840/4P 1CT/25	25	25
PHL	PL3683	8711500706744	MASTER PL-L 36W/830/4P 1CT/25	25	25
PHL	PL3682	8711500706737	MASTER PL-L 36W/827/4P 1CT/25	25	25
PHL	PL2484	8711500706720	MASTER PL-L 24W/840/4P 1CT/25	25	25
PHL	PL2483	8711500706713	MASTER PL-L 24W/830/4P 1CT/25	25	25
PHL	PL2482	8711500706706	MASTER PL-L 24W/827/4P 1CT/25	25	25
PHL	PL1886	8711500635143	MASTER PL-L 18W/865/4P 1CT/25	25	25
PHL	PL1884	8711500706690	MASTER PL-L 18W/840/4P 1CT/25	25	25
PHL	PL1883	8711500706683	MASTER PL-L 18W/830/4P 1CT/25	25	25
PHL	PL1882	8711500706676	MASTER PL-L 18W/827/4P 1CT/25	25	25
PHL	PL11844P	8711500261229	MASTER PL-S 11W/840/4P 1CT/5X10BOX	50	10
PHL	PL1184	8711500261090	MASTER PL-S 11W/840/2P 1CT/5X10BOX	50	10
PHL	PL11834P	8711500261199	MASTER PL-S 11W/830/4P 1CT/5X10BOX	50	10
PHL	PL1183	8711500261069	MASTER PL-S 11W/830/2P 1CT/5X10BOX	50	10
PHL	PL11824P	8711500261144	MASTER PL-S 11W/827/4P 1CT/5X10BOX	50	50
PHL	PL1182	8711500261014	MASTER PL-S 11W/827/2P 1CT/5X10BOX	50	10
PHL	PHILEDVEN40E14D	8718696709962	CLA LEDCandle D 5-40W BA35 E14 827 CL	10	10
PHL	PHILEDVEN25E14	8718696574096	CLA LEDCandle ND 2-25W BA35 E14 827 CL	10	10
PHL	PHILEDTOR25E14	8718696574119	CLA LEDCandle ND 2-25W ST35 E14 827 CL	10	10
PHL	PHILEDST6460DT	8718696709764	CLA LEDBulb DT 8-60W ST64 E27 CL	10	10
PHL	PHILEDST6460D	8718696814277	CLA LEDBulb D 8-60W ST64 E27 827 CL	6	6
PHL	PHILEDST6460	8718696742754	CLA LEDBulb ND 7-60W E27 WW ST64 CL	10	10
PHL	PHILEDST6440D	8718696814253	CLA LEDBulb D 5.5-40W ST64 E27 827 CL	6	6
PHL	PHILEDST6440	8718696574034	CLA LEDBulb ND 4-40W ST64 E27 827 CL	10	10
PHL	PHILEDLUS40E14D	8718696709900	CLA LEDLuster D 5-40W P45 E14 827 CL	10	10
PHL	PHILEDLUS40E14	8718696809716	CLA LEDLuster ND 4.3-40W E14 827 P45 CL	10	10
PHL	PHILEDLUS40D	8718696709924	CLA LEDLuster D 5-40W P45 E27 827 CL	10	10
PHL	PHILEDLUS40	8718696809730	CLA LEDLuster ND 4.3-40W E27 827 P45 CL	10	10
PHL	PHILEDLUS25E14D	8718696709863	CLA LEDLuster D 2.7-25W P45 E14 827 CL	10	10
PHL	PHILEDLUS25E14	8718696574133	CLA LEDLuster ND 2-25W P45 E14 827 CL	10	10
PHL	PHILEDLUS25D	8718696709887	CLA LEDLuster D 2.7-25W P45 E27 827 CL	10	10
PHL	PHILEDLUS25	8718696574157	CLA LEDLuster ND 2-25W P45 E27 827 CL	10	10
PHL	PHILEDGL60D	8718696814314	CLA LEDBulb D 8-60W G93 E27 827 CL	6	6
PHL	PHILEDGL60	8718696742716	CLA LEDBulb ND 7-60W E27 WW G93 CL	6	6
PHL	PHILEDGL12060D	8718699593391	LEDClassic 60W G120 E27 2700K CL D	4	4
PHL	PHILEDCAN40E14D	8718696709825	CLA LEDCandle D 5-40W B35 E14 827 CL	10	10

Signify Classified - Internal

PHL	PHILEDCAN40E14	8718696808535	CLA LEDCandle ND 4.3-40W E14 827 B35 CL	10	10
PHL	PHILEDCAN25E14D	8718696709801	CLA LEDCandle D 2.7-25W B35 E14 827 CL	10	10
PHL	PHILEDCAN25E14	8718696574072	CLA LEDCandle ND 2-25W B35 E14 827 CL	10	10
PHL	PHILED75865	8718696767061	CLA LEDBulb ND 8-75W A60 E27 865 CL	10	10
PHL	PHILED75840	8718696742617	CLA LEDBulb ND 8-75W E27 CW A60 CL	10	10
PHL	PHILED75	8718696809518	CLA LEDBulb ND 8-75W E27 827 A60 CL	10	10
PHL	PHILED60DT	8718696709726	CLA LEDBulb DT 8-60W A60 E27 CL	10	10
PHL	PHILED60D	8718696709443	CLA LEDBulb D 8-60W A60 E27 827 CL	10	10
PHL	PHILED60865	8718696767047	CLA LEDBulb ND 7-60W A60 E27 865 CL	10	10
PHL	PHILED60840	8718696767023	CLA LEDBulb ND 7-60W A60 E27 840 CL	10	10
PHL	PHILED60	8718696742730	CLA LEDBulb ND 7-60W E27 WW A60 CL	10	10
PHL	PHILED40DT	8718696709689	CLA LEDBulb DT 5.5-40W A60 E27 CL	10	10
PHL	PHILED40D	8718696709405	CLA LEDBulb D 5.5-40W A60 E27 827 CL	10	10
PHL	PHILED40865	8718696767009	CLA LEDBulb ND 4-40W A60 E27 865 CL	10	10
PHL	PHILED40840	8718696766989	CLA LEDBulb ND 4-40W A60 E27 840 CL	10	10
PHL	PHILED100D	8718696806319	CLA LEDBulb D 12-100W A67 E27 827 CL	6	6
PHL	PHILED100865	8718696767085	CLA LEDBulb ND 11-100W E27 865 A67 CL	10	10
PHL	PHILED100840	8718696742679	CLA LEDBulb ND 11-100W E27 840 A67 CL	10	10
PHL	PHILED100	8718696809594	CLA LEDBulb ND 11-100W E27 827 A67 CL	10	10
PHL	MZDLUS40E14	3139188162785	MZD LED 40W P45 E14 WW FR ND 1CT/10	10	10
PHL	MZDLUS40865E14	3139188162600	MZD LED 40W P45 E14 CDL FR ND 1CT/10 G3	10	10
PHL	MZDLUS40865	3139188162624	MZD LED 40W P45 E27 CDL FR ND 1CT/10 G3	10	10
PHL	MZDLUS40840E14	3139188162846	MZD LED 40W P45 E14 CW FR ND 1CT/10	10	10
PHL	MZDLUS40840	3139188162860	MZD LED 40W P45 E27 CW FR ND 1CT/10	10	10
PHL	MZDLUS40	3139188162808	MZD LED 40W P45 E27 WW FR ND 1CT/10	10	10
PHL	MZDLUS25E14	3139188161375	MZD LED 25W E14 827 P45 FR ND 1CT/10	10	10
PHL	MZDLUS25865E14	3139188162587	MZD LED 25W P45 E14 CDL FR ND 1CT/10 G3	10	10
PHL	MZDLUS25840E14	3139188162822	MZD LED 25W P45 E14 CW FR ND 1CT/10	10	10
PHL	MZDLUS25	3139188161399	MZD LED 25W E27 827 P45 FR ND 1CT/10	10	10
PHL	MZDGU535084050	3139188161337	MZD LED 50W GU5.3 840 12V 50D ND 1CT/10	10	10
PHL	MZDGU535084036	3139188161894	MZD LED 50W GU5.3 840 12V 36D ND	10	10
PHL	MZDGU535083050	3139188161313	MZD LED 50W GU5.3 830 12V 60D ND 1CT/10	10	10
PHL	MZDGU535082736	3139188161870	MZD LED 50W GU5.3 827 12V 36D ND	10	10
PHL	MZDGU533584036	3139188161856	MZD LED 35W GU5.3 840 12V 36D ND	10	10
PHL	MZDGU533582736	3139188161832	MZD LED 35W GU5.3 827 12V 36D ND	10	10
PHL	MZDGU1070865120	3139188161733	MZD LED 500lm GU10 865 120D ND 1CT/10	10	10
PHL	MZDGU1070840120	3139188161696	MZD LED 500lm GU10 840 120D ND 1CT/10	10	10
PHL	MZDGU1070827120	3139188161719	MZD LED 500lm GU10 827 120D ND 1CT/10	10	10
PHL	MZDGU106584036	3139188161658	MZD LED 65W GU10 840 36D ND 1CT/10	10	10
PHL	MZDGU106582736	3139188161634	MZD LED 65W GU10 827 36D ND 1CT/10	10	10
PHL	MZDGU105086536	3139188162648	MZD LED 50W GU10 865 36D ND 1CT/10	10	10
PHL	MZDGU105084060	3139188161290	MZD LED 50W GU10 840 60D ND 1CT/10	10	10
PHL	MZDGU105084036	3139188162662	MZD LED 50W GU10 840 36D ND 1CT/10	10	10
PHL	MZDGU105083060	3139188161276	MZD LED 50W GU10 830 60D ND 1CT/10	10	10

Signify Classified - Internal

PHL	MZDGU105082736	3139188161252	MZD LED 50W GU10 827 36D ND 1CT/10	10	10
PHL	MZDCAN60865	3139188163249	MZD LED 60W B35 E14 865 ND 1CT/10	10	10
PHL	MZDCAN60840	3139188163225	MZD LED 60W B35 E14 840 ND 1CT/10	10	10
PHL	MZDCAN60827	3139188163201	MZD LED 60W B35 E14 827 ND 1CT/10	10	10
PHL	MZDCAN40E14	3139188162723	MZD LED 40W B35 E14 WW FR ND 1CT/10	10	10
PHL	MZDCAN40865E14	3139188162686	MZD LED 40W B35 E14 CDL FR ND 1CT/10 G3	10	10
PHL	MZDCAN40840E14	3139188162884	MZD LED 40W B35 E14 CW FR ND 1CT/10	10	10
PHL	MZDCAN25E14	3139188161351	MZD LED 25W E14 827 B35 FR ND 1CT/10	10	10
PHL	MZDCAN25865E14	3139188162563	MZD LED 25W B35 E14 CDL FR ND 1CT/10 G3	10	10
PHL	MZDCAN25840E14	3139188162549	MZD LED 25W B35 E14 CW FR ND 1CT/10 G3	10	10
PHL	MZD75865	3139188162488	MZD LED 75W A60 E27 CDL FR ND 1CT/6 G3	6	6
PHL	MZD75840	3139188161511	MZD LED 75W A60 E27 840 FR ND 1CT/6 G3	6	6
PHL	MZD75	3139188161498	MZD LED 75W A60 E27 827 FR ND 1CT/6 G3	6	6
PHL	MZD60865	3139188162327	MZD LED 60W A60 E27 865 FR ND 1CT/6	6	6
PHL	MZD60840	3139188161474	MZD LED 60W A60 E27 840 FR ND 1CT/6	6	6
PHL	MZD60	3139188161450	MZD LED 60W A60 E27 827 FR ND 1CT/6	6	6
PHL	MZD58865	8718696717394	MZD LEDtube 1500mm 20W 865	10	10
PHL	MZD58840	8718696717370	MZD LEDtube 1500mm 20W 840	10	10
PHL	MZD40865	3139188162266	MZD LED 40W A60 E27 CDL FR ND 1CT/6 G3	6	6
PHL	MZD40840	3139188161436	MZD LED 40W E27 840 A60 ND 1CT/6	6	6
PHL	MZD40	3139188161412	MZD LED 40W A60 E27 827 FR ND 1CT/6	6	6
PHL	MZD36865	8718696717431	MZD LEDtube 1200mm 14.5W 865	10	10
PHL	MZD36840	8718696717417	MZD LEDtube 1200mm 14.5W 840	10	10
PHL	MZD18865	8718696717479	MZD LEDtube 600mm 8W 865	10	10
PHL	MZD18840	8718696717455	MZD LEDtube 600mm 8W 840	10	10
PHL	MZD100865	3139188162501	MZD LED 100W A67 E27 CDL FR ND 1CT/6 G3	6	6
PHL	MZD100840	3139188161559	MZD LED 100W A67 E27 CW FR ND 1CT/6 G3	6	6
PHL	MZD100	3139188161535	MZD LED 100W E27 827 A67 FR ND 1CT/6	6	6
PHL	MTOR8Y32CDL	8727900876307	Tornado T3 32W CDL E27 220-240V 1PF/6	6	6
PHL	MTOR8Y32	8727900876284	Tornado T3 32W WW E27 220-240V 1PF/6	6	6
PHL	MTOR12Y8E14	8718291117162	Tornado T2 8W WW E14 220-240V 1PF/6	6	6
PHL	MTOR12Y8CDL	8718291117049	Tornado T2 8W CDL E27 220-240V 1PF/6	6	6
PHL	MTOR12Y8	8718291117087	Tornado T2 8W WW E27 220-240V 1PF/6	6	6
PHL	MTOR12Y5E14	8718291116905	Tornado T2 5W WW E14 220-240V 1PF/6	6	6
PHL	MTOR12Y5	8718291116820	Tornado T2 5W WW E27 220-240V 1PF/6	6	6
PHL	MTOR12Y23CDL	8727900926002	Tornado T2 23W CDL E27 220-240V 1PF/6	6	6
PHL	MTOR12Y23	8727900925944	Tornado T2 23W WW E27 220-240V 1PF/6	6	6
PHL	MTOR12Y20CDL	8710163405155	Tornado T2 20W CDL E27 220-240V 1PF/6	6	6
PHL	MTOR12Y20	8710163405179	Tornado T2 20W WW E27 220-240V 1PF/6	6	6
PHL	MTOR12Y15CDL	8727900925845	Tornado T2 15W CDL E27 220-240V 1PF/6	6	6
PHL	MTOR12Y15	8727900925784	Tornado T2 15W WW E27 220-240V 1PF/6	6	6
PHL	MTOR12Y12E14CDL	8718291117209	Tornado T2 12W CDL E14 220-240V 1PF/6	6	6
PHL	MTOR12Y12E14	8718291117247	Tornado T2 12W WW E14 220-240V 1PF/6	6	6
PHL	MTOR12Y12CDL	8718291116943	Tornado T2 12W CDL E27 220-240V 1PF/6	6	6

Signify Classified - Internal

PHL	MTOR12Y12	8718291116981	Tornado T2 12W WW E27 220-240V 1PF/6	6	6
PHL	MPLE8	8711500263582	MASTER PLE-C 8W/827 E27 230-240V 1CT/6	6	6
PHL	MPLE11	8711500263681	MASTER PLE-C 11W/827 E27 230-240V 1CT/6	6	6
PHL	MLVGU535084060	8718696815649	MAS LED SPOT VLE D 7-50W MR16 840 60D	10	10
PHL	MLVGU535084036	8718696815588	MAS LED SPOT VLE D 7-50W MR16 840 36D	10	10
PHL	MLVGU535083060	8718696815625	MAS LED SPOT VLE D 7-50W MR16 830 60D	10	10
PHL	MLVGU535083036	8718696815564	MAS LED SPOT VLE D 7-50W MR16 830 36D	10	10
PHL	MLVGU535082760	8718696815601	MAS LED SPOT VLE D 7-50W MR16 827 60D	10	10
PHL	MLVGU535082736	8718696815540	MAS LED SPOT VLE D 7-50W MR16 827 36D	10	10
PHL	MLVGU533584060	8718696708330	MAS LED spot VLE D 5.5-35W MR16 840 60D	10	10
PHL	MLVGU533584036	8718696708279	MAS LED spot VLE D 5.5-35W MR16 840 36D	10	10
PHL	MLVGU533583060	8718696708316	MAS LED spot VLE D 5.5-35W MR16 830 60D	10	10
PHL	MLVGU533583036	8718696708255	MAS LED spot VLE D 5.5-35W MR16 830 36D	10	10
PHL	MLVGU533582760	8718696708293	MAS LED spot VLE D 5.5-35W MR16 827 60D	10	10
PHL	MLVGU533582736	8718696708231	MAS LED spot VLE D 5.5-35W MR16 827 36D	10	10
PHL	MLVGU10865120	8718696724354	MAS LED spot VLE D 680lm GU10 865 120D	10	10
PHL	MLVGU10840120	8718696724330	MAS LED spot VLE D 680lm GU10 840 120D	10	10
PHL	MLVGU10830120	8718696724316	MAS LED spot VLE D 650lm GU10 830 120D	10	10
PHL	MLVGU108086536	8718696708019	MAS LED spot VLE D 7-80W GU10 865 36D	10	10
PHL	MLVGU108084036	8718696707999	MAS LED spot VLE D 7-80W GU10 840 36D	10	10
PHL	MLVGU108083036	8718696707975	MAS LED spot VLE D 7-80W GU10 830 36D	10	10
PHL	MLVGU105094060	8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	10	10
PHL	MLVGU105094036	8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	10	10
PHL	MLVGU105093060	8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	10	10
PHL	MLVGU105093036	8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	10	10
PHL	MLVGU105092760	8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	10	10
PHL	MLVGU105092736	8718696707852	MAS LED spot VLE D 4.9-50W GU10 927 36D	10	10
PHL	MLVGU103594060	8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	10	10
PHL	MLVGU103594036	8718696707777	MAS LED spot VLE D 3.7-35W GU10 940 36D	10	10
PHL	MLVGU103593060	8718696707814	MAS LED spot VLE D 3.7-35W GU10 930 60D	10	10
PHL	MLVGU103593036	8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	10	10
PHL	MLVGU103592760	8718696707791	MAS LED spot VLE D 3.7-35W GU10 927 60D	10	10
PHL	MLVGU103592736	8718696707739	MAS LED spot VLE D 3.7-35W GU10 927 36D	10	10
PHL	MLVEN40827E14	8718696453544	MAS LEDcandle DT 6-40W E14 BA38 CL	10	10
PHL	MLVEN25827E14	8718696453766	MAS LEDcandle DT 4-25W E14 BA38 CL	10	10
PHL	MLTVAL900MEAT	8718696763919	MAS LEDtube 900mm 8.5W833 T8 FOOD	10	10
PHL	MLTVAL58865UOUN	8718696705353	MAS LEDtube UN 1500mm UO 24W865 T8	10	10
PHL	MLTVAL58865UOHF	8718696688045	MAS LEDtube HF 1500mm UO 24W865 T8	10	10
PHL	MLTVAL58865UO	8718696687468	MAS LEDtube 1500mm UO 24W 865 T8	10	10
PHL	MLTVAL58865UE	8718696731567	MAS LEDtube 1500mm UE 21.5W 865 T8	10	10
PHL	MLTVAL58865HOHF	8718696687567	MAS LEDtube HF 1500mm HO 20W865 T8	10	10
PHL	MLTVAL58865HO	8718699592455	MAS LEDtube 1500mm HO 18.2W 865 T8	10	10
PHL	MLTVAL58840UOUN	8718696705339	MAS LEDtube UN 1500mm UO 24W840 T8	10	10
PHL	MLTVAL58840UOHF	8718696688021	MAS LEDtube HF 1500mm UO 24W840 T8	10	10

Signify Classified - Internal

PHL	MLTVAL58840UO	8718696687444	MAS LEDtube 1500mm UO 24W 840 T8	10	10
PHL	MLTVAL58840UE	8718696731543	MAS LEDtube 1500mm UE 21.5W 840 T8	10	10
PHL	MLTVAL58840HOHF	8718696687543	MAS LEDtube HF 1500mm HO 20W840 T8	10	10
PHL	MLTVAL58840HO	8718699592431	MAS LEDtube 1500mm HO 18.2W 840 T8	10	10
PHL	MLTVAL58830UOUN	8718696728512	MAS LEDtube UN 1500mm UO 24W830 T8	10	10
PHL	MLTVAL58830UOHF	8718696688069	MAS LEDtube HF 1500mm UO 24W830 T8	10	10
PHL	MLTVAL58830UO	8718696687420	MAS LEDtube 1500mm UO 24W 830 T8	10	10
PHL	MLTVAL58830HOHF	8718696687581	MAS LEDtube HF 1500mm HO 20W830 T8	10	10
PHL	MLTVAL58830HO	8718699592417	MAS LEDtube 1500mm HO 18.2W 830 T8	10	10
PHL	MLTVAL36865UOUN	8718696705391	MAS LEDtube UN 1200mm UO 16W865 T8	10	10
PHL	MLTVAL36865UOHF	8718696687987	MAS LEDtube HF 1200mm UO 16W865 T8	10	10
PHL	MLTVAL36865UO	8718696687406	MAS LEDtube 1200mm UO 16W 865 T8	10	10
PHL	MLTVAL36865UE	8718696731529	MAS LEDtube 1200mm UE 14.5W 865 T8	10	10
PHL	MLTVAL36865HOHF	8718696687505	MAS LEDtube HF 1200mm HO 14W865 T8	10	10
PHL	MLTVAL36865HO	8718699592394	MAS LEDtube 1200mm HO 12.5W 865 T8	10	10
PHL	MLTVAL36840UOUN	8718696705377	MAS LEDtube UN 1200mm UO 16W840 T8	10	10
PHL	MLTVAL36840UOHF	8718696687963	MAS LEDtube HF 1200mm UO 16W840 T8	10	10
PHL	MLTVAL36840UO	8718696687383	MAS LEDtube 1200mm UO 16W 840 T8	10	10
PHL	MLTVAL36840UE	8718696731505	MAS LEDtube 1200mm UE 14.5W 840 T8	10	10
PHL	MLTVAL36840HOHF	8718696687482	MAS LEDtube HF 1200mm HO 14W840 T8	10	10
PHL	MLTVAL36840HO	8718699592370	MAS LEDtube 1200mm HO 12.5W 840 T8	10	10
PHL	MLTVAL36830UOUN	8718696728536	MAS LEDtube UN 1200mm UO 16W830 T8	10	10
PHL	MLTVAL36830UOHF	8718696688007	MAS LEDtube HF 1200mm UO 16W830 T8	10	10
PHL	MLTVAL36830UO	8718696687369	MAS LEDtube 1200mm UO 16W 830 T8	10	10
PHL	MLTVAL36830HOHF	8718696687529	MAS LEDtube HF 1200mm HO 14W830 T8	10	10
PHL	MLTVAL36830HO	8718699592356	MAS LEDtube 1200mm HO 12.5W 830 T8	10	10
PHL	MLTVAL30865HO	8718696687109	MAS LEDtube 900mm HO 12W 865 T8	10	10
PHL	MLTVAL30840HO	8718696687086	MAS LEDtube 900mm HO 12W 840 T8	10	10
PHL	MLTVAL18865HF	8718696743676	MAS LEDtube HF 600mm HO 8W865 T8	10	10
PHL	MLTVAL18865	8718696697511	MAS LEDtube 600mm HO 8W865 T8	10	10
PHL	MLTVAL18840HF	8718696743553	MAS LEDtube HF 600mm HO 8W840 T8	10	10
PHL	MLTVAL18840	8718696697498	MAS LEDtube 600mm HO 8W840 T8	10	10
PHL	MLTVAL18830HF	8718696743539	MAS LEDtube HF 600mm HO 8W830 T8	10	10
PHL	MLTVAL18830	8718696697474	MAS LEDtube 600mm HO 8W830 T8	10	10
PHL	MLTVAL1500MEAT	8718696763957	MAS LEDtube 1500mm 20W833 T8 FOOD	10	10
PHL	MLTVAL1200MEATH	8718696566169	MAS LEDtube HF 1200mm 16.5W833 T8 FOOD	10	10
PHL	MLTVAL1200MEAT	8718696763933	MAS LEDtube 1200mm 12W833 T8 FOOD	10	10
PHL	MLTCON58865UO	8718696773529	MAScon LEDtube IA 1500mm UO 25.5W865 T8	10	10
PHL	MLTCON58840UO	8718696773505	MAScon LEDtube IA 1500mm UO 25.5W840 T8	10	10
PHL	MLTCON58830UO	8718696773482	MAScon LEDtube IA 1500mm UO 25.5W830 T8	10	10
PHL	MLTCON36865UO	8718696773468	MAScon LEDtube IA 1200mm UO 16.5W865 T8	10	10
PHL	MLTCON36840UO	8718696773444	MAScon LEDtube IA 1200mm UO 16.5W840 T8	10	10
PHL	MLTCON36830UO	8718696773420	MAScon LEDtube IA 1200mm UO 16.5W830 T8	10	10
PHL	MLT580865	8718696706053	MAS LEDtube HF 1500mm UO 36W 865 T5	10	10

Signify Classified - Internal

PHL	MLT580840	8718696706039	MAS LEDtube HF 1500mm UO 36W 840 T5	10	10
PHL	MLT580830	8718696705995	MAS LEDtube HF 1500mm UO 36W 830 T5	10	10
PHL	MLT554865	8718696705315	MAS LEDtube HF 1200mm HO 26W 865 T5	10	10
PHL	MLT554840	8718696705292	MAS LEDtube HF 1200mm HO 26W 840 T5	10	10
PHL	MLT554830	8718696705278	MAS LEDtube HF 1200mm HO 26W 830 T5	10	10
PHL	MLT549865	8718696685563	MAS LEDtube HF 1500mm HO 26W 865 T5	10	10
PHL	MLT549840	8718696685549	MAS LEDtube HF 1500mm HO 26W 840 T5	10	10
PHL	MLT549830	8718696685525	MAS LEDtube HF 1500mm HO 26W 830 T5	10	10
PHL	MLT535865	8718696743393	MAS LEDtube HF 1500mm HE 20W 865 T5	10	10
PHL	MLT535840	8718696743379	MAS LEDtube HF 1500mm HE 20W 840 T5	10	10
PHL	MLT535830	8718696743355	MAS LEDtube HF 1500mm HE 20W 830 T5	10	10
PHL	MLT528865	8718696743331	MAS LEDtube HF 1200mm HE 16.5W 865 T5	10	10
PHL	MLT528840	8718696743317	MAS LEDtube HF 1200mm HE 16.5W 840 T5	10	10
PHL	MLT528830	8718696743294	MAS LEDtube HF 1200mm HE 16.5W 830 T5	10	10
PHL	MLT514865	8718696743270	MAS LEDtube HF 600mm HE 8W 865 T5	10	10
PHL	MLT514840	8718696743256	MAS LEDtube HF 600mm HE 8W 840 T5	10	10
PHL	MLT514830	8718696743232	MAS LEDtube HF 600mm HE 8W 830 T5	10	10
PHL	MLR1117594040	8718696718360	MAS LEDspotLV D 15-75W 940 AR111 40D	6	6
PHL	MLR1117594024	8718696718346	MAS LEDspotLV D 15-75W 940 AR111 24D	6	6
PHL	MLR1117593040	8718696515020	MAS LEDspotLV D 15-75W 930 AR111 40D	6	6
PHL	MLR1117593024	8718696514986	MAS LEDspotLV D 15-75W 930 AR111 24D	6	6
PHL	MLR1117592740	8718696515006	MAS LEDspotLV D 15-75W 927 AR111 40D	6	6
PHL	MLR1117592724	8718696514962	MAS LEDspotLV D 15-75W 927 AR111 24D	6	6
PHL	MLR111509308	8718696578353	MAS LEDspotLV D 11-50W 930 AR111 8D	6	6
PHL	MLR1115093040	8718696514948	MAS LEDspotLV D 11-50W 930 AR111 40D	6	6
PHL	MLR1115093024	8718696514900	MAS LEDspotLV D 11-50W 930 AR111 24D	6	6
PHL	MLR111509278	8718696578339	MAS LEDspotLV D 11-50W 927 AR111 8D	6	6
PHL	MLR1115092740	8718696514924	MAS LEDspotLV D 11-50W 927 AR111 40D	6	6
PHL	MLR1115092724	8718696514887	MAS LEDspotLV D 11-50W 927 AR111 24D	6	6
PHL	MLR11110084040	8718696725344	MAS LEDspotLV D 20-100W 840 AR111 40D	6	6
PHL	MLR11110084024	8718696725320	MAS LEDspotLV D 20-100W 840 AR111 24D	6	6
PHL	MLR11110083040	8718696707470	MAS LEDspotLV D 20-100W 830 AR111 40D	6	6
PHL	MLR11110083024	8718696707432	MAS LEDspotLV D 20-100W 830 AR111 24D	6	6
PHL	MLR11110082740	8718696707456	MAS LEDspotLV D 20-100W 827 AR111 40D	6	6
PHL	MLR11110082724	8718696515044	MAS LEDspotLV D 20-100W 827 AR111 24D	6	6
PHL	MLPAR3860827	8718696714560	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	6	6
PHL	MLPAR38100827	8718696713761	MAS LEDspot CLA D 13-100W 827 PAR38 25D	6	6
PHL	MLPAR307584025D	8718696713846	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	6	6
PHL	MLPAR307583025D	8718696713907	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	6	6
PHL	MLPAR307582725D	8718696713808	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	6	6
PHL	MLPAR205084040	8718696713747	MAS LEDspot CLA D 6-50W 840 PAR20 40D	6	6
PHL	MLPAR205084025	8718696713686	MAS LEDspot CLA D 6-50W 840 PAR20 25D	6	6
PHL	MLPAR205083040	8718696713723	MAS LEDspot CLA D 6-50W 830 PAR20 40D	6	6
PHL	MLPAR205083025	8718696713662	MAS LEDspot CLA D 6-50W 830 PAR20 25D	6	6

Signify Classified - Internal

PHL	MLPAR205082740	8718696713709	MAS LEDspot CLA D 6-50W 827 PAR20 40D	6	6
PHL	MLPAR205082725	8718696713563	MAS LEDspot CLA D 6-50W 827 PAR20 25D	6	6
PHL	MLLUS60827E14	8718696580677	MAS LEDlustre DT 8-60W P50 E14 827 CL	10	10
PHL	MLLUS40827E14	8718696453582	MAS LEDlustre DT 6-40W E14 P48 CL	10	10
PHL	MLLUS40827	8718696453605	MAS LEDlustre DT 6-40W E27 P48 CL	10	10
PHL	MLLUS25827E14	8718696453780	MAS LEDlustre DT 4-25W E14 P48 CL	10	10
PHL	MLLUS25827	8718696453803	MAS LEDlustre DT 4-25W E27 P48 CL	10	10
PHL	MLGU535084036D	8718696812716	MAS LEDspotLV D 8-50W 840 MR16 36D	10	10
PHL	MLGU535084024D	8718696812655	MAS LEDspotLV D 8-50W 840 MR16 24D	10	10
PHL	MLGU535083036D	8718696812693	MAS LEDspotLV D 8-50W 830 MR16 36D	10	10
PHL	MLGU535083024D	8718696812631	MAS LEDspotLV D 8-50W 830 MR16 24D	10	10
PHL	MLGU535082736D	8718696812679	MAS LEDspotLV D 8-50W 827 MR16 36D	10	10
PHL	MLGU535082724D	8718696812532	MAS LEDspotLV D 8-50W 827 MR16 24D	10	10
PHL	MLGU534394036X	8718696735480	MAS LED ExpertColor 7.5-43W MR16 940 36D	10	10
PHL	MLGU534394024X	8718696735428	MAS LED ExpertColor 7.5-43W MR16 940 24D	10	10
PHL	MLGU534393036X	8718696735466	MAS LED ExpertColor 7.5-43W MR16 930 36D	10	10
PHL	MLGU534393024X	8718696735404	MAS LED ExpertColor 7.5-43W MR16 930 24D	10	10
PHL	MLGU534392736X	8718696735442	MAS LED ExpertColor 7.5-43W MR16 927 36D	10	10
PHL	MLGU534392724X	8718696735381	MAS LED ExpertColor 7.5-43W MR16 927 24D	10	10
PHL	MLGU533594060X	8718696757550	MAS LED ExpertColor 6.5-35W MR16 940 60D	10	10
PHL	MLGU533594036X	8718696738870	MAS LED ExpertColor 6.5-35W MR16 940 36D	10	10
PHL	MLGU533594024X	8718696738818	MAS LED ExpertColor 6.5-35W MR16 940 24D	10	10
PHL	MLGU533594010X	8718696738757	MAS LED ExpertColor 6.5-35W MR16 940 10D	10	10
PHL	MLGU533593060X	8718696757536	MAS LED ExpertColor 6.5-35W MR16 930 60D	10	10
PHL	MLGU533593036X	8718696738856	MAS LED ExpertColor 6.5-35W MR16 930 36D	10	10
PHL	MLGU533593024X	8718696738795	MAS LED ExpertColor 6.5-35W MR16 930 24D	10	10
PHL	MLGU533593010X	8718696738733	MAS LED ExpertColor 6.5-35W MR16 930 10D	10	10
PHL	MLGU533592760X	8718696757512	MAS LED ExpertColor 6.5-35W MR16 927 60D	10	10
PHL	MLGU533592736X	8718696738832	MAS LED ExpertColor 6.5-35W MR16 927 36D	10	10
PHL	MLGU533592724X	8718696738771	MAS LED ExpertColor 6.5-35W MR16 927 24D	10	10
PHL	MLGU533592710X	8718696738719	MAS LED ExpertColor 6.5-35W MR16 927 10D	10	10
PHL	MLGU533582736	8718696815380	MAS LEDspotLV DimTone 5-35W MR16 36D	10	10
PHL	MLGU533582724	8718696442135	MAS LEDspotLV DimTone 6.5-35W MR16 24D	10	10
PHL	MLGU43XW24	8718696410196	MAS LEDspotLV 3.5-20W 827 MR11 24D	12	12
PHL	MLGU105094036X	8718696707715	MAS LED ExpertColor 5.5-50W GU10 940 36D	10	10
PHL	MLGU105094025X	8718696707654	MAS LED ExpertColor 5.5-50W GU10 940 25D	10	10
PHL	MLGU105093036X	8718696707692	MAS LED ExpertColor 5.5-50W GU10 930 36D	10	10
PHL	MLGU105093025X	8718696707630	MAS LED ExpertColor 5.5-50W GU10 930 25D	10	10
PHL	MLGU105092736X	8718696707678	MAS LED ExpertColor 5.5-50W GU10 927 36D	10	10
PHL	MLGU105092725X	8718696707616	MAS LED ExpertColor 5.5-50W GU10 927 25D	10	10
PHL	MLGU103594036X	8718696707593	MAS LED ExpertColor 3.9-35W GU10 940 36D	10	10
PHL	MLGU103594025X	8718696707531	MAS LED ExpertColor 3.9-35W GU10 940 25D	10	10
PHL	MLGU103593036X	8718696707579	MAS LED ExpertColor 3.9-35W GU10 930 36D	10	10
PHL	MLGU103593025X	8718696707517	MAS LED ExpertColor 3.9-35W GU10 930 25D	10	10

PHL	MLGU103592736X	8718696707555	MAS LED ExpertColor 3.9-35W GU10 927 36D	10	10
PHL	MLGU103592725X	8718696707494	MAS LED ExpertColor 3.9-35W GU10 927 25D	10	10
PHL	MLCAN60827E14	8718696555996	MAS LEDcandle DT 8-60W B40 E14 827 CL	10	10
PHL	MLCAN40827E14	8718696453506	MAS LEDcandle DT 6-40W E14 B38 CL	10	10
PHL	MLCAN25827E14	8718696453681	MAS LEDcandle DT 4-25W E14 B38 CL	10	10
PHL	ML75927DT	8718696826188	MAS LED bulb DT 12-75WE27 927-922 A67 FR	10	10
PHL	ML75827	8718696555514	MAS LEDbulb DT 11-75W A67 E27 827 FR	6	6
PHL	ML60927DT	8718696707111	MAS LED bulb DT 9-60W E27 927-922 A60 FR	10	10
PHL	ML60827CL	8718696481325	MAS LEDbulb DT 8.5-60W E27 A60 CL	10	10
PHL	ML40927DT	8718696707098	MAS LED bulb DT 5.5-40WE27 927-922 A60FR	10	10
PHL	ML40827CL	8718696481288	MAS LEDbulb DT 6-40W E27 A60 CL	10	10
PHL	ML100927DT	8718696826201	MASLEDbulb DT 15-100WE27 927-922 A67FR	10	10
PHL	ML100827	8718696555552	MAS LEDbulb DT 15-100W A67 E27 827 FR	6	6
PHL	MHNTD70	8718291215325	MHN-TD 70W/842 RX7s 1CT/12	12	12
PHL	MHNTD250	8711500734006	MHN-TD 250W/842 FC2 1CT/12	12	12
PHL	MHNTD2000S	8711500200747	MASTER MHN-LA 2000W/842 400V XWH	1	1
PHL	MHNTD1000S	8711500200785	MASTER MHN-LA 1000W/842 230V XWH	1	1
PHL	MHNSE200095HO	8727900928778	MASTER MHN-SE 2000W/956 GX22 400V HO UNP	1	1
PHL	MHNSB200095HO	8727900928600	MST MHN-SB 2000W/956 400V K12s-7 WH HO	1	1
PHL	MHNF1000740	8711500214249	MASTER MHN-FC 1000W/740 230V XW	1	1
PHL	MHDTD2000S	8711500200730	MASTER MHN-LA 2000W/956 400V XWH	1	1
PHL	MHDTD1000S	8711500200778	MASTER MHN-LA 1000W/956 230V XWH	1	1
PHL	MHD200095HO	8718291241836	MASTER MHN-SA 2000W/956 400V XW HO UNP/1	1	1
PHL	MHD1800S	8711500200754	MASTER MHN-SA 1800W/956 (P)SFC 230V	1	1
PHL	MHD18004S	8711500200761	MASTER MHN-SA 1800W/956 (P)SFC 400V	1	1
PHL	MCLAGU1050927	8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	10	10
PHL	MCLAGU1035927	8718696708095	MAS LED spot VLE DT 3.7-35W GU10 927 36D	10	10
PHL	M6533	8711500724861	TL-M RS 65W/33-640 1SL/25	25	25
PHL	M4084	8711500724625	TL-M RS Super 80 40W/840 1SL/25	25	25
PHL	M4054	8711500724410	TL-M RS 40W/54-765 1SL/25	25	25
PHL	M4033	8711500724298	TL-M RS 40W/33-640 SLV/25	25	25
PHL	M2033	8711500723727	TL-M RS 20W/33-640 SLV/25	25	25
PHL	LEDVEN40CLDIM	8718696581032	LED 40W BA38 E14 WW CL WGD SRT4	4	4
PHL	LEDVEN25CLDIM	8718696453742	LED 25W BA38 E14 WW CL WGD SRT4	4	4
PHL	LEDTWIST80WH	8718696708132	LED 80W GU10 WH 36D D RF 1BC/6	6	6
PHL	LEDTWIST80CW	8718696708156	LED 80W GU10 CW 36D D RF 1BC/6	6	6
PHL	LEDTWIST80CDL	8718696711224	LED 80W GU10 WW 36D D 1SRT4	4	4
PHL	LEDTSTART	8718696819654	MASTER LEDtube Starter EMP GenII OP	40	40
PHL	LEDT25SM25	8718696703137	LED 25W T25 E14 WW FR ND SRT4	4	4
PHL	LEDT25SM15	8718696703113	LED 15W T25 E14 WW FR ND SRT4	4	4
PHL	LEDSSSTWIST50	8718696710937	LED SSW 50W GU10 WW 36D RF ND 1BC/6	6	6
PHL	LEDSS603STEP	8718696588840	LED SSW 60W A60 E27 WW FR ND 1BC/4	4	4
PHL	LEDSS602STEP	8718696598375	LED SSW 60W A60 E27 WW-CW FR ND SRT4	4	4
PHL	LEDSS1003STEP	8718696706794	LED SSW 100W A67 E27 WW FR ND 1BC/6	6	6

Signify Classified - Internal

PHL	LEDSS1002STEP	8718696706831	LED SSW 100W A67 E27 WW-CW FR ND 1BC/6	6	6
PHL	LEDSONT150740	8718696699386	TForce LED SOX D 40-31W B22d 740 FR	6	6
PHL	LEDSONT70740	8718696811177	TForce LED Road 60-35W E27 740	6	6
PHL	LEDSONT70730	8718696811153	TForce LED Road 55-35W E27 730	6	6
PHL	LEDSONT150740	8718699639105	TForce LED Road 120-68W E40 740	6	6
PHL	LEDSONT150730	8718699639082	TForce LED Road 112-68W E40 730	6	6
PHL	LEDSONT100740	8718699639068	TForce LED Road 90-55W E40 740	6	6
PHL	LEDSONT100730	8718699639044	TForce LED Road 84-55W E40 730	6	6
PHL	LEDSF60SME14CW	8718696702956	LED 60W P48 E14 CW FR ND RF 1BC/6	6	6
PHL	LEDSF60SME14CDL	8718696746790	LED 60W P48 E14 CDL FR ND RF 1BC/6	6	6
PHL	LEDSF60SME14	8718696702895	LED 60W P48 E14 WW FR ND RF 1BC/6	6	6
PHL	LEDSF60SMCW	8718696702970	LED 60W P48 E27 CW FR ND 1BC/6	6	6
PHL	LEDSF60SM	8718696702918	LED 60W P48 E27 WW FR ND RF 1BC/6	6	6
PHL	LEDSF60CLD	8718696580653	LED 60W P50 E14 WW CL WGD SRT4	4	4
PHL	LEDSF40SME14CW	8718696543580	LED 40W P45 E14 CW FR ND SRP 1BC/6	6	6
PHL	LEDSF40SME14CDL	8718696746752	LED 40W P45 E14 CDL FR ND RF 1BC/6	6	6
PHL	LEDSF40SME14	8718696475003	LED 40W P45 E14 WW FR ND SRT4	4	4
PHL	LEDSF40SM	8718696505786	LED 40W P45 E27 WW FR ND SRT4	4	4
PHL	LEDSF40CLE14CW	8718696543429	LED 40W P45 E14 CW CL ND 1BC/6	6	6
PHL	LEDSF40CLE14	8718696454817	LED 40W P45 E14 WW CL ND SRT4	4	4
PHL	LEDSF40CLDIM	8718696453568	LED 40W P48 E14 WW CL WGD SRT4	4	4
PHL	LEDSF40CL	8718696505762	LED 40W P45 E27 WW CL ND SRT4	4	4
PHL	LEDSF25SME14CW	8718696543504	LED 25W P45 E14 CW FR ND SRP 1BC/6	6	6
PHL	LEDSF25SME14	8718696474945	LED 25W P45 E14 WW FR ND SRT4	4	4
PHL	LEDSF25SM	8718696474969	LED 25W P45 E27 WW FR ND SRT4	4	4
PHL	LEDSF25CLE14	8718696454718	LED 25W P45 E14 WW CL ND SRT4	4	4
PHL	LEDSF25CL	8718696454756	LED 25W P45 E27 WW CL ND SRT4	4	4
PHL	LEDSSENS60WW	8718696739402	LED D2D 60W A60 E27 WW FR ND SRT4	4	4
PHL	LEDSSENS60CW	8718696739426	LED D2D 60W A60 E27 CW FR ND 1BC/6	6	6
PHL	LEDR7S7860WH	8718696713402	LED 60W R7S 78mm WH ND SRT4	4	4
PHL	LEDR7S7860CW	8718696713440	LED 60W R7S 78mm CW ND 1BC/6	6	6
PHL	LEDR7S60WH	8718696522516	LED 60W R7S 118mm WH ND SRT4	4	4
PHL	LEDR7S120WHD	8718696713464	LED 120W R7S 118mm WH D SRT4	4	4
PHL	LEDR7S120CWD	8718696713488	LED 120W R7S 118mm CW D 1BC/6	6	6
PHL	LEDR7S100WHD	8718696578735	LED 100W R7S 118mm WH D SRT4	4	4
PHL	LEDR7S100CWD	8718696578759	LED 100W R7S 118mm CW D 1BC/6	6	6
PHL	LEDOL60SMCW	8718696702932	LED 60W B38 E14 CW FR ND RF 1BC/6	6	6
PHL	LEDOL60SMCDL	8718696746776	LED 60W B38 E14 CDL FR ND RF 1BC/6	6	6
PHL	LEDOL60CLDIM	8718696555972	LED 60W B40 E14 WW CL WGD SRT4	4	4
PHL	LEDOL40SMCW	8718696543542	LED 40W B35 E14 CW FR ND 1BC/6	6	6
PHL	LEDOL40SMCDL	8718696746738	LED 40W B35 E14 CDL FR ND RF 1BC/6	6	6
PHL	LEDOL40SM	8718696474983	LED 40W B35 E14 WW FR ND SRT4	4	4
PHL	LEDOL40CW	8718696543382	LED 40W B35 E14 CW CL ND 1BC/6	6	6
PHL	LEDOL40CLDIM	8718696453483	LED 40W B38 E14 WW CL WGD SRT4	4	4

Signify Classified - Internal

PHL	LEDOL40CL	8718696454770	LED 40W B35 E14 WW CL ND SRT4	4	4
PHL	LEDOL25SMCW	8718696543467	LED 25W B35 E14 CW FR ND 1BC/6	6	6
PHL	LEDOL25SM	8718696474914	LED 25W B35 E14 WW FR ND SRT4	4	4
PHL	LEDOL25CLDIM	8718696453667	LED 25W B38 E14 WW CL WGD SRT4	4	4
PHL	LEDOL25CL	8718696454695	LED 25W B35 E14 WW CL ND SRT4	4	4
PHL	LEDMR1120	8718696708668	LED 20W MR11 GU4 WW ND RF 1BC/6	6	6
PHL	LEDHPL80840	8718699638160	TForce LED HPL ND 30-21W E27 840	6	6
PHL	LEDHPL80830	8718699638146	TForce LED HPL ND 28-21W E27 830	6	6
PHL	LEDHPL80740CL	8718696811115	TForce LED HPL ND 32-25W E27 740 CL	6	6
PHL	LEDHPL80740	8718696811139	TForce LED HPL ND 29-25W E27 740 FR	6	6
PHL	LEDHPL80730CL	8718696811078	TForce LED HPL ND 31-25W E27 730 CL	6	6
PHL	LEDHPL80730	8718696811092	TForce LED HPL ND 28-25W E27 730 FR	6	6
PHL	LEDHPL6000840	8718699638245	TForce LED HPL ND 60-42W E27 840	6	6
PHL	LEDHPL570084040	8718699638283	TForce LED HPL ND 60-42W E40 840	6	6
PHL	LEDHPL570083040	8718699638269	TForce LED HPL ND 57-42W E40 830	6	6
PHL	LEDHPL5700830	8718699638221	TForce LED HPL ND 57-42W E27 830	6	6
PHL	LEDHPL125840	8718699638207	TForce LED HPL ND 40-28W E27 840	6	6
PHL	LEDHPL125830	8718699638184	TForce LED HPL ND 38-28W E27 830	6	6
PHL	LEDHPL125740CL	8718696811030	TForce LED HPL ND 48-33W E27 740 CL	6	6
PHL	LEDHPL125740	8718696811054	TForce LED HPL ND 44-33W E27 740 FR	6	6
PHL	LEDHPL125730CL	8718696810996	TForce LED HPL ND 46-33W E27 730 CL	6	6
PHL	LEDHPL125730	8718696811016	TForce LED HPL ND 42-33W E27 730 FR	6	6
PHL	LEDHPI40084060	8718696713860	TForce LED HPI ND 200-145W E40 840 60D	2	2
PHL	LEDHPI400840120	8718696713884	TForce LED HPI ND 200-145W E40 840 120D	2	2
PHL	LEDHPI25084060	8718696713785	TForce LED HPI ND 110-88W E40 840 60D	2	2
PHL	LEDHPI250840120	8718696713822	TForce LED HPI ND 110-88W E40 840 120D	2	2
PHL	LEDGL75CDL	8718696742990	LED Globe 75W G120 E27 CDL FR ND 1PPF	6	6
PHL	LEDGL60CDL	8718696742976	LED Globe 60W G93 E27 CDL FR ND 1CT/6	6	6
PHL	LEDGL120SM	8718696567593	LED Globe 120W G120 E27 WW 230V ND 1CT/4	4	4
PHL	LEDGL10G93	8718696580639	LED Globe 60W G93 E27 WW FR ND 1CT/4	4	4
PHL	LEDGL100SM	8718696580615	LED Globe 100W G93 E27 WW FR ND 1CT/4	4	4
PHL	LEDGL100CDL	8718696743010	LED Globe 100W G93 E27 CDL FR ND 1CT/6	6	6
PHL	LEDG925D	8718696578674	LED 25W G9 WW 230V Dim SRT4	4	4
PHL	LEDG925	8718696713389	LED 25W G9 WW ND SRT4	4	4
PHL	LEDG420WWD	8718696578636	LED 20W G4 WW 12V Dim SRT4	4	4
PHL	LEDFLSF15ED	8718696649022	LEDFlame 15W P48 E14 230V FR D SRT4	4	4
PHL	LEDFLSF15E27D	8718696649046	LEDFlame 15W P48 E27 230V FR D SRT4	4	4
PHL	LEDFLSF15E27	8718696760703	LEDFlame 15W P48 E27 230V FR ND SRT4	4	4
PHL	LEDFLSF15	8718696760680	LEDFlame 15W P48 E14 230V FR ND SRT4	4	4
PHL	LEDFLOL15D	8718696649008	LEDFlame 15W B38 E14 230V FR D SRT4	4	4
PHL	LEDFLOL15	8718696760666	LEDFlame 15W B38 E14 230V FR ND SRT4	4	4
PHL	LEDFL45D	8718696652275	LED Flame 45W A60 E27 230V FR D SRT4	4	4
PHL	LEDFL45	8718696760727	LED Flame 45W A60 E27 230V FR ND SRT4	4	4
PHL	LEDFL25D	8718696652299	LED Flame 25W A60 E27 230V FR D SRT4	4	4

Signify Classified - Internal

PHL	LEDFL25	8718696760741	LED Flame 25W A60 E27 230V FR ND SRT4	4	4
PHL	LEDFILVEN40D	8718696710142	LED classic 40W BA35 E14 WW CL D SRT4	4	4
PHL	LEDFILVE25CL	8718696573877	LED classic 25W BA35 E14 WW CL ND SRT4	4	4
PHL	LEDFILST6460	8718696742433	LED classic 60W ST64 E27 WW CL ND SRT4	4	4
PHL	LEDFILST6450GD	8718696575390	LED classic 50W ST64 E27 2200K GOLD SRT4	4	4
PHL	LEDFILSF40E27D	8718696710104	LED classic 40W P45 E27 WW CL D SRT4	4	4
PHL	LEDFILSF40D	8718696710081	LED classic 40W P45 E14 WW CL D SRT4	4	4
PHL	LEDFILSF25D	8718696710043	LED classic 25W P45 E14 WW CL D SRT4	4	4
PHL	LEDFILSF25CLE27	8718696573938	LED classic 25W P45 E27 WW CL ND SRT4	4	4
PHL	LEDFILSF25CL	8718696573914	LED classic 25W P45 E14 WW CL ND SRT4	4	4
PHL	LEDFILOL40D	8718696710005	LED classic 40W B35 E14 WW CL D SRT4	4	4
PHL	LEDFILOL40CL	8718696587355	LED classic 40W B35 E14 WW CL ND SRT4	4	4
PHL	LEDFILOL25D	8718696709986	LED classic 25W B35 E14 WW CL D SRT4	4	4
PHL	LEDFILOL25CL	8718696573853	LED classic 25W B35 E14 WW CL ND SRT4	4	4
PHL	LEDFILGL60D	8718696575413	LED classic 60W G93 E27 WW CL D 1PF	4	4
PHL	LEDFILGL60	8718696742457	LED classic 60W G93 E27 WW CL ND 1PF	4	4
PHL	LEDFIL75CL	8718696742372	LED classic 75W A60 E27 WW CL ND SRT4	4	4
PHL	LEDFIL60CL	8718696742419	LED classic 60W A60 E27 WW CL ND SRT4	4	4
PHL	LEDFIL48CM	8718696709269	LED classic CM 48W A60 E27 WW CL D SRT4	4	4
PHL	LEDFIL40CL	8718696573815	LED classic 40W A60 E27 WW CL ND SRT4	4	4
PHL	LEDFIL25E27D	8718696710067	LED classic 25W P45 E27 WW CL D SRT4	4	4
PHL	LEDFIL100CLCW	8718696742518	LED classic 100W A67 E27 CW CL ND 1BC/6	6	6
PHL	LEDFIL100CL	8718696742396	LED classic 100W A67 E27 WW CL ND SRT4	4	4
PHL	LEDDIC35DIM	8718696708477	LED 35W MR16 WW 36D D RF 1BC/6	6	6
PHL	LEDDIC35CWD	8718696708491	LED 35W MR16 CW 36D D RF 1BC/6	6	6
PHL	LEDDIC35CW	8718696710531	LED 35W MR16 CW 36D ND RF 1BC/6	6	6
PHL	LEDDIC35	8718696710494	LED 35W MR16 WW 36D ND SRT4	4	4
PHL	LEDDIC20	8718696710470	LED 20W MR16 WW 36D ND 1SRT4	4	4
PHL	LEDCLSF40E14	8718696706299	LED classic 40W P45 E14 WW FR ND SRT4	4	4
PHL	LEDCLSF40	8718696706336	LED classic 40W P45 E27 WW FR ND SRT4	4	4
PHL	LEDCLSF25E14	8718696706275	LED classic 25W P45 E14 WW FR ND SRT4	4	4
PHL	LEDCLSF25	8718696706312	LED classic 25W P45 E27 WW FR ND SRT4	4	4
PHL	LEDCLOL40	8718696706251	LED classic 40W B35 E14 WW FR ND SRT4	4	4
PHL	LEDCLOL25	8718696706237	LED classic 25W B35 E14 WW FR ND SRT4	4	4
PHL	LEDCLATWIST50WH	8718696562727	LED classic 50W GU10 WH 36D ND 1BC/6	6	6
PHL	LEDCLATWIST50CW	8718696562741	LED classic 50W GU10 CW 36D ND SRT4	4	4
PHL	LEDCLATWIST35CW	8718696562703	LED classic 35W GU10 CW 36D ND 1BC/6	6	6
PHL	LEDCLATWIST25WH	8718696562628	LED classic 25W GU10 WH 36D ND SRT4	4	4
PHL	LEDCLATWIST25CW	8718696562642	LED classic 25W GU10 CW 36D ND 1BC/6	6	6
PHL	LEDCLASS603STEP	8718696743096	LEDClassic SSW 60W A60 E27 WW CL ND 1SRT	4	4
PHL	LEDCL75CW	8718696705599	LED classic 75W A60 E27 CW FR ND 1BC/6	6	6
PHL	LEDCL75CDL	8718696740668	LED classic 75W A60 E27 CDL FR ND 1BC/6	6	6
PHL	LEDCL75	8718696705537	LED classic 75W A60 E27 WW FR ND 1SRT4	4	4
PHL	LEDCL60CW	8718696703335	LED classic 60W A60 E27 CW FR ND 1BC/6	6	6

Signify Classified - Internal

PHL	LEDCL60CDL	8718696740729	LED classic 60W A60 E27 CDL FR ND 1BC/6	6	6
PHL	LEDCL60	8718696576632	LED classic 60W A60 E27 WW FR ND SRT4	4	4
PHL	LEDCL42R63CM	8718696714508	LED Classic 42W R63 CM E27 WW ND SRT4	4	4
PHL	LEDCL40CW	8718696705490	LED classic 40W A60 E27 CW FR ND 1BC/6	6	6
PHL	LEDCL40CDL	8718696740705	LED classic 40W A60 E27 CDL FR ND 1BC/6	6	6
PHL	LEDCL40	8718696576571	LED classic 40W A60 E27 WW FR ND SRT4	4	4
PHL	LEDCL100CW	8718696739228	LED classic 100W A67 CW FR ND 1BC/6	6	6
PHL	LEDCL100CDL	8718696739242	LED classic 100W A67 CDL FR ND 1BC/6	6	6
PHL	LEDCL100	8718696739105	LED classic 100W A67 WW FR ND SRT4	4	4
PHL	LED75SMDIM	8718696706954	LED 75W A60 E27 WW FR WGD SRT4	4	4
PHL	LED75SMCW	8718696510162	LED 75W A60 E27 CW 230V FR ND 1BC/6	6	6
PHL	LED75SMCDL	8718696510506	LED 75W A60 E27 CDL 230V FR ND 1BC/6	6	6
PHL	LED75SM	8718696577059	LED 75W A60 E27 WW 230V FR ND SRT4	4	4
PHL	LED60SMDIM	8718696706916	LED 60W A60 E27 WW FR WGD SRT4	4	4
PHL	LED60SMCW	8718696577257	LED 60W A60 E27 CW 230V FR ND SRT4	4	4
PHL	LED60SMCDL	8718696577332	LED 60W A60 E27 CDL 230V FR ND 1BC/6	6	6
PHL	LED60SM	8718696577073	LED 60W A60 E27 WW 230V FR ND SRT4	4	4
PHL	LED60CLDIM	8718696572177	LED 60W A60 E27 WW CL WGD SRT4	4	4
PHL	LED40SMDIM	8718696706893	LED 40W A60 E27 WW FR WGD SRT4	4	4
PHL	LED40SMCW	8718696577271	LED 40W A60 E27 CW 230V FR ND 1BC/6	6	6
PHL	LED40SMCDL	8718696577356	LED 40W A60 E27 CDL 230V FR ND 1BC/6	6	6
PHL	LED40SM	8718696577097	LED 40W A60 E27 WW 230V FR ND SRT4	4	4
PHL	LED40CLDIM	8718696481202	LED 40W A60 E27 WW CL WGD SRT4	4	4
PHL	LED120SMCW	8718696701638	LED Bulb 120W E27 CW 230V A67 FR 1BC/6	6	6
PHL	LED120SMCDL	8718696701652	LED Bulb 120W E27 CDL 230V A67 FR 1BC/6	6	6
PHL	LED120SM	8718696701614	LED Bulb 120W E27 WW 230V A67 FR 1BC/6	6	6
PHL	LED100SMCW	8718696577219	LED 100W A60 E27 CW 230V FR ND 1BC/6	6	6
PHL	LED100SMCDL	8718696577295	LED 100W A60 E27 CDL 230V FR ND 1BC/6	6	6
PHL	LED100SM	8718696577035	LED 100W A60 E27 WW 230V FR ND SRT4	4	4
PHL	LCLATWIST75WH	8718696750391	LEDClassic 550lm GU10 WH 120D ND 1BC/6	6	6
PHL	LCLATWIST75CW	8718696750377	LEDClassic 550lm GU10 CW 120D ND 1BC/6	6	6
PHL	LCLATWIST65WH	8718696733431	LEDClassic 65W GU10 WH 36D ND 1BC/6	6	6
PHL	LCLATWIST65CW	8718696732670	LEDClassic 65W GU10 CW 36D ND 1BC/6	6	6
PHL	LCLATWIST65CDL	8718696732694	LEDClassic 65W GU10 CDL 36D ND 1BC/6	6	6
PHL	LCLATWIST50WW	8718696582572	LED classic 50W GU10 WW 36D ND SRT4	4	4
PHL	LCLATWIST50WHD	8718696581650	LED Classic 50W GU10 WH 36D DIM 1BC/6	6	6
PHL	LCLATWIST50WH60	8718696562789	LED classic 50W GU10 WH 60D ND RF 1BC/6	6	6
PHL	LCLATWIST50CWD	8718696562888	LED Classic 50W GU10 CW 36D DIM 1BC/6	6	6
PHL	LCLATWIST50CW60	8718696562802	LEDClassic 50W GU10 CW 230V 60D ND 1BC/6	6	6
PHL	LCLATWIST50CDL	8718696562765	LED classic 50W GU10 CDL 36D ND 1BC/6	6	6
PHL	LCLATWIST35WHD	8718696721636	LED Classic 35W GU10 WH 36D DIM 1BC/6	6	6
PHL	LCLATWIST35WG	8718696562826	LED Classic 35W GU10 WW 36D DIM 1BC/4	4	4
PHL	LCLATWIST35CWD	8718696721476	LED Classic 35W GU10 CW 36D DIM 1BC/6	6	6
PHL	LCLATWIST25WW	8718696562604	LED classic 25W GU10 WW 36D ND SRT4	4	4

PHL	K4010R	8711500612236	Actinic BL TL-K 40W/10-R	25	25
PHL	IR375CH	8711500126597	R125 IR 375W E27 230-250V CL 1CT/10	10	10
PHL	IR250RH	8711500575210	BR125 IR 250W E27 230-250V Red 1CT/10	10	10
PHL	IR250CH	8711500575234	BR125 IR 250W E27 230-250V CL 1CT/10	10	10
PHL	IR150RH	8711500575203	BR125 IR 150W E27 230-250V Red 1CT/10	10	10
PHL	INCAVEN25	8718696706497	CLA LEDCandle ND 2.2-25W BA35 E14 FR	10	10
PHL	INCALUS40E14	8718696706435	CLA LEDLuster ND 4.3-40W E14 827 P45 FR	10	10
PHL	INCALUS40	8718696706473	CLA LEDLuster ND 4.3-40W E27 827 P45 FR	10	10
PHL	INCALUS25E14	8718696706411	CLA LEDLuster ND 2.2-25W P45 E14 FR	10	10
PHL	INCALUS25	8718696706459	CLA LEDLuster ND 2.2-25W P45 E27 FR	10	10
PHL	INCALED75865	8718699691219	LED classic 75W A60 E27 CDL FR ND 1CT/10	10	10
PHL	INCALED75840	8718696705612	LED classic 75W A60 E27 CW FR ND 1CT/10	10	10
PHL	INCALED75	8718696705551	LED classic 75W A60 E27 WW FR ND 1CT/10	10	10
PHL	INCALED60865	8718696740644	LED classic 60W A60 E27 CDL FR ND 1CT/10	10	10
PHL	INCALED60840	8718696705438	LED classic 60W A60 E27 CW FR ND 1CT/10	10	10
PHL	INCALED60	8718696472187	LED classic 60W A60 E27 WW FR ND 1CT/10	10	10
PHL	INCALED40865	8718696740620	LED classic 40W A60 E27 CDL FR ND 1CT/10	10	10
PHL	INCALED40840	8718696705513	LED classic 40W A60 E27 CW FR ND 1CT/10	10	10
PHL	INCALED40	8718696419656	LED classic 40W A60 E27 WW FR ND 1CT/10	10	10
PHL	INCALED100865	8718699691257	LED classic 100W A67 CDL FR ND 1CT/10	10	10
PHL	INCALED100840	8718696739280	LED classic 100W A67 CW FR ND 1CT/10	10	10
PHL	INCALED100	8718696739266	LED classic 100W A67 WW FR ND 1CT/10	10	10
PHL	INCACAN40	8718696706398	CLA LEDCandle ND 4.3-40W E14 827 B35 FR	10	10
PHL	INCACAN25	8718696706374	CLA LEDCandle ND 2.2-25W B35 E14 FR	10	10
PHL	HTORN75WW	8727900808322	Tornado High Lumen 75W WW E40 1CT/6	6	6
PHL	HTORN75CDL	8727900807233	Tornado High Lumen 75W CDL E40 1CT/6	6	6
PHL	HTORN65WW	8727900808247	Tornado High Lumen 60W WW E27 1CT/6	6	6
PHL	HTORN65CDL	8727900807219	Tornado High Lumen 60W CDL E27 1CT/6	6	6
PHL	HTORN45WW	8727900808223	Tornado High Lumen 45W WW E27 1CT/6	6	6
PHL	HTORN45CDL	8727900807196	Tornado High Lumen 45W CDL E27 1CT/6	6	6
PHL	HPIT450	8718696736531	MASTER HPI-T PLUS 450W/645 E40 1SL/12	12	12
PHL	HPIT20003HO	8711500202352	HPI-T 2000W/542 E40 380V 1SL/4	4	4
PHL	HPIT20002	8711500183767	HPI-T 2000W/646 E40 220V CRP/4	4	4
PHL	HPIT1000	8711500183736	HPI-T 1000W/543 E40 1SL/4	4	4
PHL	HPI450	8718696736555	MASTER HPI PLUS 450W/645 BU E40 1SL/6	6	6
PHL	HOK2	8718291999676	HOK 20/100 1CT/4	4	4
PHL	HIDPVXT250SON	8718291222712	HID-PV Xt 250 SON C2 208-277V	6	1
PHL	HIDPVXT210	8718291219934	HID-PV Xt 210 CDMe/CPO C2 208-277V	6	1
PHL	HIDPVM35SHPF	8718291671619	HID-PV m 35 /S CDM 220-240V 50/60Hz	12	1
PHL	HIDPVM20SHPF	8718291671596	HID-PV m 20 /S CDM 220-240V 50/60Hz	12	1
PHL	HIDPVM020I	8711500909817	HID-PV m PGJ5 20 /I CDM LPF 220-240V	12	1
PHL	HIDPVBSON70	8718696531518	HID-PV Base 70 SON C3 220-240V	12	1
PHL	HIDPVBSON50	8718696531471	HID-PV Base 50 SON C3 220-240V	12	12
PHL	HIDPVBSON150	8718696531570	HID-PV Base 150 SON/CDO Q 220-240V	12	12

PHL	HIDPVBSON100	8718696531556	HID-PV Base 100 SON/CDO Q 220-240V	12	1
PHL	HIDPV90CPOQ	8718291241454	HID-PV Xt 90 CPO Q 208-277V	12	1
PHL	HIDPV60CPOQ	8718291241430	HID-PV Xt 60 CPO Q 208-277V	12	1
PHL	HIDPV45CPOQ	8718291668961	HID-PV Xt 45 CPO Q 208-277V	12	1
PHL	HIDPV315S	8727900843118	HID-PV 315 /S CDM 220-240V 50/60Hz	4	1
PHL	HIDPV150CDOQ	8718291698906	PV Xt Q 150W CDO	12	12
PHL	HIDPV140CPOQ	8718291241478	HID-PV Xt 140 CPO Q 208-277V	12	1
PHL	HIDPV100CDOQ	8718291698883	PV Xt Q 100W CDO	12	12
PHL	HIDPCV70S	8727900859744	HID-PV C 70 /S CDM 220-240V 50/60Hz NG	12	1
PHL	HIDDVXT250SON	8718291219910	HID-DV PROG Xt 250 SON C2 208-277V	6	1
PHL	HIDDVXT250CDO	8718291222613	HID-DV PROG Xt 250 CDO C2 208-277V	6	1
PHL	HIDDVXT210	8718291222699	HID-DV PROG Xt 210 CDMe/CPO C2 208-277V	6	1
PHL	HIDVDALX90CPO	8718291204558	HID-DV PROG Xt 90 CPO C1 208-277V	12	1
PHL	HIDVDALX60CPO	8718291204534	HID-DV PROG Xt 60 CPO C1 208-277V	12	1
PHL	HIDVDALX140CPO	8718291204572	HID-DV PROG Xt 140 CPO C1 208-277V	12	1
PHL	HIDDV90CPOQ	8718291241515	HID-DV PROG Xt 90 CPO Q 208-277V	12	1
PHL	HIDDV70SONQ	8718291669265	HID-DV PROG Xt 70 SON Q 208-277V	12	1
PHL	HIDDV70SON	8718291212225	HID-DV PROG Xt 70 SON C1 208-277V	12	1
PHL	HIDDV70CDOQ	8718291669180	HID-DV PROG Xt 70 CDO Q 208-277V	12	1
PHL	HIDDV70CDO	8718291212140	HID-DV PROG Xt 70 CDO C1 208-277V	12	1
PHL	HIDDV60CPOQ	8718291241492	HID-DV PROG Xt 60 CPO Q 208-277V	12	1
PHL	HIDDV50SONQ	8718291669241	HID-DV PROG Xt 50 SON Q 208-277V	12	1
PHL	HIDDV50CDOQ	8718291669166	HID-DV PROG Xt 50 CDO Q 208-277V	12	1
PHL	HIDDV45CPOQ	8718291669142	HID-DV PROG Xt 45 CPO Q 208-277V	12	1
PHL	HIDDV45CPO	8718291212102	HID-DV PROG Xt 45 CPO C1 208-277V	12	1
PHL	HIDDV150SONQ	8718291669302	HID-DV PROG Xt 150 SON Q 208-277V	12	1
PHL	HIDDV150SON	8718291212263	HID-DV PROG Xt 150 SON C1 208-277V	12	1
PHL	HIDDV150CDOQ	8718291669227	HID-DV PROG Xt 150 CDO Q 208-277V	12	1
PHL	HIDDV140CPOQ	8718291241539	HID-DV PROG Xt 140 CPO Q 208-277V	12	1
PHL	HIDDV100SONQ	8718291669289	HID-DV PROG Xt 100 SON Q 208-277V	12	1
PHL	HIDDV100SON	8718291212249	HID-DV PROG Xt 100 SON C1 208-277V	12	1
PHL	HIDDV100CDOQ	8718291669203	HID-DV PROG Xt 100 CDO Q 208-277V	12	1
PHL	HIDCPVM35I	8727900891645	HID-PV m 35/I CDM 220-240V 50/60Hz	10	1
PHL	HIDCPVM20PJ5S	8727900771282	HID-PV m PGJ5 20/S CDM HPF 220-240V	12	1
PHL	HIDCPVM20I	8727900890600	HID-PV m 20 /I CDM 220-240V 50/60Hz	10	1
PHL	HIDCPV70NI	8727900859881	HID-PV C 70 /I CDM 220-240V 50/60Hz NG	12	1
PHL	HIDCPV50SDWTG	8727900887532	HID-PV 50 /S SDW-TG 220-240V 50/60Hz	10	1
PHL	HIDCPV50S	8727900933635	HID-PV C 50 /S CDM 220-240V 50/60Hz	12	1
PHL	HIDCPV50I	8727900933659	HID-PV C 50 /I CDM 220-240V 50/60Hz	12	1
PHL	HIDCPV35NS	8727900859621	HID-PV C 35 /S CDM 220-240V 50/60Hz NG	12	12
PHL	HIDCPV35NI	8727900859737	HID-PV C 35 /I CDM 220-240V 50/60Hz NG	12	1
PHL	HIDCPV235NS	8727900895728	HID-PV C 2x35 /S CDM 220-240V 50/60Hz	12	1
PHL	HIDCPV150S	8711500910523	HID-PV C 150 /S CDM 220-240V 50/60Hz	12	1
PHL	HIDCPV150I	8711500912879	HID-PV C 150 /I CDM 220-240V 50/60Hz	10	1

Signify Classified - Internal

PHL	HIDCPV100SDWTG	8727900887549	HID-PV 100 /S SDW-TG 220-240V 50/60Hz	10	1
PHL	HIDCPV100S	8727900897623	HID-PV C 100 /S CDM 220-240V 50/60Hz G5	12	1
PHL	HIDCPV100I	8727900899511	HID-PV C 100 /I CDM 220-240V 50/60Hz G5	10	10
PHL	HIDCPV070P	8727900865530	HID-PV C 70 /P CDM 220-240V 50/60Hz	12	1
PHL	HIDCAV70I	8727900885224	HID-AV C 70 /I CDM 220-240V 50/60Hz	12	1
PHL	HIDCAV35I	8727900885248	HID-AV C 35 /I CDM 220-240V 50/60Hz	12	1
PHL	HIDAV3570S	8718291233107	HID-AV C 35-70 /S CDM 220-240V 50/60Hz	12	12
PHL	HIDAV3570I	8718291233121	HID-AV C 35-70 /I CDM 220-240V 50/60Hz	12	12
PHL	HFS226PLTCRIND	8718291169598	HF-S 1/226 PL-T/C II SR 220-240V 50/60Hz	12	1
PHL	HFS218PLTCRIND	8718291169635	HF-S 1/218 PL-T/C II SR 220-240V 50/60Hz	12	1
PHL	HFRTDI41424	8718291156789	HF-Ri TD 4 14/24 TL5 E+ 195-240V	10	1
PHL	HFRTDI31424	8718291156765	HF-Ri TD 3 14/24 TL5 E+ 195-240V	10	1
PHL	HFRTDI228354954	8718291662099	HF-Ri TD 2 28/35/49/54 TL5 E+ 195-240V	12	1
PHL	HFRTDI22642PLTC	8718291241690	HF-Ri TD 2 26-42 PL-T/C E+	12	12
PHL	HFRTDI1354980	8718291662075	HF-Ri TD 1 35/49/80 TL5 E+ 195-240V	12	1
PHL	HFRTDI128354954	8718291662051	HF-Ri TD 1 28/35/49/54 TL5 E+ 195-240V	12	1
PHL	HFRTDI12642PLTC	8718291241676	HF-Ri TD 1 26-42 PL-T/C E+	12	12
PHL	HFRTD280TL5	8711500910677	HF-Ri TD 280 TL5/PL-L E+ 220-240V	12	1
PHL	HFRTD239TL5	8718291696919	HF-Ri TD 2 14/21/24/39 E+	12	12
PHL	HFRTD160TL5	8718291718628	HF-Ri TD 160 TL5C E+ 195-240V 50/60Hz	12	1
PHL	HFRTD155TL5	8718291718642	HF-Ri TD 155 TL5C E+ 195-240V 50/60Hz	12	1
PHL	HFRTD139TL5	8718291696896	HF-Ri TD 1 14/21/24/39 E+	12	12
PHL	HFR280TL5	8711500910653	HF-R 280 TL5/PL-L EII 220-240V 50/60Hz	12	1
PHL	HFPXT136	8711500912008	HF-P Xt 136 TL-D EII 220-240V 50/60Hz	12	1
PHL	HFPI22880TL5	8727900862508	HF-Pi 2 28/35/49/80 TL5 EII	12	12
PHL	HFPI22854TL5	8711500915023	HF-Pi 2 28/35/49/54 TL5 EII 220-240V	12	1
PHL	HFPI21439TL5	8711500915009	HF-Pi 2 14/21/24/39 TL5 EII 220-240V	12	1
PHL	HFPI1424TL5	8727900887754	HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V	12	1
PHL	HFPI12880TL5	8727900862492	HF-Pi 1 28/35/49/80 TL5 EII	12	12
PHL	HFPI12854TL5	8711500914965	HF-Pi 1 28/35/49/54 TL5 EII 220-240V	12	1
PHL	HFPI11439TL5	8711500914941	HF-Pi 1 14/21/24/39 TL5 EII 220-240V	12	1
PHL	HFP160TL5C	8711500927781	HF-P 160 TL5C 220-240V 50/60Hz	36	1
PHL	HFP155TL5C	8711500927767	HF-P 155 TL5C 220-240V 50/60Hz	36	1
PHL	HFMRED124S	8711500910400	HF-M RED 124 SH TL/TL5/PL-L 230-240V	50	1
PHL	HFMRED114S	8711500931405	HF-M RED 114 SH TL/TL5/PL-C/S 230-240V	50	1
PHL	HFMRED109S	8711500931429	HF-M RED 109 SH TL/PL-S 230-240V	50	1
PHL	HFM209SH	8718291152712	HF-M RED 209 SH	50	1
PHL	HFM128L	8711500932433	HF-M BLUE 128 LH TL5 230-240V	50	1
PHL	HFM124S	8711500536389	HF-M BLUE 124 SH TL/TL5/PL-L 230-240V	50	1
PHL	HFM124L	8711500536402	HF-M BLUE 124 LH TL/TL5/PL-L 230-240V	50	1
PHL	HFM121L	8711500536464	HF-M BLUE 121 LH TL5 230-240V	50	1
PHL	HFM114L	8711500536822	HF-M BLUE 114 LH TL/PL-S/PL-C 230-240V	50	1
PHL	HFM109L	8711500536808	HF-M BLUE 109 LH TL/PL-S 230-240V	50	1
PHL	HFE418TLD	8718291770602	HF-E II 418 TL-D 220-240V 50/60Hz	20	20

PHL	HFE3414TL5	8718291770626	HF-E 3/4 14 TL5 II 220-240V 50/60Hz	20	20
PHL	HFE236TLD	8718291770589	HF-E II 236 TL-D 220-240V 50/60Hz	20	20
PHL	HFE136TLD	8718291770565	HF-E II 136 TL-D 220-240V 50/60Hz	20	20
PHL	HFE128	8718291668831	HF-E 128 TL5 220-240 50/60Hz	50	1
PHL	HFE1258TLD	8718291770640	HF-E 1/2 58 TL-D II 220-240V 50/60Hz	20	20
PHL	HFE1254TL5	8718291770664	HF-E 1/2 54 TL5 II 220-240V 50/60Hz	50	50
PHL	HFE1249TL5	8718291770688	HF-E 1/2 49 TL5 II 220-240V 50/60Hz	50	50
PHL	HF3P3418	8727900911626	HF-P 3/418 TL-D III 220-240V 50/60Hz IDC	10	1
PHL	HF3P336	8727900911688	HF-P 336 TL-D III 220-240V 50/60Hz IDC	10	1
PHL	HF3P280HOPLL	8727900952308	HF-P 280 TL5/PL-L III 220-240V 50/60Hz	12	1
PHL	HF3P258	8727900911725	HF-P 258 TL-D III 220-240V 50/60Hz IDC	12	1
PHL	HF3P25455HOPL	8727900863512	HF-P 254/255 TL5 HO/PLL III 220-240V IDC	12	1
PHL	HF3P249HO	8727900863475	HF-P 249 TL5 HO III 220-240V 50/60Hz IDC	12	1
PHL	HF3P236	8727900911664	HF-P 218/236 TL-D III 220-240V 50/60 Hz	12	1
PHL	HF3P226PLTC	8727900834239	HF-P 1/226 PL-T/C III 220-240V	12	1
PHL	HF3P22439HO	8727900952261	HF-P 2 24/39 TL5 III 220-240V 50/60Hz	12	1
PHL	HF3P218PLTC	8727900834178	HF-P 1/218 PL-T/C III 220-240V	12	1
PHL	HF3P21435HE	8727900905038	HF-P 2 14-35 TL5 HE III 220-240V	12	1
PHL	HF3P180HOPLL	8727900952285	HF-P 180 TL5 III 220-240V 50/60Hz	12	1
PHL	HF3P158	8727900911701	HF-P 158 TL-D III 220-240V 50/60Hz IDC	12	1
PHL	HF3P15455HOPL	8727900863482	HF-P 154/155 TL5 HO/PLL III 220-240V IDC	12	1
PHL	HF3P14TL5	8718291721253	HF-P 3/4 14 TL5 III 220-240V 50/60Hz IDC	10	1
PHL	HF3P149HO	8727900863192	HF-P 149 TL5 HO III 220-240V 50/60Hz IDC	12	1
PHL	HF3P136	8727900911640	HF-P 118/136 TL-D III 220-240V 50/60 Hz	12	1
PHL	HF3P12439HO	8727900952247	HF-P 1 24/39 TL5 III 220-240V 50/60Hz	12	1
PHL	HF2S3424HO	8727900939378	HF-S 3/424 TL5 II 220-240V 50/60Hz	10	1
PHL	HF2S3418	8727900905557	HF-S 3/4 18 TL-D II 220-240V 50/60Hz	10	1
PHL	HF2S3414TL5	8727900883350	HF-S 3/414 TL5 II 220-240V 50/60Hz	10	1
PHL	HF2S336	8727900897470	HF-S 336 TL-D II 220-240V 50/60Hz	10	1
PHL	HF2S258	8727900897463	HF-S 258 TL-D II 220-240V 50/60Hz	12	1
PHL	HF2S254TL5	8727900905625	HF-S 254 TL5 II 220-240V 50/60Hz	12	1
PHL	HF2S254	8718291656135	HF-S 254 TL5 II HT 220-240V 50/60Hz	12	1
PHL	HF2S249TL5	8727900905601	HF-S 249 TL5 II 220-240V 50/60Hz	12	1
PHL	HF2S249	8718291667797	HF-S 249 TL5 II HT 220-240V 50/60Hz	12	1
PHL	HF2S236	8727900905533	HF-S 218/236 TL-D II 220-240V 50/60Hz	12	1
PHL	HF2S22439HO	8727900939354	HF-S 2 24-39 TL5 II 220-240V 50/60Hz	12	1
PHL	HF2S218	8727900905526	HF-S 218 TL-D II 220-240V 50/60Hz	12	1
PHL	HF2S21435HE	8718291758440	HF-S 2 14-35 TL5 HE II 220-240V	12	12
PHL	HF2S180TL5	8718291758464	HF-S 180 TL5/PL-L II 220-240V 50/60Hz	12	12
PHL	HF2S158	8727900897395	HF-S 158 TL-D II 220-240V 50/60Hz	12	1
PHL	HF2S154	8727900905618	HF-S 154 TL5 II 220-240V 50/60Hz	12	1
PHL	HF2S149TL5	8727900905588	HF-S 149 TL5 II 220-240V 50/60Hz	12	1
PHL	HF2S136	8727900905519	HF-S 118/136 TL-D II 220-240V 50/60Hz	12	1
PHL	HF2S12439HO	8727900939330	HF-S 124-39 TL5 II 220-240V 50/60Hz	12	1

Signify Classified - Internal

PHL	HF2S11435HE	8718291758426	HF-S 1 14-35 TL5 HE II 220-240V	12	12
PHL	HF2R424TL5PLL	8711500913746	HF-R 424 TL5/PL-L EII 220-240V 50/60Hz	10	1
PHL	HF2R418TLD	8711500913661	HF-R 418 TL-D EII 220-240V 50/60Hz	10	1
PHL	HF2R414TL5	8711500913647	HF-R 414 TL5 EII 220-240V 50/60Hz	10	1
PHL	HF2R324TL5PLL	8711500913708	HF-R 324 TL5/PL-L EII 220-240V 50/60Hz	10	1
PHL	HF2R318TLD	8711500913760	HF-R 318 TL-D EII 220-240V 50/60Hz	10	1
PHL	HF2R258	8711500910196	HF-R 258 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2R254TL5	8711500910080	HF-R 254 TL5 EII 220-240V 50/60Hz	12	1
PHL	HF2R249TL5	8711500910035	HF-R 249 TL5 EII 220-240V 50/60Hz	12	1
PHL	HF2R239TL5PLL	8711500914743	HF-R 239 TL5 EII 220-240V 50/60Hz	12	1
PHL	HF2R236	8711500910158	HF-R 236 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2R22642PLTC	8727900809725	HF-R 2 26-42 PL-T/C EII 220-240V 50/60Hz	12	1
PHL	HF2R224TL5PLL	8711500914729	HF-R 224 TL5/PL-L EII 220-240V 50/60Hz	12	1
PHL	HF2R218PLTC	8718291176985	HF-R 218 PL-T/C EII 220-240V 50/60Hz	12	1
PHL	HF2R158	8711500910172	HF-R 158 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2R149TL5	8711500909985	HF-R 149 TL5 EII 220-240V 50/60Hz	12	1
PHL	HF2R136	8711500910134	HF-R 136 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2R12642PLTC	8727900809718	HF-R 1 26-42 PL-T/C EII 220-240V 50/60Hz	12	1
PHL	HF2R118PLTC	8718291176923	HF-R 118 PL-T/C EII 220-240V 50/60Hz	12	1
PHL	HF2R118	8711500911902	HF-R 118 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2P22242PLT5C	8711500913999	HF-P 2 22-42 PL-T/C/L/TL5C EII 220-240V	12	1
PHL	HF2P21317PLTCR	8711500914095	HF-P 2 13-17 PL-T/C/R EII 220-240V	12	1
PHL	HF2P12242PLT5C	8711500913975	HF-P 1 22-42 PL-T/C/L/TL5C EII 220-240V	12	1
PHL	HF2P11317PLTCR	8711500914071	HF-P 1 13-17 PL-T/C/R EII 220-240V	12	1
PHL	HF2B258	8711500931603	HF-B 158/258 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2B236	8711500931580	HF-B 136/236 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2B158	8711500931566	HF-B 158 TL-D EII 220-240V 50/60Hz	12	1
PHL	HF2B136	8711500931542	HF-B 136 TL-D EII 220-240V 50/60Hz	12	1
PHL	GEN8E14CDL	8711500801050	GENIE 8W CDL E14 220-240V 1PF/6	6	6
PHL	GEN8E14	8711500801159	GENIE 8W WW E14 220-240V 1PF/6	6	6
PHL	GEN8CDL	8711500802286	GENIE 8W CDL E27 220-240V 1PF/6	6	6
PHL	GEN8	8711500801180	GENIE 8W WW E27 220-240V 1PF/6	6	6
PHL	GEN5E14	8711500801142	GENIE 5W WW E14 220-240V 1PF/6	6	6
PHL	GEN5	8711500801173	Genie ES 5W WW E27 220-240V 1PF/6	6	6
PHL	GEN23CDL	8718291144151	Genie 23W CDL E27 220-240V 1PF/6	6	6
PHL	GEN23	8727900897135	Genie 23W WW E27 220-240V 1PF/6	6	6
PHL	GEN18CDL	8711500801081	GENIE 18W CDL E27 220-240V 1PF/6	6	6
PHL	GEN18	8711500801210	GENIE 18W WW E27 220-240V 1PF/6	6	6
PHL	GEN14CDL	8711500801074	GENIE 14W CDL E27 220-240V 1PF/6	6	6
PHL	GEN14	8711500801203	GENIE 14W WW E27 220-240V 1PF/6	6	6
PHL	GEN11E14CDL	8711500802576	GENIE 11W CDL E14 220-240V 1PF/6	6	6
PHL	GEN11E14	8711500801166	GENIE 11W WW E14 220-240V 1PF/6	6	6
PHL	GEN11CDL	8711500801067	GENIE 11W CDL E27 220-240V 1PF/6	6	6
PHL	GEN11	8711500801197	GENIE 11W WW E27 220-240V 1PF/6	6	6

PHL	G5TUV11	8711500559654	TUV 11W FAM/10X25BOX	250	25
PHL	FOR40SFEMGB1	8711500157546	Appl 40W E14 240V P45 CL OV 1BL/10	10	10
PHL	EXC091S50NEW	8711500741080	EXC 91 SOX-E 220-240V 50/60Hz	10	1
PHL	EXC066S50NEW	8711500062444	EXC 66 SOX-E 220-240V 50/60Hz	25	1
PHL	EXC055S50NEW	8711500062420	EXC 55 SOX 220-240V 50/60Hz	25	1
PHL	EXC036S50NEW	8711500062406	EXC 36 SOX-E 220-240V 50/60Hz	25	1
PHL	EXC035S50NEW	8711500062383	EXC 35 SOX 220-240V 50/60Hz	25	1
PHL	ELITETMGU6535	8718291153825	MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT	12	12
PHL	ELITETM35EV	8718696402450	CDM-Tm Evolution Mini 35W/930 GU6.5	12	12
PHL	ELITETC70942	8718291163688	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	12	12
PHL	ELITETC70930	8727900911534	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	12	12
PHL	ELITETC50942	8718291201632	MASTERC CDM-TC Elite 50W/942 G8.5 1CT	12	12
PHL	ELITETC50930	8727900930627	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	12	12
PHL	ELITETC35942	8718291163664	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	12	12
PHL	ELITETC35930	8727900911497	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	12	12
PHL	ELITET70942	8718291163626	MASTERC CDM-T Elite 70W/942 G12 1CT	12	12
PHL	ELITET70930	8727900911411	MASTERC CDM-T Elite 70W/930 G12 1CT/12	12	12
PHL	ELITET50942	8718291201595	MASTERC CDM-T Elite 50W/942 G12 1CT	12	12
PHL	ELITET50930	8727900930603	MASTERC CDM-T Elite 50W/930 G12 1CT/12	12	12
PHL	ELITET35942	8718291163640	MASTERC CDM-T Elite 35W/942 G12 1CT	12	12
PHL	ELITET35930	8727900911374	MASTERC CDM-T Elite 35W/930 G12 1CT/12	12	12
PHL	ELITET150930	8711500213129	MASTERC CDM-T Elite 150W/930 G12 1CT/12	12	12
PHL	ELITET100942	8718291231783	MASTERC CDM-T Elite 100W/942 G12 1CT	12	12
PHL	ELITET100930	8727900871692	MASTERC CDM-T Elite 100W/930 G12 1CT/12	12	12
PHL	ELITER7040942	8718291651697	MC CDM-R Elite 70W/942 E27 PAR30L 40D	6	6
PHL	ELITER7040930	8718291241904	MC CDM-R Elite 70W/930 E27 PAR30L 40D	6	6
PHL	ELITER7030942	8718291651673	MC CDM-R Elite 70W/942 E27 PAR30L 30D	6	6
PHL	ELITER7030930	8727900865325	MC CDM-R Elite 70W/930 E27 PAR30L 30D	6	6
PHL	ELITER7010930	8718291241867	MC CDM-R Elite 70W/930 E27 PAR30L 10D	6	6
PHL	ELITER3530930	8718291241942	MC CDM-R Elite 35W/930 E27 PAR30L 30D	6	6
PHL	ELITER3510930	8718291241928	MC CDM-R Elite 35W/930 E27 PAR30L 10D	6	6
PHL	ELITER1117040	8718291689782	MASTERC CDM-R111 Elite 70W/930 GX8.5 40D	6	6
PHL	ELITER1117024	8718291689706	MASTERC CDM-R111 Elite 70W/930 GX8.5 24D	6	6
PHL	ELITER1117010	8718291689621	MASTERC CDM-R111 Elite 70W/930 GX8.5 10D	6	6
PHL	ELITER1113540	8718291689522	MASTERC CDM-R111 Elite 35W/930 GX8.5 40D	6	6
PHL	ELITER1113524	8718291689447	MASTERC CDM-R111 Elite 35W/930 GX8.5 24D	6	6
PHL	ELITER1113510	8718291689188	MASTERC CDM-R111 Elite 35W/930 GX8.5 10D	6	6
PHL	ELITETP203530930	8718291651574	MC CDM-R Elite 35W/930 E27 PAR20 30D	12	12
PHL	ELITETP203510930	8718291651550	MC CDM-R Elite 35W/930 E27 PAR20 10D	12	12
PHL	ECTOR42CL	8727900820768	Halogen 42W E14 230V BW35 1CT/15 SRP	15	15
PHL	ECTOR28CL	8727900820706	Halogen 28W E14 230V BW35 1CT/15 SRP	15	15
PHL	ECTOR18CL	8727900820669	Halogen 18W E14 230V BW35 1CT/15 SRP	15	15
PHL	ECSFE42CLE14	8727900831481	Halogen 42W E14 230V P45 1CT/15 SRP	15	15
PHL	ECSFE42CL	8727900831429	Halogen 42W E27 230V P45 1CT/15 SRP	15	15

Signify Classified - Internal

PHL	ECSFE18CL	8727900831382	Halogen 18W E27 230V P45 1CT/15 SRP	15	15
PHL	ECO80ESCOMB1	8727900920949	Halogen 78MM 2Y 80W R7S 230V 1BC/10	10	10
PHL	ECO50DB24Y	8718696588789	Hal-Dich 4y 50W GU5.3 12V 36D 2BC/10	10	10
PHL	ECO50CB2	8711500413949	Hal-Caps 2y 50W GY6.35 12V CL 2BL/10	10	10
PHL	ECO48ESCOMB1	8727900920925	Halogen 78MM 2Y 48W R7S 230V 1BC/10	10	10
PHL	ECO400ESPLUSB1	8727900922318	Halogen 118MM 2Y 400W R7S 230V 1BC/10	10	10
PHL	ECO35ESCAPSB1	8727900252989	Halogen Caps 35W GY6.35 12V CL 1BC/10	10	10
PHL	ECO35DB24Y	8718696588765	Hal-Dich 4y 35W GU5.3 12V 36D 2BC/10	10	10
PHL	ECO28T25E14	8718291230793	Halogen 28W E14 230V T25L 1CT/20 SRP	20	20
PHL	ECO25ESCAPSB1	8727900252972	Halogen Caps 25W GY6.35 12V CL 1BC/10	10	10
PHL	ECO240ESPLUSB1	8727900922233	Halogen 118MM 2Y 240W R7S 230V 1BC/10	10	10
PHL	ECO20DB24Y	8718696588703	Hal-Dich 4y 20W GU5.3 12V 36D 2BC/10	10	10
PHL	ECO20CB2	8711500413925	Hal-Caps 2y 20W G4 12V CL 2BL/10	10	10
PHL	ECO160ESPLUSB1	8727900920888	Halogen 118MM 2Y 160W R7S 230V 1BC/10	10	10
PHL	ECO14ESCAPSB1	8727900823585	Halogen Caps 14W G4 12V CL 1BC/10	10	10
PHL	ECO120ESPLUSB1	8727900920901	Halogen 118MM 2Y 120W R7S 230V 1BC/10	10	10
PHL	ECO120ESCOMB1	8727900920963	Halogen 78MM 2Y 120W R7S 230V 1BC/10	10	10
PHL	EC2YVEN28B1	8727900925081	Halogen 28W E14 230V BXS35 CL 1BC/10	10	10
PHL	EC2YTOR42B1	8727900820980	Halogen 42W E14 230V BW35 CL 1BC/10	10	10
PHL	EC2YTOR28B1	8727900820942	Halogen 28W E14 230V BW35 CL 1BC/10	10	10
PHL	EC2YTOR18B1	8727900820904	Halogen 18W E14 230V BW35 CL 1BC/10	10	10
PHL	EC2YT2528CAP	8718291223481	Halogen CH 28W E14 230V T25L 1CT/20 SRP	20	20
PHL	EC2YGL70	8718291226130	Halogen 70W E27 230V G95 CL 1PF/10	10	10
PHL	EC28VEN	8727900925067	Halogen 28W E14 230V BXS35 1CT/10 SRP	10	10
PHL	EC18VEN	8718291204435	Halogen 18W E14 230V BXS35 1CT/10 SRP	10	10
PHL	E4086	8727900840575	TL-E 40W/865 1CT/12	12	12
PHL	E4084	8711500284747	TL-E 40W/840 1CT/12	12	12
PHL	E4083	8711500284761	TL-E 40W/830 1CT/12	12	12
PHL	E3286	8727900840551	TL-E 32W/865 1CT/12	12	12
PHL	E3284	8711500559685	TL-E 32W/840 1CT/12	12	12
PHL	E3283	8711500559678	TL-E 32W/830 1CT/12	12	12
PHL	E2286	8727900840537	TL-E 22W/865 1CT/12	12	12
PHL	E2284	8727900840506	TL-E 22W/840 1CT/12	12	12
PHL	CSLS50	8711500908087	CSLS 50 SDW-T 220-240V 50/60Hz	18	1
PHL	CSLS100	8711500908704	CSLS 100 SDW-T 220-240V 50/60Hz	18	1
PHL	CPOTW90	8711500211217	MST CosmoWh CPO-TW Xtra 90W/728 PGZ12	12	12
PHL	CPOTW60	8711500208514	MST CosmoWh CPO-TW Xtra 60W/728 PGZ12	12	12
PHL	CPOTW45	8718291150015	MST CosmoWh CPO-TW Xtra 45W/628 PGZ12	12	12
PHL	CPOTW140840	8718291137917	MST CosmoWh CPO-TW 140W/840 PGZ12 1CT	12	12
PHL	CPOTW140	8711500208538	MST CosmoWh CPO-TW Xtra 140W/728 PGZ12	12	12
PHL	CPOTTEXTRA90	8718291681151	MST CosmoWhite CPO-TT Xtra 90W/628 E40	12	12
PHL	CPOTTEXTRA140	8718291690320	MST CosmoWhite CPO-TT Xtra 140W/628 E40	12	12
PHL	CORESTICK75840	8718696814536	CorePro LED Stick ND 9.5-75W T38 E27 840	10	10
PHL	CORESTICK68830	8718696814512	CorePro LED Stick ND 9.5-68W T38 E27 830	10	10

PHL	CLAR806082736	8718696811832	CoreProLEDspot ND 4-60W R80 E27 827 36D	6	6
PHL	CLAR8010082736	8718696811856	CoreProLEDspot ND 8-100W R80 E27 827 36D	6	6
PHL	CORER7S60840C	8718696713969	CorePro LEDlinear ND 7.5-60W R7S 78mm840	10	10
PHL	CORER7S60830C	8718696713945	CorePro LEDlinear ND 7.5-60W R7S 78mm830	10	10
PHL	CORER7S60830	8718696522530	CorePro R7S 118mm 6.5-60W 830	10	10
PHL	CORER7S120840D	8718696714065	CorePro LED linear D 14-120W R7S 118 840	10	10
PHL	CORER7S120830D	8718696714003	CorePro LED linear D 14-120W R7S 118 830	10	10
PHL	CORER7S100840D	8718696578810	CorePro R7S 118mm 14-100W 840 D	10	10
PHL	CORER7S100830D	8718696578797	CorePro R7S 118mm 14-100W 830 D	10	10
PHL	COREPHIL60	8718291789505	LED 4.5W 500mm S14S WW ND 1CT/4	4	4
PHL	COREPHIL35	8718291789482	LED 3W 300mm S14S WW ND 1CT/4	4	4
PHL	CORELUS60E14	8718696703014	CorePro lustre ND 7-60W E14 827 P48 FR	10	10
PHL	CORELUS60865E14	8718696746875	CorePro lustre ND 7-60W E14 865 P48 FR	10	10
PHL	CORELUS60840E14	8718696703076	CorePro lustre ND 7-60W E14 840 P48 FR	10	10
PHL	CORELUS60840	8718696703090	CorePro lustre ND 7-60W E27 840 P48 FR	10	10
PHL	CORELUS60	8718696703038	CorePro lustre ND 7-60W E27 827 P48 FR	10	10
PHL	CORELUS40E14C	8718696454831	Corepro lustre ND 5.5-40W E14 827 P45 CL	10	10
PHL	CORELUS40E14	8718696474891	CorePro lustre ND 5.5-40W E14 827 P45 FR	10	10
PHL	CORELUS40C	8718696507636	Corepro Lustre ND 5.5-40W E27 827 P45 CL	10	10
PHL	CORELUS40865	8718696746837	CorePro lustre ND 5.5-40W E14 865 P45 FR	10	10
PHL	CORELUS40840C	8718696543443	Corepro lustre ND 5.5-40W E14 840 P45 CL	10	10
PHL	CORELUS40840	8718696543603	CorePro lustre ND 5.5-40W E14 840 P45 FR	10	10
PHL	CORELUS40	8718696507650	Corepro Lustre ND 5.5-40W E27 827 P45 FR	10	10
PHL	CORELUS25E14	8718291787037	CorePro lustre ND 4-25W E14 827 P45 FR	10	10
PHL	CORELUS25C	8718696507674	Corepro Lustre ND 4-25W E27 827 P45 CL	10	10
PHL	CORELUS25840	8718696543528	CorePro lustre ND 3.5-25W E14 840 P45 FR	10	10
PHL	CORELUS25	8718291787051	CorePro lustre ND 4-25W E27 827 P45 FR	10	10
PHL	COREHPL80840	8718699594404	TForce Core LED PT 30-27W E27 840 FR	4	4
PHL	COREHPL80830	8718699594381	TForce Core LED PT 30-27W E27 830 FR	4	4
PHL	COREHPL125840	8718699594442	TForce Core LED PT 50-42W E27 840 FR	4	4
PHL	COREHPL125830	8718699594428	TForce Core LED PT 50-42W E27 830 FR	4	4
PHL	COREHPI42840	8718699597184	TForce Core HB MV ND 50-42W E27 840	6	6
PHL	COREHPI42830	8718699597160	TForce Core HB MV ND 48-42W E27 830	6	6
PHL	COREHPI35840	8718699597344	TForce Core HB MV ND 40-35W E27 840	6	6
PHL	COREHPI35830	8718699597320	TForce Core HB MV ND 37-35W E27 830	6	6
PHL	COREHPI24840	8718699597306	TForce Core HB MV ND 28-24W E27 840	6	6
PHL	COREHPI24830	8718699597283	TForce Core HB MV ND 26-24W E27 830	6	6
PHL	COREGU42036	8718696708682	CorePro LED spot 2.6-20W 827 MR11 36D	12	12
PHL	COREG940830	8718696815281	CorePro LEDcapsule ND 3.2-40W G9 830	12	12
PHL	COREG940827	8718696815267	CorePro LEDcapsule ND 3.2-40W G9 827	12	12
PHL	COREG925830	8718696724231	CorePro LEDcapsule ND 1.9-25W G9 830	12	12
PHL	COREG925827D	8718696578698	CorePro LEDcapsuleMV 2.3-25W G9 827 D	12	12
PHL	COREG925827	8718696713921	CorePro LEDcapsule ND 1.9-25W G9 827	12	12
PHL	COREG63520830	8718696797693	CorePro LEDcapsuleLV 1.7-20W GY6.35 830	12	12

Signify Classified - Internal

PHL	COREG63520827	8718696797679	CorePro LEDcapsuleLV 1.7-20W GY6.35 827	12	12
PHL	COREG420830	8718696793084	CorePro LEDcapsuleLV 1.7-20W G4 830	12	12
PHL	COREG420827D	8718696578650	CorePro LEDcapsuleLV 2-20W G4 827 D	12	12
PHL	COREG420827	8718696793107	CorePro LEDcapsuleLV 1.7-20W G4 827	12	12
PHL	COREG410830	8718696793060	CorePro LEDcapsuleLV 0.9-10W G4 830	12	12
PHL	COREG410827	8718696793121	CorePro LEDcapsuleLV 0.9-10W G4 827	12	12
PHL	CORECAN60865	8718696746851	CorePro candle ND 7-60W E14 865 B38 FR	10	10
PHL	CORECAN60840	8718696703052	CorePro candle ND 7-60W E14 840 B38 FR	10	10
PHL	CORECAN60	8718696702994	CorePro candle ND 7-60W E14 827 B38 FR	10	10
PHL	CORECAN40E14C	8718696454794	Corepro candle ND 5.5-40W E14 827 B35 CL	10	10
PHL	CORECAN40865	8718696746813	CorePro candle ND 5.5-40W E14 865 B35 FR	10	10
PHL	CORECAN40840C	8718696543405	Corepro candle ND 5.5-40W E14 840 B35 CL	10	10
PHL	CORECAN40840	8718696543566	CorePro candle ND 5.5-40W E14 840 B35 FR	10	10
PHL	CORECAN40	8718291762386	CorePro candle ND 5.5-40W E14 827 B35 FR	10	10
PHL	CORECAN25E14C	8718696507575	Corepro Candle ND 4-25W E14 827 B35 CL	10	10
PHL	CORECAN25840	8718696543481	CorePro candle ND 3.5-25W E14 840 B35 FR	10	10
PHL	CORECAN25	8718291787013	CorePro candle ND 4-25W E14 827 B35 FR	10	10
PHL	CORE75865	8718696497586	CorePro LEDbulb ND 10-75W A60 E27 865	10	10
PHL	CORE75840	8718696510322	CorePro LEDbulb ND 10-75W A60 E27 840	10	10
PHL	CORE75830	8718696497524	CorePro LEDbulb ND 10.5-75W A60 E27 830	10	10
PHL	CORE75827D	8718696762745	CorePro LEDbulb D 11-75W A60 E27 827	10	10
PHL	CORE60865	8718696577851	CorePro LED bulb ND 7.5-60W A60 E27 865	10	10
PHL	CORE60840	8718696577776	CorePro LEDbulb ND 7.5-60W A60 E27 840	10	10
PHL	CORE60830	8718696577714	CorePro LEDbulb ND 7.5-60W A60 E27 830	10	10
PHL	CORE60827D	8718696762707	CorePro LEDbulb D 8.5-60W A60 E27 827	10	10
PHL	CORE58865UN	8718696801765	CorePro LEDtube UN 1500mm HO 23W865 T8	10	10
PHL	CORE58865HF	8718696592052	CorePro LEDtube HF 1500mm 20W865 T8 G	10	10
PHL	CORE58865	8718696710951	CorePro LEDtube 1500mm 20W 865	10	10
PHL	CORE58840UN	8718696801741	CorePro LEDtube UN 1500mm HO 23W840 T8	10	10
PHL	CORE58840HF	8718696592038	CorePro LEDtube HF 1500mm 20W840 T8 G	10	10
PHL	CORE58840	8718696710913	CorePro LEDtube 1500mm 20W 840	10	10
PHL	CORE58830UN	8718696801727	CorePro LEDtube UN 1500mm HO 23W830 T8	10	10
PHL	CORE40865	8718696577875	CorePro LED bulb ND 5-40W A60 E27 865	10	10
PHL	CORE40840	8718696577790	CorePro LEDbulb ND 5-40W A60 E27 840	10	10
PHL	CORE40830	8718696579930	CorePro LEDbulb ND 5-40W A60 E27 830	10	10
PHL	CORE40827D	8718696762660	CorePro LEDbulb D 5.5-40W A60 E27 827	10	10
PHL	CORE36865UN	8718696801703	CorePro LEDtube UN 1200mm HO 18W865 T8	10	10
PHL	CORE36865HF	8718696581292	CorePro LEDtube HF 1200mm 15W865 T8 G	10	10
PHL	CORE36865	8718696711095	CorePro LEDtube 1200mm 14.5W865	10	10
PHL	CORE36840UN	8718696801680	CorePro LEDtube UN 1200mm HO 18W840 T8	10	10
PHL	CORE36840HF	8718696581278	CorePro LEDtube HF 1200mm 15W840 T8 G	10	10
PHL	CORE36840	8718696711071	CorePro LEDtube 1200mm 14.5W840	10	10
PHL	CORE36830UN	8718696801666	CorePro LEDtube UN 1200mm HO 18W830 T8	10	10
PHL	CORE18865HF	8718696652190	CorePro LEDtube HF 600mm 9W865 T8 G	10	10

Signify Classified - Internal

PHL	CORE18865	8718696711057	CorePro LEDtube 600mm 8W865	10	10
PHL	CORE18840HF	8718696652176	CorePro LEDtube HF 600mm 9W840 T8 G	10	10
PHL	CORE18840	8718696711033	CorePro LEDtube 600mm 8W840	10	10
PHL	CORE150865	8718696813898	CorePro LED bulb ND 17.5-150W A67E27 865	6	6
PHL	CORE150840	8718696813874	CorePro LED bulb ND 17.5-150W A67E27 840	6	6
PHL	CORE150	8718696813850	CorePro LED bulb ND 19.5-150W A67E27 827	6	6
PHL	CORE120865	8718696701713	CorePro LEDbulb ND 18-120W A67 865 E27	10	10
PHL	CORE120840	8718696701690	CorePro LEDbulb ND 18-120W E27 840 A67	10	10
PHL	CORE120	8718696701676	CorePro LEDbulb ND 18.5-120W E27 827 A67	10	10
PHL	CORE100865	8718696577813	CorePro LEDbulb ND 12.5-100W A60 E27 865	10	10
PHL	CORE100840	8718696510308	CorePro LEDbulb ND 12.5-100W A60 E27 840	10	10
PHL	CORE100830	8718696577677	CorePro LEDbulb ND 13-100W A60 E27 830	10	10
PHL	CORE100827DA60	8718696816677	CorePro LEDbulb D 13.5-100W A60 E27 827	10	10
PHL	CLICKES53CL	8727900895834	Halogen MV Click 53W G9 230V CL 1CT	100	100
PHL	CLICKES42CLB1	8727900252910	Halogen MV Caps 42W G9 230V CL 1BC/10	10	10
PHL	CLICKES42CL	8727900864014	Halogen MV Click 42W G9 230V CL 1CT	100	100
PHL	CLICKES28CLB1	8727900252873	Halogen MV Caps 28W G9 230V CL 1BC/10	10	10
PHL	CLICKES28CL	8727900863987	Halogen MV Click 28W G9 230V CL 1CT	100	100
PHL	CLICKES18CL	8727900895773	Halogen MV Click 18W G9 230V CL 1CT	100	100
PHL	CLAGU535084036	8718696814796	CorePro LED spot ND 7-50W MR16 840 36D	10	10
PHL	CLAGU535083036	8718696814772	CorePro LED spot ND 7-50W MR16 830 36D	10	10
PHL	CLAGU535082736	8718696814710	CorePro LED spot ND 7-50W MR16 827 36D	10	10
PHL	CLAGU533584036	8718696710654	CorePro LED spot ND 5-35W MR16 840 36D	10	10
PHL	CLAGU533582736	8718696710630	CorePro LED spot ND 5-35W MR16 827 36D	10	10
PHL	CLAGU532082736	8718696710616	CorePro LED spot ND 3-20W MR16 827 36D	10	10
PHL	CLAGU109086560	8718696813379	Corepro LEDspot 730lm GU10 865 60D	10	10
PHL	CLAGU109084060	8718696813355	Corepro LEDspot 730lm GU10 840 60D	10	10
PHL	CLAGU109083060	8718696813331	Corepro LEDspot 670lm GU10 830 60D	10	10
PHL	CLAGU1070865120	8718696686928	Corepro LEDspot 550lm GU10 865 120D	10	10
PHL	CLAGU1070840120	8718696686904	Corepro LEDspot 550lm GU10 840 120D	10	10
PHL	CLAGU1070830120	8718696686881	Corepro LEDspot 550lm GU10 830 120D	10	10
PHL	CLAGU106584036	8718696743874	CorePro LEDspot 5-65W GU10 840 36D ND	10	10
PHL	CLAGU106583036	8718696743850	CorePro LEDspot 5-65W GU10 830 36D ND	10	10
PHL	CLAGU105086536	8718696728413	Corepro LEDspot 4.6-50W GU10 865 36D	10	10
PHL	CLAGU105084036D	8718696730249	CorePro LEDspot 5-50W GU10 840 36D DIM	10	10
PHL	CLAGU105084036	8718696728390	Corepro LEDspot 4.6-50W GU10 840 36D	10	10
PHL	CLAGU105083036D	8718696721391	CorePro LEDspot 5-50W GU10 830 36D DIM	10	10
PHL	CLAGU105083036	8718696728376	Corepro LEDspot 4.6-50W GU10 830 36D	10	10
PHL	CLAGU105082736D	8718696721377	CorePro LEDspot 5-50W GU10 827 36D DIM	10	10
PHL	CLAGU105082736	8718696752517	Corepro LEDspot 4.6-50W GU10 827 36D	10	10
PHL	CLAGU103584036D	8718696730225	CorePro LEDspot 4-35W GU10 840 36D DIM	10	10
PHL	CLAGU103584036	8718696728352	Corepro LEDspot 3.5-35W GU10 840 36D	10	10
PHL	CLAGU103583036D	8718696721353	CorePro LEDspot 4-35W GU10 830 36D DIM	10	10
PHL	CLAGU103583036	8718696728338	Corepro LEDspot 3.5-35W GU10 830 36D	10	10

PHL	CLAGU103582736D	8718696721339	CorePro LEDspot 4-35W GU10 827 36D DIM	10	10
PHL	CLAGU103582736	8718696752531	Corepro LEDspot 3.5-35W GU10 827 36D	10	10
PHL	CLAGU102584036	8718696728314	Corepro LEDspot 2.7-25W GU10 840 36D	10	10
PHL	CLAGU102583036	8718696728291	Corepro LEDspot 2.7-25W GU10 830 36D	10	10
PHL	CLAGU102582736	8718696752098	Corepro LEDspot 2.7-25W GU10 827 36D	10	10
PHL	CDOTT70PLUS	8718291120308	MASTER CityWh CDO-TT Plus 70W/828 E27	12	12
PHL	CDOTT50PLUS	8718291185611	MASTER CityWh CDO-TT Plus 50W/828 E27	12	12
PHL	CDOTT250PLUS	8718291121978	MASTER CityWh CDO-TT Plus 250W/830 E40	12	12
PHL	CDOTT150PLUS	8718291120346	MASTER CityWh CDO-TT Plus 150W/828 E40	12	12
PHL	CDOTT100PLUS	8718291120322	MASTER CityWh CDO-TT Plus 100W/828 E40	12	12
PHL	CDOET70PLUS	8718291158752	MASTER CityWh CDO-ET Plus 70W/828 E27	24	24
PHL	CDOET150PLUS	8718291158813	MASTER CityWh CDO-ET Plus 150W/828 E40	12	12
PHL	CDOET100PLUS	8718291158776	MASTER CityWh CDO-ET Plus 100W/828 E40	12	12
PHL	CDMTP70830	8711500201270	MASTERC CDM-TP 70W/830 PG12-2 1CT/12	12	12
PHL	CDMTP150942	8711500201119	MASTERC CDM-TP 150W/942 PGX12-2 1CT/12	12	12
PHL	CDMTP150830	8711500201256	MASTERC CDM-TP 150W/830 PGX12-2 1CT/12	12	12
PHL	CDMTMW360	8718696646106	MASTERColour CDM-T MW eco 360W/842 E40	12	12
PHL	CDMTMW230	8718696596814	MASTERColour CDM-T MW eco 230W/842 E40	12	12
PHL	CDMTMGU6520	8727900890839	MC CDM-Tm Elite Mini 20W/830 GU6.5 1CT	12	12
PHL	CDMTM35930	8711500211491	MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12	12	12
PHL	CDMTM20830	8711500207517	MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12	12	12
PHL	CDMTD70942	8711500200020	MASTERC CDM-TD 70W/942 RX7s 1CT/12	12	12
PHL	CDMTD70	8711500197825	MASTERC CDM-TD 70W/830 RX7s 1CT/12	12	12
PHL	CDMTD150942	8711500200259	MASTERC CDM-TD 150W/942 RX7s 1CT	12	12
PHL	CDMTD150	8711500197849	MASTERC CDM-TD 150W/830 RX7s 1CT	12	12
PHL	CDMTC70842	8711500212757	MASTERC CDM-TC 70W/842 G8.5 1CT/12	12	12
PHL	CDMTC35842	8711500209573	MASTERC CDM-TC 35W/842 G8.5 1CT/12	12	12
PHL	CDMTC2083	8727900871586	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	12	12
PHL	CDMT35842	8711500211262	MASTERC CDM-T 35W/842 G12 1CT/12	12	12
PHL	CDMT250942	8711500211125	MASTERC CDM-T 250W/942 G12 1CT/12	12	12
PHL	CDMT250	8711500208019	MASTERC CDM-T 250W/830 G12 1CT/12	12	12
PHL	CDMT20	8727900871562	MASTERC CDM-T Elite 20W/830 G12 1CT/12	12	12
PHL	CDMRM3540942	8718291691815	CDM-Rm Elite Mini 35W/942 GX10 MR16 40D	12	12
PHL	CDMRM3540	8718291163060	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	12	12
PHL	CDMRM3525942	8718291691792	CDM-Rm Elite Mini 35W/942 GX10 MR16 25D	12	12
PHL	CDMRM3525	8718291163008	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D	12	12
PHL	CDMRM3510942	8718291691778	CDM-Rm Elite Mini 35W/942 GX10 MR16 10D	12	12
PHL	CDMRM3510	8718291162964	CDM-Rm Elite Mini 35W/930 GX10 MR16 10D	12	12
PHL	CDMRM2040	8718291203032	CDM-Rm Elite Mini 20W/830 GX10 MR16 40D	12	12
PHL	CDMRM2025	8718291203018	CDM-Rm Elite Mini 20W/830 GX10 MR16 25D	12	12
PHL	CDMRM2010	8718291202745	CDM-Rm Elite Mini 20W/830 GX10 MR16 10D	12	12
PHL	CDMEMW360P	8718696734810	MSTColour CDM-EP MW eco 360W/840 E40 CL	6	6
PHL	CDMEMW360	8718696595688	MASTERColour CDM-E MW eco 360W/842 E40	12	12
PHL	CDMEMW230P	8718696734797	MSTColour CDM-EP MW eco 230W/840 E40 CL	12	12

PHL	CDMEMW230	8718696596647	MASTERColour CDM-E MW eco 230W/842 E40	12	12
PHL	CAPS7G4	8718696827864	Caps 3000h 7W G4 12V CL 1CT/10x10F	100	1
PHL	CAPS25GY6	8718696827802	Caps 3000h 25W GY6.35 12V CL 1CT/10x10F	100	1
PHL	CAPS14GY6	8718696827772	Caps 3000h 14W GY6.35 12V CL 1CT/10x10F	100	1
PHL	CAPS14G4	8718696827741	Caps 3000h 14W G4 12V CL 1CT/10x10F	100	1
PHL	BSX91H96	8711500920393	BSX 91 H96 220-240V 50Hz CW-149/67	8	1
PHL	BSX90L40	8711500919939	BSX 90 L40 230V 50Hz HD1-118	6	1
PHL	BSX90H26	8711500919908	BSX 90 H26 220-230V 50Hz CW-173/52	10	1
PHL	BSX55H26	8711500919960	BSX 55 H26 220-230V 50Hz CW-173/44	12	1
PHL	BSX36H66	8711500920034	BSX 36 H66 240V 50Hz CW-173/44	12	1
PHL	BSX3555L82	8711500920539	BSX 35/55 L82 240V 50Hz BC0-196	24	1
PHL	BSX135	8711500920072	BSX 135 H96 220-240V 50Hz CW-149/67	8	1
PHL	BSX131	8711500919786	BSX 131 H96 220-240V 50Hz CW-178/78	4	1
PHL	BSN70L33TS	8711500059680	BSN 70 L33-A2-TS 230V 50Hz HD1-118	6	1
PHL	BSN70K302ITS	8718696740828	BSN 70 K302-A2-ITS 230V 50Hz	6	6
PHL	BSN70100K302TS	8718696741122	BSN 100/70 K302-A2-TS 230V 50Hz	6	6
PHL	BSN50K302ITS	8718696740781	BSN 50 K302-A2-ITS 230V 50Hz	6	6
PHL	BSN5070K302TS	8718696741108	BSN 70/50 K302-A2-TS 230V 50Hz	6	6
PHL	BSN400TS	8711500059765	BSN 400 L33-A2-TS 230V 50Hz HD3-166	4	1
PHL	BSN400K407ITS	8727900887044	BSN 400 K407-A2-ITS 230/240V 50Hz BC3	2	2
PHL	BSN250TS	8718696741085	BSN 250 L33-A2-TS 230V 50Hz	6	6
PHL	BSN250K302ITS	8718696741023	BSN 250 K302-A2-ITS 230V 50Hz	6	6
PHL	BSN150TS	8718696741009	BSN 150 L33-A2-TS 230V 50Hz	6	6
PHL	BSN150K302ITS	8718696740965	BSN 150 K302-A2-ITS 230V 50Hz	6	6
PHL	BSN100TS	8718696740941	BSN 100 L33-A2-TS 230V 50Hz	6	6
PHL	BSN100K302ITS	8718696740866	BSN 100 K302-A2-ITS 230V 50Hz	6	6
PHL	BSN100150K302TS	8718696741146	BSN 150/100 K302-A2-TS 230V 50Hz	6	6
PHL	BSN1000L78	8711500062369	BSN 1000 L78-A2 230/240V 50Hz HP-257	1	1
PHL	BSL100K202	8718696740767	BSL 100 K202-A2-TS 230V 50Hz	6	1
PHL	BRILL35GU4	8718699591397	Brill EC 35W GU4 12V 30D 1CT/10X5F	50	1
PHL	BRILL20GU4	8718699591373	Brill EC 20W GU4 12V 30D 1CT/10X5F	50	1
PHL	BMH70K302ITS	8718696740743	BMH 70 K302-A2-ITS 230V 50Hz	6	6
PHL	BMH35K302ITS	8718696740682	BMH 35 K302-A2-ITS 230V 50Hz	6	6
PHL	BHL400K307	8727900887037	BHL 400 K307-A2 230/240V 50Hz BC2-160	6	1
PHL	BHL400K202	8727900940763	BHL 400 K202-A2 230V 50Hz BC2-151	6	1
PHL	BHL400	8711500919533	BHL 400 L40-A2 230V 50Hz HD2-151	6	1
PHL	BHL250K307	8727900887013	BHL 250 K307-A2 230/240V 50Hz BC2-134	6	6
PHL	BHL250K202	8727900940640	BHL 250 K202-A2 230V 50Hz BC2-126	6	1
PHL	BHL250	8711500919502	BHL 250 L40-A2 230V 50Hz HD2-126	6	1
PHL	BHL2000L76	8711500063847	BHL 2000 L76-A2 380/400/415V 50Hz HP-317	1	1
PHL	BHL1000L78	8711500062376	BHL 1000 L78-A2 230/240V 50Hz HP-207	1	1
PHL	BHL1000L02	8711500062314	BHL 1000 L02-A2 220V 50Hz HP-207	1	1
PHL	BHD2000L76	8711500742766	BHD 2000 L76-A2 380/400/415V 50Hz HP-317	1	1
PHL	AUTOTOR15	8727900844481	Tornado T2 Autom 15W WW E27 1PF/6	6	6

Signify Classified - Internal

PHL	ATLEDTWIST65CW	8710619391698	ATR LED 65W GU10 CW 36D ND 1BC/6	6	6
PHL	ATLEDTWIST65	8710619391674	ATR LED 65W GU10 WW 36D ND 1BC/6	6	6
PHL	ATLEDTWIST50CW	8710619391551	ATR LED 50W GU10 CW 36D ND 1BC/6	6	6
PHL	ATLEDTWIST50	8710619391490	ATR LED 50W GU10 WW 36D ND 1BC/6	6	6
PHL	ATLEDTWIST35CW	8710619391452	ATR LED 35W GU10 CW 36D ND 1BC/6	6	6
PHL	ATLEDTWIST35	8710619391391	ATR LED 35W GU10 WW 36D ND 1BC/6	6	6
PHL	ATLEDTWIST25CW	8710619391377	ATR LED 25W GU10 CW 36D ND 1BC/6 SRT	6	6
PHL	ATLEDTWIST25	8710619391353	ATR LED 25W GU10 WW 36D ND 1BC/6 SRT	6	6
PHL	ATLEDSF40SME27	8710619391032	ATR LED 40W P45 E27 WW FR ND 1BC/6 SRP	6	6
PHL	ATLEDSF40SME14	8710619391018	ATR LED 40W P45 E14 WW FR ND 1BC/6 SRP	6	6
PHL	ATLEDSF25SME27	8710619390837	ATR LED 25W P45 E27 WW FR ND 1BC/6 SRP	6	6
PHL	ATLEDSF25SME14	8710619390851	ATR LED 25W P45 E14 WW FR ND 1BC/6 SRP	6	6
PHL	ATLEDSF25CL	8710619390875	ATR LED 25W P45 E14 WW CL ND 1BC/6 SRP	6	6
PHL	ATLEDOL40SM	8710619390776	ATR LED 40W B35 E14 WW FR ND 1BC/6 SRP	6	6
PHL	ATLEDOL25SM	8710619390677	ATR LED 25W B35 E14 WW FR ND 1BC/6 SRP	6	6
PHL	ATLEDOL25CL	8710619390691	ATR LED 25W B35 E14 WW CL ND 1BC/6 SRP	6	6
PHL	ATLEDDIC35	8710619391810	ATR LED 35W GU5.3 WW 12V 36D ND 1BC/6	6	6
PHL	ATLEDDIC20	8710619391759	ATR LED 20W GU5.3 WW 12V 36D ND 1BC/6	6	6
PHL	ATLED75SMCW	8710619390615	ATR LED 75W A60 E27 CW FR ND 1BC/6	6	6
PHL	ATLED75SM	8710619390592	ATR LED 75W A60 E27 WW FR ND 1BC/6	6	6
PHL	ATLED60SMCW	8710619390493	ATR LED 60W A60 E27 CW FR ND 1BC/6 G3	6	6
PHL	ATLED60SM	8710619390479	ATR LED 60W A60 E27 WW FR ND 1BC/6	6	6
PHL	ATLED40SMCW	8710619390417	ATR LED 40W A60 E27 CW FR ND 1BC/6 SRP	6	6
PHL	ATLED40SM	8710619390394	ATR LED 40W A60 E27 WW FR ND 1BC/6 SRP	6	6
PHL	ATLED3G9B1	8710619365989	ATR LED 25W G9 WW ND 1BC/8 SRP	8	8
PHL	ATLED20G4	8710619391315	ATR LED 20W G4 WW 12V ND 1BC/8	8	8
PHL	ATLED100SMCW	8710619390233	ATR LED 100W A67 E27 CW FR ND 1BC/6	6	6
PHL	ATLED100SM	8710619390196	ATR LED 100W A67 E27 WW FR ND 1BC/6 SRP	6	6
PHL	8LG420WH	8718696793282	LED 20W G4 WH 12V ND RF 1BC/6	6	6
PHL	8LG410WH	8718696793268	LED 10W G4 WH 12V ND RF 1BC/6	6	6
PHL	8LFILVEN35GD	8718696814130	LED classic 32W BA35 E14 2200K GOLD SRT4	4	4
PHL	8LFILST6460WG	8718696810712	LED classic 60W ST64 E27 WW CL WGD SRT4	4	4
PHL	8LFILSF35GD	8718696814154	LED classic 32W P45 E14 2200K GOLD SRT4	4	4
PHL	8LFILSF35E27GD	8718696814116	LED classic 32W P45 E27 2200K GOLD SRT4	4	4
PHL	8LFILOL35GD	8718696814093	LED classic 32W B35 E14 2200K GOLD SRT4	4	4
PHL	8LFIL60WGD	8718696810675	LED classic 60W A60 E27 WW CL WGD SRT4	4	4
PHL	8LDIC50WWD	8718696815526	LED 50W MR16 WW 36D D 1SRT4	4	4
PHL	8LDIC50CW	8718696813973	LED 50W MR16 CW 36D ND 1SRT4	4	4
PHL	8LDIC50	8718696813959	LED 50W MR16 WW 36D ND SRT4	4	4
PHL	8LDIC35WG	8718696815403	LED 35W GU5.3 WW 12V 36D WGD 1SRT4	4	4
PHL	8L60R80B1	8718696813232	LED CLA 60W R80 E27 WW 36D ND RF SRT4	4	4
PHL	8L60R63DMB1	8718696811597	LED CLA 60W R63 E27 WW 36D D SRT4	4	4
PHL	8L60R50D	8718696811559	LED CLA 60W R50 E14 WW 36D D SRT4	4	4
PHL	8L40R63B1	8718696811573	LED CLA 40W R63 E27 WW 36D ND SRT4	4	4

Signify Classified - Internal

PHL	8L40R50B1	8718696811474	LED CLA 40W R50 E14 WW 36D ND SRT4	4	4
PHL	8L30R39B1	8718696811412	LED CLA 30W R39 E14 WW 36D ND SRT4	4	4
PHL	8L150SMCW	8718696813812	LED 150W A67 E27 CW 230V FR ND 1PF/6	6	6
PHL	8L150SMCDL	8718696813836	LED 150W A67 E27 CDL 230V FR ND 1PF/6	6	6
PHL	8L150SM	8718696813799	LED 150W A67 E27 WW 230V FR ND 1PF/6	6	6
PHL	8L100SMDIM	8718696814987	LED 100W A60 E27 WW FR WGD SRT4	4	4
PHL	8L100R80B1	8718696813256	LED CLA 100W R80 E27 WW 36D ND RF SRT4	4	4
PHL	884	8711500716422	MST TL Mini 8W/840 FAM/10X25BOX	250	25
PHL	883	8711500716385	MST TL Mini 8W/830 FAM/10X25BOX	250	25
PHL	882	8711500704740	MST TL Mini 8W/827 FAM/10X25BOX	250	25
PHL	854	8711500716286	TL Mini 8W/54-765 FAM/10X25BOX	250	25
PHL	833	8711500704733	TL Mini 8W/33-640 FAM/10X25BOX	250	25
PHL	810N	8711500260420	Actinic BL TL 8W/10 1FM/10X25CC	250	25
PHL	80ESCOMPLUS	8727900852288	Plusline 78mm 2y 80W R7s 230V 1BB	100	10
PHL	8084HOSEC	8711500952356	MASTER TL5 HO Secura 80W/840 UNP/40	40	40
PHL	8084HO	8711500644381	MASTER TL5 HO 80W/840 UNP/40	40	40
PHL	7084NG	8711500615923	MASTER TL-D Super 80 70W/840 SLV/25	25	25
PHL	684	8711500893420	MST TL Mini 6W/840 FAM/10X25BOX	250	25
PHL	6439	8718696666906	Alu 50W 12V R56 25D CL 1CT/10X5F	50	50
PHL	6438	8718696666876	Alu 50W 12V R56 10D CL 1CT/10X5F	50	50
PHL	6435	8718696666784	Alu 20W 12V R37 32D CL 1CT/10X5F	50	50
PHL	6434	8718696666753	Alu 20W 12V R37 18D CL 1CT/10X5F	50	50
PHL	6433	8718696666814	Alu 20W 12V R37 6D CL 1CT/10X5F	50	50
PHL	633	8711500715838	TL Mini 6W/33-640 FAM/10X25BOX	250	25
PHL	610N	8711500260390	Actinic BL TL 6W/10 1FM/10X25CC	250	25
PHL	6050	8711500101884	Stan ELV 60W E27/BRC 50V A60 CL 1CT	120	120
PHL	6024	8711500090188	Stan ELV 60W E27/BRC 24V A60 CL 1CT/20	20	20
PHL	6012	8711500090171	Stan ELV 60W E27/BRC 12V A60 CL 1CT/20	20	20
PHL	6010R	8711500615725	TL 60W/10-R SLV/25	25	25
PHL	5896PRO	8711500888730	MASTER TL-D 90 De Luxe 58W/965 SLV/10	10	10
PHL	5896GRA	8711500888778	MASTER TL-D 90 Graphica 58W/965 SLV/10	10	10
PHL	5895PRO	8711500888716	MASTER TL-D 90 De Luxe 58W/950 SLV/10	10	10
PHL	5895GRA	8711500888754	MASTER TL-D 90 Graphica 58W/950 SLV/10	10	10
PHL	5894PRO	8711500888693	MASTER TL-D 90 De Luxe 58W/940 SLV/10	10	10
PHL	5893PRO	8711500888679	MASTER TL-D 90 De Luxe 58W/930 SLV/10	10	10
PHL	5886XTRA	8711500892850	MASTER TL-D Xtra 58W/865 SLV	25	25
PHL	5886NG	8711500632258	MASTER TL-D Super 80 58W/865 1SL/25	25	25
PHL	5884XTREMESEC	8711500889874	MASTER TL-D Xtreme Secura 58W/840 SLV/25	25	25
PHL	5884SV	8711500610294	MASTER TL-D Super 80 58W/840 UNP/25	25	25
PHL	5884SEC	8711500640185	MASTER TL-D Secura 58W/840 SLV/25	25	25
PHL	5883NG	8711500632135	MASTER TL-D Super 80 58W/830 1SL/25	25	25
PHL	5882NG	8711500632104	MASTER TL-D Super 80 58W/827 1SL/25	25	25
PHL	5879	8711500706232	MASTER TL-D Food 58W/79 SLV/25	25	25
PHL	5818B	8711500954510	TL-D Colored 58W Blue 1SL/25	25	25

Signify Classified - Internal

PHL	5817V	8711500954497	TL-D Colored 58W Green 1SL/25	25	25
PHL	5816G	8711500954473	TL-D Colored 58W Yellow 1SL/25	25	25
PHL	5815R	8711500954459	TL-D Colored 58W Red 1SL/25	25	25
PHL	5484HO	8711500637406	MASTER TL5 HO 54W/840 UNP/40	40	40
PHL	5483HO	8711500637345	MASTER TL5 HO 54W/830 UNP/40	40	40
PHL	5186ECO	8711500264725	MASTER TL-D Eco 51W/865 SLV/25	25	25
PHL	5184ECO	8711500264701	MASTER TL-D Eco 51W/840 1SL/25	25	25
PHL	5183ECO	8711500264664	MASTER TL-D Eco 51W/830 SLV/25	25	25
PHL	5084NG	8711500631596	MASTER TL-D HF Super 80 50W/840 SLV/25	25	25
PHL	5083NG	8711500631565	MASTER TL-D HF Super 80 50W/830 SLV/25	25	25
PHL	500DEGL	8711500491268	HaIA IDE 500W E40 230V CL 1CT/6	6	6
PHL	4984HO	8711500637581	MASTER TL5 HO 49W/840 UNP/40	40	40
PHL	48ESCOMPLUS	8727900852318	Plusline 78mm 2y 48W R7s 230V 1BB	100	10
PHL	433	8711500615688	TL Mini 4W/33-640 FAM/10X25BOX	250	25
PHL	4024	8711500022936	Stan ELV 40W E27/BRC 24V A60 CL 1CT	120	120
PHL	400ESPLUS	8727900853896	Plusline 118mm 2y 400W R7s 230V 1BB	100	10
PHL	3984HO	8711500637222	MASTER TL5 HO 39W/840 UNP/40	40	40
PHL	3884NG	8711500558831	MASTER TL-D Super 80 38W/840 SLV/25	25	25
PHL	3696PRO	8711500888624	MASTER TL-D 90 De Luxe 36W/965 SLV/10	10	10
PHL	3696GRA	8711500888365	MASTER TL-D 90 Graphica 36W/965 SLV/10	10	10
PHL	3695PRO	8711500888600	MASTER TL-D 90 De Luxe 36W/950 SLV/10	10	10
PHL	3695GRA	8711500888648	MASTER TL-D 90 Graphica 36W/950 SLV/10	10	10
PHL	3694PRO	8711500888587	MASTER TL-D 90 De Luxe 36W/940 SLV/10	10	10
PHL	3693PRO	8711500888563	MASTER TL-D 90 De Luxe 36W/930 SLV/10	10	10
PHL	3686XTRA	8711500892836	MASTER TL-D Xtra 36W/865 SLV	25	25
PHL	3686NG	8711500632074	MASTER TL-D Super 80 36W/865 1SL/25	25	25
PHL	36861MNG	8727900917390	MASTER TL-D Super 80 1m 36W/865 1SL/25	25	25
PHL	3684XTREME	8711500558688	MASTER TL-D Xtreme 36W/840 SLV	25	25
PHL	3684XTRA	8711500558763	MASTER TL-D Xtra 36W/840 SLV/25	25	25
PHL	3684SV	8711500610188	MASTER TL-D Super 80 36W/840 UNP/25	25	25
PHL	3684NG	8711500632012	MASTER TL-D Super 80 36W/840 1SL/25	25	25
PHL	36841MNG	8711500558770	MASTER TL-D Super 80 1m 36W/840 SLV/25	25	25
PHL	3683XTREME	8711500558664	MASTER TL-D Xtreme 36W/830 SLV	25	25
PHL	3683XTRA	8711500558718	MASTER TL-D Xtra 36W/830 SLV/25	25	25
PHL	3683NG	8711500631954	MASTER TL-D Super 80 36W/830 1SL/25	25	25
PHL	36831MNG	8711500558749	MASTER TL-D Super 80 1m 36W/830 SLV/25	25	25
PHL	3682NG	8711500631923	MASTER TL-D Super 80 36W/827 1SL/25	25	25
PHL	3679	8711500706225	MASTER TL-D Food 36W/79 SLV/25	25	25
PHL	3618B	8711500727541	TL-D Colored 36W Blue 1SL/25	25	25
PHL	3617V	8711500643001	TL-D Colored 36W Green 1SL/25	25	25
PHL	3616G	8711500727510	TL-D Colored 36W Yellow 1SL/25	25	25
PHL	3615R	8711500727480	TL-D Colored 36W Red 1SL/25	25	25
PHL	3608	8711500951151	TL-D 36W BLB 1SL/25	25	25
PHL	3584SEC	8711500952196	MASTER TL5 HE Secura 35W/840 UNP/40	40	40

Signify Classified - Internal

PHL	3584	8711500611055	MASTER TL5 HE 35W/840 UNP/40	40	40
PHL	3583	8711500611031	MASTER TL5 HE 35W/830 UNP/40	40	40
PHL	3286ECO	8711500264640	MASTER TL-D Eco 32W/865 SLV/25	25	25
PHL	3284NG	8711500631534	MASTER TL-D HF Super 80 32W/840 SLV/25	25	25
PHL	3284ECO	8711500264626	MASTER TL-D Eco 32W/840 SLV/25	25	25
PHL	3283NG	8711500631503	MASTER TL-D HF Super 80 32W/830 SLV/25	25	25
PHL	3283ECO	8711500264589	MASTER TL-D Eco 32W/830 SLV/25	25	25
PHL	3086NG	8711500631893	MASTER TL-D Super 80 30W/865 SLV/25	25	25
PHL	3084NG	8711500631862	MASTER TL-D Super 80 30W/840 1SL/25	25	25
PHL	3083NG	8711500631831	MASTER TL-D Super 80 30W/830 1SL/25	25	25
PHL	3082NG	8711500631800	MASTER TL-D Super 80 30W/827 SLV/25	25	25
PHL	3079	8711500706249	MASTER TL-D Food 30W/79 SLV/25	25	25
PHL	300PAR56FL	8711500159618	PAR56 300W GX16d 230V FL 1CT/6	6	6
PHL	30012PAR56FL	8711500159694	PAR56 300W Multipurpose 12V UW 1CT/8	8	8
PHL	2884	8711500610904	MASTER TL5 HE 28W/840 UNP/40	40	40
PHL	2883	8711500610812	MASTER TL5 HE 28W/830 UNP/40	40	40
PHL	25T25MWB1	8711500250025	Appl 25W E14 230-240V T25 CL MWO 1BL/10	10	10
PHL	25T25F	8711500038715	App 25W E14 230-240V T25 CL OV 1CT	100	100
PHL	2484HO	8711500637048	MASTER TL5 HO 24W/840 UNP/40	40	40
PHL	240ESPLUS	8727900853803	Plusline 118mm 2y 240W R7s 230V 1BB	100	10
PHL	2386NG	8727900917376	MASTER TL-D Super 80 23W/865 1SL/25	25	25
PHL	2384NG	8711500558701	MASTER TL-D Super 80 23W/840 SLV/25	25	25
PHL	2383NG	8711500558633	MASTER TL-D Super 80 23W/830 SLV/25	25	25
PHL	2184	8711500610720	MASTER TL5 HE 21W/840 UNP/40	40	40
PHL	20T22CUCB1	8711500249975	Appl 20W E14 230-240V T22 CL SM 1BL/10	10	10
PHL	20T22	8711500250230	Appl 20W B15d 230V T22X51 - CL SM - 1CT	100	100
PHL	2052N	8711500643025	TL 20W/52 SLV/25	25	25
PHL	1896PRO	8711500888464	MASTER TL-D 90 De Luxe 18W/965 SLV/10	10	10
PHL	1896GRA	8711500888525	MASTER TL-D 90 Graphica 18W/965 SLV/10	10	10
PHL	1895PRO	8711500888433	MASTER TL-D 90 De Luxe 18W/950 SLV/10	10	10
PHL	1895GRA	8711500888501	MASTER TL-D 90 Graphica 18W/950 SLV/10	10	10
PHL	1894PRO	8711500888396	MASTER TL-D 90 De Luxe 18W/940 SLV/10	10	10
PHL	1893PRO	8711500888372	MASTER TL-D 90 De Luxe 18W/930 SLV/10	10	10
PHL	1886XTREME	8711500892751	MASTER TL-D Xtreme 18W/865 SLV	25	25
PHL	1886NG	8711500631770	MASTER TL-D Super 80 18W/865 1SL/25	25	25
PHL	1884XTREME	8711500544964	MASTER TL-D Xtreme 18W/840 SLV	25	25
PHL	1884XTRA	8711500558626	MASTER TL-D Xtra 18W/840 SLV/25	25	25
PHL	1884SV	8711500610126	MASTER TL-D Super 80 18W/840 UNP/25	25	25
PHL	1884SEC	8711500640109	MASTER TL-D Secura 18W/840 SLV/25	25	25
PHL	1884NG	8711500631718	MASTER TL-D Super 80 18W/840 1SL/25	25	25
PHL	1883XTREME	8711500544926	MASTER TL-D Xtreme 18W/830 SLV	25	25
PHL	1883NG	8711500631657	MASTER TL-D Super 80 18W/830 1SL/25	25	25
PHL	1882NG	8711500631626	MASTER TL-D Super 80 18W/827 1SL/25	25	25
PHL	1879	8711500706218	MASTER TL-D Food 18W/79 SLV/25	25	25

Signify Classified - Internal

PHL	1818B	8711500726902	TL-D Colored 18W Blue 1SL/25	25	25
PHL	1817V	8711500642981	TL-D Colored 18W Green 1SL/25	25	25
PHL	1816G	8711500726872	TL-D Colored 18W Yellow 1SL/25	25	25
PHL	1815R	8711500726841	TL-D Colored 18W Red 1SL/25	25	25
PHL	1810SEC	8727900853834	Actinic BL TL-D 18W/10 Secura 1SL/25	25	25
PHL	1808	8711500951113	TL-D 18W BLB 1SL/25	25	25
PHL	1686ECO	8711500268716	MASTER TL-D Eco 16W/865 SLV/25	25	25
PHL	1684NG	8711500631473	MASTER TL-D HF Super 80 16W/840 SLV/25	25	25
PHL	1684ECO	8711500268617	MASTER TL-D Eco 16W/840 SLV/25	25	25
PHL	1683NG	8711500631442	MASTER TL-D HF Super 80 16W/830 SLV/25	25	25
PHL	1683ECO	8711500268570	MASTER TL-D Eco 16W/830 SLV/25	25	25
PHL	160ESPLUS	8727900852196	Plusline 118mm 2y 160W R7s 230V 1BB	100	10
PHL	15T22FORB2	8711500249517	App 15W E14 230-240V T22 CL OV 2BL/10	10	10
PHL	15T22F	8711500036599	App 15W E14 230-240V T22 CL OV 1CT	100	100
PHL	1586	8727900917314	MASTER TL-D Super 80 15W/865 1SL/25	25	25
PHL	1584	8711500702807	MASTER TL-D Super 80 15W/840 SLV/25	25	25
PHL	1583	8711500702791	MASTER TL-D Super 80 15W/830 SLV/25	25	25
PHL	1582	8711500702784	MASTER TL-D Super 80 15W/827 SLV/25	25	25
PHL	15220T25	8711500038517	Appl 15W E14 230-240V T25 CL RF 1CT	100	100
PHL	1510T5	8711500951489	Actinic BL TL MINI 15W/10 /10X25CC	250	25
PHL	1510SEC	8711500898586	Actinic BL TL-D 15W/10 Secura 1SL/25	25	25
PHL	1510N	8711500710932	Actinic BL TL-D 15W/10 1SL/25	25	25
PHL	1500PLUS	8711500494351	Plusline L 1500W R7s 230V 1CT/10	10	10
PHL	1484NG	8711500953810	MASTER TL-D Super 80 14W/840 SLV/25	25	25
PHL	1484	8711500610669	MASTER TL5 HE 14W/840 UNP/40	40	40
PHL	1483	8711500610638	MASTER TL5 HE 14W/830 UNP/40	40	40
PHL	14743ES	8711500411136	MASTERLine 111 60W G53 12V 45D 1CT/6	6	6
PHL	14742ES	8711500411150	MASTERLine 111 60W G53 12V 24D 1CT/6	6	6
PHL	14740ES	8711500411099	MASTERLine 111 45W G53 12V 45D 1CT/6	6	6
PHL	14739ES	8711500411075	MASTERLine 111 45W G53 12V 24D 1CT/6	6	6
PHL	14738ES	8711500411051	MASTERLine 111 45W G53 12V 8D 1CT/6	6	6
PHL	14737ES	8711500411037	MASTERLine 111 30W G53 12V 24D 1CT/6	6	6
PHL	14736ES	8711500411013	MASTERLine 111 30W G53 12V 8D 1CT/6	6	6
PHL	14717	8711500430793	BrillIAI 50W GU5.3 12V MR16 36D 1CT/10X5F	50	5
PHL	14716	8711500430755	BrillIAI 35W GU5.3 12V MR16 36D 1CT/10X5F	50	5
PHL	14715	8711500430724	BrillIAI 20W GU5.3 12V MR16 36D 1CT/10X5F	50	5
PHL	14621	8711500425195	Brill 50W GU5.3 12V 60D 1CT/10X5F	50	5
PHL	14620	8711500425164	Brill 50W GU5.3 12V 36D 1CT/10X5F	50	5
PHL	14616	8711500425041	Brill 35W GU5.3 12V 36D 1CT/10X5F	50	5
PHL	14615	8711500424938	Brill 35W GU5.3 12V 24D 1CT/10X5F	50	5
PHL	14613	8711500424877	Brill 20W GU5.3 12V 60D 1CT/10X5F	50	5
PHL	14612	8711500424846	Brill 20W GU5.3 12V 36D 1CT/10X5F	50	5
PHL	14611	8711500424716	Brill 20W GU5.3 12V 24D 1CT/10X5F	50	5
PHL	14600ACC4Y	8718696588451	Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F	50	50

Signify Classified - Internal

PHL	14598ACC4Y	8718696588420	Accent 35W 4000h GU5.3 12V 36D 1CT/10X5F	50	50
PHL	14596ACC4Y	8718696588390	Accent 20W 4000h GU5.3 12V 36D 1CT/10X5F	50	50
PHL	14591ES	8711500424471	MASTERL ES 45W GU5.3 12V 60D 1CT/4X5F	20	20
PHL	14590ES	8711500424440	MASTERL ES 45W GU5.3 12V 36D 1CT/4X5F	20	20
PHL	14587ES	8711500424358	MASTERL ES 35W GU5.3 12V 60D 1CT/4X5F	20	20
PHL	14586ES	8711500424327	MASTERL ES 35W GU5.3 12V 36D 1CT/4X5F	20	20
PHL	14585ES	8711500413970	MASTERL ES 35W GU5.3 12V 24D 1CT/4X5F	20	20
PHL	14582ES	8711500413789	MASTERL ES 30W GU5.3 12V 36D 1CT/4X5F	20	20
PHL	14581ES	8711500413758	MASTERL ES 30W GU5.3 12V 24D 1CT/4X5F	20	20
PHL	14579ES	8711500413673	MASTERL ES 20W GU5.3 12V 36D 1CT/4X5F	20	20
PHL	14003	8711500720948	TL 140W/03	25	25
PHL	1384	8711500716859	MST TL Mini 13W/840 FAM/10X25BOX	250	25
PHL	1383	8711500716811	MST TL Mini 13W/830 FAM/10X25BOX	250	25
PHL	1382	8711500704764	MST TL Mini 13W/827 FAM/10X25BOX	250	25
PHL	1354	8711500716712	TL Mini 13W/54-765 FAM/10X25BOX	250	25
PHL	1333	8711500704757	TL Mini 13W/33-640 FAM/10X25BOX	250	25
PHL	13283	8711500409690	Caps 5W G4 12V CL 4000h 1CT/10X10F	100	10
PHL	12NOTCH	8711500042217	Deco 10W E14 230-240V T25 CL 1CT/10X10F	100	100
PHL	120ESPLUS	8727900852165	Plusline 118mm 2y 120W R7s 230V 1BB	100	10
PHL	120ESCOMPLUS	8727900852233	Plusline 78mm 2y 120W R7s 230V 1BB	100	10
PHL	1000PLUS	8711500494344	Plusline L 1000W R7s 230V 1CT/10	10	10
PHL	1000DEGL	8711500491282	HaLa IDE 1000W E40 230V CL 1CT/6	6	6
PHL	LEDSSOL40	8718696598474	LED SSW 40W B38 E14 WW CL ND 1SRT4	4	4
PHL	PHILED40	8718696808672	CLA LEDBulb ND 4.3-40W E27 827 A60 CL	10	10
PHL	COREG428827	8718696826942	CorePro LEDcapsuleLV 2.5-28W G4 827	12	12
PHL	COREG428830	8718696826966	CorePro LEDcapsuleLV 2.5-28W G4 830	12	12
PHL	CAPS35GY6	8718696827833	Caps 3000h 35W GY6.35 12V CL 1CT/10x10F	100	1
PHL	CLAR393082736	8718696811719	CoreProLEDspot ND1.8-30W R39 E14 827 36D	6	6
PHL	CLAR502582736	8718696811733	CoreProLEDspot ND1.4-25W R50 E14 827 36D	6	6
PHL	CLAR504082736	8718696811757	CoreProLEDspot ND2.8-40W R50 E14 827 36D	6	6
PHL	CLAR506082736D	8718696811771	CoreProLEDspot D 4.3-60W R50 E14 827 36D	6	6
PHL	CLAR634082736	8718696811795	CoreProLEDspot ND 3-40W R63 E27 827 36D	6	6
PHL	CLAR636082736D	8718696811818	CoreProLEDspot D 4.5-60W R63 E27 827 36D	6	6
PHL	5884NG	8711500632197	MASTER TL-D Super 80 58W/840 1SL/25	25	25

Quantità minima ordinazione	Quantità massima ordinazione	Lead Time	Prezzo al grossista	Prezzo al Pubblico	Moltiplicatore prezzo	Codice Valuta	Unità di misura	Prodotto Composto	Stato del prodotto	Data ultima variazione	Famiglia di sconto	Famiglia statistica	Electrocod
25	999999	3	47.41	47.41	1	EUR	PCE	0	2	20190501	ITF	90019174PA10414	2523
25	999999	3	44.31	44.31	1	EUR	PCE	0	2	20190501	ITF	90019174PA10414	2523
32	999999	3	64.33	64.33	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552658	257
32	999999	3	48.59	48.59	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552658	257
60	999999	3	37.11	37.11	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
25	999999	3	23.30	23.30	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
6	999999	3	73.84	73.84	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552658	257
25	999999	3	20.20	20.20	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
6	999999	3	55.46	55.46	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
25	999999	3	18.73	18.73	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
6	999999	3	66.50	66.50	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552659	257
25	999999	3	53.85	53.85	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552659	257
25	999999	3	35.77	35.77	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552659	257
25	999999	3	25.34	25.34	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
25	999999	3	33.93	33.93	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552659	257
20	999999	3	218.30	218.30	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552658	257
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.13	12.13	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.31	12.31	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.31	12.31	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	12.31	12.31	1	EUR	PCE	0	1	20190501	ITK	90019174AU57481	2531
6	999999	3	12.31	12.31	1	EUR	PCE	0	3	20190501	ITK	90019174AU57481	2531
6	999999	3	25.97	25.97	1	EUR	PCE	0	2	20190501	ITL	90019174AU59174	2531
6	999999	3	25.97	25.97	1	EUR	PCE	0	2	20190501	ITL	90019174AU59174	2531
25	999999	3	19.87	19.87	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2523
25	999999	3	18.11	18.11	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2523
25	999999	3	35.68	35.68	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257

Signify Classified - Internal

25	999999	3	18.56	18.56	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
10	999999	3	46.96	46.96	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
10	999999	3	46.96	46.96	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
10	999999	3	46.96	46.96	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
10	999999	3	46.96	46.96	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
10	999999	3	46.96	46.96	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
10	999999	3	46.96	46.96	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
10	999999	3	38.06	38.06	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
10	999999	3	38.06	38.06	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
40	999999	3	10.24	10.24	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	41.57	41.57	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
20	999999	3	10.24	10.24	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	10.24	10.24	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	19.64	19.64	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
20	999999	3	34.72	34.72	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
20	999999	3	32.46	32.46	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
20	999999	3	34.72	34.72	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
40	999999	3	9.62	9.62	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	40.79	40.79	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
20	999999	3	9.62	9.62	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	40.79	40.79	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
20	999999	3	9.62	9.62	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	15.42	15.42	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
20	999999	3	33.93	33.93	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
20	999999	3	31.71	31.71	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
20	999999	3	33.93	33.93	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
40	999999	3	9.62	9.62	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	38.89	38.89	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
20	999999	3	9.62	9.62	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	9.62	9.62	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	15.42	15.42	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
40	999999	3	15.03	15.03	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
40	999999	3	15.03	15.03	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
40	999999	3	9.70	9.70	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	9.70	9.70	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.70	9.70	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	15.25	15.25	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
40	999999	3	13.90	13.90	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
40	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522

Signify Classified - Internal

20	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.36	9.36	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	13.90	13.90	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
40	999999	3	13.55	13.55	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
20	999999	3	32.00	32.00	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
20	999999	3	29.91	29.91	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
20	999999	3	32.00	32.00	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10246	2522
40	999999	3	9.70	9.70	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	9.70	9.70	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.70	9.70	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	14.68	14.68	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
40	999999	3	11.30	11.30	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
40	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
20	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	8.82	8.82	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	11.25	11.25	1	EUR	PCE	0	2	20190501	ITZ	90019174PA10246	2522
40	999999	3	10.99	10.99	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
25	999999	3	14.28	14.28	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
25	999999	3	18.11	18.11	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2523
25	999999	3	20.06	20.06	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
6	999999	3	13.46	13.46	1	EUR	PCE	0	9	20190501	ITK	90019174AU57484	2531
6	999999	3	14.07	14.07	1	EUR	PCE	0	3	20190501	ITK	90019174AU57482	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
6	999999	3	14.70	14.70	1	EUR	PCE	0	3	20190501	ITK	90019174AU57478	2531
1	999999	3	70.34	70.34	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
1	999999	3	66.99	66.99	1	EUR	PCE	0	2	20190501	ITS	90014035B560993	0931
1	999999	3	112.09	112.09	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
1	999999	3	42.74	42.74	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
1	999999	3	42.74	42.74	1	EUR	PCE	0	2	20190501	ITS	90014035B560993	0931
1	999999	3	112.09	112.09	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
12	999999	3	201.15	201.15	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542

Signify Classified - Internal

12	999999	3	171.05	171.05	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	139.26	139.26	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	139.26	139.26	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	139.26	139.26	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
6	999999	3	321.39	321.39	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	151.79	151.79	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	139.26	139.26	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	139.26	139.26	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
6	999999	3	318.21	318.21	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	196.42	196.42	1	EUR	PCE	0	2	20190501	ITO	90019174PA00310	2542
12	999999	3	30.40	30.40	1	EUR	PCE	0	3	20190501	ITM	90019174PA00360	2543
12	999999	3	110.21	110.21	1	EUR	PCE	0	3	20190501	ITM	90019174PA79157	2543
12	999999	3	28.17	28.17	1	EUR	PCE	0	3	20190501	ITM	90019174PA00360	2543
12	999999	3	71.87	71.87	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
12	999999	3	60.51	60.51	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
12	999999	3	58.07	58.07	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
12	999999	3	34.51	34.51	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
12	999999	3	36.30	36.30	1	EUR	PCE	0	9	20190501	ITM	90019174PA00360	2543
12	999999	3	51.15	51.15	1	EUR	PCE	0	9	20190501	ITM	90019174PA00437	2543
12	999999	3	78.96	78.96	1	EUR	PCE	0	9	20190501	ITM	90019174PA00437	2543
12	999999	3	43.33	43.33	1	EUR	PCE	0	9	20190501	ITM	90019174PA00437	2543
12	999999	3	66.59	66.59	1	EUR	PCE	0	9	20190501	ITM	90019174PA00437	2543
12	999999	3	63.79	63.79	1	EUR	PCE	0	9	20190501	ITM	90019174PA00437	2543
12	999999	3	40.92	40.92	1	EUR	PCE	0	9	20190501	ITM	90019174PA00437	2543
12	999999	3	97.73	97.73	1	EUR	PCE	0	2	20190501	ITM	90019174PA79157	2543
4	999999	3	186.74	186.74	1	EUR	PCE	0	3	20190501	ITM	90019174PA01611	2543
24	999999	3	30.10	30.10	1	EUR	PCE	0	3	20190501	ITM	90019174PA00360	2543
12	999999	3	71.88	71.88	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
12	999999	3	60.51	60.51	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
12	999999	3	58.07	58.07	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
12	999999	3	31.72	31.72	1	EUR	PCE	0	3	20190501	ITM	90019174PA00437	2543
24	999999	3	30.45	30.45	1	EUR	PCE	0	3	20190501	ITM	90019174PA00360	2543
24	999999	3	29.01	29.01	1	EUR	PCE	0	3	20190501	ITM	90019174PA00360	2543
24	999999	3	41.02	41.02	1	EUR	PCE	0	3	20190501	ITM	90019174PA00360	2543
4	999999	3	30.82	30.82	1	EUR	PCE	0	9	20190501	ITL	90019174AU59174	2531
120	999999	3	55.16	55.16	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0932
1	999999	3	35.44	35.44	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0932
1	999999	3	49.61	49.61	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
1	999999	3	49.61	49.61	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
1	999999	3	24.26	24.26	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0932
1	999999	3	24.70	24.70	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0932
1	999999	3	40.91	40.91	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
1	999999	3	21.62	21.62	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931
1	999999	3	18.20	18.20	1	EUR	PCE	0	3	20190501	ITS	90014035B560993	0931

Signify Classified - Internal

32	999999	3	74.97	74.97	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552658	257
32	999999	3	69.90	69.90	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552658	257
32	999999	3	64.33	64.33	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552658	257
32	999999	3	41.48	41.48	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552659	257
12	999999	3	207.66	207.66	1	EUR	PCE	0	3	20190501	IT1	90019174PA50326	2544
12	999999	3	207.66	207.66	1	EUR	PCE	0	3	20190501	IT1	90019174PA50326	2544
12	999999	3	154.26	154.26	1	EUR	PCE	0	3	20190501	IT1	90019174PA50326	2544
12	999999	3	154.26	154.26	1	EUR	PCE	0	3	20190501	IT1	90019174PA50326	2544
12	999999	3	160.20	160.20	1	EUR	PCE	0	3	20190501	IT1	90019174PA50326	2544
25	999999	3	8.44	8.44	1	EUR	PCE	0	3	20190501	ITH	90019174PA20450	0932
300	999999	3	0.86	0.86	1	EUR	PCE	0	3	20190501	ITH	90019174PA20450	0932
25	999999	3	8.44	8.44	1	EUR	PCE	0	3	20190501	ITH	90019174PA20450	0932
10	999999	3	2.48	2.48	1	EUR	BLI	0	3	20190501	ITH	90019174PA20450	0932
300	999999	3	0.86	0.86	1	EUR	PCE	0	3	20190501	ITH	90019174PA20450	0932
10	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
50	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
50	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
50	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
50	999999	3	29.56	29.56	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
50	999999	3	67.49	67.49	1	EUR	PCE	0	9	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
50	999999	3	67.49	67.49	1	EUR	PCE	0	9	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
50	999999	3	67.49	67.49	1	EUR	PCE	0	9	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	25.19	25.19	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	25.19	25.19	1	EUR	PCE	0	2	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	25.19	25.19	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532

Signify Classified - Internal

10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	25.19	25.19	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	26.94	26.94	1	EUR	PCE	0	3	20190501	ITI	90019174PA30475	2532
10	999999	3	25.19	25.19	1	EUR	PCE	0	2	20190501	ITI	90019174PA30475	2532
20	999999	3	12.00	12.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
20	999999	3	12.00	12.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	17.47	17.47	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
10	999999	3	42.14	42.14	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2532
10	999999	3	24.34	24.34	1	EUR	PCE	0	3	20190501	ITI	90019174PA30463	2532
10	999999	3	24.34	24.34	1	EUR	PCE	0	3	20190501	ITI	90019174PA30463	2532
10	999999	3	22.89	22.89	1	EUR	PCE	0	3	20190501	ITI	90019174PA30463	2532
10	999999	3	22.89	22.89	1	EUR	PCE	0	3	20190501	ITI	90019174PA30463	2532
10	999999	3	43.12	43.12	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	43.12	43.12	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	30.79	30.79	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	30.79	30.79	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	32.28	32.28	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	22.59	22.59	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	30.79	30.79	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	22.59	22.59	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
10	999999	3	22.59	22.59	1	EUR	PCE	0	3	20190501	ITI	90019174PA30404	2532
25	999999	3	78.03	78.03	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552659	257
25	999999	3	54.94	54.94	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
10	999999	3	35.00	35.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	35.00	35.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	35.00	35.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	29.00	29.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	29.00	29.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	29.00	29.00	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
25	999999	3	164.19	164.19	1	EUR	PCE	0	3	20190501	ITJ	90019174Q562835	257
25	999999	3	20.79	20.79	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
6	999999	3	28.85	28.85	1	EUR	PCE	0	9	20190501	ITL	90019174AU47475	2531
6	999999	3	28.85	28.85	1	EUR	PCE	0	9	20190501	ITL	90019174AU47475	2531
6	999999	3	28.85	28.85	1	EUR	PCE	0	9	20190501	ITL	90019174AU47475	2531
6	999999	3	28.85	28.85	1	EUR	PCE	0	9	20190501	ITL	90019174AU47475	2531
6	999999	3	26.90	26.90	1	EUR	PCE	0	9	20190501	ITL	90019174AU47475	2531
6	999999	3	26.90	26.90	1	EUR	PCE	0	9	20190501	ITL	90019174AU47475	2531
4	999999	3	38.48	38.48	1	EUR	PCE	0	9	20190501	ITL	90019174AU59174	2531
10	999999	3	16.34	16.34	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	16.34	16.34	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	15.02	15.02	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	15.02	15.02	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	13.50	13.50	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553
10	999999	3	13.50	13.50	1	EUR	PCE	0	3	20190501	IT3	92400118D577493	2553

Signify Classified - Internal

25	999999	3	19.83	19.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	34.35	34.35	1	EUR	PCE	0	9	20190501	ITI	90019174PA30472	2532
25	999999	3	19.83	19.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	19.83	19.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	17.78	17.78	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	17.78	17.78	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	64.91	64.91	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552659	257
25	999999	3	26.67	26.67	1	EUR	PCE	0	9	20190501	ITI	90019174PA30472	2532
25	999999	3	15.20	15.20	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	15.20	15.20	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	15.20	15.20	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	15.20	15.20	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	15.20	15.20	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	15.20	15.20	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	14.35	14.35	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	14.35	14.35	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	14.35	14.35	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
25	999999	3	14.35	14.35	1	EUR	PCE	0	3	20190501	ITI	90019174PA30472	2532
10	999999	3	6.83	6.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30470	2532
10	999999	3	6.83	6.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30470	2532
10	999999	3	6.83	6.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30470	2532
10	999999	3	6.83	6.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30470	2532
50	999999	3	6.83	6.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30470	2532
10	999999	3	6.83	6.83	1	EUR	PCE	0	3	20190501	ITI	90019174PA30470	2532
10	999999	3	8.70	8.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	6.70	6.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	6.70	6.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	19.00	19.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
6	999999	3	15.50	15.50	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
10	999999	3	12.50	12.50	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
6	999999	3	13.50	13.50	1	EUR	PCE	0	2	20190501	IT3	92400118L667496	2551
10	999999	3	11.50	11.50	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
10	999999	3	8.70	8.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	7.70	7.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	8.70	8.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	7.70	7.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	7.70	7.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	6.70	6.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	7.70	7.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	6.70	6.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
6	999999	3	16.50	16.50	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
6	999999	3	12.50	12.50	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
4	999999	3	24.00	24.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
10	999999	3	8.70	8.70	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551

Signify Classified - Internal

10	999999	3	17.80	17.80	1	EUR	PCE	0	3	20190501	ITT	92400118A136975	2552
10	999999	3	17.80	17.80	1	EUR	PCE	0	3	20190501	ITT	92400118A136975	2552
10	999999	3	12.50	12.50	1	EUR	PCE	0	3	20190501	ITT	92400118L707012	2551
10	999999	3	9.45	9.45	1	EUR	PCE	0	3	20190501	ITT	92400118L707012	2551
10	999999	3	8.10	8.10	1	EUR	PCE	0	3	20190501	ITT	92400118L707012	2551
10	999999	3	27.00	27.00	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
6	999999	3	27.00	27.00	1	EUR	PCE	0	9	20190501	ITT	92400118L667011	2551
10	999999	3	12.51	12.51	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
10	999999	3	12.51	12.51	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
10	999999	3	10.80	10.80	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
10	999999	3	10.80	10.80	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
10	999999	3	31.50	31.50	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
6	999999	3	31.50	31.50	1	EUR	PCE	0	9	20190501	ITT	92400118L667011	2551
12	999999	3	31.50	31.50	1	EUR	PCE	0	2	20190501	IT1	90019174PA50328	2545
12	999999	3	109.17	109.17	1	EUR	PCE	0	9	20190501	ITV	90019174PA50328	2545
1	999999	3	695.54	695.54	1	EUR	PCE	0	6	20190501	ITN	90019174PA00280	2545
1	999999	3	622.38	622.38	1	EUR	PCE	0	6	20190501	ITN	90019174PA00280	2545
1	999999	3	1455.60	1455.60	1	EUR	PCE	0	3	20190501	ITN	90019174PA00280	2545
1	999999	3	727.19	727.19	1	EUR	PCE	0	3	20190501	ITN	90019174PA00280	2545
1	999999	3	617.20	617.20	1	EUR	PCE	0	3	20190501	ITN	90019174PA00280	2545
1	999999	3	728.90	728.90	1	EUR	PCE	0	6	20190501	ITN	90019174PA00280	2545
1	999999	3	623.30	623.30	1	EUR	PCE	0	6	20190501	ITN	90019174PA00280	2545
1	999999	3	1185.49	1185.49	1	EUR	PCE	0	3	20190501	ITN	90019174PA00280	2545
1	999999	3	1373.11	1373.11	1	EUR	PCE	0	6	20190501	ITN	90019174PA00280	2545
1	999999	3	1373.11	1373.11	1	EUR	PCE	0	6	20190501	ITN	90019174PA00280	2545
10	999999	3	12.00	12.00	1	EUR	PCE	0	3	20190501	ITT	92400118A136972	2552
10	999999	3	10.00	10.00	1	EUR	PCE	0	3	20190501	ITT	92400118A136972	2552
25	999999	3	31.43	31.43	1	EUR	PCE	0	3	20190501	ITF	90019174PA10414	2523
25	999999	3	36.98	36.98	1	EUR	PCE	0	3	20190501	ITF	90019174PA10414	2523
25	999999	3	22.08	22.08	1	EUR	PCE	0	2	20190501	ITF	90019174PA10414	2523
25	999999	3	22.08	22.08	1	EUR	PCE	0	3	20190501	ITF	90019174PA10414	2523
25	999999	3	22.08	22.08	1	EUR	PCE	0	3	20190501	ITF	90019174PA10414	2523
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	9.75	9.75	1	EUR	PCE	0	1	20190501	IT3	92400118A136972	2552
6	999999	3	9.75	9.75	1	EUR	PCE	0	1	20190501	IT3	92400118A136972	2552
4	999999	3	9.75	9.75	1	EUR	PCE	0	1	20190501	IT3	92400118A136972	2552
40	999999	3	3.33	3.33	1	EUR	PCE	0	3	20190501	ITT	92400118D571533	2553
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	6.20	6.20	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
6	999999	3	11.00	11.00	1	EUR	PCE	0	3	20190501	ITT	92400118A130235	2551
4	999999	3	14.00	14.00	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
4	999999	3	10.50	10.50	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
6	999999	3	21.00	21.00	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551

Signify Classified - Internal

6	999999	3	20.00	20.00	1	EUR	PCE	0	3	20190501	ITT	92400118L667011	2551
6	999999	3	102.00	102.00	1	EUR	PCE	0	3	20190501	ITT	92400118AG08790	2552
6	999999	3	134.00	134.00	1	EUR	PCE	0	3	20190501	ITT	92400118AG08790	2552
6	999999	3	134.00	134.00	1	EUR	PCE	0	3	20190501	ITT	92400118AG08790	2552
6	999999	3	170.00	170.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08790	2552
6	999999	3	170.00	170.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08790	2552
6	999999	3	145.00	145.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08790	2552
6	999999	3	145.00	145.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08790	2552
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	10.65	10.65	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	14.99	14.99	1	EUR	PCE	0	3	20190501	IT3	92400118L667011	2551
6	999999	3	14.99	14.99	1	EUR	PCE	0	3	20190501	IT3	92400118L667011	2551
4	999999	3	16.31	16.31	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
6	999999	3	16.31	16.31	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	12.29	12.29	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	24.51	24.51	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
6	999999	3	24.51	24.51	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	20.48	20.48	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
6	999999	3	20.48	20.48	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	10.65	10.65	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551

Signify Classified - Internal

4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
6	999999	3	12.29	12.29	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
6	999999	3	149.00	149.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	149.00	149.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	149.00	149.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	149.00	149.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	142.00	142.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	142.00	142.00	1	EUR	PCE	0	1	20190501	ITT	92400118AG08793	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
6	999999	3	135.00	135.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
6	999999	3	142.00	142.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
6	999999	3	142.00	142.00	1	EUR	PCE	0	9	20190501	ITT	92400118AG08793	2552
2	999999	3	350.00	350.00	1	EUR	PCE	0	3	20190501	ITT	92400118AG08792	2552
2	999999	3	350.00	350.00	1	EUR	PCE	0	3	20190501	ITT	92400118AG08792	2552
2	999999	3	250.00	250.00	1	EUR	PCE	0	3	20190501	ITT	92400118AG08792	2552
2	999999	3	250.00	250.00	1	EUR	PCE	0	3	20190501	ITT	92400118AG08792	2552
6	999999	3	13.00	13.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
6	999999	3	11.00	11.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
4	999999	3	16.70	16.70	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
4	999999	3	11.00	11.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
4	999999	3	15.00	15.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
6	999999	3	15.00	15.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L707012	2551
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551
4	999999	3	10.57	10.57	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551

Signify Classified - Internal

4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	9.01	9.01	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	10.65	10.65	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	14.75	14.75	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	9.01	9.01	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	9.01	9.01	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	9.01	9.01	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	14.75	14.75	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	10.65	10.65	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	9.01	9.01	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
6	999999	3	13.03	13.03	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	13.03	13.03	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
6	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118A137022	2552
6	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118A137022	2552
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A137018	2552
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A137018	2552
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A137018	2552
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
4	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
4	999999	3	13.00	13.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667011	2552
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551

Signify Classified - Internal

6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2551
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
6	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
6	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L669037	2551
4	999999	3	9.01	9.01	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	9.83	9.83	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551
6	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2552
6	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2552
4	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2552
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551
6	999999	3	10.57	10.57	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	10.57	10.57	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	10.57	10.57	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	9.83	9.83	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	9.83	9.83	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	9.83	9.83	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
4	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
4	999999	3	6.55	6.55	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552
4	999999	3	4.09	4.09	1	EUR	PCE	0	1	20190501	IT3	92400118A130235	2552

Signify Classified - Internal

25	999999	3	31.97	31.97	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
10	999999	3	26.37	26.37	1	EUR	PCE	0	3	20190501	ITE	90019174A549008	2511
10	999999	3	16.49	16.49	1	EUR	PCE	0	3	20190501	ITE	90019174A549008	2511
10	999999	3	16.49	16.49	1	EUR	PCE	0	3	20190501	ITE	90019174A549008	2511
10	999999	3	16.49	16.49	1	EUR	PCE	0	3	20190501	ITE	90019174A549008	2511
10	999999	3	4.50	4.50	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	4.90	4.90	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	4.90	4.90	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	4.50	4.50	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	4.50	4.50	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	5.13	5.13	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	5.13	5.13	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	5.13	5.13	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	4.00	4.00	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	4.00	4.00	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	4.00	4.00	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	3.33	3.33	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	3.33	3.33	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	3.33	3.33	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	8.00	8.00	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	8.00	8.00	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	8.00	8.00	1	EUR	PCE	0	3	20190501	IT3	92400118L669037	2551
10	999999	3	4.90	4.90	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
10	999999	3	4.50	4.50	1	EUR	PCE	0	3	20190501	IT3	92400118L703946	2551
6	999999	3	88.77	88.77	1	EUR	PCE	0	3	20190501	ITL	90019174AU57482	2531
6	999999	3	88.77	88.77	1	EUR	PCE	0	3	20190501	ITL	90019174AU57482	2531
6	999999	3	75.29	75.29	1	EUR	PCE	0	3	20190501	ITL	90019174AU57482	2531
6	999999	3	75.29	75.29	1	EUR	PCE	0	3	20190501	ITL	90019174AU57482	2531
6	999999	3	61.27	61.27	1	EUR	PCE	0	3	20190501	ITL	90019174AU57482	2531
6	999999	3	61.27	61.27	1	EUR	PCE	0	3	20190501	ITL	90019174AU57482	2531
12	999999	3	71.20	71.20	1	EUR	PCE	0	3	20190501	ITN	90019174PA00330	2545
4	999999	3	354.20	354.20	1	EUR	PCE	0	3	20190501	ITN	90019174PA00280	2545
4	999999	3	354.20	354.20	1	EUR	PCE	0	3	20190501	ITN	90019174PA00280	2545
4	999999	3	268.88	268.88	1	EUR	PCE	0	3	20190501	ITN	90019174PA00280	2545
6	999999	3	74.11	74.11	1	EUR	PCE	0	3	20190501	ITN	90019174PA00330	2545
4	999999	3	231.38	231.38	1	EUR	PCE	0	2	20190501	ITP	90019174Q552658	257
1	999999	3	345.00	345.00	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
1	999999	3	345.00	345.00	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
1	999999	3	113.19	113.19	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	113.19	113.19	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	110.88	110.88	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	97.47	97.47	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
12	999999	3	86.01	86.01	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
12	999999	3	129.74	129.74	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971

Signify Classified - Internal

1	999999	3	119.25	119.25	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
1	999999	3	236.78	236.78	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
1	999999	3	231.00	231.00	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
1	999999	3	231.00	231.00	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
1	999999	3	378.26	378.26	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
12	999999	3	209.00	209.00	1	EUR	PCE	0	9	20190501	ITS	90014035C060933	0971
1	999999	3	241.40	241.40	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0971
12	999999	3	207.90	207.90	1	EUR	PCE	0	9	20190501	ITS	90014035C060933	0971
1	999999	3	78.54	78.54	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	399.05	399.05	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0971
1	999999	3	399.05	399.05	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	399.05	399.05	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0971
1	999999	3	359.05	359.05	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0971
1	999999	3	350.07	350.07	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0971
1	999999	3	367.61	367.61	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0971
1	999999	3	297.99	297.99	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	293.37	293.37	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0951
1	999999	3	309.54	309.54	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0951
1	999999	3	293.37	293.37	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	309.54	309.54	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	293.37	293.37	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	293.37	293.37	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0951
1	999999	3	293.37	293.37	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	293.37	293.37	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	315.32	315.32	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0971
1	999999	3	302.61	302.61	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0951
1	999999	3	327.44	327.44	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0951
1	999999	3	300.30	300.30	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	302.61	302.61	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	297.41	297.41	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0951
1	999999	3	321.67	321.67	1	EUR	PCE	0	2	20190501	ITS	90014035C064874	0951
1	999999	3	300.30	300.30	1	EUR	PCE	0	3	20190501	ITS	90014035C064874	0971
1	999999	3	123.01	123.01	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	122.52	122.52	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	123.01	123.01	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	87.69	87.69	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	237.93	237.93	1	EUR	PCE	0	3	20190501	ITS	90014035C044872	0951
1	999999	3	78.54	78.54	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	86.49	86.49	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
12	999999	3	78.54	78.54	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	87.69	87.69	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	189.79	189.79	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	149.55	149.55	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	162.76	162.76	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971

Signify Classified - Internal

1	999999	3	234.23	234.23	1	EUR	PCE	0	3	20190501	ITS	90014035C044872	0951
1	999999	3	143.80	143.80	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
10	999999	3	156.50	156.50	1	EUR	PCE	0	2	20190501	ITS	90014035C040930	0971
1	999999	3	95.17	95.17	1	EUR	PCE	0	3	20190501	ITS	90014035C040930	0971
1	999999	3	98.18	98.18	1	EUR	PCE	0	3	20190501	ITS	90014035C044872	0971
1	999999	3	98.18	98.18	1	EUR	PCE	0	3	20190501	ITS	90014035C044872	0971
12	999999	3	113.02	113.02	1	EUR	PCE	0	3	20190501	ITS	90014035C044872	0971
12	999999	3	118.97	118.97	1	EUR	PCE	0	3	20190501	ITS	90014035C044872	0971
1	999999	3	30.03	30.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	30.03	30.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	132.73	132.73	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
1	999999	3	127.63	127.63	1	EUR	PCE	0	2	20190501	ITS	90014035B540631	0911
1	999999	3	114.92	114.92	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
12	999999	3	121.28	121.28	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
1	999999	3	119.54	119.54	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
1	999999	3	110.88	110.88	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
12	999999	3	115.50	115.50	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
1	999999	3	132.83	132.83	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
12	999999	3	94.71	94.71	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
1	999999	3	110.88	110.88	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
1	999999	3	110.88	110.88	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
12	999999	3	90.09	90.09	1	EUR	PCE	0	3	20190501	ITS	90014035B540631	0911
1	999999	3	132.83	132.83	1	EUR	PCE	0	3	20190501	ITS	90014035B540642	0911
1	999999	3	71.50	71.50	1	EUR	PCE	0	9	20190501	ITS	90014035B540510	0911
12	999999	3	67.57	67.57	1	EUR	PCE	0	3	20190501	ITS	90014035B540510	0911
1	999999	3	65.47	65.47	1	EUR	PCE	0	3	20190501	ITS	90014035B540510	0911
1	999999	3	65.47	65.47	1	EUR	PCE	0	3	20190501	ITS	90014035B540510	0911
1	999999	3	55.25	55.25	1	EUR	PCE	0	3	20190501	ITS	90014035B540510	0911
12	999999	3	67.87	67.87	1	EUR	PCE	0	3	20190501	ITS	90014035B540510	0911
1	999999	3	58.86	58.86	1	EUR	PCE	0	3	20190501	ITS	90014035B540510	0911
1	999999	3	56.60	56.60	1	EUR	PCE	0	3	20190501	ITS	90014035B540510	0911
1	999999	3	50.24	50.24	1	EUR	PCE	0	9	20190501	ITS	90014035B540510	0911
1	999999	3	50.24	50.24	1	EUR	PCE	0	9	20190501	ITS	90014035B540510	0911
1	999999	3	31.84	31.84	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	25.99	25.99	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	25.99	25.99	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	26.57	26.57	1	EUR	PCE	0	2	20190501	ITS	90014035B540558	0911
1	999999	3	27.03	27.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	27.03	27.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	27.03	27.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	27.03	27.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	21.62	21.62	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
1	999999	3	21.62	21.62	1	EUR	PCE	0	3	20190501	ITS	90014035B540558	0911
20	999999	3	19.82	19.82	1	EUR	PCE	0	3	20190501	ITS	90014035B540571	0911

Signify Classified - Internal

20	999999	3	20.79	20.79	1	EUR	PCE	0	3	20190501	ITS	90014035B540571	0911
20	999999	3	17.33	17.33	1	EUR	PCE	0	3	20190501	ITS	90014035B540571	0911
20	999999	3	15.02	15.02	1	EUR	PCE	0	3	20190501	ITS	90014035B540571	0911
1	999999	3	18.12	18.12	1	EUR	PCE	0	9	20190501	ITS	90014035B540571	0911
20	999999	3	20.21	20.21	1	EUR	PCE	0	3	20190501	ITS	90014035B540571	0911
50	999999	3	20.79	20.79	1	EUR	PCE	0	3	20190501	ITS	90014035B540571	0911
50	999999	3	20.79	20.79	1	EUR	PCE	0	3	20190501	ITS	90014035B540571	0911
1	999999	3	39.64	39.64	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	39.64	39.64	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	57.75	57.75	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	33.03	33.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	39.04	39.04	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	39.04	39.04	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	32.43	32.43	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	36.38	36.38	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	39.04	39.04	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	36.38	36.38	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	39.04	39.04	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	42.74	42.74	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	27.63	27.63	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	33.50	33.50	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	30.03	30.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	33.50	33.50	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	26.43	26.43	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	33.50	33.50	1	EUR	PCE	0	3	20190501	ITS	90014035B540924	0911
1	999999	3	30.03	30.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	28.88	28.88	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	30.03	30.03	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	28.88	28.88	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	26.43	26.43	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	27.72	27.72	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	29.37	29.37	1	EUR	PCE	0	9	20190501	ITS	90014035B540926	0911
1	999999	3	27.72	27.72	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	29.61	29.61	1	EUR	PCE	0	2	20190501	ITS	90014035B540926	0911
1	999999	3	26.43	26.43	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	27.72	27.72	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	24.20	24.20	1	EUR	PCE	0	9	20190501	ITS	90014035B540926	0911
12	999999	3	27.72	27.72	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
12	999999	3	32.34	32.34	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	23.10	23.10	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	24.26	24.26	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	24.26	24.26	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	23.10	23.10	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911
1	999999	3	24.26	24.26	1	EUR	PCE	0	3	20190501	ITS	90014035B540926	0911

Signify Classified - Internal

25	999999	3	23.88	23.88	1	EUR	PCE	0	3	20190501	ITJ	90019174Q552657	257
10	999999	3	3.71	3.71	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
1	999999	3	158.81	158.81	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0961
1	999999	3	153.04	153.04	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0961
1	999999	3	153.04	153.04	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0961
1	999999	3	153.04	153.04	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0961
1	999999	3	153.04	153.04	1	EUR	PCE	0	3	20190501	ITS	90014035C060933	0961
12	999999	3	112.35	112.35	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	111.09	111.09	1	EUR	PCE	0	9	20190501	ITN	90019174PA50278	2544
12	999999	3	106.50	106.50	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	84.25	84.25	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	101.43	101.43	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	84.25	84.25	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	106.50	106.50	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	84.25	84.25	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	106.50	106.50	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	84.25	84.25	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	101.43	101.43	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	84.25	84.25	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	106.50	106.50	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	84.25	84.25	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	112.07	112.07	1	EUR	PCE	0	2	20190501	IT1	90019174PA50278	2544
12	999999	3	112.07	112.07	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
6	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	155.01	155.01	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	155.01	155.01	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	155.01	155.01	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	155.01	155.01	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	155.01	155.01	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	155.01	155.01	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	155.01	155.01	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	126.97	126.97	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
15	999999	3	3.14	3.14	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
15	999999	3	3.14	3.14	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
15	999999	3	3.14	3.14	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
15	999999	3	3.14	3.14	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
15	999999	3	3.14	3.14	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511

Signify Classified - Internal

15	999999	3	3.14	3.14	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
10	999999	3	6.03	6.03	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	8.82	8.82	1	EUR	BLI	0	3	20190501	ITX	90019174A140565	2512
10	999999	3	2.61	2.61	1	EUR	BLI	0	2	20190501	ITC	90019174A140521	2512
10	999999	3	6.01	6.01	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	6.01	6.01	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	4.94	4.94	1	EUR	PCE	0	3	20190501	ITC	90019174A140551	2512
10	999999	3	8.82	8.82	1	EUR	BLI	0	3	20190501	ITX	90019174A140565	2512
20	999999	3	5.46	5.46	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2512
10	999999	3	4.94	4.94	1	EUR	PCE	0	2	20190501	ITC	90019174A140551	2512
10	999999	3	6.03	6.03	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	8.82	8.82	1	EUR	BLI	0	3	20190501	ITX	90019174A140565	2512
10	999999	3	2.49	2.49	1	EUR	BLI	0	9	20190501	ITC	90019174A140521	2512
10	999999	3	6.03	6.03	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	4.70	4.70	1	EUR	PCE	0	9	20190501	ITC	90019174A140551	2512
10	999999	3	6.03	6.03	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	6.03	6.03	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	4.71	4.71	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
10	999999	3	3.65	3.65	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
10	999999	3	3.65	3.65	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
10	999999	3	3.34	3.34	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
20	999999	3	5.46	5.46	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
10	999999	3	12.63	12.63	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
10	999999	3	4.71	4.71	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
10	999999	3	4.71	4.71	1	EUR	PCE	0	9	20190501	ITC	90019174A010583	2511
12	999999	3	15.18	15.18	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
12	999999	3	15.18	15.18	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
12	999999	3	15.18	15.18	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
12	999999	3	10.84	10.84	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
12	999999	3	10.84	10.84	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
12	999999	3	10.84	10.84	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
12	999999	3	10.84	10.84	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
12	999999	3	10.84	10.84	1	EUR	PCE	0	3	20190501	ITG	90019174PA10412	2523
1	999999	3	171.99	171.99	1	EUR	PCE	0	3	20190501	ITS	90014035B560655	0951
1	999999	3	178.28	178.28	1	EUR	PCE	0	3	20190501	ITS	90014035B560655	0951
12	999999	3	138.05	138.05	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	135.28	135.28	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	128.85	128.85	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	147.25	147.25	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	147.25	147.25	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	89.78	89.78	1	EUR	PCE	0	9	20190501	ITN	90019174PA00346	2544
12	999999	3	104.74	104.74	1	EUR	PCE	0	9	20190501	ITN	90019174PA00346	2544
10	999999	3	5.00	5.00	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551

Signify Classified - Internal

6	999999	3	9.00	9.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
6	999999	3	10.00	10.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
10	999999	3	18.00	18.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
10	999999	3	18.00	18.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
10	999999	3	13.99	13.99	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
10	999999	3	27.00	27.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
10	999999	3	27.00	27.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
10	999999	3	23.00	23.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
10	999999	3	23.00	23.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
4	999999	3	21.50	21.50	1	EUR	PCE	0	3	20190501	IT3	92400118D574388	2553
4	999999	3	17.50	17.50	1	EUR	PCE	0	3	20190501	IT3	92400118D574388	2553
10	999999	3	9.50	9.50	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	9.50	9.50	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	9.50	9.50	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	9.50	9.50	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	9.50	9.50	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	6.75	6.75	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	6.75	6.75	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	6.75	6.75	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	6.75	6.75	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	6.75	6.75	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	6.75	6.75	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	6.75	6.75	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118L707012	2551
4	999999	3	30.00	30.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08793	2552
4	999999	3	30.00	30.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08793	2552
4	999999	3	39.00	39.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08793	2552
4	999999	3	39.00	39.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08793	2552
6	999999	3	32.00	32.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08792	2552
6	999999	3	32.00	32.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08792	2552
6	999999	3	25.00	25.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08792	2552
6	999999	3	25.00	25.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08792	2552
6	999999	3	19.00	19.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08792	2552
6	999999	3	19.00	19.00	1	EUR	PCE	0	3	20190501	IT3	92400118AG08792	2552
12	999999	3	9.50	9.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
12	999999	3	8.00	8.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
12	999999	3	8.00	8.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
12	999999	3	6.50	6.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
12	999999	3	8.70	8.70	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
12	999999	3	6.50	6.50	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
12	999999	3	6.70	6.70	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552

Signify Classified - Internal

10	999999	3	10.36	10.36	1	EUR	PCE	0	3	20190501	IT3	92400118D574387	2553
10	999999	3	15.50	15.50	1	EUR	PCE	0	2	20190501	IT3	92400118D573893	2553
10	999999	3	10.36	10.36	1	EUR	PCE	0	3	20190501	IT3	92400118D574387	2553
6	999999	3	28.00	28.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
6	999999	3	28.00	28.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
6	999999	3	28.00	28.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
10	999999	3	20.00	20.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
10	999999	3	20.00	20.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
10	999999	3	20.00	20.00	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
10	999999	3	13.60	13.60	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
10	999999	3	13.60	13.60	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
10	999999	3	13.60	13.60	1	EUR	PCE	0	3	20190501	IT3	92400118L667009	2551
10	999999	3	13.60	13.60	1	EUR	PCE	0	3	20190501	IT3	92400118L667011	2551
100	999999	3	8.03	8.03	1	EUR	PCE	0	9	20190501	ITC	90019174A140572	2511
10	999999	3	8.70	8.70	1	EUR	PCE	0	3	20190501	ITC	90019174A140572	2511
100	999999	3	8.43	8.43	1	EUR	PCE	0	3	20190501	ITC	90019174A140572	2511
10	999999	3	8.70	8.70	1	EUR	PCE	0	3	20190501	ITC	90019174A140572	2511
100	999999	3	8.43	8.43	1	EUR	PCE	0	3	20190501	ITC	90019174A140572	2511
100	999999	3	8.43	8.43	1	EUR	PCE	0	3	20190501	ITC	90019174A140572	2511
10	999999	3	14.00	14.00	1	EUR	PCE	0	3	20190501	IT3	92400118A137018	2552
10	999999	3	14.00	14.00	1	EUR	PCE	0	3	20190501	IT3	92400118A137018	2552
10	999999	3	14.00	14.00	1	EUR	PCE	0	3	20190501	IT3	92400118A137018	2552
10	999999	3	10.00	10.00	1	EUR	PCE	0	3	20190501	IT3	92400118A137018	2552
10	999999	3	10.00	10.00	1	EUR	PCE	0	3	20190501	IT3	92400118A137018	2552
10	999999	3	6.95	6.95	1	EUR	PCE	0	1	20190501	IT3	92400118A137018	2552
10	999999	3	10.00	10.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	10.00	10.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	10.00	10.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	7.80	7.80	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	7.80	7.80	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	7.80	7.80	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	7.20	7.20	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	7.20	7.20	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	6.50	6.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	8.50	8.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	6.50	6.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	8.50	8.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	6.50	6.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	8.50	8.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	6.50	6.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	7.50	7.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	5.80	5.80	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	7.50	7.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	5.80	5.80	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552

Signify Classified - Internal

10	999999	3	7.50	7.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	5.80	5.80	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
10	999999	3	5.00	5.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130235	2552
12	999999	3	72.79	72.79	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	70.84	70.84	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	142.81	142.81	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	74.33	74.33	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	76.56	76.56	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
24	999999	3	74.97	74.97	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	76.56	76.56	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	75.42	75.42	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	211.81	211.81	1	EUR	PCE	0	3	20190501	IT1	90019174PA50323	2544
12	999999	3	274.10	274.10	1	EUR	PCE	0	3	20190501	IT1	90019174PA50323	2544
12	999999	3	236.72	236.72	1	EUR	PCE	0	3	20190501	IT1	90019174PA50323	2544
12	999999	3	83.78	83.78	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	80.96	80.96	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	100.86	100.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	102.99	102.99	1	EUR	PCE	0	3	20190501	IT1	90019174PA50323	2544
12	999999	3	102.99	102.99	1	EUR	PCE	0	3	20190501	IT1	90019174PA50323	2544
12	999999	3	54.11	54.11	1	EUR	PCE	0	3	20190501	ITV	90019174PA50323	2544
12	999999	3	54.11	54.11	1	EUR	PCE	0	3	20190501	ITV	90019174PA50323	2544
12	999999	3	54.11	54.11	1	EUR	PCE	0	3	20190501	ITV	90019174PA50323	2544
12	999999	3	54.11	54.11	1	EUR	PCE	0	3	20190501	ITV	90019174PA50323	2544
12	999999	3	74.88	74.88	1	EUR	PCE	0	3	20190501	IT1	90019174PA50323	2544
12	999999	3	74.88	74.88	1	EUR	PCE	0	3	20190501	IT1	90019174PA50323	2544
12	999999	3	74.88	74.88	1	EUR	PCE	0	3	20190501	IT1	90019174PA50278	2544
12	999999	3	55.88	55.88	1	EUR	PCE	0	3	20190501	ITV	90019174PA50323	2544
12	999999	3	261.64	261.64	1	EUR	PCE	0	3	20190501	ITV	90019174PA00346	2544
12	999999	3	261.64	261.64	1	EUR	PCE	0	3	20190501	ITV	90019174PA00346	2544
12	999999	3	55.88	55.88	1	EUR	PCE	0	3	20190501	ITV	90019174PA50278	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	9	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	9	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
12	999999	3	121.86	121.86	1	EUR	PCE	0	3	20190501	IT1	90019174PA50279	2544
6	999999	3	100.28	100.28	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	89.92	89.92	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
12	999999	3	107.10	107.10	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544

Signify Classified - Internal

12	999999	3	85.21	85.21	1	EUR	PCE	0	3	20190501	ITN	90019174PA00346	2544
1	999999	3	1.43	1.43	1	EUR	PCE	0	3	20190501	ITC	90019174A140551	2544
1	999999	3	5.39	5.39	1	EUR	PCE	0	3	20190501	ITC	90019174A140551	2544
1	999999	3	5.39	5.39	1	EUR	PCE	0	3	20190501	ITC	90019174A140551	2544
1	999999	3	1.43	1.43	1	EUR	PCE	0	3	20190501	ITC	90019174A140551	2544
1	999999	3	416.22	416.22	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0961
1	999999	3	94.05	94.05	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0961
1	999999	3	244.52	244.52	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0961
1	999999	3	244.52	244.52	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0961
1	999999	3	244.52	244.52	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0961
1	999999	3	46.08	46.08	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0961
1	999999	3	412.21	412.21	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0961
1	999999	3	400.21	400.21	1	EUR	PCE	0	2	20190501	ITS	90014035B550601	0961
1	999999	3	59.45	59.45	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	40.62	40.62	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	47.36	47.36	1	EUR	PCE	0	9	20190501	ITS	90014035B550601	0981
6	999999	3	40.62	40.62	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	44.47	44.47	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	132.65	132.65	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
2	999999	3	106.72	106.72	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	97.44	97.44	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0982
6	999999	3	77.18	77.18	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	83.28	83.28	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	62.37	62.37	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	68.79	68.79	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	44.10	44.10	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	66.62	66.62	1	EUR	PCE	0	2	20190501	ITS	90014035B550601	0981
1	999999	3	412.13	412.13	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	30.32	30.32	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	2.57	2.57	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2511
1	999999	3	2.57	2.57	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2511
6	999999	3	40.40	40.40	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
6	999999	3	40.40	40.40	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	65.36	65.36	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	65.49	65.49	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	80.04	80.04	1	EUR	PCE	0	2	20190501	ITS	90014035B550601	0981
6	999999	3	52.11	52.11	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	47.36	47.36	1	EUR	PCE	0	9	20190501	ITS	90014035B550601	0981
1	999999	3	66.71	66.71	1	EUR	PCE	0	2	20190501	ITS	90014035B550601	0981
1	999999	3	486.49	486.49	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	369.37	369.37	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0981
1	999999	3	479.28	479.28	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0971
1	999999	3	530.72	530.72	1	EUR	PCE	0	3	20190501	ITS	90014035B550601	0971
6	999999	3	34.38	34.38	1	EUR	PCE	0	9	20190501	ITK	90019174AU57480	2531

Signify Classified - Internal

6	999999	3	5.03	5.03	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	5.03	5.03	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	4.46	4.46	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	4.46	4.46	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	3.94	3.94	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	3.94	3.94	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	3.71	3.71	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	3.71	3.71	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	4.20	4.20	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	4.20	4.20	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	3.26	3.26	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	3.26	3.26	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	3.91	3.91	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	4.20	4.20	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	3.26	3.26	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	3.91	3.91	1	EUR	PCE	0	2	20190501	IT4	92400118L703947	2551
6	999999	3	4.94	4.94	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	4.49	4.49	1	EUR	PCE	0	2	20190501	IT4	92400118A137064	2552
6	999999	3	6.46	6.46	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
6	999999	3	6.46	6.46	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
6	999999	3	5.00	5.00	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
6	999999	3	5.00	5.00	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
6	999999	3	4.06	4.06	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
6	999999	3	4.06	4.06	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
8	999999	3	7.00	7.00	1	EUR	PCE	0	9	20190501	IT4	92400118A137064	2552
8	999999	3	5.23	5.23	1	EUR	PCE	0	9	20190501	IT4	92400118A137064	2552
6	999999	3	9.23	9.23	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
6	999999	3	9.23	9.23	1	EUR	PCE	0	2	20190501	IT4	92400118L663901	2551
6	999999	3	5.73	5.73	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
6	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	15.49	15.49	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L703946	2551
4	999999	3	8.93	8.93	1	EUR	PCE	0	1	20190501	IT3	92400118L667496	2551
4	999999	3	16.39	16.39	1	EUR	PCE	0	1	20190501	IT3	92400118A137022	2552
4	999999	3	11.90	11.90	1	EUR	PCE	0	1	20190501	IT3	92400118A137018	2552
4	999999	3	11.90	11.90	1	EUR	PCE	0	1	20190501	IT3	92400118A137018	2552
4	999999	3	12.29	12.29	1	EUR	PCE	0	1	20190501	IT3	92400118A137022	2552
4	999999	3	9.83	9.83	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	10.65	10.65	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	8.19	8.19	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	9.83	9.83	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552

Signify Classified - Internal

4	999999	3	7.37	7.37	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
4	999999	3	4.91	4.91	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2552
6	999999	3	12.21	12.21	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	12.21	12.21	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
6	999999	3	12.21	12.21	1	EUR	PCE	0	1	20190501	IT3	92400118L667009	2551
4	999999	3	11.47	11.47	1	EUR	PCE	0	1	20190501	IT3	92400118L667011	2551
4	999999	3	10.65	10.65	1	EUR	PCE	0	1	20190501	IT3	92400118A130183	2551
25	999999	3	11.91	11.91	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	11.91	11.91	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	12.74	12.74	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	10.77	10.77	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	10.77	10.77	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	22.06	22.06	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
10	999999	3	5.61	5.61	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
40	999999	3	53.89	53.89	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522
40	999999	3	9.99	9.99	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
25	999999	3	21.72	21.72	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	12.74	12.74	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
50	999999	3	26.10	26.10	1	EUR	PCE	0	3	20190501	ITX	90019174A140524	2512
50	999999	3	26.10	26.10	1	EUR	PCE	0	2	20190501	ITX	90019174A140524	2512
50	999999	3	22.13	22.13	1	EUR	PCE	0	3	20190501	ITX	90019174A140524	2512
50	999999	3	22.13	22.13	1	EUR	PCE	0	3	20190501	ITX	90019174A140524	2512
50	999999	3	22.13	22.13	1	EUR	PCE	0	3	20190501	ITX	90019174A140524	2512
25	999999	3	10.07	10.07	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	22.06	22.06	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
120	999999	3	3.97	3.97	1	EUR	PCE	0	3	20190501	ITA	90019174A540011	2511
20	999999	3	3.97	3.97	1	EUR	PCE	0	3	20190501	ITA	90019174A540011	2511
20	999999	3	3.97	3.97	1	EUR	PCE	0	3	20190501	ITA	90019174A540011	2511
25	999999	3	40.85	40.85	1	EUR	PCE	0	3	20190501	ITJ	90019174Q562838	257
10	999999	3	26.79	26.79	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	28.08	28.08	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	20.41	20.41	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	22.33	22.33	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	20.41	20.41	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	20.41	20.41	1	EUR	PCE	0	2	20190501	ITF	90019174PA10409	2521
25	999999	3	32.21	32.21	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	8.84	8.84	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	74.97	74.97	1	EUR	PCE	0	9	20190501	ITF	90019174PA10405	2521
25	999999	3	8.58	8.58	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	29.63	29.63	1	EUR	PCE	0	9	20190501	ITF	90019174PA10409	2521
25	999999	3	8.84	8.84	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	8.84	8.84	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	27.37	27.37	1	EUR	PCE	0	3	20190501	ITJ	90019174PA10409	2521
25	999999	3	25.60	25.60	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521

Signify Classified - Internal

25	999999	3	25.60	25.60	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	26.90	26.90	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	26.90	26.90	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
40	999999	3	9.40	9.40	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.40	9.40	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
25	999999	3	13.49	13.49	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	13.49	13.49	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	13.49	13.49	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	18.96	18.96	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	18.96	18.96	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
6	999999	3	67.58	67.58	1	EUR	PCE	0	3	20190501	ITX	90019174A140548	2511
40	999999	3	9.40	9.40	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
10	999999	3	5.61	5.61	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
25	999999	3	10.77	10.77	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
120	999999	3	3.97	3.97	1	EUR	PCE	0	3	20190501	ITA	90019174A540011	2511
10	999999	3	5.61	5.61	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
40	999999	3	9.47	9.47	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
25	999999	3	20.82	20.82	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
10	999999	3	20.64	20.64	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	22.34	22.34	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	15.24	15.24	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	18.22	18.22	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	15.24	15.24	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	15.24	15.24	1	EUR	PCE	0	2	20190501	ITF	90019174PA10409	2521
25	999999	3	25.19	25.19	1	EUR	PCE	0	9	20190501	ITF	90019174PA10405	2521
25	999999	3	8.03	8.03	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	20.54	20.54	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	49.41	49.41	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	26.45	26.45	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	7.81	7.81	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	8.03	8.03	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	20.54	20.54	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	49.41	49.41	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	26.45	26.45	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	8.03	8.03	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	20.54	20.54	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	8.03	8.03	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	20.38	20.38	1	EUR	PCE	0	3	20190501	ITJ	90019174PA10409	2521
25	999999	3	25.44	25.44	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	25.44	25.44	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	26.73	26.73	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	26.73	26.73	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	44.98	44.98	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
40	999999	3	48.35	48.35	1	EUR	PCE	0	9	20190501	ITZ	90019174PA10246	2522

Signify Classified - Internal

40	999999	3	9.12	9.12	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.12	9.12	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
25	999999	3	11.13	11.13	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	14.47	14.47	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	11.13	11.13	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	14.47	14.47	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	11.13	11.13	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	19.04	19.04	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	19.04	19.04	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	19.04	19.04	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	19.04	19.04	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	28.39	28.39	1	EUR	PCE	0	3	20190501	ITJ	90019174PA10409	2521
6	999999	3	96.97	96.97	1	EUR	PCE	0	9	20190501	ITB	90019174A540060	2511
8	999999	3	96.97	96.97	1	EUR	PCE	0	9	20190501	ITB	90019174A540060	2511
40	999999	3	9.12	9.12	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	9.12	9.12	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
10	999999	3	3.05	3.05	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
100	999999	3	4.54	4.54	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
40	999999	3	9.47	9.47	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
10	999999	3	5.61	5.61	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
25	999999	3	18.41	18.41	1	EUR	PCE	0	9	20190501	ITF	90019174PA10411	2521
25	999999	3	19.33	19.33	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	19.33	19.33	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
40	999999	3	8.59	8.59	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
10	999999	3	3.53	3.53	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
100	999999	3	6.01	6.01	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
25	999999	3	47.10	47.10	1	EUR	PCE	0	3	20190501	ITJ	90019174Q562835	257
10	999999	3	20.64	20.64	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	22.34	22.34	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	15.24	15.24	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	18.22	18.22	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	15.24	15.24	1	EUR	PCE	0	3	20190501	ITF	90019174PA10409	2521
10	999999	3	15.24	15.24	1	EUR	PCE	0	2	20190501	ITF	90019174PA10409	2521
25	999999	3	49.41	49.41	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	7.85	7.85	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	49.41	49.41	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	26.45	26.45	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	7.61	7.61	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	27.60	27.60	1	EUR	PCE	0	2	20190501	ITF	90019174PA10409	2521
25	999999	3	7.85	7.85	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	49.41	49.41	1	EUR	PCE	0	3	20190501	ITF	90019174PA10405	2521
25	999999	3	7.85	7.85	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	7.85	7.85	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	20.38	20.38	1	EUR	PCE	0	3	20190501	ITJ	90019174PA10409	2521

Signify Classified - Internal

25	999999	3	21.48	21.48	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	21.48	21.48	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	19.15	19.15	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	19.15	19.15	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	40.55	40.55	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
25	999999	3	42.84	42.84	1	EUR	PCE	0	3	20190501	ITJ	90019174Q567589	2521
25	999999	3	10.74	10.74	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	14.47	14.47	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	10.74	10.74	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
25	999999	3	13.78	13.78	1	EUR	PCE	0	9	20190501	ITF	90019174PA10411	2521
25	999999	3	10.74	10.74	1	EUR	PCE	0	3	20190501	ITF	90019174PA10406	2521
10	999999	3	5.61	5.61	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	8.02	8.02	1	EUR	BLI	0	3	20190501	ITA	90019174A540014	2511
100	999999	3	4.54	4.54	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
25	999999	3	17.93	17.93	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	17.93	17.93	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	17.93	17.93	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
25	999999	3	17.93	17.93	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
100	999999	3	3.16	3.16	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
25	999999	3	12.92	12.92	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
25	999999	3	30.14	30.14	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
25	999999	3	14.75	14.75	1	EUR	PCE	0	3	20190501	ITJ	90019174Q560903	257
10	999999	3	19.48	19.48	1	EUR	PCE	0	3	20190501	ITX	90019174A140532	2511
25	999999	3	20.98	20.98	1	EUR	PCE	0	3	20190501	ITF	90019174PA10411	2521
40	999999	3	8.59	8.59	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
40	999999	3	8.59	8.59	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10481	2522
6	999999	3	22.29	22.29	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
6	999999	3	22.29	22.29	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
6	999999	3	22.29	22.29	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
6	999999	3	22.29	22.29	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
6	999999	3	22.29	22.29	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
6	999999	3	22.29	22.29	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
6	999999	3	22.29	22.29	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
5	999999	3	6.33	6.33	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2512
5	999999	3	6.33	6.33	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2512
5	999999	3	6.33	6.33	1	EUR	PCE	0	9	20190501	ITX	90019174A140565	2512
5	999999	3	5.39	5.39	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2512
5	999999	3	5.39	5.39	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
5	999999	3	5.39	5.39	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
5	999999	3	5.39	5.39	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
5	999999	3	5.13	5.13	1	EUR	PCE	0	9	20190501	ITX	90019174A140565	2512
5	999999	3	5.13	5.13	1	EUR	PCE	0	9	20190501	ITX	90019174A140565	2512
5	999999	3	5.13	5.13	1	EUR	PCE	0	9	20190501	ITX	90019174A140565	2512
50	999999	3	2.93	2.93	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2512

Signify Classified - Internal

50	999999	3	2.93	2.93	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2512
50	999999	3	2.93	2.93	1	EUR	PCE	0	3	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
20	999999	3	9.68	9.68	1	EUR	PCE	0	2	20190501	ITX	90019174A140565	2512
25	999999	3	41.20	41.20	1	EUR	PCE	0	3	20190501	ITJ	90019174Q562838	2523
25	999999	3	14.26	14.26	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	14.26	14.26	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	14.26	14.26	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	12.89	12.89	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
25	999999	3	12.89	12.89	1	EUR	PCE	0	3	20190501	ITZ	90019174PA10480	2523
10	999999	3	2.45	2.45	1	EUR	PCE	0	9	20190501	ITC	90019174A140521	2512
100	999999	3	4.60	4.60	1	EUR	PCE	0	3	20190501	ITA	90019174A540014	2511
10	999999	3	5.61	5.61	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	5.61	5.61	1	EUR	PCE	0	3	20190501	ITC	90019174A140569	2511
10	999999	3	17.07	17.07	1	EUR	PCE	0	3	20190501	ITX	90019174A140532	2511
6	999999	3	75.13	75.13	1	EUR	PCE	0	3	20190501	ITX	90019174A140548	2511
4	999999	3	12.00	12.00	1	EUR	PCE	0	3	20190501	ITT	92400118L707012	2552
10	999999	3	8.50	8.50	1	EUR	PCE	0	3	20190501	IT3	92400118L667496	2551
12	999999	3	6.50	6.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
12	999999	3	6.50	6.50	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
1	999999	3	2.45	2.45	1	EUR	PCE	0	3	20190501	ITC	90019175A140551	2512
6	999999	3	7.00	7.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
6	999999	3	7.90	7.90	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
6	999999	3	8.80	8.80	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
6	999999	3	9.20	9.20	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
6	999999	3	9.20	9.20	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
6	999999	3	12.00	12.00	1	EUR	PCE	0	3	20190501	IT3	92400118A130183	2552
25	999999	3	8.84	8.84	1	EUR	PCE	0	3	20190502	ITF	90019174PA10411	2521

Raggruppamento
T12 Lamps
T12 Lamps
Municipal & Industrial Water
Municipal & Industrial Water
Residential Water & Air
Residential Water & Air
Municipal & Industrial Water
Residential Water & Air
Residential Water & Air
Residential Water & Air
Commercial & Professional Air
Commercial & Professional Air
Commercial & Professional Air
Residential Water & Air
Commercial & Professional Air
Municipal & Industrial Water
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
Twister Entry
CFLi Specialties
CFLi Specialties
Color and BlackLightBlue
Color and BlackLightBlue
Insect trap

Signify Classified - Internal

PL-T lamps
PL-T lamps
PL-T lamps
PL-T lamps
PLED
PLED
Insect trap
Color and BlackLightBlue
PL-R lamps
PL-R lamps
PL-R lamps
PL-R lamps
PL-Q lamps
PL-Q lamps
PL-Q lamps
PL-Q lamps
PL-Q lamps
PL-Q lamps
PL-Q lamps
PL-Q lamps
PL-Q lamps
Commercial & Professional Air
Residential Water & Air
PLED
PLED
PLED
PLED
PLED
PLED
Medical
Insect trap
Master Stick
Master Stick
Master Stick
Master Stick
Master Stick
Master Stick
CFLi Specialties
PLED
PLED
PLED
PLED
PLED
PLED

Signify Classified - Internal

PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
Commercial & Professional Air
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-L lamps
PL-S lamps
PL-S lamps
PL-S lamps
PL-S lamps
PL-S lamps
PL-S lamps
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Candles & Lustres - Glass

Signify Classified - Internal

T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
T5 - HF
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
AR111
PAR38
PAR38
PAR30S/L
PAR30S/L
PAR30S/L
PAR16/20
PAR16/20
PAR16/20
PAR16/20

Signify Classified - Internal

GU10 - Premium
GU10 - Premium
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Bulbs Premium
Bulbs Premium
Bulbs Premium
Bulbs Premium
Bulbs Premium
Bulbs Premium
Bulbs Premium
Bulbs Premium
MHN-TD
MHN-TD
Sports
Sports
Sports
Sports
Sports
Sports
Sports
Sports
Sports
Sports
Sports
Sports
GU10 - Value
GU10 - Value
T12 Lamps
T12 Lamps
T12 Lamps
T12 Lamps
T12 Lamps
Candles & Lustres - Plastic
Candles & Lustres - Plastic
GU10 - Value
GU10 - Value
GU10 - Value
MAG D57 Undivided
Candles & Lustres - Plastic
Candles & Lustres - Plastic
GU10 - Affordable
Bulbs Premium
Bulbs Premium
Bulbs Premium

Signify Classified - Internal

Bulbs Entry - Plastic
Candles & Lustres - Glass
Candles & Lustres - Glass
Bulbs Glass - Clear
Bulbs Glass - Clear
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Bulbs Glass - Clear
Candles & Lustres - Glass
Bulbs Glass - Clear
Bulbs Glass - Clear
MR16 - Value
MR16 - Value
MR16 - Affordable
MR16 - Affordable
MR16 - Affordable
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
GU10 - Affordable
GU10 - Affordable
GU10 - Affordable
GU10 - Affordable
GU10 - Affordable
Bulbs Premium
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted

Signify Classified - Internal

Insect trap
GLS IR Heat Reflector
GLS IR Heat Reflector
GLS IR Heat Reflector
GLS IR Heat Reflector
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Bulbs Glass - Frosted
Candles & Lustres - Glass
Candles & Lustres - Glass
Twister HL
Twister HL
Twister HL
Twister HL
Twister HL
Twister HL
HPI & QMH
Sports
Sports
Sports
HPI & QMH
Municipal & Industrial Water
eHID Outdoor
eHID Outdoor
eHID Indoor PV
eHID Indoor PV
eHID Indoor PV
eHID Outdoor
eHID Outdoor
eHID Outdoor

Signify Classified - Internal

Bulbs Deco
MV DE ES Linears
LV ES Reflectors
LV Capsules
MV DE ES Linears
MV DE ES Linears
LV ES Capsules
LV ES Reflectors
Bulbs Deco
LV ES Capsules
MV DE ES Linears
LV ES Reflectors
LV Capsules
MV DE ES Linears
LV ES Capsules
MV DE ES Linears
MV DE ES Linears
Bulbs Deco
Bulbs Deco
Bulbs Deco
Bulbs Deco
Bulbs Deco
Bulbs Deco
Bulbs Deco
Bulbs Deco
Circular & U-bent lamps
Circular & U-bent lamps
Circular & U-bent lamps
Circular & U-bent lamps
Circular & U-bent lamps
Circular & U-bent lamps
Circular & U-bent lamps
Circular & U-bent lamps
CSLS
CSLS
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
Bulbs Entry - Plastic
Bulbs Entry - Plastic

Signify Classified - Internal

Spots - Others
Spots - Others
Spots - Others
Spots - Others
Spots - Others
Spots - Others
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Candles & Lustres - Plastic
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Premium
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Premium
T8 - HF - Core
T8 - HF - Entry
T8 - EM/Mains - Core
T8 - HF - Core
T8 - HF - Entry
T8 - EM/Mains - Core
T8 - HF - Core
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Premium
T8 - HF - Core
T8 - HF - Entry
T8 - EM/Mains - Core
T8 - HF - Core
T8 - HF - Entry
T8 - EM/Mains - Core
T8 - HF - Core
T8 - HF - Entry

Signify Classified - Internal

GU10 - Affordable
GU10 - Affordable
GU10 - Affordable
GU10 - Affordable
GU10 - Affordable
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CMH Outdoor
CDM Lamp
CDM Lamp
CDM Lamp
CMH Outdoor
CMH Outdoor
CDM Elite Lamp
CDM Lamp
CDM Lamp
CDM Lamp
CDM Lamp
CDM Lamp
CDM Lamp
CDM Lamp
CDM Lamp
CDM Lamp
CDM Elite Lamp
CDM Lamp
CMH Outdoor
CMH Outdoor
CDM Elite Lamp
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CDM Elite Reflector
CMH Outdoor
CMH Outdoor
CMH Outdoor

Signify Classified - Internal

Spots - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Candle - B-Brand & PL
Candle - B-Brand & PL
Candle - B-Brand & PL
Candle - B-Brand & PL
Candle - B-Brand & PL
Candle - B-Brand & PL
Candle - B-Brand & PL
Candle - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Bulbs - B-Brand & PL
Bulbs - B-Brand & PL
Bulbs - B-Brand & PL
Bulbs - B-Brand & PL
Bulbs - B-Brand & PL
Bulbs - B-Brand & PL
Bulbs - B-Brand & PL
Spots - B-Brand & PL
Spots - B-Brand & PL
Bulbs - B-Brand & PL
Bulbs - B-Brand & PL
Spots - Others
Spots - Others
Candles & Lustres - Glass
Bulbs Glass - Clear
Candles & Lustres - Glass
Candles & Lustres - Glass
Candles & Lustres - Glass
Bulbs Glass - Clear
MR16 - Value
MR16 - Affordable
MR16 - Affordable
MR16 - Value
Spots - Others
Spots - Others
Spots - Others
Spots - Others

Signify Classified - Internal

Spots - Others
Spots - Others
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Entry - Plastic
Bulbs Premium
Spots - Others
T5 lamps Miniature
T5 lamps Miniature
T5 lamps Miniature
T5 lamps Miniature
T5 lamps Miniature
Insect trap
MV DE ES Linears
T5 Lamps Others
T5 lamps MASTER
T8 lamps Super 80
T5 lamps Miniature
LV Reflectors
LV Reflectors
LV Reflectors
LV Reflectors
LV Reflectors
T5 lamps Miniature
Insect trap
GLS Special Service
GLS Special Service
GLS Special Service
Reprography
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Long Life
T8 lamps Super 80
T8 lamps Long Life
T8 lamps Super 80
T8 lamps Special Purpose
T8 lamps Super 80
T8 lamps Super 80
T8 lamps Special Purpose
Color and BlackLightBlue

Signify Classified - Internal

T5 lamps MASTER
T5 lamps MASTER
T8 lamps Energy Advantage
T8 lamps Super 80
T8 lamps Energy Advantage
T8 lamps Super 80
T8 lamps Energy Advantage
T8 lamps Super 80
T8 lamps Super 80
T8 lamps Super 80
T8 lamps Super 80
T8 lamps Special Purpose
GLS PAR Reflector
GLS PAR Reflector
T5 lamps MASTER
T5 lamps MASTER
Tubular & Appliance lamps
Tubular & Appliance lamps
T5 lamps MASTER
MV DE ES Linears
T8 lamps Super 80
T8 lamps Super 80
T8 lamps Super 80
T5 lamps MASTER
Tubular & Appliance lamps
Tubular & Appliance lamps
Medical
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Special Purpose
T8 lamps Long Life
T8 lamps Super 80
T8 lamps Long Life
T8 lamps Long Life
T8 lamps Super 80
T8 lamps Special Purpose
T8 lamps Super 80
T8 lamps Long Life
T8 lamps Super 80
T8 lamps Super 80
T8 lamps Special Purpose

