

PHILIPS

Badkamer





1.



3.



2.

1. **Hotstone 34049 11 16**
H67 L146 D147
LED - 2x 2,5W incl. - 350lm
15.000 hrs - Class II - IP44
metal - synthetics

2. **Hotstone 34050 11 16**
H59 L346 D144
LED - 4x 2,5W incl. - 2x 350lm
15.000 hrs - Class II - IP44
metal - synthetics

3. **Care 34107 11 16**
H180 L91 D134
E14 - 1x 12W incl. - 737lm
Class II - IP44
glass - metal



1.



2.



3.



4.

1. **Fit 34058 11 16**
 H63 L333 D64
 LED - 2x 2,5W incl. - 350lm
 15.000 hrs - Class II - IP44
 metal - synthetics



2. **Fit 34059 11 16**
 H63 L483 D67
 LED - 3x 2,5W incl. - 520lm
 15.000 hrs - Class II - IP44
 metal - synthetics



3. **Vitalise 34093 11 16**
 H60 L388 D77
 G5 - 1x 8W incl. - 470lm
 Class II - IP44
 glass - metal



4. **Vitalise 34094 11 16**
 H60 L616 D77
 G5 - 1x 13W incl. - 1000lm
 Class II - IP44
 glass - metal





1.



2.



3.

-
1. **Salts ceiling lamp 32010 17 16**
 H100 D315
 E27 - 1x 20 W incl.
 Class I - IP44
 mat chrome - metal

-
2. **Fountain ceiling lamp 32020 67 16**
 H95 D350
 E27 - 1x 20 W incl.
 Class I - IP21
 mat glass - glass

-
3. **Pool ceiling lamp 32081 31 16**
 H110 D270
 E27 - 1x 20 W incl.
 Class II - IP44
 white - glass

1.



2.



1.

Baume 32053 31 16

H71 L262 D262
LED - 3x 2,5W incl. - 530lm
15.000 hrs - Class II - IP44
synthetics

2.

Cool 32063 31 16

H78 L352 D352
LED - 3x 4W incl. - 820lm
15.000 hrs - Class II - IP44
metal - synthetics

3.

Seru 32065 31 16

H66 L364 D340
LED - 3x 4,7W incl. - 1060lm
15.000 hrs - Class II - IP44
metal - synthetics



1.



2.

1. **Beach 32070 17 16**
H55 L360 D360
2GX13 - 1x 40W incl. - 3300lm
Class I - IP44
synthetics - metal

2. **Thermen 32082 87 16**
H65 L400 D400
2GX13 - 1x 40W incl. - 3300lm
Class I - IP44
glass - metal



1.

1. **Spa 32005 31 16**
H120 L260 D260
E27 - 1x 20W incl. - 1250lm
Class II - IP44
glass



1.



2.

1. **Roots recessed 59902 17 16**

H39 D100
GU10 - 3x 35W incl.
Class II - IP23
mat chrome - metal

2. **Roots recessed 59902 11 16**

H39 D100
GU10 - 3x 35 W incl.
Class II - IP23
chrome - metal




1.



2.



3.



2.

1. **Wash 59905 11 16**
 L105 D105 R150 C90 x90
 GU10 - 1x 35W incl.
 Class II - IP44
 metal



2. **Wash 59905 17 16**
 L105 D105 R150 C90 x90
 GU10 - 1x 35W incl. -
 Class II - IP44
 metal



3. **Tub 59925 17 16**
 L92 D92 R57 C80 x80
 Power LED - 1x 7,5W incl. - 350lm
 Class III - IP65
 glass



