

LED Inspection lamp

With 100-240V cable – CBL 30

3211 008 20211



www.philips.com/support

EN	LED Inspection lamp
DE	LED-Inspektionslampe
FR	Lampe baladeuse à LED
NL	LED-inspectielamp
ES	Lámpara de inspección LED
IT	Lampada di ispezione a LED
PT	Lâmpada de inspeção LED
RU	Светодиодный инспекционный фонарь
PL	Lampa inspekcyjna LED
SV	Inspektionslampe med LED
NO	LED-inspeksjonslampe
DA	LED inspektionslampe
SU	LED-tarkastuslamppu
AR	المصباح أو مصباح LED

PHILIPS

English

Before you start

Thank you for buying the Philips LED Inspection lamp. Its high-quality LED lighting offers a powerful wide-angle light output that will let you work in your workshop, garage or any other professional environment under the best lighting conditions.



The Philips LED Inspection lamp bears the official Philips Original Quality Equipment seal. It is your assurance that it is manufactured or licensed by Philips using the highest-quality components and materials. Philips, #1 in automotive lighting worldwide, brings you the professional lighting tool you need. It combines Philips Original Quality, durability, and simple-to-use design.

Important

Please read this user guide carefully before using your LED inspection lamp. This guide contains important health and safety information.







If you need further assistance, please dial the Philips Lighting consumer care **toll-free number** in your region

Europe +800 7445 47 75





Or visit your local Philips Dealer

For more information visit
www.philips.com


















EN	Important health and safety information
DE	Wichtige Sicherheitshinweise
FR	Instructions de sécurité
NL	Belangrijke veiligheidsinformatie
ES	Importante: información de seguridad
IT	Informazioni importanti sulla sicurezza
PT	Instruções de segurança
RU	Инструкции по безопасности
PL	Ważne zalecenia bezpieczeństwa
SV	Viktig säkerhetsinformation
NO	Kople støpselet til en elektrisk stikkontakt
DA	Vigtige sikkerhedsoplysninger
SU	Tärkeitä turvallisuustietoja



EN	How to operate the Philips LED Inspection lamp
DE	Betrieb der Philips LED-Inspektionslampe
FR	Comment utiliser la lampe baladeuse à LED Philips
NL	Gebruiksaanwijzing voor de Philips LED-inspectielamp
ES	Cómo funciona la lámpara de inspección LED de Philips
IT	Come far funzionare la lampada di ispezione a LED Philips
PT	Modo de utilização da lâmpada de inspeção LED da Philips
RU	Принцип функционирования светодиодного инспекционного фонаря Philips
PL	Obsługa lampy inspekcyjnej LED Philips
SV	Användning av Philips inspektionslampe med LED
NO	Hvordan bruke Philips LED-inspeksjonslampe
DA	Sådan bruges Philips LED inspektionslampe
SU	Miten LED-tarkastuslamppua käytetään



Technical specifications

Description	EU
 Operating line voltage	100~240V
 Power consumption	5W
 Number of LED	10
 Light output	330 lumens
 Focus light	90 lumens
 Light angle	100°
 Color temperature	6500 K
 Impact protection rating	IK07
 Ingress protection rating	IP54
 Operating temperature	-10°C to 40°C
 Cable Operating temperature	-25°C to 50°C
 Storage temperature	-20°C to 60°C
 Lamp dimensions (without cable)	∅ 27 x 475 mm
 Cable Length	6 meters
 Product weight (with cable) Product weight (without cable)	800 g 220 g
 360° hook	360° adjustable magnetic hook
 Plug	European plug

LED Range overview



Pen Professional Pen Premium

LED Penlight



CBL 20 CBL 30

**LED Inspection lamps
with cables**



RCH20



RCH30



MDLS

**LED Inspection lamps
rechargeable**



©2013 Koninklijke Philips Electronics N.V.
all rights reserved

www.philips.com/automotive