


# OccuSwitch - LRM1070 Movement Detector

LRM1070 is a movement detector with a built in lighting switch. The unit is designed for the automatic switching of light in indoor applications, with a light sensor range between 10 and 1000 lux. It comes with 360D movement detection, with built in photo cell sensor and adjustable switch of delay (1min - 30min). It is capable of switching 1380 VA. The product also comes with an optional surface mount box accessory.



Product ID	A max.	B max.	C max.	D max.
Occuswitch	95	80	50	2
Dimensions in mm				

## OccuSwitch - LRM1070

Shortcode	Description	Min Order Quantity	Carton Quantity
LRM1070	LRM1070/00 Sensr Mov Det St	1	42
LRH1070	LRH1070/00 Sensr Surface Box	42	42