


HID-AspiraVision and PrimaVision

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver. PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

- Benefits:**
- SOFT START allows installation with fewer circuit breakers; Loop Through (I type) allows faster, cost-efficient installation.
 - Longer lifetime.
 - Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higher-wattage lamps in the future.
 - Optimal lamp performance thanks to minimal lamp power tolerance.
 - Eliminates all visible lamp flicker.

- Features:**
- Improved thermal performance.
 - Low electromagnetic interference.
 - Voltage drop detection.
 - Lamp end-of-life detection.
 - High Tambient and Tcase temperatures.
 - Long lifetime of 40,000 hours.


"I" TYPE



| Product ID | Length A1 | Fixing Hole Distance Length A2 | Width B1 | Height C1 | Fixing Hole Diameter D1 |
|---------------------------|-----------|--------------------------------|----------|-----------|-------------------------|
| HID-AV C 35-70 /I CDM | 189.2 | 170.7 | 83.5 | 34.7 | 4.8 |
| HID-PV C 100 & 150 /I CDM | 224 | 206 | 82.7 | 34.2 | 4.8 |

Dimensions in mm

"S" TYPE



| Product ID | Length A1 | Fixing Hole Distance Length A2 | Width B1 | Height C1 | Fixing Hole Diameter D1 |
|-----------------------|-----------|--------------------------------|----------|-----------|-------------------------|
| HID-AV C 35-70 /S CDM | 110 | 98.5 | 75 | 32.1 | 4.5 |
| HID-PV C 100 /S CDM | 135 | 123.5 | 75 | 32 | 4.5 |
| HID-PV C 150 /S CDM | 135 | 123.5 | 75 | 32 | 4.8 |

Dimensions in mm

HID-Aspiravision and Primavision

| Shortcode | Description | Wattage (W) | Voltage | Min Order Quantity | Carton Qty |
|------------------|--|-------------|---------|--------------------|------------|
| HIDAVC355070ICDM | HID-AV C 35-70 /I CDM 220-240V 50/60Hz | 35/50/70 | 220-240 | 1 | 12 |
| HIDAVC355070SCDM | HID-AV C 35-70 /S CDM 220-240V 50/60Hz | 35/50/70 | 220-240 | 1 | 12 |
| HIDPVC100ICDM | HID-PV C 100 /I CDM 220-240V SOFT START | 100 | 220-240 | 10 | 10 |
| HIDPVC150ICDM | HID-PV C 150 /I CDM 220-240V 50/60Hz 190 | 150 | 220-240 | 10 | 10 |
| HIDPVC100SCDM | HID-PV C 100 /S CDM 220-240V 50/60Hz | 100 | 220-240 | 10 | 10 |
| HIDPVC150SCDM | HID-PV C 150 /S CDM 220-240V 50/60Hz | 150 | 220-240 | 10 | 10 |