

# PHILIPS

## MASTER LED lyskilder



El.nr	Produktnavn	Effekt (W)	Erstatter (W)	Farge-temp. (K)	Sokkel	Spredn. vinkel	Levetid (i tusen timer)	Lm	Cd	EEL	Dimbar
<b>MASTER LEDbulb Glødelampeerstattere</b>											
37 114 00	Filament 4,3-40W E27 klar	4,3	40	2700	E27	230	15	470	-	A+	Nei
37 114 01	Filament 7,5-60W E27 klar	7,5	60	2700	E27	330	15	806	-	A+	Nei
37 111 33	LED Normal 6-40W E27 klar Dimtone	6	40	2200-2700	E27	230	25	470	-	A+	Ja
37 111 34	LED Normal 9-60W E27 klar Dimtone	9	60	2200-2700	E27	230	25	806	-	A+	Ja
38 619 80	LED Normal 13-75W E27 827	13	75	2700	E27	310	25	1055	-	A+	Ja
38 619 79	LED Normal 13-75W B22 827	13	75	2700	B22	310	25	1055	-	A+	Ja
38 619 78	LED Normal 18-100W E27 827	18	100	2700	E27	340	25	1521	-	A+	Ja
38 619 77	LED Normal 18-100W B22 827	18	100	2700	B22	340	25	1521	-	A+	Ja



<b>MASTER LED Krone, illum og mignon - nå med DimTone!</b>											
37 110 34	LED illum flame 4-25W E14 klar	4	25	2700-2200	E14	-	25	250	-	A+	Ja
37 110 30	LED mignon 4-25W E14 klar	4	25	2700-2200	E14	-	25	250	-	A+	Ja
37 110 35	LED illum 4-25W E14 klar	4	25	2700-2200	E14	-	25	250	-	A+	Ja
37 110 56	LED krone 4-25W E27 klar	4	25	2700-2200	E27	-	25	250	-	A+	Ja
37 110 58	LED mignon flame 6-40W E14 klar	6	40	2700-2200	E14	-	25	470	-	A+	Ja
37 110 57	LED mignon 6-40W E14 klar	6	40	2700-2200	E14	-	25	470	-	A+	Ja
37 110 66	LED illum 6-40W E14 klar	6	40	2700-2200	E14	-	25	470	-	A+	Ja
37 110 67	LED krone 6-40W E27 klar	6	40	2700-2200	E27	-	25	470	-	A+	Ja



<b>MASTER LEDspot Perfekt erstatning for halogenlamper</b>											
<b>Ra90</b>											
37 110 68	LED spot 230V 4-35W GU10 927 25D	4	35	2700	GU10	25	50	250	925	A+	Ja
37 110 76	LED spot 230V 4-35W GU10 927 40D	4	35	2700	GU10	40	50	262	560	A+	Ja
37 110 69	LED spot 230V 4-35W GU10 930 25D	4	35	3000	GU10	25	50	260	962	A+	Ja
37 110 84	LED spot 230V 4-35W GU10 930 40D	4	35	3000	GU10	40	50	272	582	A+	Ja
37 110 99	LED spot 230V 5,4-50W GU10 927 25D	5,4	50	2700	GU10	25	50	360	1350	A+	Ja
37 111 05	LED spot 230V 5,4-50W GU10 927 40D	5,4	50	2700	GU10	40	50	378	800	A+	Ja
37 111 03	LED spot 230V 5,4-50W GU10 930 25D	5,4	50	3000	GU10	25	50	360	1350	A+	Ja
37 111 07	LED spot 230V 5,4-50W GU10 930 40D	5,4	50	3000	GU10	40	50	378	800	A+	Ja



<b>Dimtone</b>											
37 111 09	LED spot 230V DimTone 4-35W GU10 25D	4	35	2700-2200	GU10	25	50	280	1000	A+	Ja
37 111 10	LED spot 230V DimTone 4-35W GU10 40D	4	35	2700-2200	GU10	40	50	280	600	A+	Ja
37 111 11	LED spot 230V DimTone 4,5-50W GU10 25D	4,5	50	2700-2200	GU10	25	50	355	1400	A+	Ja
37 111 12	LED spot 230V DimTone 4,5-50W GU10 40D	4,5	50	2700-2200	GU10	40	50	355	800	A+	Ja

<b>Value</b>											
37 110 97	LED spot 230V VLE D 3,5-35W GU10 827 25D	3,5	35	2700	GU10	25	35	260	1000	A++	Ja
37 110 85	LED spot 230V VLE D 3,5-35W GU10 827 40D	3,5	35	2700	GU10	40	35	260	600	A++	Ja
37 110 98	LED spot 230V VLE D 3,5-35W GU10 830 25D	3,5	35	3000	GU10	25	35	270	1000	A++	Ja
37 110 86	LED spot 230V VLE D 3,5-35W GU10 830 40D	3,5	35	3000	GU10	40	35	270	600	A++	Ja

El.nr	Produktnavn	Effekt (W)	Erstatter (W)	Farge-temp. (K)	Sokkel	Spredn. vinkel	Levetid (T)	Lm	Cd	EEL	Dimbar
-------	-------------	------------	---------------	-----------------	--------	----------------	-------------	----	----	-----	--------

**forts. MASTER LEDspot (Value)**

37 111 13	LED spot 230V VLE D 4.3-50W GU10 827	4,3	50	2700	GU10	25	35	355	1400	A++	Ja
37 111 16	LED spot 230V VLE D 4.3-50W GU10 827	4,3	50	2700	GU10	40	35	355	800	A++	Ja
37 111 14	LED spot 230V VLE D 4.3-50W GU10 830	4,3	50	3000	GU10	25	35	365	1400	A++	Ja
37 111 17	LED spot 230V VLE D 4.3-50W GU10 830	4,3	50	3000	GU10	40	35	365	800	A++	Ja

**MASTER LEDspot for lavvolt - perfekt for effektbelysning!**

37 111 35	LED spot 12V 7-35W 827 MR16 24D	7	35	2700	GU5.3	24	40	390	2100	A	Ja
37 111 36	LED spot 12V 7-35W 827 MR16 36D	7	35	2700	GU5.3	36	40	385	1150	A	Ja
37 111 37	LED spot 12V 7-35W 830 MR16 24D	7	35	3000	GU5.3	24	40	410	2200	A	Ja
37 111 38	LED spot 12V 7-35W 830 MR16 36D	7	35	3000	GU5.3	36	40	405	1200	A	Ja
37 111 24	LED spot 12V 8.0-50W 827 MR16 24D	8	50	2700	GU5.3	24	40	621	3100	A	Ja
37 111 28	LED spot 12V 8.0-50W 830 MR16 24D	8	50	3000	GU5.3	24	40	621	3250	A	Ja

**Dimtone**

37 111 26	LED spot 12V DimTone 6.5-35W MR16 24D	6,5	50	2700-2200	GU5.3	24	25	370	1800	A	Ja
37 111 27	LED spot 12V DimTone 6.5-35W MR16 36D	6,5	50	2700-2200	GU5.3	36	25	370	900	A	Ja

**Value**

37 111 19	LED spot 12V 3.4-20W 827 MR16 24D	3,4	20	2700	GU5.3	24	25	220	1000	A+	Ja
37 111 21	LED spot 12V 3.4-20W 827 MR16 36D	3,4	20	2700	GU5.3	36	25	220	550	A+	Ja
37 111 20	LED spot 12V 3.4-20W 830 MR16 24D	3,4	20	3000	GU5.3	24	25	225	1000	A+	Ja
37 111 23	LED spot 12V 3.4-20W 830 MR16 36D	3,4	20	3000	GU5.3	36	25	225	600	A+	Ja
37 111 39	LED spot 12V 6.3-35W 827 MR16 24D	6,3	35	2700	GU5.3	24	25	380	1800	A	Ja
37 111 40	LED spot 12V 6.3-35W 830 MR16 24D	6,3	35	3000	GU5.3	24	25	395	1800	A	Ja
37 111 41	LED spot 12V 6.3-35W 840 MR16 24D	6,3	35	4000	GU5.3	24	25	410	1800	A	Ja
37 111 42	LED spot 12V 6.3-35W 827 MR16 36D	6,3	35	2700	GU5.3	36	25	380	980	A	Ja
37 111 43	LED spot 12V 6.3-35W 830 MR16 36D	6,3	35	3000	GU5.3	36	25	395	1000	A	Ja

**MASTER LEDspot - PAR-lamper**

37 110 09	LED spot 230V 5.5-50W 2700K PAR20 25D	5,5	50	2700	E27	25	45	440	2000	A+	Ja
37 110 13	LED spot 230V 5.5-50W 2700K PAR20 40D	5,5	50	2700	E27	40	45	420	950	A+	Ja
37 110 11	LED spot 230V 5.5-50W 3000K PAR20 25D	5,5	50	3000	E27	25	45	450	2050	A+	Ja
37 110 16	LED spot 230V 5.5-50W 3000K PAR20 40D	5,5	50	3000	E27	40	45	430	970	A+	Ja
37 110 12	LED spot 230V 5.5-50W 4000K PAR20 25D	5,5	50	4000	E27	25	45	475	2150	A++	Ja
37 110 28	LED spot 230V 5.5-50W 4000K PAR20 40D	5,5	50	4000	E27	40	45	455	1000	A+	Ja
38 209 46	LED spot 230V PAR30S 9,5-75W 827 25D	9,5	75	2700	E27	25	40	650	3500	A+	Ja
38 209 52	LED spot 230V PAR30S 9,5-75W 840 25D	9,5	75	4000	E27	25	40	750	3850	A+	Ja
37 112 04	LED spot 230V PAR38 D 13-100W 827 25D	13	100	2700	E27	25	40	1000	5000	A+	Ja

**MASTER LED AR111**

37 111 44	LED spot 12V 11-50W 927 AR111 24D	11	50	2700	G53	24	40	620	2900	A	Ja
37 111 45	LED spot 12V 11-50W 927 AR111 40D	11	50	2700	G53	40	40	547	1150	A	Ja
37 111 46	LED spot 12V 11-50W 930 AR111 24D	11	50	3000	G53	24	40	578	3370	A	Ja
37 111 47	LED spot 12V 11-50W 930 AR111 40D	11	50	3000	G53	40	40	572	1210	A	Ja
37 111 48	LED spot 12V 15-75W 927 AR111 24D	15	75	2700	G53	24	40	830	4560	A	Ja
37 111 49	LED spot 12V 15-75W 927 AR111 40D	15	75	2700	G53	40	40	830	1550	A	Ja
37 111 50	LED spot 12V 15-75W 930 AR111 24D	15	75	3000	G53	24	40	745	4240	A	Ja
37 111 51	LED spot 12V 15-75W 930 AR111 40D	15	75	2700	G53	40	40	830	1400	A	Ja