




AMBIUM®LED SLIMBRIGHT 250

Constantly improving light output and the quality of light, the Slimbright 250 is extremely robust and flexible. Guaranteed uniform color bin and lighting. Easy in length adjustable. Very easy to install with our adhesive tape or mounting strips.



KOLEDO
PROFESSIONAL LED SOLUTIONS


AMBIUM[®]LED SLIMBRIGHT 250

SPECIFICATIONS

PRODUCT	COLOR TEMP.	LUMEN OUTPUT	LEDS/PITCH	POWER	INGRESS PROTECTION	CASETEMP @30°C	CRI	AMBIENT TEMPRANGE
Outdoor	K	Lm/mtr	pcs/mm	W/mtr	IP	°C		°C
SB250 Warm White 24V - clear	3200-3400	750	48/20	8.5W	67	48	80	-20/55
SB250 Medium White 24V - clear	3700-4500	800	48/20	8.5W	67	48	80	-20/56
SB250 Daylight White 24V- clear	5600-6300	800	48/20	8.5W	67	48	80	-20/57
Indoor								
SB250 Warm White 24V - clear / frosted	3200-3400	750	48/20	8.5W	21	48	80	-20/55
SB250 Medium White 24V - clear / frosted	3700-4500	800	48/20	8.5W	21	48	80	-20/56
SB250 Daylight White 24V- clear	5600-6300	800	48/20	8.5W	21	48	80	-20/57

DIMENSIONS (MM)

	A1	A2	B1	C1	# LED'S
	mm	mm	mm	mm	
Single colors	520	500	10,2	5,4	24
Single colors	1020	1000	10,2	5,4	48
Single colors	5020	5000	10,2	5,4	240
RGB	520	500	12,6	5,4	18
RGB	1030	1000	12,6	5,4	36
RGB	5020	5000	12,6	5,4	180



EXAMPLES

- cabinet lighting
- bar lighting
- outdoor cove lighting
- kick boards
- counter lighting
- architectural lighting
- signage and sign lighting
- task lighting



All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication there of does not convey nor imply any license under patent- or other industrial or intellectual property rights.

KOLEDO
PROFESSIONAL LED SOLUTIONS

KOLEDO.EU • EKKERSRIJT 7051 • 5692 HB SON
THE NETHERLANDS • +31 40 23 50 112
DEVELOPED AND MANUFACTURED USING PHILIPS TECHNOLOGY