





EnvisionGateway 10/100 BaseT Gateway

Multipurpose Ethernet connection

EnvisionGateway provides a multipurpose Ethernet connection to a Philips lighting control system. It supports access to both the home or office lighting via a dedicated Philips app as well as providing a web interface delivering access to the inbuilt timeclock and schedule editor functions. It provides bridging functionality between Ethernet backbone and the DyNet fieldbus devices.

- Large storage capacity — The device stores large project files internally, which apps use to autoconfigure their settings. This saves configuration time and ensures accuracy for phone and tablet control.
- Inbuilt web server — Allows the user to check system settings via the Network Hardware Checker and System Roll Call tools.
- No technical skills needed — Inbuilt timeclock and schedule manager allow the user to manage operation and task scheduling without advanced technical knowledge.
- Powerful custom task engine — Allows users or third-party systems to run macros, such as 'After Hours', 'Shut Down', 'Welcome' and more.
- Advanced interoperability — Supports management of Philips Dynalite and LightMaster-IP fittings on a single system.




For detailed product information, please refer to the product information pages at www.philips.com/dynalite and follow the links.

Specifications

Due to continuous improvements and innovations, specifications may change without notice.

Item	Specification	Details
Electrical	Dual supply option	12 / 24 VDC from an external regulated SELV / Class 2 power supply. Max 100 mA @ 12V plus DyNet load, max 50 mA @ 24V plus DyNet load or ; 12 / 24 VDC from DyNet (no external PS connected). Max 100 mA @ 12V, max 50 mA @ 24V
	DyNet DC Supply	Max 200 mA contribution to the network (when powered from external power supply) Power supply voltage shall match network voltage
Control	Communications Ports	One RS-485 DyNet serial port One 10/100BaseT Ethernet port
	Supported Ethernet Protocols	TCP/IP (TCP, UDP) HTTP, FTP IPv4, IPv6
	Storage Capacity	Max 16 MB for XML file storage 28 day rolling network log
	User Controls	Service switch Service LED Ethernet LED's status
	Diagnostic Functions	Device Online / Offline status
Physical	RS-485 Port Connections	Shield, GND, D-, D+, +Ve, AUX All available on screw terminals 1 x 2.5 mm ² conductor size Also available on RJ12 socket
	Ethernet Port Connections	Female RJ45 socket
	Supply Terminals	1 x 2 pole 5 mm pluggable screw terminal (+, -), 1 x 2.5 mm ² max conductor size per pole
	Dimensions (H x W x D)	97 mm x 110 mm x 38 mm (3.8" x 4.3" x 1.5")
	Packed Weight	0.21 kg
	Construction	Low profile DIN-rail polycarbonate (6 unit)
	Operating Conditions	Temperature: -5 to 50° C ambient Humidity: 0 to 90% non-condensing
	Storage & Transport	Temperature: -25 to 70° C ambient Humidity: 0 to 90% non-condensing
Certification	Certification	CE, C-Tick, UL, FCC, ICES
Options & Ordering	Standard Product	EnvisionGateway DL-ETHENVG-101 (Philips 12 NC - 913703013809)

Electrical Diagram



Philips Dyalite
6 / 691 Gardeners Road
Mascot, NSW 2020
Australia
Tel: +61 2 8338 9899
Email: dyalite.info@philips.com
Web: www.philips.com/dyalite

Specifications subject to change without notice. ©WMGD Pty Ltd Trading as Dyalite. Unit 6, 691 Gardeners Road Mascot 2020 Australia. ABN 33 097 246 921. All rights reserved. Dyalite, DyNet and associated logos are the registered trademarks of WMGD Pty Ltd. Not to be reproduced without permission.