


**GREAT LIGHT,  
SOLID DESIGN**

# LUMINARIAS DE INTERIOR MAZDA

## AHORRO ENERGÉTICO INSTANTÁNEO

Tipo de producto	Flujo luminoso	Consumo energético	Temperatura de color	IP / IK	Sensor de movimiento	Clase I/II	12NC	EOC
	lm	W	K					
<b>Regleta</b>								
<b>NUEVO</b> MAZDA BN007C LED32S/840 PSU L1200	3200	32	4000	IP20		I	911401800480	33804099
<b>Aplique LED</b>								
<b>NUEVO</b> MAZDA WL007C LED14S/740 PSU OVL WH	1400	15	4000	IP65 / IK06		II	911401800780	33807199
MAZDA WL007C LED13S/740 PSU RND MDU WH	1300	15	4000	IP54 / IK06	Sí	II	911401800880	33808899
<b>Estanca</b>								
<b>NUEVO</b> MAZDA WT007C LED17S/740 PSU L600	1700	17	4000	IP65 / IK06		II	911401800980	33877499
MAZDA WT007C LED34S/740 PSU L1200	3400	34	4000	IP65 / IK06		II	911401800580	33805799
MAZDA WT007C LED54S/740 PSU L1500	5400	54	4000	IP65 / IK06		II	911401800680	33806499



**MAZDA BN007C LED32S/840  
PSU L1200**

12NC: **911401800480**

EOC: **33804099**

1200 mm 3200lm

4000K

35.000 horas

IP20



**MAZDA WL007C LED13S/840  
PSU RND MDU WH**

12NC: **911401800880**

EOC: **33808899**


1300lm

4000K

20.000 horas

IP54 / IK06

Sensor de movimiento integrado



**MAZDA WT007C LED54S/840  
PSU L1500**

12NC: **911401800680**

EOC: **33806499**

1500 mm 5400lm

4000K

35.000 horas

IP65 / IK06