



PHILIPS

LEDlamps

LEDtube Ultra Output



The right LEDtube for demanding applications

Whatever your lighting application, the Philips MASTER LEDtube portfolio has the right LEDtube for you.

With an ultra output of 2300 lm to 3700 lm, our Ultra Output LEDtube range combines outstanding efficiency of up to 148 lm/W with the high quality light required by the most demanding applications. A simple switch that comes in a choice of two lengths and three colour temperatures, with rotating end-caps.

The right choice for offices, schools, supermarkets, healthcare and industrial applications.



Product data

MASTER LEDtube Ultra Output



3000/4000/6500



G13



ROTATABLE
(ROT)



NON-
DIMMABLE



50,000 H

A⁺/A⁺⁺

EEL*



BEAM ANGLE
160°




DIMENSIONS
27.3 | 1198 | 1498



EM

Product type	LED	Traditional	Lumen output	Operation	Beam angle	CRI	Color temperature	EOC 1 pcs (C)*
MASTER LEDtube	Wattage	Equivalent	Lumen		°		K	
1200mm UO	20 W	36 W	2300 lm	EM & Mains	160°	83	3000	871869646149500
1200mm UO	20 W	36 W	2500 lm	EM & Mains	160°	83	4000	871869646151800
1200mm UO	20 W	36 W	2500 lm	EM & Mains	160°	83	6500	871869646155600
1500mm UO	25 W	58 W	3400 lm	EM & Mains	160°	83	3000	871869646157000
1500mm UO	25 W	58 W	3700 lm	EM & Mains	160°	83	4000	871869646159400
1500mm UO	25 W	58 W	3700 lm	EM & Mains	160°	83	6500	871869646163100



HF

NEW 1200mm UO	22 W	36 W	2300 lm	HF	160°	83	3000	871869655282700
NEW 1200mm UO	22 W	36 W	2500 lm	HF	160°	83	4000	871869655278000
NEW 1200mm UO	22 W	36 W	2500 lm	HF	160°	83	6500	871869655280300
NEW 1500mm UO	26 W	58 W	3400 lm	HF	160°	83	3000	871869655288900
NEW 1500mm UO	26 W	58 W	3700 lm	HF	160°	83	4000	871869655284100
NEW 1500mm UO	26 W	58 W	3700 lm	HF	160°	83	6500	871869655286500

* EEL 1200mm UO = A⁺ / EEL 1500mm UO = A⁺⁺

