



Supported Device list – MultiOne Engineering/Workflow 3.12

Type	Type Name	version	Interface: USB2..		
CONTROL	CT_OLC CB	0	DALI		
CONTROL	CT_OLC PB	0	DALI		
CONTROL	DLMC	1.1	DALI		
CONTROL	EasySense	1.13		SimpleSet	
CONTROL	EasySense	1.14		SimpleSet	
CONTROL	EasySense	2.1		SimpleSet	
CONTROL	EasySense	2.39		SimpleSet	
CONTROL	LLC1663/00 ActiLume DALI gen2	1	DALI		
CONTROL	LLC1663/01 ActiLume DALI gen2	2	DALI		
CONTROL	LLC1663/01 ActiLume DALI gen2	2.1	DALI		
CONTROL	LLC1663/01 ActiLume DALI gen2	2.2	DALI		
CONTROL	LLC1663/01 ActiLume DALI gen2	2.3	DALI		
CONTROL	LLC1663/01 ActiLume DALI gen2	2.4	DALI		
CONTROL	LLC1681/10 ActiLume	4.1.10.30011			ZigBee
CONTROL	LLC1682/11 ActiLume	4.1.10.30011			ZigBee
CONTROL	LLC1682/13 ActiLume	4.1.13.30377			ZigBee
CONTROL	LLC1682/13 ActiLume	4.1.15.30594			ZigBee
CONTROL	LLC1682/13 ActiLume	4.1.16.30731			ZigBee
CONTROL	LLC1682/13 ActiLume	4.1.18.31450			ZigBee

CONTROL	LLC1685/11 ActiLume	4.1.10.30011			ZigBee
CONTROL	LLC1685/12 ActiLume	4.1.13.30377			ZigBee
CONTROL	LLC1685/13 ActiLume	4.1.15.30594			ZigBee
CONTROL	LLC1685/13 ActiLume	4.1.16.30731			ZigBee
CONTROL	LLC1685/13 ActiLume	4.1.18.31394			ZigBee
CONTROL	LLC1685/13 ActiLume	4.1.18.31450			ZigBee
CONTROL	LLC1685/14 ActiLume	4.1.19.31531			ZigBee
CONTROL	LLC1685/15 ActiLume	4.1.20.31800			ZigBee
CONTROL	LLC1686/11 ActiLume	4.1.10.30011			ZigBee
CONTROL	LLC1686/12 ActiLume	4.1.13.30377			ZigBee
CONTROL	LLC1686/13 ActiLume	4.1.15.30594			ZigBee
CONTROL	LLC1686/13 ActiLume	4.1.16.30731			ZigBee
CONTROL	LLC1686/13 ActiLume	4.1.18.31450			ZigBee
CONTROL	LLC1686/14 ActiLume	4.1.19.31531			ZigBee
CONTROL	LLC1686/15 ActiLume	4.1.20.31800			ZigBee
CONTROL	LLC1687/12 ActiLume	4.1.13.30377			ZigBee
CONTROL	LLC1687/13 ActiLume	4.1.15.30594			ZigBee
CONTROL	LLC1687/13 ActiLume	4.1.16.30731			ZigBee
CONTROL	LLC1687/13 ActiLume	4.1.18.31450			ZigBee
CONTROL	PoELC Dual Channel 25W	3		SimpleSet	
CONTROL	PoELC Dual Channel 25W	3.1		SimpleSet	
CONTROL	PoELC Dual Channel 45W	3		SimpleSet	
CONTROL	PoELC Dual Channel 45W	3.1		SimpleSet	
CONTROL	PoELC Gen2 25W	2		SimpleSet	
CONTROL	PoELC Gen2 25W	2.1		SimpleSet	
CONTROL	PoELC Gen2 45W	2		SimpleSet	
CONTROL	PoELC Gen2 45W	2.1		SimpleSet	
CONTROL	SNH400	4.3		SimpleSet	
CONTROL	SNS200	2.51		SimpleSet	
CONTROL	SNS200	2.57		SimpleSet	
CONTROL	SNS200	2.58		SimpleSet	
CONTROL	SNS400	4.3		SimpleSet	
CONTROL	SNS441 IR Wireless Transceiver	2.8		SimpleSet	
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	2.41	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	2.61	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.4	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.6	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.1	DALI		

FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.4	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.6	DALI		
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1	DALI		
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1.1	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.41	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.61	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.4	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.6	DALI		
FLUO	HF-Ri TD 280 TL5/PL-L E+	1	DALI		
FLUO	HF-Ri TD 280 TL5/PL-L E+	1.2	DALI		
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.4	DALI		
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.7	DALI		
FLUO	HF-Ri TD 3 14/24 TL5 E+	2.7	DALI		
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.4	DALI		
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.7	DALI		
FLUO	HF-Ri TD 4 14/24 TL5 E+	2.7	DALI		
HID	Dynavision DALI	R1.5	DALI		
HID	Dynavision DALI	R1.6	DALI		
HID	Dynavision DALI	R1.7	DALI		
HID	Dynavision DALI	R1.8	DALI		
HID	Dynavision DALI	R2.0	DALI		
HID	Dynavision Prog	R2.1	DALI		
HID	Dynavision Prog	R2.2	DALI		
LED	929001743413	1.1		SimpleSet	
LED	929001743513	1.2		SimpleSet	
LED	929001743613	1.2		SimpleSet	
LED	929001743713	1.1		SimpleSet	
LED	929001743813	1.1		SimpleSet	
LED	929001743913	1.1		SimpleSet	
LED	929001744013	1.1		SimpleSet	
LED	929001744113	1.2		SimpleSet	
LED	929001744213	1.2		SimpleSet	
LED	929001744313	1.2		SimpleSet	
LED	929001744413	1.2		SimpleSet	
LED	929001744513	1.1		SimpleSet	
LED	929001747513	1.1		SimpleSet	
LED	BAC40EM10	1		SimpleSet	

LED	BAC40EM6	1		SimpleSet	
LED	LDP 100W 1.05A IP67	2		SimpleSet	
LED	LDP 150W 1.05A IP67	2		SimpleSet	
LED	LDP 220W 1.05A IP67	1		SimpleSet	
LED	LDP 65W 1.05A IP67	1.1		SimpleSet	
LED	LED 929000712603	1.1	DALI		
LED	LED 929000712803	1.1	DALI		
LED	LED 929001743113M	1		SimpleSet	
LED	LED HP 350W 1.10	1.16	DALI		Art-Net
LED	LED HP 350W 1.20	1.32	DALI		Art-Net
LED	LHP 1710W 200-242V E2 RDM JPN	2.1	DALI		Art-Net
LED	LHP 1710W 220-400V E2 DALI	2.1	DALI		
LED	LHP 1710W 220-400V E2 DALI	2.2	DALI		
LED	LHP 1710W 220-400V E2 RDM	2.1	DALI		Art-Net
LED	LHP 1710W 220-400V E2 RDM	2.2	DALI		Art-Net
LED	LHP 1710W 230-400V	1	DALI		
LED	LHP 1710W 230-400V E2 DALI	2	DALI		
LED	LHP 1710W 230-400V E2 RDM	2	DALI		Art-Net
LED	LHP 350W 110-277V	2	DALI		Art-Net
LED	LHP 350W 110-277V E2	2.1	DALI		Art-Net
LED	LHP 350W 347-480V	2	DALI		Art-Net
LED	TrustSight DALI 15-55V LFP	1	DALI	SimpleSet	
LED	TrustSight DALI 15-55V NMC	1	DALI	SimpleSet	
LED	TrustSight DALI 15-55V NiMH	1	DALI	SimpleSet	
LED	TrustSight DALI 45-300V LFP	1	DALI	SimpleSet	
LED	TrustSight DALI 45-300V NMC	1	DALI	SimpleSet	
LED	TrustSight DALI 45-300V NiMH	1	DALI	SimpleSet	
LED	TrustSight DALI L 20-95V 3W 1hr kit	1	DALI		
LED	TrustSight DALI L 20-95V 3W 3hrs kit	1	DALI		
LED	TrustSight DALI L 20-95V 3W xxhrs kit	1	DALI		
LED	TrustSight DALI L 20-95V 6W 1hr kit	1	DALI		
LED	TrustSight DALI P 15-55V 3W 1hr kit	1	DALI		
LED	TrustSight DALI P 15-55V 3W 3hrs kit	1	DALI		
LED	TrustSight DALI P 15-55V 3W xxhrs kit	1	DALI		
LED	X*050C100V054XPM1M	1.12	DALI		
LED	X*050C100V054XPM1M	1.18	DALI		
LED	X*060C100V080XPM1M	1.12	DALI		
LED	X*060C100V080XPM1M	1.18	DALI		
LED	X*060C100V080XPM1M	1.2	DALI		
LED	XG020C056V054BST1	1		SimpleSet	
LED	XG040C110V054BST1	1		SimpleSet	
LED	XG054C150V054BST1	1		SimpleSet	
LED	XG075C200V054BST1	1		SimpleSet	
LED	XH055C180V054BSY1	1		SimpleSet	
LED	XH075C120V075KPF1M	3.2	DALI		
LED	XH075C120V075KPF1M	4.2	DALI		
LED	XH095C275V054BSF1	1.1		SimpleSet	

LED	XH095C275V054BSF1	1.2		SimpleSet	
LED	XH100C110V143BSY1	1		SimpleSet	
LED	XH100C110V143BSY1	1.1		SimpleSet	
LED	XH100C150V091BSY1	1		SimpleSet	
LED	XH150C120V150KPF1M	3.2	DALI		
LED	XH150C120V150KPF1M	4.2	DALI		
LED	XH180C090V285BSF1	1.1		SimpleSet	
LED	XH180C090V285BSF1	1.2		SimpleSet	
LED	XH180C125V200BSF1	1.1		SimpleSet	
LED	XH180C125V200BSF1	1.2		SimpleSet	
LED	XH180C125V200PSF1	1		SimpleSet	
LED	XH180C125V200PSF1	1.1		SimpleSet	
LED	XH180C125V200PSF2	1		SimpleSet	
LED	XH180C180V144BSF1	1.1		SimpleSet	
LED	XH180C180V144BSF1	1.2		SimpleSet	
LED	XH190C275V054BSG1	1		SimpleSet	
LED	XH190C275V054BSG1	1.1		SimpleSet	
LED	XH190C275V054BSG1	1.2		SimpleSet	
LED	XH190C275V054PSG1	1		SimpleSet	
LED	XH190C275V054PSG1	1.1		SimpleSet	
LED	XH190C275V054PSG1	1.2		SimpleSet	
LED	XH300C150V300BSR1	1		SimpleSet	
LED	XH300C150V300BSR1	1.1		SimpleSet	
LED	XH300C150V300BSR1M	1		SimpleSet	
LED	XI 100W 0.15-0.5A 300V iXt TDCL 230V	2.1	DALI	SimpleSet	
LED	XI 150W 0.2-0.7A 300V iXt TDCL 230V	2.1	DALI	SimpleSet	
LED	XI 60W 0.08-0.35A 300V TD16CL 230V	2.1	DALI	SimpleSet	
LED	XI020C056V054BST2	2		SimpleSet	
LED	XI025C070V054DSM1	1		SimpleSet	
LED	XI025C070V054DSM1	2		SimpleSet	
LED	XI025C070V054DSM5	1		SimpleSet	
LED	XI025C070V054DSM5	2		SimpleSet	
LED	XI025C100V036DSM1	1		SimpleSet	
LED	XI025C100V036DSM5	1		SimpleSet	
LED	XI030C080V054BSJ1	1		SimpleSet	
LED	XI030C090V054BST1	1		SimpleSet	
LED	XI030C090V054BST1	1.1		SimpleSet	
LED	XI030C090V054PST1	1		SimpleSet	
LED	XI030C090V054PST1	1.1		SimpleSet	
LED	XI030C090V054PST1	2		SimpleSet	
LED	XI030C120V040BSJ1	1		SimpleSet	
LED	XI036C100V054DSM1	1		SimpleSet	
LED	XI036C100V054DSM1	2		SimpleSet	
LED	XI036C100V054DSM5	1		SimpleSet	
LED	XI036C100V054DSM5	2		SimpleSet	
LED	XI040C110V050VWT1	1	DALI	SimpleSet	
LED	XI040C110V054BST1	2		SimpleSet	

LED	XI040C110V054BST1	3		SimpleSet	
LED	XI040C110V054BST2	1		SimpleSet	
LED	XI040C110V054BST2	1.1		SimpleSet	
LED	XI040C110V054BST2	2		SimpleSet	
LED	XI040C110V054PST1	1		SimpleSet	
LED	XI040C110V054PST1	1.1		SimpleSet	
LED	XI040C110V054SST1	1		SimpleSet	
LED	XI050C100V054XPL1M	1.1	DALI		
LED	XI050C100V054XPL1M	1.18	DALI		
LED	XI050C140V054BST1	1		SimpleSet	
LED	XI050C140V054BST1	1.1		SimpleSet	
LED	XI050C140V054BST1	2		SimpleSet	
LED	XI050C140V054DSM1	1		SimpleSet	
LED	XI050C140V054DSM1	2		SimpleSet	
LED	XI050C140V054DSM5	1		SimpleSet	
LED	XI050C140V054DSM5	2		SimpleSet	
LED	XI050C140V054PST1	1		SimpleSet	
LED	XI050C140V054PST1	1.1		SimpleSet	
LED	XI054C150V054BST1	2		SimpleSet	
LED	XI054C150V054BST1	3		SimpleSet	
LED	XI054C150V054SST1	1		SimpleSet	
LED	XI055C180V054BSJ1	1		SimpleSet	
LED	XI055C180V054BSJ1	1.1		SimpleSet	
LED	XI075C070V118VSY1M	1	DALI	SimpleSet	
LED	XI075C070V118VSY2	1	DALI	SimpleSet	
LED	XI075C105V079VSY1M	1	DALI	SimpleSet	
LED	XI075C105V079VSY2	1	DALI	SimpleSet	
LED	XI075C200V054BST1	2		SimpleSet	
LED	XI075C200V054DSM1	1		SimpleSet	
LED	XI075C200V054DSM5	1		SimpleSet	
LED	XI075C200V054PST1	2		SimpleSet	
LED	XI075C200V054SST1	1		SimpleSet	
LED	XI075C200V054XPT1	1.1	DALI		
LED	XI075C200V054XPT1	1.2	DALI		
LED	XI075C200V054XPT1	1.4	DALI		
LED	XI075C200V054XPT1	1.5	DALI		
LED	XI075C200V054XPT1	1.6	DALI		
LED	XI075C200V054XPT1	1.7	DALI		
LED	XI075C200V054XPT1	2	DALI		
LED	XI075C200V054XPT1	2.1	DALI		
LED	XI075C200V054XPT1	2.3	DALI		
LED	XI075C200V054YPT1	1.1	DALI		
LED	XI075C200V054YPT1	1.2	DALI		
LED	XI075C200V054YPT1	1.4	DALI		
LED	XI075C200V054YPT1	1.5	DALI		
LED	XI075C200V054YPT1	1.6	DALI		
LED	XI075C200V054YPT1	2.2	DALI		

LED	XI075C200V054YPT1	2.4	DALI		
LED	XI095C275V054BSF1	1		SimpleSet	
LED	XI095C275V054BSS1	1.1		SimpleSet	
LED	XI095C275V054BSS1	1.2		SimpleSet	
LED	XI095C275V054VPF1M	1	DALI	SimpleSet	
LED	XI095C275V054VSF1M	1	DALI	SimpleSet	
LED	XI100C110V143BSY1	1		SimpleSet	
LED	XI100C110V143BSY1	1.1		SimpleSet	
LED	XI100C110V143DSY1	1		SimpleSet	
LED	XI100C110V143DSY1	1.1		SimpleSet	
LED	XI100C150V091BSY1	1		SimpleSet	
LED	XI100C150V091BSY1	1.1		SimpleSet	
LED	XI150C070V235VSF1M	1	DALI	SimpleSet	
LED	XI150C070V235VSF1M	1.1	DALI	SimpleSet	
LED	XI150C105V157VSF1M	1	DALI	SimpleSet	
LED	XI150C105V157VSF1M	1.1	DALI	SimpleSet	
LED	XI180C090V285BSF1	1.1		SimpleSet	
LED	XI180C090V285BSF1	1.2		SimpleSet	
LED	XI180C090V285VSF1M	1.1	DALI	SimpleSet	
LED	XI180C125V200BSF1	1.1		SimpleSet	
LED	XI180C125V200BSF1	1.2		SimpleSet	
LED	XI180C125V200PSF1	1		SimpleSet	
LED	XI180C125V200PSF1	1.1		SimpleSet	
LED	XI180C125V210VSF1M	1.1	DALI	SimpleSet	
LED	XI180C180V144BSF1	1.1		SimpleSet	
LED	XI180C180V144BSF1	1.2		SimpleSet	
LED	XI180C180V144VSF1M	1.1	DALI	SimpleSet	
LED	XI190C275V054BSG1	1		SimpleSet	
LED	XI190C275V054BSG1	1.1		SimpleSet	
LED	XI300C150V300BSR1	1.2		SimpleSet	
LED	XJ180C090V285BSF2	1		SimpleSet	
LED	XJ180C125V200BSF2	1		SimpleSet	
LED	XJ180C180V144BSF2	1		SimpleSet	
LED	XR025C100V036YPM1M	1.1	DALI		
LED	XR025C100V036YPM1M	1.4	DALI		
LED	Xi BP 12W 0.1-0.5A 230V C100	1		SimpleSet	
LED	Xi BP 22W 0.2-0.7A S 230V C123 sXt	1		SimpleSet	
LED	Xi BP 40W 0.2-0.7A S 230V C123 sXt	1		SimpleSet	
LED	Xi BP 40W 0.3-1.0A S 230V C123 sXt	1		SimpleSet	
LED	Xi FP 100W 0.2-0.7A SNLDAE 230V C165 sXt	1	DALI	SimpleSet	
LED	Xi FP 100W 0.2-0.7A SNLDAE 230V C165 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 100W 0.2-0.7A SNLDAE 230V C165 sXt	2	DALI	SimpleSet	
LED	Xi FP 110W 0.2-0.7A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi FP 110W 0.2-0.7A SNLDAE 230V C133 sXt	2	DALI	SimpleSet	
LED	Xi FP 110W 0.3-1.0A NLD 230V C150 sXt	1.4	DALI		
LED	Xi FP 110W 0.3-1.0A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi FP 110W 0.3-1.0A SNLDAE 230V C133 sXt	2	DALI	SimpleSet	

LED	Xi FP 150W 0.2-0.7A SNLCDAE 230V S240 sX	1	DALI	SimpleSet	
LED	Xi FP 150W 0.2-0.7A SNLCDAE 230V S240 sX	2	DALI	SimpleSet	
LED	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt	2	DALI	SimpleSet	
LED	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt	3	DALI	SimpleSet	
LED	Xi FP 150W 0.3-1.0A SNLCDAE 230V S240 sX	2	DALI	SimpleSet	
LED	Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt	2	DALI	SimpleSet	
LED	Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt	3	DALI	SimpleSet	
LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1	DALI	SimpleSet	
LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1.2	DALI	SimpleSet	
LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1.3	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1.2	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1.3	DALI	SimpleSet	
LED	Xi FP 22W 0.2-0.7A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 22W 0.2-0.7A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V C123 sXt	1	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	1	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 330W 2:0.2-0.75A SNDAE C240 sXt	1	DALI	SimpleSet	
LED	Xi FP 35W 0.3-1.0A NLD 230V C150 sXt	1.4	DALI		
LED	Xi FP 40W 0.2-0.7A SNLCDAE 230V S175 sX	1	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V C123 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	3	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V C123 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 70W 0.3-1.0A NLD 230V C150 sXt	1.4	DALI		
LED	Xi FP 75W 0.2-0.7A SNLCDAE 230V S240 sX	1	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLCDAE 230V S240 sX	2	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V C133 sXt	2	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	

LED	Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt	2	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt	3	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLCDAE 230V S240 sX	2	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V C133 sXt	2	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt	2	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt	3	DALI	SimpleSet	
LED	Xi FP 75W 0.5-1.5A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.5-1.5A SNLDAE 230V C133 sXt	2	DALI	SimpleSet	
LED	Xi LP 100W 0.3-1.05A S1 230V I175	1		SimpleSet	
LED	Xi LP 100W 0.3-1.05A S1 230V I175	2		SimpleSet	
LED	Xi LP 100W 0.3-1.05A S1 230V I175C	1		SimpleSet	
LED	Xi LP 100W 0.3-1.05A S1 230V I175CF	1		SimpleSet	
LED	Xi LP 100W 0.3-1.05A S1 230V I175CF	2		SimpleSet	
LED	Xi LP 100W 0.5-1.5A S1 230V I175	2		SimpleSet	
LED	Xi LP 100W 0.5-1.5A S1 230V I175CF	2		SimpleSet	
LED	Xi LP 110W 0.2-0.7A S1 230V C133 sXt	1		SimpleSet	
LED	Xi LP 110W 0.2-0.7A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.2-0.7A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 110W 0.2-0.7A SL 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.2-0.7A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 110W 0.3-1.0A S1 230V C133 sXt	1		SimpleSet	
LED	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 110W 0.3-1.0A SL 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.3-1.0A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 150W 0.2-0.7A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.2-0.7A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 150W 0.2-0.7A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.2-0.7A SN 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.3-1.05A S1 230V I175	1		SimpleSet	
LED	Xi LP 150W 0.3-1.05A S1 230V I175	2		SimpleSet	
LED	Xi LP 150W 0.3-1.05A S1 230V I175C	1		SimpleSet	
LED	Xi LP 150W 0.3-1.05A S1 230V I175CF	1		SimpleSet	
LED	Xi LP 150W 0.3-1.05A S1 230V I175CF	2		SimpleSet	
LED	Xi LP 150W 0.3-1.0A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.3-1.0A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 150W 0.3-1.0A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.5-1.5A S1 230V I175	2		SimpleSet	
LED	Xi LP 150W 0.5-1.5A S1 230V I175CF	2		SimpleSet	
LED	Xi LP 150W 0.5-1.5A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.5-1.5A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 165W 0.2-0.7A S1 230V C170 sXt	1		SimpleSet	
LED	Xi LP 165W 0.3-1.0A S1 230V C170 sXt	1		SimpleSet	
LED	Xi LP 165W 0.5-1.5A S1 230V C170 sXt	1		SimpleSet	

LED	Xi LP 200W 0.3-1.05A S1 230V F3	1		SimpleSet	
LED	Xi LP 220W 0.3-1.05A S1 230V F3	1		SimpleSet	
LED	Xi LP 220W 0.3-1.05A S1 230V I230	1		SimpleSet	
LED	Xi LP 220W 0.3-1.05A S1 230V I230C	1		SimpleSet	
LED	Xi LP 220W 0.3-1.05A S1 230V I230CF	1		SimpleSet	
LED	Xi LP 220W 0.3-1.05A S1 TWE I230	1		SimpleSet	
LED	Xi LP 220W 0.3-1.05A S1 TWE I230C	1		SimpleSet	
LED	Xi LP 220W 0.3-1.05A S1 TWE I230CF	1		SimpleSet	
LED	Xi LP 220W 0.5-1.5A S1 230V I230	1		SimpleSet	
LED	Xi LP 220W 0.5-1.5A S1 230V I230C	1		SimpleSet	
LED	Xi LP 220W 0.5-1.5A S1 230V I230CF	1		SimpleSet	
LED	Xi LP 220W 0.5-1.5A S1 TWE I230	1		SimpleSet	
LED	Xi LP 22W 0.2-0.7A S1 230V C123 sXt	2		SimpleSet	
LED	Xi LP 22W 0.2-0.7A S1 230V C123 sXt	2.1		SimpleSet	
LED	Xi LP 22W 0.2-0.7A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 22W 0.3-1.0A S1 230V C123 sXt	1		SimpleSet	
LED	Xi LP 22W 0.3-1.0A S1 230V C123 sXt	2		SimpleSet	
LED	Xi LP 22W 0.3-1.0A S1 230V C123 sXt	2.1		SimpleSet	
LED	Xi LP 22W 0.3-1.0A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 35W 0.3-1.0A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V C123 sXt	1		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V C123 sXt	2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V C123 sXt	2.1		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A SL 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.2-0.7A SL 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A SN 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.3-1.05A S1 230V I150	1		SimpleSet	
LED	Xi LP 40W 0.3-1.05A S1 TWE I175	1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V C123 sXt	1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V C123 sXt	2		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V C123 sXt	2.1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 40W 0.3-1.0A SL 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A SL 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 65W 0.3-1.05A S1 230V I150	1.1		SimpleSet	
LED	Xi LP 65W 0.3-1.05A S1 230V I150C	1.1		SimpleSet	
LED	Xi LP 65W 0.3-1.05A S1 TWE I175	1.1		SimpleSet	
LED	Xi LP 65W 0.5-1.5A S1 230V I150	1.1		SimpleSet	
LED	Xi LP 65W 0.5-1.5A S1 230V I150C	1.1		SimpleSet	
LED	Xi LP 70W 0.2-0.7A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 70W 0.2-0.7A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 70W 0.2-0.7A SL 230V C150 sXt	1.1		SimpleSet	

LED	Xi LP 70W 0.2-0.7A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 70W 0.3-1.0A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 70W 0.3-1.0A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 70W 0.3-1.0A SL 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 70W 0.3-1.0A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 75W 0.2-0.7A S1 230V C133 sXt	1		SimpleSet	
LED	Xi LP 75W 0.2-0.7A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.2-0.7A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 75W 0.2-0.7A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.2-0.7A SN 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.3-1.0A S1 230V C133 sXt	1		SimpleSet	
LED	Xi LP 75W 0.3-1.0A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.3-1.0A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 75W 0.3-1.0A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.5-1.5A S1 230V C133 sXt	1		SimpleSet	
LED	Xi LP 75W 0.5-1.5A S1 230V S240 sXt	2		SimpleSet	
LED	Xi SR 110W 0.2-0.7A SNEMP 230V C150 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 110W 0.3-1.0A SNEMP 230V C150 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 12W 0.2-0.7A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNDAEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xi SR 150W 0.27-0.7A SMP TWE I250	1.2	DALI	SimpleSet	
LED	Xi SR 150W 0.27-0.7A SMP TWE I250C	1.2	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xi SR 165W 0.2-0.7A SNEMP 230V C170 sXt	1	DALI	SimpleSet	
LED	Xi SR 165W 0.3-1.0A SNEMP 230V C170 sXt	1	DALI	SimpleSet	
LED	Xi SR 22W 0.2-0.7A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 22W 0.3-1.0A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 40W 0.2-0.7A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 40W 0.2-0.7A SNEMP 230V C133 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 40W 0.3-1.0A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNDAEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V C150 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xi SR 75W 0.27-0.7A SMP TWE I200	1.2	DALI	SimpleSet	

LED	Xi SR 75W 0.3-1.0A SNEMP 230V C150 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V CL 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V SR 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V SR 230V iXt	2.1	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V TD 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V iXt 230V	1		SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V iXt TD 230V	2.1	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V iXt TD 230V	3	DALI	SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V S 230V	1		SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V TD16 230V	2	DALI	SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V TD16 230V	2.1	DALI	SimpleSet	
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1	DALI		
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.1	DALI		
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.2	DALI		
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.3	DALI		
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.4	DALI		
LED	Xitanium 150W 0.2-0.7A 300V CL 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V SR 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V SR 230V iXt	2.1	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.1	DALI		
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.2	DALI		
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.3	DALI		
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V iXt 230V	1		SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V iXt TD 230V	2.1	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V iXt TD 230V	3	DALI	SimpleSet	
LED	Xitanium 150W 0.7A sProg 230V-6 I66	2.3	DALI		
LED	Xitanium 150W 0.7A sProg 230V-6 I66	3.3	DALI		
LED	Xitanium 150W 0.7A sProg 230V-6C I66	2.3	DALI		
LED	Xitanium 150W 0.7A sProg 230V-6C I66	3.3	DALI		
LED	Xitanium 150W 1.1A Prog+ GL-F sXt	1.1	DALI		
LED	Xitanium 150W 1.2A sProg 230V-F sXt	1.2	DALI		
LED	Xitanium 150W 1.2A sProg GL-F sXt	1.2	DALI		
LED	Xitanium 17W 0.12-0.4A 54V 1-10V 230V	1.7	DALI		
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.13	DALI		
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.14	DALI		
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.7	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.1	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.2	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.3	DALI		

LED	Xitanium 20W 0.1-0.56A 54V 0-10V 120-277	1		SimpleSet	
LED	Xitanium 20W LH 0.15-0.5A 48V 230V	1		SimpleSet	
LED	Xitanium 20W LH 0.15-0.5A 48V TD/Is 230V	1.2	DALI		
LED	Xitanium 20W WH 0.15-0.5A 54V Is	1		SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V Is G2	1		SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V S	1		SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is 230V	1	DALI	SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is 230V	1.1	DALI	SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is 230V	2	DALI	SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is CL	1	DALI	SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is CL	2	DALI	SimpleSet	
LED	Xitanium 20W/m 0.15-0.5A 54V 230V	1		SimpleSet	
LED	Xitanium 20W/m 0.15-0.5A 54V 230V	2		SimpleSet	
LED	Xitanium 20W/m 0.15-0.5A 54V S TD 230V	1	DALI	SimpleSet	
LED	Xitanium 20W/m 0.15-0.5A 54V TD 230V	1.16	DALI		
LED	Xitanium 20W/m 0.15-0.5A 54V TD 230V	1.8	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.1	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.18	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.4	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.5	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.6	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.7	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.9	DALI		
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.2	DALI		
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.3	DALI		
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.4	DALI		
LED	Xitanium 300W 0.1-1.5A 0-10V 120-277V	1		SimpleSet	
LED	Xitanium 300W 0.1-1.5A 0-10V 120-277V	1.1		SimpleSet	
LED	Xitanium 300W 0.5-1.4A 300V iXt TD 230V	1	DALI	SimpleSet	
LED	Xitanium 300W 0.5-1.4A 300V iXt TD 230V	1.1	DALI	SimpleSet	
LED	Xitanium 300W 1.5A Prog+ GL-F2 sXt	1.1	DALI		
LED	Xitanium 30W 0.5-0.7A 42V WZ 240V /I	1		SimpleSet	
LED	Xitanium 320W 0.5-1.4A SR 400V GV2	1	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V S 230V	1		SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V S/16 230V	1		SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V SR 230V	2.1	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V TD 230V	2	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V TD16 230V	2	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V TD16 230V	2.1	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 220V TD11 230V	1	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 220V TD16 230V	1	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 220V TD21 230V	1	DALI		
LED	Xitanium 36W 0.12-0.4A 100V 1-10V 230V	1.7	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.13	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.14	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.16	DALI		

LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.17	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.7	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.3	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.4	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.5	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.6	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	2	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	2.1	DALI		
LED	Xitanium 36W 0.3-1.05A 54V S 230V	1		SimpleSet	
LED	Xitanium 36W 0.3-1A 54V SR 230V	4	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V SR 230V	4.1	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V SR 230V	4.2	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.1	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.2	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.3	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.5	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.6	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.7	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.8	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.9	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	4	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V TD 230V	4.1	DALI	SimpleSet	
LED	Xitanium 36W 0.5-0.85A 42V WZ 230V /I	1		SimpleSet	
LED	Xitanium 36W LH 0.3-1A 48V I 230V	1		SimpleSet	
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.1	DALI		
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.2	DALI		
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.3	DALI		
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.4	DALI		
LED	Xitanium 36W WH 0.3-1.05A 54V Is	1		SimpleSet	
LED	Xitanium 36W WH 0.3-1.05A 54V Is G2	1		SimpleSet	
LED	Xitanium 36W WH 0.3-1.05A 54V S	1		SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.1	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.3	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.4	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.5	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	2	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is CL	1	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is CL	2	DALI	SimpleSet	
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1	DALI		
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1.1	DALI		
LED	Xitanium 36W/m 0.3-1.05A 54V 230V	1		SimpleSet	
LED	Xitanium 36W/m 0.3-1.05A 54V 230V	2		SimpleSet	
LED	Xitanium 36W/m 0.3-1.05A 54V OffDiag	1		SimpleSet	
LED	Xitanium 36W/m 0.3-1.05A 54V S TD 230V	1	DALI	SimpleSet	
LED	Xitanium 36W/m 0.3-1.05A 54V TD 230V	1.14	DALI		
LED	Xitanium 36W/m 0.3-1.05A 54V TD 230V	1.5	DALI		

LED	Xitanium 36W/xs 0.3-1.05A 48V 120V	1		SimpleSet	
LED	Xitanium 36W/xs 0.3-1.05A 48V 230V	1		SimpleSet	
LED	Xitanium 36W/xs 0.3-1.05A 48V D 230V	1	DALI	SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1		SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.1		SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.2		SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.3		SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V INT SR	1	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI INT	2	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.2	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.3	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.4	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.5	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	2	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR JPN	2	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR SPC	2	DALI	SimpleSet	
LED	Xitanium 40W/t 0.3-1A 54V TD 230V PCBA	1	DALI	SimpleSet	
LED	Xitanium 42W 0.5-1A 42V WZ 240V /I	1		SimpleSet	
LED	Xitanium 43W/m 0.7-1.2A 54V 230V	1		SimpleSet	
LED	Xitanium 43W/m 0.7-1.2A 54V 230V	2		SimpleSet	
LED	Xitanium 50/75W 0.3-1A 62V TD/TE 230V	1	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.1	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.2	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.3	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.1	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.11	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.16	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.18	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.8	DALI		
LED	Xitanium 50W LH 0.7-1.5A 48V 230V	1		SimpleSet	
LED	Xitanium 50W LH 0.7-1.5A 48V 230V	1.1		SimpleSet	
LED	Xitanium 50W LH 0.7-1.5A 48V TD/I 230V	1.1	DALI		
LED	Xitanium 50W WH 0.7-1.5A 54V Is	1		SimpleSet	
LED	Xitanium 50W WH 0.7-1.5A 54V Is G2	1		SimpleSet	
LED	Xitanium 50W WH 0.7-1.5A 54V S	1		SimpleSet	
LED	Xitanium 50W WH 0.7-1.5A 54V TD/Is 230V	1	DALI	SimpleSet	
LED	Xitanium 50W WH 0.7-1.5A 54V TD/Is CL	1	DALI	SimpleSet	
LED	Xitanium 50W/m 0.7-1.5A 54V 230V	1		SimpleSet	
LED	Xitanium 54W 0.1-1.5A 54V 0-10V 347V	1		SimpleSet	
LED	Xitanium 54W 0.15-0.3A 180V WZ 240V	1		SimpleSet	
LED	Xitanium 54W 0.24-0.3A 180V WZ 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V S 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V S/16 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V SR 230V	2.1	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V TD16 230V	2	DALI	SimpleSet	

LED	Xitanium 60W 0.08-0.35A 300V CL 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V S 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V S/16 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V SR 230V	2.1	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD16 230V	1	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD16 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD16 230V	2.1	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD21 230V	1	DALI		
LED	Xitanium 60W 0.15-0.5A 220V TD11 230V	1	DALI	SimpleSet	
LED	Xitanium 60W 0.15-0.5A 220V TD16 230V	1	DALI	SimpleSet	
LED	Xitanium 60W 0.15-0.5A 220V TD21 230V	1	DALI		
LED	Xitanium 65W 0.5-1.4A 54V S 230V	1		SimpleSet	
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1		SimpleSet	
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1.1		SimpleSet	
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.3	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.4	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.5	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.6	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.7	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	2	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD CL 230V	1.3	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD CL 230V	1.4	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.3	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.4	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.5	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.6	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.7	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2.1	DALI		
LED	Xitanium 75W 0.7-2A 54V SR 230V	4	DALI	SimpleSet	
LED	Xitanium 75W 0.7-2A 54V SR 230V	4.1	DALI	SimpleSet	
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.3	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.4	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.5	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.6	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.2	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.4	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	3	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.1	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.2	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	4	DALI	SimpleSet	
LED	Xitanium 75W 0.7-2A 54V TD 230V	4.1	DALI	SimpleSet	
LED	Xitanium 75W 1.1A Prog+ GL-F sXt	1.1	DALI		
LED	Xitanium 75W 1.2A sProg 230V-F sXt	1.2	DALI		
LED	Xitanium 75W 1.2A sProg GL-F sXt	1.2	DALI		

LED	Xitanium 75W 2A 54V DALI INT	2	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.1	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.2	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.4	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.5	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	2	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR SPC	2	DALI	SimpleSet	
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.1	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.2	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.3	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.4	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.5	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.14	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.15	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.16	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.3	DALI		
LED	Xitanium 75W/0.2-0.4A 200V 1-10V 230V	1.3	DALI		
LED	Xitanium FULL PROG 110W1000 NL1 C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 110W1000 NLD C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 35W1000 NL1 C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 35W1000 NLD C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 70W1000 NL1 C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 70W1000 NLD C150 Xt	1.3	DALI		
LED	Xitanium LITE PROG 110W1000 NL C150 OD	1.3	DALI		
LED	Xitanium LITE PROG 70W1000 NL C150 OD	1.3	DALI		
LED	Xitanium Outdoor 100W .53 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 100W .53 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 100W .53 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 100W 0.7 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 100W 0.7 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 100W 0.7 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V01E01	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V02E01	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V03E02	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V04E03	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V05E03	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V06E03	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V01E01	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V02E01	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V03E02	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V04E03	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V05E03	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V06E03	DALI		
LED	Xitanium Outdoor 150W 0.7 DD Prog+ 230V	V05E05	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ 230V	V01E01	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ 230V	V02E01	DALI		

LED	Xitanium Outdoor 150W 0.7 Prog+ 230V	V03E01	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V02E01	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V03E02	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V04E02	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V05E02	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V02E02	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V03E03	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V04E03	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V05E03	DALI		
LED	Xitanium Outdoor 150W Prog	V03E02	DALI		
LED	Xitanium Outdoor 150W Prog	V04E03	DALI		
LED	Xitanium Outdoor 150W Prog	V05E03	DALI		
LED	Xitanium Outdoor 150W Prog	V06E03	DALI		
LED	Xitanium Outdoor 150W Prog	V07E04	DALI		
LED	Xitanium Outdoor 150W Prog	V08E05	DALI		
LED	Xitanium Outdoor 150W Prog	V09E05	DALI		
LED	Xitanium Outdoor 150W Prog	V10E05	DALI		
LED	Xitanium Outdoor 150W Prog+	V01E01	DALI		
LED	Xitanium Outdoor 150W Prog+	V02E01	DALI		
LED	Xitanium Outdoor 150W Prog+	V03E01	DALI		
LED	Xitanium Outdoor 150W Prog+	V04E02	DALI		
LED	Xitanium Outdoor 150W Prog+	V05E03	DALI		
LED	Xitanium Outdoor 150W Prog+	V06E03	DALI		
LED	Xitanium Outdoor 150W Prog+	V07E03	DALI		
LED	Xitanium Outdoor 27W 1.0 Prog	V01E01	DALI		
LED	Xitanium Outdoor 27W 1.0 Prog	V02E01	DALI		
LED	Xitanium Outdoor 27W 1.0 Prog	V03E02	DALI		
LED	Xitanium Outdoor 40W .53 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 40W .53 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 40W .53 Prog+	V03E02	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog 230V	V01E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog 230V	V02E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog 230V	V03E02	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+ 230V	V01E01	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+ 230V	V02E01	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+ 230V	V03E01	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V02E02	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V03E03	DALI		

LED	Xitanium Outdoor 75W 1.0 Prog+	V04E03	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V05E03	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V01E01	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V02E01	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V03E02	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V04E03	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V05E03	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V06E03	DALI		
LED	Xitanium Outdoor 75W Prog	V02E02	DALI		
LED	Xitanium Outdoor 75W Prog	V03E03	DALI		
LED	Xitanium Outdoor 75W Prog	V04E03	DALI		
LED	Xitanium Outdoor 75W Prog	V05E03	DALI		
LED	Xitanium Outdoor 75W Prog	V06E04	DALI		
LED	Xitanium Outdoor 75W Prog	V07E05	DALI		
LED	Xitanium Outdoor 75W Prog	V08E05	DALI		
LED	Xitanium Outdoor 75W Prog	V09E05	DALI		
LED	Xitanium Outdoor 75W Prog+	V01E01	DALI		
LED	Xitanium Outdoor 75W Prog+	V02E01	DALI		
LED	Xitanium Outdoor 75W Prog+	V03E01	DALI		
LED	Xitanium Outdoor 75W Prog+	V04E02	DALI		
LED	Xitanium Outdoor 75W Prog+	V05E03	DALI		
LED	Xitanium Outdoor 75W Prog+	V06E03	DALI		
LED	Xitanium Outdoor 75W Prog+	V07E03	DALI		
SwitchBox	CodedLightInjector	1		SimpleSet	
SwitchBox	LLC7730/00 Coded Mains Receiver	1	DALI		
SwitchBox	SR Bridge SRB-BS	1	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-BS	1.1	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-BS2	2	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-LD	1	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-LD	1.1	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-LD2	2	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge built-in	1	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge built-in	1.1	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge independent	1	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge independent	1.1	DALI	SimpleSet	



Document: 19-06-2019
No: SDL2 2019
Author: E.Bos