

Select the right DuraMax™ decorative bulb for your home lighting needs!



BA9 Clear BA9 Frost BA9.5 Clear

**BENT TIPS**

- Life: Lasts 1 ½ years
- Wattages: 15, 25, 40 and 60 watt
- Finishes: Clear and Frost
- Base Sizes: Candelabra and Medium bases



B10.5 B13

**BLUNT TIPS**

- Life: Lasts 1 ½ years
- Wattages: 25, 40 and 60 watt
- Finishes: Clear Only
- Base Sizes: Candelabra and Medium bases



F10 Clear F15 Iridescent

**FLAMES**

- Life: Lasts 1 ½ years
- Wattages: 15, 25, 40 and 60 watt
- Finishes: Clear, White, Iridescent and Amber
- Base Sizes: Candelabra and Medium bases



F20 Clear

**POST LIGHT**

- Life: Lasts 1 year
- Wattages: 60 and 100 watt
- Finishes: Clear Only
- Base Sizes: Medium Base Only



G16.5 Clear G16.5 White

**DECORATIVE GLOBES**

- Life: Lasts 2 years
- Wattages: 25 and 40 Watt
- Finishes: Clear and White
- Base Sizes: Candelabra Base Only



Ideal for use in chandeliers, wall sconces and other decorative light fixtures

- Lasts At Least One Year!\***  
Tired of changing light bulbs that burn out too frequently? DuraMax™ Decorative light bulbs now last at least one year!
- Adds a Pleasant Touch to Home Décor**  
—Clear light bulbs provide decorative sparkle.  
—Frosted light bulbs add a soft glow.  
—Iridescent and amber light bulbs add a dash of shimmer and color.  
—White light bulbs provide a soft white glow.
- Consumer Friendly Packaging**  
Fresh, new packaging graphics make life, lumen and wattage information easy to find and read.
- Full Family of Products**  
Available in a variety of shapes, sizes, wattages and finishes.

\* See next page for details.



# DuraMax™ Long Life Decoratives

Electrical, Technical and Ordering Data (Subject to change without notice)

Shipping Data (Subject to change without notice)

| DuraMax Product Number                     | Previous Product Number | Alternate Product Number | Product Description          | Bulb Finish | Nom. Watts | Bulb Type | Base Type | Volts | Published Lumens | Rated Avg Life (Hrs.) | Life, in Years* | M.O.L (In.) | Operating Position  | DuraMax Product Number                     | UPC Code | OUTER Bar Code | Lamps Per SKU | Case Qty. Per SKU | Case Wt. (lbs.) | Case Cube (cu. ft.) | Pallet Qty. Per Case | Pallet Qty. Per Case | Pallet Wt. (lbs.) | Pallet Cube (cu. ft.) | SKUs Per Layer | SKU Layers High | SKU Dim. (in.) W x D x H | Case Dim. (in.) W x D x H | Pallet Dim. (in.) W x D x H |
|--|-------------------------|--------------------------|------------------------------|-------------|------------|-----------|-----------|-------|------------------|-----------------------|-----------------|-------------|---------------------|--|----------|----------------|---------------|-------------------|-----------------|---------------------|----------------------|----------------------|-------------------|-----------------------|----------------|-----------------|--------------------------|---------------------------|-----------------------------|
| <b>BA9—Bent Tip, Candelabra Base</b>       |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>BA9—Bent Tip, Candelabra Base</b>       |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168112                                     | 390310                  | N/A                      | BC15BA9C/CL/LL 120V 6/2      | CLEAR       | 15         | BA-9      | CAND.     | 120   | 110              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168112                                     | 16811 7  | 16811 2        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168062                                     | 390328                  | 231589                   | BC25BA9C/CL/LL 120V 6/2      | CLEAR       | 25         | BA-9      | CAND.     | 120   | 150              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168062                                     | 16806 3  | 16806 8        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168104                                     | 390377                  | 253260                   | BC25BA9C/F/LL 120V 6/2       | FROST       | 25         | BA-9      | CAND.     | 120   | 145              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168104                                     | 16810 0  | 16810 5        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 167197                                     | 278002                  | N/A                      | BC25BA9C/CL/LL 6/4           | CLEAR       | 25         | BA-9      | CAND.     | 120   | 150              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 167197                                     | 16802 5  | 16719 1        | 4             | 6/4               | 1               | 0.27                | 1080                 | 180                  | 180.0             | 48.60                 | 180            | 6               | 6.4 x 1.4 x 7.0          | 8.9 x 6.8 x 7.7           | 44.4 x 40.5 x 46.1          |
| 168070                                     | 390336                  | 231761                   | BC40BA9C/CL/LL 120V 6/2      | CLEAR       | 40         | BA-9      | CAND.     | 120   | 300              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168070                                     | 16807 0  | 16807 5        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 167205                                     | 278010                  | N/A                      | BC40BA9C/CL/LL 6/4           | CLEAR       | 40         | BA-9      | CAND.     | 120   | 300              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 167205                                     | 16803 2  | 16720 7        | 4             | 6/4               | 1               | 0.27                | 1080                 | 180                  | 180.0             | 48.60                 | 180            | 6               | 6.4 x 1.4 x 7.0          | 8.9 x 6.8 x 7.7           | 44.4 x 40.5 x 46.1          |
| 168096                                     | 390369                  | 253252                   | BC40BA9C/F/LL 120V 6/2       | FROST       | 40         | BA-9      | CAND.     | 120   | 295              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168096                                     | 16809 4  | 16809 9        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168088                                     | 390344                  | 231951                   | BC60BA9C/CL/LL 120V 6/2      | CLEAR       | 60         | BA-9      | CAND.     | 120   | 550              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168088                                     | 16808 7  | 16808 2        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 167213                                     | 278044                  | N/A                      | BC60BA9C/CL/LL 6/4           | CLEAR       | 60         | BA-9      | CAND.     | 120   | 550              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 167213                                     | 16804 9  | 16721 4        | 4             | 6/4               | 1               | 0.27                | 1080                 | 180                  | 180.0             | 48.60                 | 180            | 6               | 6.4 x 1.4 x 7.0          | 8.9 x 6.8 x 7.7           | 44.4 x 40.5 x 46.1          |
| 168054                                     | 390351                  | 222067                   | BC60BA9C/F/LL 120V 6/2       | FROST       | 60         | BA-9      | CAND.     | 120   | 545              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168054                                     | 16805 6  | 16805 1        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| <b>Case Pk.</b>                            |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>Case Pk.</b>                            |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168187                                     | 380766                  | N/A                      | CS-BC40BA9C/CL/LL 120V 12/4  | CLEAR       | 40         | BA-9      | CAND.     | 120   | 300              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168187                                     | 16803 2  | 16818 1        | 4             | 12/4              | 3               | 0.66                | 768                  | 64                   | 192.0             | 42.24                 | 96             | 8               | 6.4 x 1.4 x 7.0          | 29.6 x 6.9 x 5.6          | 48.2 x 36.5 x 44.5          |
| <b>Display</b>                             |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>Display</b>                             |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168047                                     | 206870                  | N/A                      | DIS48-60BA9C/CL/LL 120V 48/4 | CLEAR       | 60         | BA-9      | CAND.     | 120   | 550              | 2000                  | 1 1/2           | 4 3/16      | BASE DOWN TO HORIZ. | 168047                                     | 16804 9  | 16804 4        | 4             | 48/4              | 12.13           | 2.76                | 864                  | 18                   | 218.3             | 49.68                 | 432            | 2               | 6.4 x 1.4 x 7.0          | 14.8 x 12.8 x 25.4        | 44.3 x 38.3 x 50.8          |
| <b>BA9.5—Bent Tip, Medium Base</b>         |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>BA9.5—Bent Tip, Medium Base</b>         |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168195                                     | 389528                  | 329581                   | BC25BA9-1/2/CL/LL 120V 6/2   | CLEAR       | 25         | BA-9.5    | MED.      | 120   | 150              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168195                                     | 16819 3  | 16819 8        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168203                                     | 389536                  | 231894                   | BC40BA9-1/2/CL/LL 120V 6/2   | CLEAR       | 40         | BA-9.5    | MED.      | 120   | 300              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168203                                     | 16820 9  | 16820 4        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 167601                                     | 278051                  | N/A                      | BC40BA9-1/2/CL/LL 120V 6/4   | CLEAR       | 40         | BA-9.5    | MED.      | 120   | 300              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 167601                                     | 16760 8  | 16760 3        | 4             | 6/4               | 1               | 0.27                | 1080                 | 180                  | 180.0             | 48.60                 | 180            | 6               | 6.4 x 1.4 x 7.0          | 8.9 x 6.8 x 7.7           | 44.4 x 40.5 x 46.1          |
| 168211                                     | 389544                  | 221606                   | BC40BA9-1/2/F/LL 120V 6/2    | FROST       | 40         | BA-9.5    | MED.      | 120   | 295              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168211                                     | 16821 6  | 16821 1        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168229                                     | 389551                  | 329623                   | BC60BA9-1/2/CL/LL 120V 6/2   | CLEAR       | 60         | BA-9.5    | MED.      | 120   | 550              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168229                                     | 16822 3  | 16822 8        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168237                                     | 389569                  | 329631                   | BC60BA9-1/2/F/LL 120V 6/2    | FROST       | 60         | BA-9.5    | MED.      | 120   | 545              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168237                                     | 16823 0  | 16823 5        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| <b>B10.5—Blunt Tip, Candelabra Base</b>    |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>B10.5—Blunt Tip, Candelabra Base</b>    |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168245                                     | 389577                  | 329672                   | BC25B10-1/2C/CL/LL 120V 6/2  | CLEAR       | 25         | B-10.5    | CAND.     | 120   | 150              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168245                                     | 16824 7  | 16824 2        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168252                                     | 389585                  | 329680                   | BC40B10-1/2C/CL/LL 120V 6/2  | CLEAR       | 40         | B-10.5    | CAND.     | 120   | 300              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168252                                     | 16825 4  | 16825 9        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168260                                     | 389593                  | 329698                   | BC60B10-1/2C/CL/LL 120V 6/2  | CLEAR       | 60         | B-10.5    | CAND.     | 120   | 550              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 168260                                     | 16826 1  | 16826 6        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| <b>B13—Blunt Tip, Medium Base</b>          |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>B13—Blunt Tip, Medium Base</b>          |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168278                                     | 389601                  | 353555                   | BC25B13/CL/LL 120V 6/2       | CLEAR       | 25         | B-13      | MED.      | 120   | 150              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN           | 168278                                     | 16827 8  | 16827 3        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168286                                     | 389619                  | 354563                   | BC40B13/CL/LL 120V 6/2       | CLEAR       | 40         | B-13      | MED.      | 120   | 300              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN           | 168286                                     | 16828 5  | 16828 0        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168294                                     | 389627                  | 354571                   | BC60B13/CL/LL 120V 6/2       | CLEAR       | 60         | B-13      | MED.      | 120   | 550              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN           | 168294                                     | 16829 2  | 16829 7        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| <b>F10—Flame, Candelabra Base</b>          |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>F10—Flame, Candelabra Base</b>          |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168302                                     | 389643                  | N/A                      | BC15F10/CL/LL 120V 6/2       | CLEAR       | 15         | F-10      | CAND.     | 120   | 95               | 2000                  | 1 1/2           | 3 1/16      | BASE DOWN TO HORIZ. | 168302                                     | 16830 8  | 16830 3        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168310                                     | 329656                  | N/A                      | BC15F10C/A/LL 120V 6/2       | AMBER       | 15         | F-10      | CAND.     | 120   | 85               | 2000                  | 1 1/2           | 3 1/16      | BASE DOWN TO HORIZ. | 168310                                     | 16831 5  | 16831 0        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| 168328                                     | 329664                  | N/A                      | BC25F10C/CL/LL 120V 6/2      | CLEAR       | 25         | F-10      | CAND.     | 120   | 105              | 2000                  | 1 1/2           | 3 1/16      | BASE DOWN TO HORIZ. | 168328                                     | 16832 2  | 16832 7        | 2             | 6/2               | 1               | 0.22                | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 x 7.4          | 42.2 x 38.0 x 44.6          |
| <b>CA10—Flicker Flame, Candelabra Base</b> |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>CA10—Flicker Flame, Candelabra Base</b> |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 166982                                     | N/A                     | N/A                      | BC3CA10C/CL/LL 120V 6/1      | CLEAR       | 3          | CA-10     | CAND.     | 120   | N/A              | 2000                  | 1 1/2           | 4 1/16      | BASE DOWN TO HORIZ. | 166982                                     | 16698 4  | 16698 9        | 1             | 6/1               | 1               | .22                 | 1152                 | 192                  | 192.0             | 42.24                 | 192            | 6               | 4.0 x 1.4 x 7.0          | 10.6 x 4.8 .7.4           | 42.2 x 38.0 x 44.6          |
| <b>F15—Flame, Medium Base</b>              |                         |                          |                              |             |            |           |           |       |                  |                       |                 |             |                     | <b>F15—Flame, Medium Base</b>              |          |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |
| 168336                                     | 389668                  | 231449                   | BC25F15/CL/LL 120V 6/2       | CLEAR       | 25         | F-15      | MED.      | 120   | 150              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168336                                     | 16833 9  | 16833 4        | 2             | 6/2               | 1.8             | 0.39                | 648                  | 108                  | 194.4             | 42.12                 | 108            | 6               | 5.4 x 2.0 x 7.0          | 14.8 x 6.1 x 7.4          | 44.4 x 36.8 x 44.6          |
| 168401                                     | 389684                  | N/A                      | BC25F15/W/LL 120V 6/2        | WHITE       | 25         | F-15      | MED.      | 120   | 120              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168401                                     | 16840 7  | 16840 2        | 2             | 6/2               | 1.8             | 0.39                | 648                  | 108                  | 194.4             | 42.12                 | 108            | 6               | 5.4 x 2.0 x 7.0          | 14.8 x 6.1 x 7.4          | 44.4 x 36.8 x 44.6          |
| 168419                                     | 389650                  | 329706                   | BC25F15/A/LL 120V 6/2        | AMBER       | 25         | F-15      | MED.      | 120   | 130              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168419                                     | 16841 4  | 16841 9        | 2             | 6/2               | 1.8             | 0.39                | 648                  | 108                  | 194.4             | 42.12                 | 108            | 6               | 5.4 x 2.0 x 7.0          | 14.8 x 6.1 x 7.4          | 44.4 x 36.8 x 44.6          |
| 168393                                     | 389676                  | 284612                   | BC25F15/IR/LL 120V 6/2       | IRIDES.     | 25         | F-15      | MED.      | 120   | 150              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168393                                     | 16839 1  | 16839 6        | 2             | 6/2               | 1.8             | 0.39                | 648                  | 108                  | 194.4             | 42.12                 | 108            | 6               | 5.4 x 2.0 x 7.0          | 14.8 x 6.1 x 7.4          | 44.4 x 36.8 x 44.6          |
| 168351                                     | 389692                  | 231456                   | BC40F15/CL/LL 120V 6/2       | CLEAR       | 40         | F-15      | MED.      | 120   | 385              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168351                                     | 16835 3  | 16835 8        | 2             | 6/2               | 1.8             | 0.39                | 648                  | 108                  | 194.4             | 42.12                 | 108            | 6               | 5.4 x 2.0 x 7.0          | 14.8 x 6.1 x 7.4          | 44.3 x 36.8 x 44.6          |
| 168385                                     | 389700                  | 329722                   | BC40F15/W/LL 120V 6/2        | WHITE       | 40         | F-15      | MED.      | 120   | 300              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168385                                     | 16838 4  | 16838 9        | 2             | 6/2               | 1.8             | 0.39                | 648                  | 108                  | 194.4             | 42.12                 | 108            | 6               | 5.4 x 2.0 x 7.0          | 14.8 x 6.1 x 7.4          | 44.4 x 36.8 x 44.6          |
| 168377                                     | 389635                  | 284448                   | BC40F15/IR/LL 120V 6/2       | IRIDES.     | 40         | F-15      | MED.      | 120   | 370              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168377                                     | 16837 7  | 16837 2        | 2             | 6/2               | 1.8             | 0.39                | 648                  | 108                  | 194.4             | 42.12                 | 108            | 6               | 5.4 x 2.0 x 7.0          | 14.8 x 6.1 x 7.4          | 44.4 x 36.8 x 44.6          |
| 168427                                     | 389718                  | 329730                   | BC60F15/CL/LL 120V 6/2       | CLEAR       | 60         | F-15      | MED.      | 120   | 630              | 2000                  | 1 1/2           | 4 1/2       | BASE DOWN TO HORIZ. | 168427                                     | 16842 1  |                |               |                   |                 |                     |                      |                      |                   |                       |                |                 |                          |                           |                             |