

DuraMax™

LONG LIFE GLOBES



Ideal for use in pendent or hanging fixtures, as well as bathroom vanity strips

▶ Lasts 2 Years!*

Tired of changing light bulbs that burn out too frequently? DuraMax™ Globes now last two years!

▶ Adds a Decorative Touch to Vanity Strips and Hanging Light Fixtures

Clear globes add decorative sparkle, while white globes emit soft white light.

▶ Consumer Friendly Packaging

Fresh, new packaging graphics make life, lumen and wattage information easy to find and read.

▶ Full Family of Products

Available in clear and white, in a variety of sizes and wattages.

* See back page for details.



PHILIPS

DuraMax™ Long Life Globes

Electrical, Technical and Ordering Data (Subject to change without notice)

DuraMax Product Number	Previous Product Number	Product Description	Bulb Finish	Nom. Watts	Bulb Type	Base Type	Volts	Published Lumens	Rated Avg Life (Hrs.)	Life, in Years*	M.O.L (In.)	Operating Position
G-25 Vanity Globe												
168872	250035	25G25/CL/LL 120V 12/1	CLEAR	25	G-25	MED.	120	235	2000	2	4 7/16	ANY
167486	250050	25G25/W/LL 120V 12/1	WHITE	25	G-25	MED.	120	210	2000	2	4 7/16	ANY
167478	250043	40G25/CL/LL 120V 12/1	CLEAR	40	G-25	MED.	120	460	2000	2	4 7/16	ANY
167460	250019	40G25/W/LL 120V 12/1	WHITE	40	G-25	MED.	120	415	2000	2	4 7/16	ANY
168962	250464	60G25/CL/LL 120V 12/1	CLEAR	60	G-25	MED.	120	775	2000	2	4 7/16	ANY
167494	250498	60G25/W/LL 120V 12/1	WHITE	60	G-25	MED.	120	700	2000	2	4 7/16	ANY
G-25 Vanity Chrome Top Globe												
167023	N/A	40G25/CT 120V 6/1	CLEAR-CHROME	40	G-25	MED.	120	200	2000	2	4 7/16	ANY
3-Packs												
169011	250522	25G25/CL/LL 120V 4/3	CLEAR	25	G-25	MED.	120	235	2000	2	4 7/16	ANY
169029	250530	25G25/W/LL 120V 4/3	WHITE	25	G-25	MED.	120	210	2000	2	4 7/16	ANY
169037	250548	40G25/CL/LL 120V 4/3	CLEAR	40	G-25	MED.	120	460	2000	2	4 7/16	ANY
169045	250555	40G25/W/LL 120V 4/3	WHITE	40	G-25	MED.	120	415	2000	2	4 7/16	ANY
168996	250506	60G25/CL/LL 120V 4/3	CLEAR	60	G-25	MED.	120	775	2000	2	4 7/16	ANY
169003	250514	60G25/W/LL 120V 4/3	WHITE	60	G-25	MED.	120	700	2000	2	4 7/16	ANY
Display												
169078	373654	DIS48-40G25/W/LL 120V 1/48	WHITE	40	G-25	MED.	120	415	2000	2	4 7/16	ANY
G-30 Globe												
168492	281410	60G30/W/LL 120V 6/1	WHITE	60	G-30	MED.	120	580	3000	2	5 1/2	ANY
168500	281501	100G30/W/LL 120V 6/1	WHITE	100	G-30	MED.	120	945	3000	2	5 1/2	ANY
G-40 Globe												
168575	361683	40G40/CL/LL 120V 6/1	CLEAR	40	G-40	MED.	120	305	3000	2	6 15/16	ANY
168583	361824	40G40/W/LL 120V 6/1	WHITE	40	G-40	MED.	120	335	3000	2	6 15/16	ANY
168526	202028	60G40/CL/LL 120V 6/1	CLEAR	60	G-40	MED.	120	665	3000	2	6 15/16	ANY
168518	202010	60G40/W/LL 120V 6/1	WHITE	60	G-40	MED.	120	595	3000	2	6 15/16	ANY
168591	361873	100G40/CL/LL 120V 6/1	CLEAR	100	G-40	MED.	120	1100	3000	2	6 15/16	ANY
168534	202481	100G40/W/LL 120V 6/1	WHITE	100	G-40	MED.	120	985	3000	2	6 15/16	ANY
168542	202655	150G40/W/LL 120V 6/1	WHITE	150	G-40	MED.	120	1770	3000	2	6 15/16	ANY

Shipping Data (Subject to change without notice)

DuraMax Product Number	Product Description	UPC Code	Outer Bar Code	Lamps Per SKU	Case Qty. Per SKU	Case Wt. (lbs.)	Case Cube (cu. ft.)	Pallet Qty. Per Case	Pallet Qty. Per Case	Pallet Wt. (lbs.)	Pallet Cube (cu. ft.)	SKUs Per Layer	SKU Layers High	SKU Dim. (In.) W x D x H	Case Dim. (In.) W x D x H	Pallet Dim. (In.) W x D x H
G-25 Vanity Globe																
168872	25G25/CL/LL 120V 12/1	16887 2	16887 7	1	12/1	2	0.37	1800	150	300.0	55.50	180	10	3.1 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
167486	25G25/W/LL 120V 12/1	16748 6	16748 1	1	12/1	2	0.37	1800	150	300.0	55.50	180	10	3.1 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
167478	40G25/CL/LL 120V 12/1	16747 9	16747 4	1	12/1	2	0.37	1800	150	300.0	55.50	180	10	3.1 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
167460	40G25/W/LL 120V 12/1	16746 2	16746 7	1	12/1	2	0.37	1800	150	300.0	55.50	180	10	3.1 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
168962	60G25/CL/LL 120V 12/1	16896 4	16896 9	1	12/1	2	0.37	1800	150	300.0	55.50	180	10	3.1 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
167494	60G25/W/LL 120V 12/1	16749 3	16749 8	1	12/1	2	0.37	1800	150	300.0	55.50	180	10	3.1 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
G-25 Vanity Chrome Top Globe																
167023	40G25/CT 120V 12/1	16702 8	16702 3	1	6/1	1	0.17	1800	180	360.0	51.00	180	10	3.1 x 3.1 x 4.3	6.5 x 4.6 x 4.6	48.8 x 39.0 x 46.3
3-Packs																
169011	25G25/CL/LL 120V 4/3	16901 5	16901 0	3	4/3	2	0.37	600	150	300.0	55.50	60	10	9.5 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
169029	25G25/W/LL 120V 4/3	16902 2	16902 7	3	4/3	2	0.37	600	150	300.0	55.50	60	10	9.5 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
169037	40G25/CL/LL 120V 4/3	16903 4	16903 9	3	4/3	2	0.37	600	150	300.0	55.50	60	10	9.5 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
169045	40G25/W/LL 120V 4/3	16910 7	16904 1	3	4/3	2	0.37	600	150	300.0	55.50	60	10	9.5 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
168996	60G25/CL/LL 120V 4/3	16914 5	16899 0	3	4/3	2	0.37	600	150	300.0	55.50	60	10	9.5 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
169003	60G25/W/LL 120V 4/3	16916 9	16900 3	3	4/3	2	0.37	600	150	300.0	55.50	60	10	9.5 x 3.1 x 4.3	13.1 x 9.9 x 4.9	49.7 x 39.2 x 49.4
Display																
169078	DIS48-40G25/W/LL 120V 1/48	16746 2	16907 2	1	48/1	11.2	2.59	720	15	168.0	38.85	144	5	3.1 x 3.1 x 4.3	33.8 x 15.4 x 8.6	46.1 x 33.8 x 43.2
G-30 Globe																
168492	60G30/W/LL 120V 6/1	16849 0	16849 5	1	6/1	1	0.31	960	160	160.0	49.60	120	8	3.8 x 3.8 x 5.3	11.8 x 8.0 x 5.8	47.0 x 40.0 x 46.0
168500	100G30/W/LL 120V 6/1	16850 6	16850 1	1	6/1	1	0.31	960	160	160.0	49.60	120	8	3.8 x 3.8 x 5.3	11.8 x 8.0 x 5.8	47.0 x 40.0 x 46.0
G-40 Globe																
168575	40G40/CL/LL 120V 6/1	16857 5	16857 0	1	6/1	3	0.86	360	60	180.0	51.60	60	6	5.1 x 5.1 x 7.6	16.4 x 10.9 x 8.3	49.3 x 38.4 x 49.5
168583	40G40/W/LL 120V 6/1	16858 2	16858 7	1	6/1	3	0.86	360	60	180.0	51.60	60	6	5.1 x 5.1 x 7.6	16.4 x 10.9 x 8.3	49.3 x 38.4 x 49.5
168526	60G40/CL/LL 120V 6/1	16852 0	16852 5	1	6/1	3	0.86	360	60	180.0	51.60	60	6	5.1 x 5.1 x 7.6	16.4 x 10.9 x 8.3	49.3 x 38.4 x 49.5
168518	60G40/W/LL 120V 6/1	16851 3	16851 8	1	6/1	3	0.86	360	60	180.0	51.60	60	6	5.1 x 5.1 x 7.6	16.4 x 10.9 x 8.3	49.3 x 38.4 x 49.5
168591	100G40/CL/LL 120V 6/1	16859 9	16859 4	1	6/1	3	0.86	360	60	180.0	51.60	60	6	5.1 x 5.1 x 7.6	16.4 x 10.9 x 8.3	49.3 x 38.4 x 49.5
168534	100G40/W/LL 120V 6/1	16853 7	16853 2	1	6/1	3	0.86	360	60	180.0	51.60	60	6	5.1 x 5.1 x 7.6	16.4 x 10.9 x 8.3	49.3 x 38.4 x 49.5
168542	150G40/W/LL 120V 6/1	16854 4	16854 9	1	6/1	3	0.86	360	60	180.0	51.60	60	6	5.1 x 5.1 x 7.6	16.4 x 10.9 x 8.3	49.3 x 38.4 x 49.5

* G-25s last 2 years based on 2 1/2 hours usage per day/7 days per week; G-30s and G-40s last 2 years based on 4 hours usage per day/7 days per week.

