

# Light to go



Things just got easier. Introducing our new lineup of lighting essentials – quick to order, easy on your wallet and simple to use.

Make your next outdoor lighting choice a brand you can trust. **Make it Philips Lighting.**

[philips.com/Lighttogo](http://philips.com/Lighttogo)

## Philips Light to go luminaires

Philips knows contractors look for dependability and ease of installation when choosing their lighting – and these LED luminaires were designed with that in mind. Strong and long lasting with solid performance, adding light where you need it is quick and easier than ever.

You've found your **go to** lights,

Philips **Light to go**



**PHILIPS**

Light to go

Indoor Luminaires

Real professionals choose Lighttogo



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify, Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

PLT-17100LL 02/19 [philips.com/lighttogo](http://philips.com/lighttogo)

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9

**REAL PROs**  
**REAL QUALITY**




Real professionals choose Lighttogo

## Flat panel



- High quality fixture that will pay off in the long run.
- Help bolster wellbeing and productivity without worrying about flicker and other undesired effects.
- Immerse users in comfortable, welcoming spaces that are free of glare with color that remains consistent throughout the space and over time.
- Protect both the integrity of electrical equipment and overall building efficiency from the effects of total harmonic distortion.

## Recessed troffer



- Discretely designed to blend seamlessly into your space.
- Access to LED boards and drivers from below the ceiling increases maintenance convenience.
- Diffused ribbed lens creates soft, even illumination.
- Choose from 3500 or 4000K color temperatures.

## Wet linear strip



- Suitable for wet locations.
- White one piece, molded fiberglass reinforced polyester body. No rusting, no oxidation, and no corrosion.
- Continuous compressible closed cell gasket provides tight seal enhancing durability.
- cETLus listed to meet UL for -20C to 40C ambient.
- LED light engines and drivers are field replaceable.
- Components are RoHS compliant.

## Linear



- Rugged and reliable, the Philips LED Linear family includes strip, industrial and wraparound luminaires.
- Simple installation.
- Efficacy up to 131 lumens per watt.

# Easy order. Budget friendly. Job ready.



Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
P2FXP38B835-2-D5-UNV-DIM	2x2'	3800	3500K	0-10V	2xF17T8
P2FXP38B840-2-D5-UNV-DIM			4000K		2xF17T8
P2FXP42B835-4-D5-UNV-DIM	2x4'	4200	3500K	0-10V	2xF32T8
P2FXP42B840-4-D5-UNV-DIM			4000K		2xF32T8

Philips Catalog Code	Size	Lumens	Color Temp	Dim.	Replaces
P2FGG38B835-2-D-UNV-DIM	2'x2'	3800	3500K	0-10V	2xF17T8
P2FGG38B840-2-D-UNV-DIM			4000K		2xF17T8
P2FGG42B835-4-D-UNV-DIM	2'x4'	4200	3500K	0-10V	2xF32T8
P2FGG42B840-4-D-UNV-DIM			4000K		2xF32T8

Philips Catalog Code	Size	Lum.	Color Temp	Replaces
PV3WEZ440L840-UNV	4'	4000	4000K	2xF32T8

Philips Catalog Code	Size	Lum.	Color Temp	Dim.	Replaces
PFSSEZ440L830-UNV (Strip)	4'	4000	3000K	N/A	2xF32T8
PFSSEZ440L840-UNV (Strip)			4000K		2xF32T8
PFSWEZ440L830-UNV (Wraparound)	4'	4000	3000K	N/A	2xF32T8
PFSWEZ440L840-UNV (Wraparound)			4000K		2xF32T8
PFSI45L840-UNV-DIM (Industrial)	4'	5500	4000	0-10V	3xF32T8
PFSI810L840-UNV-DIM (Industrial)	8'	11000	4000	0-10V	6xF32T8

Please refer to the specification sheets for additional information and technical data, [philips.com/Lighttogo](http://philips.com/Lighttogo)

## Sealed high bay



- Corrosion resistant bronze finish.
- Heavy duty eyelet for heavy-duty suspension.
- Lumen maintenance up to 70% (L70) at 50,000 hours.
- Exposed leads for wiring connection with sleeving for environmental protection.
- Die cast frame and driver containment housing.
- cULus listed for use in wet locations up to 40°C ambient.
- Components are RoHS compliant.
- DesignLights Consortium qualified.
- IP65 rated.

## Value high bay



- Die formed sheet metal housing and end plates.
- Corrosion resistant gloss white paint after fabrication finish.
- V-hooks and 48" chains supplied (set of 2) for installation.
- Lumen maintenance up to 70% (L70) at 50,000 hours.
- Access plate located on top of housing for easy wiring.
- cULus listed for use in damp locations up to 40C ambient.
- Components are RoHS compliant.
- DesignLights Consortium qualified.

## High bay



- Versatile fixture ideal for a variety of spaces including warehouses, big box retail and school gymnasiums.
- 16,000 & 24,000 lumen versions available.
- Simple installation.
- Dimming is standard.
- Both versions are serious energy savers with outputs up to 138 lumens per watt.
- DLC listed.

## Exit & Emergency



- A complete family of dependable products to make buying, ordering & installation for large projects easier.
- Exit signs run off a long-life, 6 volt maintenance-free battery.
- All 3 versions can mount on wall or ceiling.
- Emergency unit and Exit combo can be used for indoor or covered outdoor spaces.
- Units and combos also contain a manual test switch with LED light indicator and supply emergency illumination for at least 90 minutes.

Philips Catalog Code	Lumens	Color Temp	Voltage	Replaces
PHCX15L840-UNV-DIM	15,000	4000K	120-277V	6xF32T8 or 400W HID
PHCX22L840-UNV-DIM	22,000	4000K	120-277V	8xF32T8 or 400W HID

Philips Catalog Code	Lumens	Color Temp	Voltage	Replaces
PFCX15L840-UNV-DIM	15,000	4000K	120-277V	6xF32T8 or 400W HID
PFCX22L840-UNV-DIM	22,000	4000K	120-277V	8xF32T8 or 400W HID

Philips Catalog Code	Size	Lumens	Color Temp	Dim.	Replaces
PFBX16LL40-UNV	2' x 2'	16,000	4000K	0-10V	6xF32T8 or 400W HID
PFBX16LL50-UNV			5000K		
PFBX24LL40-UNV	2' x 2'	24,000	4000K	0-10V	8xF32T8 or 400W HID
PFBX24LL50-UNV			5000K		
PFBX CHAIN KIT, PFBX-GRIP10, PFBX-GRIP5, PFBX-PENHGR	High bay mounting accessories (54" chains, 10' cable, 5' cable, pendant hanger)				

Philips Catalog Code	Letter Color	Finish	Operation	
PVERWEM (Exit Sign)	Red	White	Emergency (Nicad Battery)	
PVEGWEM (Exit Sign)	Green	White	Emergency (Nicad Battery)	
Philips Catalog Code	Voltage	Finish	# LED Lamps	Remote
PVLLCR2R (Red Letter Exit Combo)	3.6V	White	2-1W	2-1W or 1-2W Head
PVLLG2R (Green Letter Exit Combo)	3.6V	White	2-1W	2-1W or 1-2W Head
PVLLU (Emergency Unit)	3.6V	White	2-1W	None
PVLL1R (Remote Lamp Head)	3.6V	White	1-1W	Indoor
PVLL2R (Remote Lamp Head)	3.6V	White	2-1W	Indoor
PVLL1RGO (Remote Lamp Head)	3.6, 6, 9.6 or 12V	Gray	1-1W	Outdoor
PVLL2RGO (Remote Lamp Head)	3.6, 6, 9.6 or 12V	Gray	2-1W	Outdoor

Please refer to the specification sheets for additional information and technical data, [philips.com/Lighttogo](http://philips.com/Lighttogo)