

Light to go



Things just got easier. Introducing our new lineup of lighting essentials – quick to order, easy on your wallet and simple to use.

Make your next outdoor lighting choice a brand you can trust. **Make it Philips Lighting.**

philips.com/Lighttogo

Philips Lighttogo luminaires

Philips knows contractors look for dependability and ease of installation when choosing their lighting – and these LED luminaires were designed with that in mind. Strong and long lasting with solid performance, adding light where you need it is quicker and easier than ever.

Easy outdoor lighting solutions,

Look for Philips Light to go



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify, Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

PLT-17102LL 01/19 philips.com/lighttogo

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9

PHILIPS

Lighttogo

Outdoor Luminaires

Real professionals choose Lighttogo

REAL PROs
REAL QUALITY

Philips Catalog Code	Watts	Lumens	Mounting	Replaces
PFL20-NW-G1-K-FL-8-BZ*	20W	2122	Knuckle Mount 1/2" NPS male	70W PSMH
PFL40-NW-G1-K-FL-8-BZ*	39W	4433	Knuckle Mount 1/2" NPS male	150W PSMH
PFL80-NW-G1-T-FL-8-BZ*	79W	8856	Trunion	250W PSMH
PFL80-NW-G1-S-FL-8-BZ	79W	8856	Slip Fitter	250W PSMH
PFL150-NW-G1-T-FL-8-BZ*	146W	16325	Trunion	400W PSMH
PFL150-NW-G1-S-FL-8-BZ	146W	16325	Slip Fitter	400W PSMH
PFL200-NW-G1-T-FL-8-BZ	197W	24254	Trunion	400W PSMH
PFL200-NW-G1-S-FL-8-BZ	197W	24254	Slip Fitter	400W PSMH
PFL300-NW-G1-T-FL-8-BZ	301W	34025	Trunion	750W PSMH
PFL300-NW-G1-S-FL-8-BZ	301W	34025	Slip Fitter	750W PSMH

*Also available with button photocell (PCB) option.

- Complete family of LED floodlights ideal to illuminate signs, building facades or other dark areas.
- Can be mounted on the ground, wall or pole-mounted.
- IP66 rated.
- Discreet, modern design.
- 4000K Color Temperature
- 5 year limited warranty.
- All 5 sizes arrive fully assembled and ready to install. Three larger sizes have a trunion or slip fitter mount and the two smaller sizes have a knuckle mount.
- Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant.



General purpose floods



Real professionals choose Lighttogo

Philips Catalog Code	Watts	Lumens	Dist.	Replaces
PGC20-NW-G1-SM-5-8-BZ	19W	2013	Type 5	50W PSMH
PGC40-NW-G1-SM-5-8-BZ	37W	4735	Type 5	70W PSMH
PGC57-NW-G1-SM-5-8-BZ	57W	6322	Type 5	100W PSMH
PGC88-NW-G1-SM-5-8-BZ	88W	10490	Type 5	150W PSMH

- Cost-effective and efficient lighting for parking garages, covered walkways and canopies.
- Slim and compact design.
- Durable, weather-tight construction or retrofit installation.
- Great choice for new construction or retrofit.
- Easy install with the integral quick-mount plate, or pendant mount with 3/4" rigid conduit.
- 5 year limited warranty.
- IP66 rated construction with a rugged, UV stabilized, frosted lens.
- 4000K Color Temperature



Garage & Canopy

Area light



- Budget-friendly, high quality area lighting for parking and outdoor spaces.
- LED technology will save up to 68% energy over HID.*
- Enhance the sense of security.
- Square pole mounting standard, round pole mount adapter included.

- Durable aluminum construction.
- Lifetime >54,000 hours.**
- 4000K Color Temperature
- 5 year limited warranty.

* Based on comparison between 250W PSMH (at 295W) and AL-150-NW-G1 at 147W.
 ** Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology.

Dusk to Dawn



- Dusk to Dawn is sturdy, fade and abrasion resistant, built of a one-piece die-cast aluminum housing.
- This LED technology will save you up to 70% energy over HID.*
- Refracted lens design spreads light evenly to reduce glare significantly.
- Excellent choice for general areas, where lighting can enhance security.
- Direct mount or arm mount - compatible to retrofit onto existing arms easily.
- 4000K Color Temperature
- 5 year limited warranty.

* DTDLED rated 40 input watts is 70% less versus metal halide systems rated 129 input watts.

Vapor tight



- Wall or ceiling mounting available.
- Provides 83% energy savings over 100W Incandescent.*
- Heat and shock resistant glass globe with cast aluminum guard.
- Long life reduces maintenance.

- Provides up to 1,390 lumens.
- 5 year limited warranty.

* Based on comparison between 100W INC @1710 lumens and VCXL14-NW-G1 @ 1390 lumens

Commercial bollard



- Clean lines for a timeless, modern look.
- Rugged, aluminum construction and high quality finish.
- Simple installation.
- Ready-to-ship, in-stock product.

- Silicone gaskets protect internals from harsh elements.
- 50,000 hour rated life (L70).

Philips Catalog Code	Watts	Lumens	Dist.	Replaces
PAL-150-NW-G1-AR-3-8-BZ	150W	18,585	Type 3	250W PSMH
PAL-150-NW-G1-AR-4-8-BZ	150W	18,324	Type 4	250W PSMH
PAL-150-NW-G1-AR-5-8-BZ	150W	19,018	Type 5	250W PSMH
PAL-200-NW-G1-AR-3-8-BZ	200W	24,382	Type 3	400W PSMH
PAL-200-NW-G1-AR-4-8-BZ	200W	24,109	Type 4	400W PSMH
PAL-200-NW-G1-AR-5-8-BZ	200W	26,010	Type 5	400W PSMH
PAL-200-NW-G1-AR-3-8-IMRI-BZ	200W	24,382	Type 3	400W PSMH
PAL-200-NW-G1-AR-4-8-IMRI-BZ	200W	24,109	Type 4	400W PSMH

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PDTD-40-NW-G3-AR-5-TLRPC-1-GY3S	40W	4973	120V	100W MH

Accessories (order separately): PDTDARMGY3S - Mounting arm with hardware

Philips Catalog Code	Watts	Lumens	Mounting	Replaces
PVCXL-14-NW-G1-8	14W	1390	Ceiling	100W INC
PVWXL-14-NW-G1-8	14W	1390	Wall	100W INC

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PBL25-NW-G1-5-8-BZ	26W	2508	120-277V	70W MH

Please refer to the specification sheets for additional information and technical data, philips.com/Lighttogo

Low profile wall



- Budget-friendly, discreet fixture for a wide variety of outdoor spaces
- Energy efficient fixture that delivers up to 110 lumens per watt.
- Durable construction of die-cast aluminum with a UV stabilized lens and stainless steel hardware.

- Quick and easy installation - mounts to a standard 3 1/2 or 4" junction box.
- 3 size options: 15, 30 or 50 watt.
- Slim profile, just over 4 inches.
- 4000K Color Temperature
- 5 year limited warranty.

LWL Wall light



- Ideal wall mount fixture for doorways, entryways and other poorly lit areas.
- Cost-effective enhanced LED performance means you won't have to sacrifice quality for your budget.
- Strong, one-piece, die-cast aluminum housing with a tough polycarbonate lens.

- Built-in photocell for automatic dusk to dawn lighting allow for even more cost-savings.
- Easy installation, the LWL Wall Light mounts to a standard 4" junction box with a galvanized mounting plate.
- 5000K Color Temperature
- 5 year limited warranty.

Tall wall pack



- Lightweight, compact and built to last.
- Provides up to 83% energy savings over 70W Metal Halide luminaires.*
- The bronze housing is die cast aluminum and impact resistant polycarbonate, with a frosted lens.
- Rated for temperatures from -40 to 104°.

- Installation is quick and easy, it mounts to a standard 3 1/2 or 4" junction box.
- Lifetime >100,000 hours.**
- 4000K Color Temperature
- 5 year limited warranty.

* Based on comparison between TW20 @ 20W and 70W Metal halide.
 ** Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology.

Wall pack



- An easy switch from costly HID fixtures.
- Flexible options - choose from 30, 50 and 75 watts in two different sizes.
- The 50 watt Wall pack provides the same illumination as a 100 watt HID fixture, and uses over 50% less energy.*

- Glass refractor lens design cuts down on glare.
- One-piece die-cast aluminum housing.
- 4000K Color Temperature
- 5 year limited warranty.

* Based on comparison between 100W HPS Wall Pack at 115W providing 6100 lumens and 50W WP LED providing 5500 lumens

Easy order. Budget friendly. Job ready.

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PPW-15-NW-G1-8-BZ	15W	1656	120-277V	50W PSMH
PPW-30-NW-G1-8-BZ	30W	3090	120-277V	70W PSMH
PPW-50-NW-G1-8-BZ	50W	5114	120-277V	100W PSMH

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PLWLLED1C5K120PCBBZ	12W	829	120V	100W INC

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PTW-20-NW-G1-8-BZ	20W	1674	120 - 277V	100W INC
PTW-20-NW-G1-PCB-1-BZ	20W	1674	120V	100W INC

Philips Catalog Code	Watts	Lumens	Voltage	Replaces
PWP-30-NW-G1-8-BZ	30W	3355	120-277V	70W PSMH
PWP-50-NW-G1-8-BZ	50W	5541	120-277V	100W PSMH
PWP-75-NW-G1-8-BZ	75W	8999	120-277V	150-250W PSMH
PWP-30-NW-G1-PCB-8-BZ	30W	3355	120-277V	70W PSMH
PWP-50-NW-G1-PCB-8-BZ	50W	5541	120-277V	100W PSMH
PWP-75-NW-G1-PCB-8-BZ	75W	8999	120-277V	150-250W PSMH

Please refer to the specification sheets for additional information and technical data, philips.com/Lighttogo