



You work hard, so your lighting should too

Anywhere bright, uniform LED light is required, we offer the work light! These high lumen lamp replacements are ideal for garage, basements, attics and other work areas. Use them anywhere more light is desired, and since they are LED, the wattage used is still less than a conventional 60W incandescent lamp. Light up your space with the Philips LED high lumen work lights!

- 22 year lifetime when used 3 hours per day
- 3 lumen packages to meet your application needs
- Comes with a UL listed medium to mogul base adapter
- Rugged plastic construction
- Instant on, no warm up time to full lumens
- Non dimming



Philips LED work lamps



Ordering, electrical and technical data (Subject to change without notice)

Product Number	Model Number(s)	Description	Wattage	Voltage	Lumens	LED Lifetime ¹	Color Temp. (K)	Base
47928-7	9290018547	20A30/LED/865/P/E26/ND 4/1FB	20	120	2300	25,000	6500	Med (E26)
47929-5	9290018548	24A35/LED/865/P/E26E39/ND 4/1FB	24	120	3000	25,000	6500	Med (E26)
47930-3	9290018549	42A40/LED/865/P/E26E39/ND 4/1FB	42	120	5000	25,000	6500	Med (E26)

Shipping data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. Ft.)	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions (L x W x H) (in.)	Case Dimensions (L x W x H) (in.)	Pallet Dimensions (L x W x H) (in.)
47928-7	47928-2	47928-7	4	61.73	10.76	320	80	4	8.6 x 8.6 x 10.0	47.2 x 39.4 x 10.0	47.2 x 39.4 x 46.1
47929-5	47929-9	47929-4	4	56.09	11.36	320	80	4	9.7 x 9.7 x 10.6	47.2 x 39.4 x 10.6	47.2 x 39.4 x 48.3
47930-3	47930-5	47930-0	4	92.59	14.24	320	80	4	11.3 x 11.3 x 13.2	47.2 x 39.4 x 13.2	47.2 x 39.4 x 45.8

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Testing with a ballast whose ballast factor is ≤ 0.88



© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008